

Reliable

TECHNOLOGY • QUALITY • SERVICE

TAKING YOU THROUGH THE 21st CENTURY & BEYOND...

New Product Solutions

Changing the Shape of Sidewall Sprinkler Coverage! The DH80 Sprinkler Light Hazard/EC Quick Response Coverage up to 28ft. in **width** and a length of 14ft.

NYC MEA
Approved!



Install 1 Sprinkler Instead of 2!

- **The Sprinkler Designed for Long & Narrow Applications:**
 - Hallways
 - Corridors
 - Breezeways
 - Decks
 - Rooms up to 28' (8,5m) long
 - Balconies
- **Installation:**
 - Up to 28' (8,5m) apart
 - Up to 14' (4,3m) from any end wall
 - Smooth flat ceilings
 - 4" (102mm) to 12" (305mm) from the finished ceilings
 - Minimum of 12" (3,6m) apart
 - Flow: 40 gpm @ 25psi (K = 8.0)
- **Available Styles:**
 - Conical Concealed, Recessed, Standard
- **Finishes:**
 - CCP Concealed versions: White and other painted finishes
 - FP Recessed Push-On/Thread-Off Escutcheon: White & Chrome, Sprinkler: White, Chrome & Bronze
- **Temperature Rating:**
 - Sprinkler: 155°F (68°C)
 - Cover plate: 135°F (57°C)
- **cULus Listed and NYC MEA Approved**
- **US Patented**
- **For technical information refer to Bulletin 003.**

How Many Sprinklers Can You Save?

12/03