

Our NEW RFC43 Flat Concealed Residential Sprinkler!



Room Size (m)	Flow (Lpm)	Pressure (bar)
12' x 12' (3.6 x 3.6)	12 gpm (45)	7.8 (0,54)
14' x 14' (4.3 x 4.3)	13 gpm (49)	9.1 (0,63)
16' x 16' (4.9 x 4.9)	13 gpm (49)	9.1 (0,63)
18' x 18' (5.5 x 5.5)	18 gpm (68)	17.5 (1,21)
20' x 20' (6.0 x 6.0)	21 gpm (79)	23.8 (1,64)

April 2004

Dear Valued Customer:

Reliable is proud to announce our latest product development — the **Model RFC43** — the **Flat Concealed Residential Sprinkler** engineered for a minimum design density of 0.05 gpm/ft².

- Lowest flows and pressures in the industry for a flat plate design!
- ½" (13mm) total adjustment.
- Smooth aesthetic ceiling plate.
- cULus listed.

For more information on our new **RFC43 Concealed Residential Sprinkler** enclosed is a copy of Bulletin # 006. For sloped ceiling information for the RFC43 as well as our complete line of Residential Sprinklers, enclosed is Bulletin # 035.

We appreciate the opportunity to offer you over 85 years of products, services and experiences in the fire protection industry!

Sincerely,

Michael R. Fee
 V.P. Marketing & Sales Operations