

# New

## Storage Sprinklers from Reliable



### N252 EC, K-25 EC Pendant & Recessed Pendant

- An Extended Coverage Pendant & Recessed Pendant for Density/Area Design
- Approved for coverage up to 196 square feet (14' x 14') for extra hazard and storage applications
- Can be installed directly on the piping for exposed pipe systems. Unlike upright sprinklers, sprig-ups are not required for larger diameter piping.
- cULus Listed for a minimum of deflector to commodity distance of 36" and for unobstructed or non-combustible obstructed construction
- Complies with the criteria for protection of retail stores as described in NFPA 2002, section 12-7.2
- Installations for finished ceilings utilize the push-on, thread off FP recessed escutcheon which provides a 1/2" (13mm) adjustment
- Temperatures: 165°F (68°C) & 212°F (100°C)  
Finishes: Brass, Chrome, White & Black Plated
- Refer to Bulletin 008

### J168, K-16.8 Upright

- New control mode, density/area upright sprinkler
- Primarily for extra hazard and storage occupancies as designed and installed under NFPA 13 requirements
- Can allow reduced design areas, higher storage, reduced ceiling clearance to storage, and other savings in sprinkler design
- Uses the robust Model G solder capsule that has been installed in millions of sprinklers over the last 30 years
- cULus Listed
- Available with various temperature ratings and finishes
- Refer to Bulletin 011

RELIABLE ONE SOURCE  
For all your fire protection needs.

**Reliable**<sup>®</sup>  
TECHNOLOGY • QUALITY • SERVICE

1.800.431.1588  
www.reliablesprinkler.com  
The Reliable Automatic Sprinkler Co., Inc.  
Manufacturer & Distributor of Fire Protection Equipment