



**1 Sprinkler,
2 Applications!**

G4A CONCEALED

- Quick Response
- Concealed
- See Bulletin 154

G4A-300 CONCEALED

- Quick Response
- Concealed
- 300 PSI Rated
- See Bulletin 162

Please refer to the latest sales bulletin for specific approval listings and available finishes.
See our "Specialties Page" for special finish charges — including Teflon Tape.
Items that are MTO (indicated by "x") allow 7-10 work days.

| M T O | Part Number | Size | Temperature | Finish | List Price |
|---------------------------------|-------------|------------------------|-------------|-----------|------------|
| SPRINKLER ONLY | | | | | |
| | G4A1B | 1/2" x 1/2" NPT (15mm) | 165°F 74°C | Bronze | \$ 34.17 |
| | G4A13B | 3/8" x 1/2" NPT | 165°F 74°C | Bronze | \$ 42.39 |
| | G4A17B | 7/16" x 1/2" | 165°F 74°C | Bronze | \$ 42.39 |
| X | G4A1M | 1" Adjust Male | 165°F 74°C | Bronze | \$ 91.31 |
| X | G4A1F | 1" Adjust Female | 165°F 74°C | Bronze | \$ 91.31 |
| | G4A2B | 1/2" x 1/2" NPT (15mm) | 212°F 100°C | Bronze | \$ 34.17 |
| | G4A23B | 3/8" x 1/2" NPT | 212°F 100°C | Bronze | \$ 42.39 |
| | G4A27B | 7/16" x 1/2" | 212°F 100°C | Bronze | \$ 42.39 |
| SPRINKLER ONLY — 300 PSI | | | | | |
| | G4A1B3 | 1/2" x 1/2" NPT (15mm) | 165°F 74°C | Bronze | \$ 35.85 |
| X | G4A1M3 | 1" Adjust Male | 165°F 74°C | Bronze | \$ 95.33 |
| X | G4A1F3 | 1" Adjust Female | 165°F 74°C | Bronze | \$ 95.33 |
| REQUIRED COVERPLATES | | | | | |
| X | CG40B | — | 135°F 57°C | Bronze | \$ 29.70 |
| X | CG40C | — | 135°F 57°C | Chrome | \$ 21.79 |
| | CG40W | — | 135°F 57°C | White | \$ 21.79 |
| X | CG40SP | — | 135°F 57°C | Specialty | \$ 29.70 |

WG4 Requires Model G4 Wrench \$ 177.00

Notes:

For custom finishes, customer should provide paint sample.
Allow at least 2-3 weeks. A set-up charge is required for all orders under 500 pieces. Consult factory for details.



F1FR CCP

- Push-On/Thread-off
- Concealed
- See Bulletins 143

F1FR-300/CCP

- Push-On/Thread-off
- 300 PSI Rated
- Quick Response
- Concealed
- See Bulletin 164

| M T O | Part Number | Temperature | Finish | List Price |
|---|-------------|-------------|-----------|------------|
| 1/2" ORIFICE, 1/2" NPT THREADS (15MM) | | | | |
| X | F1FRC0 | 135°F 57°C | Bronze | \$ 23.91 |
| X | F1FRC1 | 155°F 68°C | Bronze | \$ 23.91 |
| X | F1FRC5 | 175°F 79°C | Bronze | \$ 23.91 |
| X | F1FRC2 | 200°F 93°C | Bronze | \$ 23.91 |
| NEW! 1/2" ORIFICE, 1/2" NPT THREADS (15MM) — 300 PSI | | | | |
| X | F1FRC03 | 135°F 57°C | Bronze | \$ 25.21 |
| X | F1FRC13 | 155°F 68°C | Bronze | \$ 25.21 |
| REQUIRED COVERPLATES (5/16") | | | | |
| | CCP05C76 | 135°F 57°C | Chrome | \$ 20.11 |
| | CCP05W76 | 135°F 57°C | White | \$ 20.11 |
| X | CCP05SP76 | 135°F 57°C | Specialty | \$ 33.79 |
| | CCP15C76 | 165°F 74°C | Chrome | \$ 20.11 |
| | CCP15W76 | 165°F 74°C | White | \$ 20.11 |
| X | CCP15SP76 | 165°F 74°C | Specialty | \$ 33.79 |
| REQUIRED COVERPLATES (1/2"-15MM) | | | | |
| | CCP0C76 | 135°F 57°C | Chrome | \$ 20.11 |
| | CCP0W76 | 135°F 57°C | White | \$ 20.11 |
| | CCP0SP76 | 135°F 57°C | Specialty | \$ 33.79 |
| | CCP1C76 | 165°F 74°C | Chrome | \$ 20.11 |
| | CCP1W76 | 165°F 74°C | White | \$ 20.11 |
| | CCP1SP76 | 165°F 74°C | Specialty | \$ 33.79 |

WRC Requires Model RC1 Sprinkler Wrench \$ 178.00

Notes:

For custom finishes, customer should provide paint sample.
Allow at least 2-3 weeks. A set-up charge is required for all orders under 500 pieces. Consult factory for details.

| Sprinkler | Coverplate |
|------------|------------|
| 135°F/57°C | 135°F/57°C |
| 155°F/68°C | 135°F/57°C |
| 175°F/79°C | 165°F/74°C |
| 200°F/93°C | 165°F/74°C |

Please refer to the latest sales bulletin for specific approval listings and available finishes.
See our "Specialties Page" for special finish charges — including Teflon Tape.
Items that are MTO (indicated by "x") allow 7-10 work days.



F4FR CONCEALED

- Quick Response
- Concealed
- See Bulletin 125

Please refer to the latest sales bulletin for specific approval listings and available finishes.
See our "Specialties Page" for special finish charges — including Teflon Tape.
Items that are MTO (indicated by "x") allow 7-10 work days.

| M T O | Part Number | Size | Temperature | Finish | List Price |
|-----------------------------|-------------|------------------------|-------------|-----------|------------|
| SPRINKLER ONLY | | | | | |
| | F4FR | 1/2" x 1/2" NPT (15mm) | 135°F 57°C | Bronze | \$ 61.21 |
| X | F4FR3 | 3/8" x 1/2" NPT | 135°F 57°C | Bronze | \$ 64.29 |
| X | F4FR7 | 7/16" x 1/2" NPT | 135°F 57°C | Bronze | \$ 64.29 |
| X | F4FRM | 1/2" Adjust. Male | 135°F 57°C | Bronze | \$ 96.64 |
| X | F4FRF | 1/2" Adjust. Female | 135°F 57°C | Bronze | \$ 96.64 |
| REQUIRED COVERPLATES | | | | | |
| | CG40B | | 135°F 57°C | Bronze | \$ 29.70 |
| | CG40C | | 135°F 57°C | Chrome | \$ 21.79 |
| | CG40W | | 135°F 57°C | White | \$ 21.79 |
| X | CG40SP | | 135°F 57°C | Specialty | \$ 29.70 |

WG4 Requires Model G4 Sprinkler Wrench \$ 177.00

Notes:

For custom finishes, customer should provide paint sample.
Allow at least 2-3 weeks. A set-up charge is required for all orders under 500 pieces. Consult factory for details.



| M T O | Part Number | Size | Temperature | | Finish | List Price |
|--------------------------------|-------------|------------------------|-------------|------|--------|------------|
| F4FR-NF WITH COVERPLATE | | | | | | |
| | F4FRNFW | 1/2" x 1/2" NPT (15mm) | 135°F | 57°C | White | \$ 481.15 |
| | F4FRNFC | 1/2" x 1/2" NPT (15mm) | 135°F | 57°C | Chrome | \$ 481.15 |
| | F4FRNF1W | 1/2" x 1/2" NPT (15mm) | 155°F | 68°C | White | \$ 481.15 |
| | F4FRNF1C | 1/2" x 1/2" NPT (15mm) | 155°F | 68°C | Chrome | \$ 481.15 |

Non-Ferrous

WG4 Requires Model G4 Sprinkler Wrench \$ 177.00

Notes:

For custom finishes, customer should provide paint sample.

Allow at least 2-3 weeks. A set-up charge is required for all orders under 500 pieces. Consult factory for details.

F4FR-NF CONC

- Designed for:
 - MRI Rooms
 - Corrosive Environments
 - Swimming Areas
- Quick Response
- Concealed
- See Bulletin 002



MODEL XL QR Commercial

- Pendent/Horizontal Sidewa
- Quick Response
- No Exposed Heating Element!
- See Bulletin 145

| M T O | Part Number | Temperature | Finish | List Price |
|--|--------------|-------------|--------|------------|
| XL PENDENT | | | | |
| | XLQRPC | 165°F 75°C | Chrome | \$ 85.53 |
| | XLQRPW | 165°F 75°C | White | \$ 88.58 |
| XL HSW | | | | |
| | XLQRHC | 165°F 75°C | Chrome | \$ 106.92 |
| | XLQRHW | 165°F 75°C | White | \$ 109.97 |
| REQUIRED ESCUTCHEONS FOR MODEL XL | | | | |
| | ZXFPC ZXCPC | | Chrome | \$ 17.05 |
| | ZXFPW ZXCPCW | | White | \$ 17.05 |
| 2-PIECE REQUIRED ESCUTCHEONS FOR MODEL XL | | | | |
| | ZX2PC | | Chrome | \$ 21.33 |
| | ZX2PW | | White | \$ 22.26 |
| REQUIRED ESCUTCHEONS FOR MODEL XL (CONICAL) | | | | |
| | ZXCHC | 165°F 75°C | Chrome | \$ 17.05 |
| | ZXCHW | 165°F 75°C | White | \$ 17.05 |
| 2-PIECE REQUIRED ESCUTCHEONS FOR MODEL XL | | | | |
| X | ZX2HC | 165°F 75°C | Chrome | \$ 21.33 |
| X | ZX2HW | 165°F 75°C | White | \$ 22.26 |

| | | | |
|------|---|----|--------|
| WZXP | Requires Model ZX (Pendent) Sprinkler Wrench | \$ | 177.00 |
| WZXH | Requires Model ZX (Horizontal) Sprinkler Wrench | \$ | 177.00 |

IMPORTANT NOTE:

- * The Model XL Quick Response Replaced our ZX Line as of 12/31/02
- * Sprinkler Components are Bright Chrome Only.
- Link is painted silver or white.

Please refer to the latest sales bulletin for specific approval listings and available finishes.

See our "Specialties Page" for special finish charges — including Teflon Tape.

Items that are MTO (indicated by "x") allow 7-10 work days.