



**1 Sprinkler,
2 Applications!**

G4A CONCEALED

- Quick Response
- Concealed
- See Bulletin 154

G4A-300 CONCEALED

- Quick Response
- Concealed
- 300 PSI Rated
- See Bulletin 162

Please refer to the latest sales bulletin for specific approval listings and available finishes.
See our "Specialties Page" for special finish charges — including Teflon Tape.
Items that are MTO (indicated by "x") allow 7-10 work days.

M T O	Part Number	Size	Temperature	Finish	List Price
SPRINKLER ONLY					
	G4A1B	1/2" x 1/2" NPT (15mm)	165°F 74°C	Bronze	\$ 35.88
	G4A13B	3/8" x 1/2" NPT	165°F 74°C	Bronze	\$ 44.51
	G4A17B	7/16" x 1/2"	165°F 74°C	Bronze	\$ 44.51
X	G4A1M	1" Adjust Male	165°F 74°C	Bronze	\$ 95.88
X	G4A1F	1" Adjust Female	165°F 74°C	Bronze	\$ 95.88
	G4A2B	1/2" x 1/2" NPT (15mm)	212°F 100°C	Bronze	\$ 35.88
	G4A23B	3/8" x 1/2" NPT	212°F 100°C	Bronze	\$ 44.51
	G4A27B	7/16" x 1/2"	212°F 100°C	Bronze	\$ 44.51
SPRINKLER ONLY — 300 PSI					
	G4A1B3	1/2" x 1/2" NPT (15mm)	165°F 74°C	Bronze	\$ 37.64
X	G4A1M3	1" Adjust Male	165°F 74°C	Bronze	\$ 100.10
X	G4A1F3	1" Adjust Female	165°F 74°C	Bronze	\$ 100.10
REQUIRED COVERPLATES					
X	CG40B	—	135°F 57°C	Bronze	\$ 31.20
X	CG40C	—	135°F 57°C	Chrome	\$ 22.88
	CG40W	—	135°F 57°C	White	\$ 22.88
X	CG40SP	—	135°F 57°C	Specialty	\$ 31.20

WG4 Requires Model G4 Wrench \$ 189.00

Notes:

For custom finishes, customer should provide paint sample.
Allow at least 2-3 weeks. A set-up charge is required for all orders under 500 pieces. Consult factory for details.



F1FR CCP

- Push-On/Thread-off
- Concealed
- See Bulletins 143

F1FR-300/CCP

- Push-On/Thread-off
- 300 PSI Rated
- Quick Response
- Concealed
- See Bulletin 164

M T O	Part Number	Temperature	Finish	List Price
1/2" ORIFICE, 1/2" NPT THREADS (15MM)				
X	F1FRC0	135°F 57°C	Bronze	\$ 25.11
X	F1FRC1	155°F 68°C	Bronze	\$ 25.11
X	F1FRC5	175°F 79°C	Bronze	\$ 25.11
X	F1FRC2	200°F 93°C	Bronze	\$ 25.11
NEW! 1/2" ORIFICE, 1/2" NPT THREADS (15MM) — 300 PSI				
X	F1FRC03	135°F 57°C	Bronze	\$ 26.47
X	F1FRC13	155°F 68°C	Bronze	\$ 26.47
REQUIRED COVERPLATES (5/16")				
	CCP05C76	135°F 57°C	Chrome	\$ 21.12
	CCP05W76	135°F 57°C	White	\$ 21.12
X	CCP05SP76	135°F 57°C	Specialty	\$ 35.48
	CCP15C76	165°F 74°C	Chrome	\$ 21.12
	CCP15W76	165°F 74°C	White	\$ 21.12
X	CCP15SP76	165°F 74°C	Specialty	\$ 35.48
REQUIRED COVERPLATES (1/2"-15MM)				
	CCP0C76	135°F 57°C	Chrome	\$ 21.12
	CCP0W76	135°F 57°C	White	\$ 21.12
	CCP0SP76	135°F 57°C	Specialty	\$ 35.48
	CCP1C76	165°F 74°C	Chrome	\$ 21.12
	CCP1W76	165°F 74°C	White	\$ 21.12
	CCP1SP76	165°F 74°C	Specialty	\$ 35.48

WRC Requires Model RC1 Sprinkler Wrench \$ 190.00

Notes:

For custom finishes, customer should provide paint sample.
Allow at least 2-3 weeks. A set-up charge is required for all orders under 500 pieces. Consult factory for details.

Sprinkler	Coverplate
135°F/57°C	135°F/57°C
155°F/68°C	135°F/57°C
175°F/79°C	165°F/74°C
200°F/93°C	165°F/74°C

Please refer to the latest sales bulletin for specific approval listings and available finishes.
See our "Specialties Page" for special finish charges — including Teflon Tape.
Items that are MTO (indicated by "x") allow 7-10 work days.



F4FR CONCEALED

- Quick Response
- Concealed
- See Bulletin 125

Please refer to the latest sales bulletin for specific approval listings and available finishes.
See our "Specialties Page" for special finish charges — including Teflon Tape.
Items that are MTO (indicated by "x") allow 7-10 work days.

M T O	Part Number	Size	Temperature	Finish	List Price
SPRINKLER ONLY					
	F4FR	1/2" x 1/2" NPT (15mm)	135°F 57°C	Bronze	\$ 64.27
X	F4FR3	3/8" x 1/2" NPT	135°F 57°C	Bronze	\$ 67.50
X	F4FR7	7/16" x 1/2" NPT	135°F 57°C	Bronze	\$ 67.50
X	F4FRM	1/2" Adjust. Male	135°F 57°C	Bronze	\$ 101.47
X	F4FRF	1/2" Adjust. Female	135°F 57°C	Bronze	\$ 101.47
REQUIRED COVERPLATES					
	CG40B		135°F 57°C	Bronze	\$ 31.20
	CG40C		135°F 57°C	Chrome	\$ 22.88
	CG40W		135°F 57°C	White	\$ 22.88
X	CG40SP		135°F 57°C	Specialty	\$ 31.20

WG4 Requires Model G4 Sprinkler Wrench \$ 189.00

Notes:

For custom finishes, customer should provide paint sample.
Allow at least 2-3 weeks. A set-up charge is required for all orders under 500 pieces. Consult factory for details.



M T O	Part Number	Size	Temperature		Finish	List Price
F4FR-NF WITH COVERPLATE						
	F4FRNFW	1/2" x 1/2" NPT (15mm)	135°F	57°C	White	\$ 125.00
	F4FRNFC	1/2" x 1/2" NPT (15mm)	135°F	57°C	Chrome	\$ 125.00
	F4FRNF1W	1/2" x 1/2" NPT (15mm)	155°F	68°C	White	\$ 125.00
	F4FRNF1C	1/2" x 1/2" NPT (15mm)	155°F	68°C	Chrome	\$ 125.00

Non-Ferrous

WG4 Requires Model G4 Sprinkler Wrench \$ 189.00

Notes:

For custom finishes, customer should provide paint sample.

Allow at least 2-3 weeks. A set-up charge is required for all orders under 500 pieces. Consult factory for details.

F4FR-NF CONC

- Designed for:
 - MRI Rooms
 - Corrosive Environments
 - Swimming Areas
- Quick Response
- Concealed
- See Bulletin 002



MODEL XL QR Commercial

- Pendent/Horizontal Sidewa
- Quick Response
- No Exposed Heating Element!
- See Bulletin 145

M T O	Part Number	Temperature	Finish	List Price
XL PENDENT				
	XLQRPC	165°F 75°C	Chrome	\$ 89.81
	XLQRPW	165°F 75°C	White	\$ 93.01
XL HSW				
	XLQRHC	165°F 75°C	Chrome	\$ 112.27
	XLQRHW	165°F 75°C	White	\$ 115.47
REQUIRED ESCUTCHEONS FOR MODEL XL				
	ZXFPC ZXCPC		Chrome	\$ 17.90
	ZXFPW ZXCPW		White	\$ 17.90
2-PIECE REQUIRED ESCUTCHEONS FOR MODEL XL				
	ZX2PC		Chrome	\$ 22.40
	ZX2PW		White	\$ 23.37
REQUIRED ESCUTCHEONS FOR MODEL XL (CONICAL)				
	ZXCHC	165°F 75°C	Chrome	\$ 17.90
	ZXCHW	165°F 75°C	White	\$ 17.90
2-PIECE REQUIRED ESCUTCHEONS FOR MODEL XL				
X	ZX2HC	165°F 75°C	Chrome	\$ 22.40
X	ZX2HW	165°F 75°C	White	\$ 23.37

WZXP	Requires Model ZX (Pendent) Sprinkler Wrench	\$	189.00
WZXH	Requires Model ZX (Horizontal) Sprinkler Wrench	\$	189.00

IMPORTANT NOTE:

- * The Model XL Quick Response Replaced our ZX Line as of 12/31/02
- * Sprinkler Components are Bright Chrome Only.
- Link is painted silver or white.

Please refer to the latest sales bulletin for specific approval listings and available finishes.
See our "Specialties Page" for special finish charges — including Teflon Tape.
Items that are MTO (indicated by "x") allow 7-10 work days.