

HANGERS



Part Name	Part Number	Box Qty	List Price
RING HANGERS			
1"	1H	100	\$ 0.85
1-1/4"	125H	100	\$ 0.90
1-1/2"	15H	100	\$ 0.91
2"	2H	100	\$ 0.96
2-1/2"	25H	50	\$ 1.51
3"	3H	50	\$ 1.66
4"	4H	50	\$ 2.33
5"	5H	25	\$ 4.30
6"	6H	20	\$ 5.00
8"	8H	15	\$ 6.77
UNIVERSAL BEAM CLAMPS			
3/8" - BLACK	38BC	100	\$ 2.45
1/2" - BLACK	12BC	50	\$ 3.60
3/8" - GALVANIZED	38BCG	100	\$ 3.93
1/2" - GALVANIZED	12BCG	50	\$ 5.46
WIDE MOUTH BEAM CLAMPS			
3/8"	38WBC	50	\$ 4.00
1/2"	12WBC	50	\$ 4.20
SIDE BEAM BRACKET			
3/8"	38SBB	100	\$ 1.73
RISER CLAMPS			
1-1/4"	125C	25	\$ 15.67
1-1/2"	15C	25	\$ 16.52
2"	2C	25	\$ 17.31
2-1/2"	25C	25	\$ 18.32
3"	3C	25	\$ 19.89
4"	4C	20	\$ 27.00
6"	6C	EA	\$ 44.91
8"	8C	EA	\$ 89.85
WALL PLATES			
PLASTIC, CHROME			
1"	7W15040000	N/A	\$ 1.44
1-1/4"	7W15050000	N/A	\$ 1.83
1-1/2"	7W15060000	N/A	\$ 1.94
2"	7W15080000	N/A	\$ 2.03
CAST IRON, GALVANIZED			
1"	7W09040000	N/A	\$ 5.65
1-1/4"	7W09050000	N/A	\$ 7.25
1-1/2"	7W09060000	N/A	\$ 7.85
2"	7W09080000	N/A	\$ 12.85
SPLIT RING HANGERS (#455)			
1/2"	12455	100	\$ 3.23
3/4"	75455	100	\$ 3.54
1"	1455	100	\$ 3.74
1-1/4"	125455	100	\$ 5.05
1-1/2"	15455	50	\$ 6.08
2"	2455	50	\$ 8.01
2-1/2"	25455	50	\$ 15.55
3"	3455	50	\$ 19.18
4"	4455	25	\$ 33.64

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.



HANGERS

Part Name	Part Number	Box Qty	List Price
EYE SOCKETS			
3/8"	38ES	250	\$ 1.31
1/2"	12ES	100	\$ 2.87
3/8" Offset	38OES	250	\$ 1.97
ALL THREAD ROD (BLACK)			
3/8" x 12'	38TR12	250	\$ 0.99
3/8" x 10'	38TR	250	\$ 0.99
3/8" x 6'	38TR6	150	\$ 0.99
1/2" x 12'	12TR12	250	\$ 1.77
1/2" x 10'	12TR	120	\$ 1.77
1/2" x 6'	12TR6	72	\$ 1.77
ALL THREAD ROD PLATED			
3/8" x 12'	38TRP12	250	\$ 1.13
3/8" x 10'	38TRP	250	\$ 1.13
3/8" x 6'	38TRP6	150	\$ 1.13
1/2" x 12'	12TRP12	250	\$ 2.04
1/2" x 10'	12TRP	120	\$ 2.04
1/2" x 6'	12TRP6	72	\$ 2.04
HEX NUTS			
3/8"	38N	N/A	\$ 0.24
1/2"	12N	N/A	\$ 0.30
5/8"	58N	N/A	\$ 0.66
3/4"	34N	N/A	\$ 0.95
ZINC FLAT WASHERS			
3/8"	38W	N/A	\$ 0.24
1/2"	12W	N/A	\$ 0.30
ZINC ROD COUPLINGS			
3/8" x 1-3/4"	38C	N/A	\$ 1.01
3/8" x 1-1/8"	38CS	N/A	\$ 0.42
1/2" x 1-3/4"	12C	N/A	\$ 1.19
DROP IN ANCHORS			
3/8"	6999991999	100	\$ 1.31
1/2"	6999992000	N/A	\$ 3.28

¹ Available in 6' (38TR6) and 10' (12TR6) lengths.

² DST516, SWD516 have only UL Approval. GST20 has FM approval only.

All other super screws are unapproved.

SPECIAL NOTE:

Earthquake and other Hanger requirements available upon request.

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.