



HANGERS

Part Name	Part Number	Box Qty	List Price
RING HANGERS			
1"	6990010526	100	\$ 0.85
1-1/4"	6990010527	100	\$ 0.92
1-1/2"	6990010528	100	\$ 0.92
2"	6990010529	100	\$ 0.98
2-1/2"	699001059C	50	\$ 1.62
3"	699001053C	50	\$ 1.75
4"	6990010531	25	\$ 2.08
5"	7M99001923	25	\$ 4.53
6"	6990010532	20	\$ 5.23
8"	7M99001924	10	\$ 7.31
BEAM CLAMPS - DOMESTIC			
3/8" - BLACK	7M99001925	100	\$ 2.84
1/2" - BLACK	7M99001926	100	\$ 4.06
3/8" - GALVANIZED	7M99001929	100	\$ 3.88
1/2" - GALVANIZED	7M99001930	100	\$ 5.68
WIDE MOUTH BEAM CLAMP - DOMESTIC			
3/8" - BLACK	7M99001939	100	\$ 3.96
1/2" - BLACK	7M99001940	100	\$ 4.48
SIDE BEAM BRACKET			
3/8"	7M99001947	100	\$ 2.57
RISER CLAMPS - GALVANIZED			
1-1/4"	7M99001950	25	\$ 12.45
1-1/2"	7M99001951	25	\$ 12.96
2"	7M99001952	25	\$ 13.39
2-1/2"	7M99001953	25	\$ 17.56
3"	7M99001954	25	\$ 18.54
4"	7M99001955	15	\$ 22.93
6"	7M99001956	10	\$ 37.43
8"	7M99001957		\$ 81.85
WALL PLATES			
PLASTIC, CHROME			
1"	7W15040000	N/A	\$ 1.44
1-1/4"	7W15050000	N/A	\$ 1.83
1-1/2"	7W15060000	N/A	\$ 1.94
2"	7W15080000	N/A	\$ 2.03
CAST IRON, GALVANIZED			
1"	7W09040000	N/A	\$ 5.65
1-1/4"	7W09050000	N/A	\$ 7.25
1-1/2"	7W09060000	N/A	\$ 7.85
2"	7W09080000	N/A	\$ 12.85
SPLIT RING HANGERS - #508R - Black			
1/2"	7M99001973	100	\$ 2.78
3/4"	7M99001974	100	\$ 3.37
1"	7M99001975	100	\$ 3.68
1-1/4"	7M99001976	100	\$ 4.05
1-1/2"	7M99001977	100	\$ 5.01
2"	7M99001978	100	\$ 7.21
2-1/2"	7M99001979	50	\$ 10.12
3"	7M99001980	25	\$ 14.41
4"	7M99001981	25	\$ 18.71

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.



HANGERS

Part Name	Part Number	Box Qty	List Price
EYE SOCKETS - #37			
3/8"	7817030000	250	\$ 3.00
1/2"	7M99001948	100	\$ 4.99
ALL THREAD ROD (BLACK)			
3/8" x 12'	38TR12	250	\$ 1.05
3/8" x 10'	38TR	250	\$ 1.05
3/8" x 6'	38TR6	150	\$ 1.05
1/2" x 12'	12TR12	250	\$ 1.94
1/2" x 10'	12TR	120	\$ 1.94
1/2" x 6'	12TR6	72	\$ 1.94
ALL THREAD ROD PLATED			
3/8" x 12'	38TRP12	250	\$ 1.20
3/8" x 10'	38TRP	250	\$ 1.20
3/8" x 6'	38TRP6	150	\$ 1.20
1/2" x 12'	12TRP12	250	\$ 2.14
1/2" x 10'	12TRP	120	\$ 2.14
1/2" x 6'	12TRP6	72	\$ 2.14
HEX NUTS			
3/8"	38N	N/A	\$ 0.24
1/2"	12N	N/A	\$ 0.30
5/8"	58N	N/A	\$ 0.66
3/4"	34N	N/A	\$ 0.95
ZINC FLAT WASHERS			
3/8"	38W	N/A	\$ 0.24
1/2"	12W	N/A	\$ 0.30
ZINC ROD COUPLINGS			
3/8" x 1-3/4"	38C	N/A	\$ 1.01
3/8" x 1-1/8"	38CS	N/A	\$ 0.42
1/2" x 1-3/4"	12C	N/A	\$ 1.19
DROP IN ANCHORS			
3/8"	6999991999	100	\$ 1.31
1/2"	6999992000	N/A	\$ 3.28
1/2"	6999992000	N/A	\$ 3.28

¹ Available in 6' (38TR6) and 10' (12TR6) lengths.

SPECIAL NOTE:

Earthquake and other Hanger requirements available upon request.

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.