

## Flexhead - Flexible Drops



Part Name	Part Number	List Price
<b>COMMERCIAL TYPE 1/2"</b>		
Model 2024SS, 2'	7M99000128	\$ 127.00
Model 2036SS, 3'	7M99000129	\$ 146.50
Model 2048SS, 4'	7M99000130	\$ 167.00
Model 2060SS, 5'	7M99000131	\$ 187.00
Model 2072SS, 6'	7M99000132	\$ 208.00
<b>COMMERCIAL TYPE 3/4"</b>		
Model 2024SS, 2'	7M99000133	\$ 127.00
Model 2036SS, 3'	7M99000134	\$ 146.50
Model 2048SS, 4'	7M99000135	\$ 167.00
Model 2060SS, 5'	7M99000136	\$ 187.00
Model 2072SS, 6'	7M99000137	\$ 208.00
<b>REPLACEMENT BRACKETS</b>		
Standard Multi Port bracket (MP24BKT2)	6990008249	\$ 26.25
Adjustable bracket, 24" (AD24BKT-2)	6990005691	\$ 31.25
Adjustable Bracket, 16" (AD16BKT-2)	6990005690	\$ 26.25
<b>DUCT TYPE</b>		
Model 1024, FRP/Phenolic	6999994971	\$ 1,463.30
Model 1036, FRP/Phenolic	6999994972	\$ 1,463.30
Model 1048, FRP/Phenolic	6999994973	\$ 1,537.70
Model 1124, SS/Galv.	6999994974	\$ 1,537.70
Model 1136, SS/Galv.	6999994975	\$ 1,537.70
Model 1148, SS/Galv.	6999994976	\$ 1,612.10
Model 1224, Polypro.	6999994977	\$ 1,488.10
Model 1236, Polypro.	6999994978	\$ 1,488.10
Model 1248, Polypro.	6999994979	\$ 1,562.50
Model 1324, CPVC	6999994980	\$ 1,488.10
Model 1336, CPVC	6999994981	\$ 1,488.10
Model 1348, CPVC	6999994982	\$ 1,562.50
<b>INSTITUTIONAL TYPE 1/2"</b>		
Model 2024I, 2'	6990001226	\$ 127.00
Model 2036I, 3'	6990001227	\$ 146.50
Model 2048I, 4'	6990001228	\$ 167.00
Model 2060I, 5'	6990001229	\$ 187.00
Model 2072I, 6'	6990001230	\$ 208.00
<b>INSTITUTIONAL TYPE 3/4"</b>		
Model 2024I, 2'	6990001231	\$ 127.00
Model 2036I, 3'	6990001232	\$ 146.50
Model 2048I, 4'	6990001233	\$ 167.00
Model 2060I, 5'	6990001234	\$ 187.00
Model 2072I, 6'	6990001235	\$ 208.00

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.



# SPRINKFLEX

## Flexible Drops

Part Name	Part Number	Box Qty.	List Price
<b>UNBRAIDED - UL APPROVED</b>			
1/2" x 28"	7M99001877	25	\$ 97.00
3/4" x 28"	7M99001878	25	\$ 97.00
1/2" x 40"	7M99001879	25	\$ 102.00
3/4" x 40"	7M99001880	25	\$ 102.00
1/2" x 48"	7M99001881	25	\$ 109.00
3/4" x 48"	7M99001882	25	\$ 109.00
1/2" x 59"	7M99001883	25	\$ 118.00
3/4" x 59"	7M99001884	25	\$ 118.00
1/2" x 71"	7M99001885	25	\$ 128.00
3/4" x 71"	7M99001886	25	\$ 128.00
<b>BRAIDED - UL APPROVED</b>			
1/2" x 28"	7M99001887	25	\$ 120.00
3/4" x 28"	7M99001888	25	\$ 120.00
1/2" x 40"	7M99001889	25	\$ 135.00
3/4" x 40"	7M99001890	25	\$ 135.00
1/2" x 48"	7M99001891	25	\$ 145.00
3/4" x 48"	7M99001892	25	\$ 145.00
1/2" x 59"	7M99001893	25	\$ 159.00
3/4" x 59"	7M99001894	25	\$ 159.00
1/2" x 71"	7M99001895	25	\$ 173.00
3/4" x 71"	7M99001896	25	\$ 173.00
<b>REPLACEMENT BRACKETS</b>			

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.