



SPECIAL HAZARDS

SPECIAL SYSTEMS

- See Bulletins 707, 708

Description	Part Number	List Price
<b>ACCELERATOR</b>		
B1 Accelerator	AE	\$ 1,514.00
B2 Accelerator Trim	ACT	\$ 622.00
B - Replacement Parts Kits	BRPK	\$ 514.00
B1 - Replacement Parts Kits	B1RPK	\$ 514.00
<b>SOLENOID VALVE &amp; PULL BOX/STATIONS</b>		
Solenoid Valve - LV2LBX25 - 24 V DC	SOL2	\$ 694.00
Solenoid Valve - LV2LBX15 - 115V AC	SOL2A	\$ 1,064.00
Model A - Hydraulic Manual Pull Box	HMBOX	\$ 486.70
Elect. Man. Emergency Station (Single)	BNG1	\$ 273.10
Elect. Man. Emergency Station (Dbl)	BNG1F	\$ 383.20
<b>RPC4410 PANEL - TYPE D SYSTEMS</b>		
RPC 4410RC Panel	PFCPANEL	\$ 3,283.30
<b>BATTERIES (2 REQUIRED)</b>		
PS 1270 12 Volt, 7 AMP (UL Systems)	BATUL	\$ 218.00
PS 12120 12 Volt, 12 AMP (FM Systems)	BATFM	\$ 323.70
<b>SYSTEM MODULES</b>		
Transmitter (4XTM)	4XTM	\$ 555.00
Annunciator Drive (4XLM)	4XLM	\$ 555.00
Remote Annunciator (RZX 4X)	RZX4X	\$ 555.00
Zone Relay (4XZM)	4XZM	\$ 555.00

Description	Part Number	List Price
<b>DRAIN ASSEMBLIES</b>		
2 - 1/2" Deluge	6501180302	\$ 618.00
4 & 6" Deluge	6501180300	\$ 666.00
2 - 1/2" Preaction	6501180102	\$ 704.00
4" Preaction	6501180100	\$ 761.00
6" Preaction	6501180200	\$ 761.00
<b>DRY PILOT ACTUATOR</b>		
Dry Pilot Actuator	71030000	\$ 1,070.00
<b>CHEMETRON 600 SERIES RATE OF RISE DETECTORS</b>		
601 -- 135°F	601	\$ 98.80
602 -- 200°F	602	\$ 98.80
603 -- 135°F Fixed	603	\$ 98.80
604 -- 200°F Fixed	604	\$ 98.80
<b>SMOKE DETECTORS</b>		
Ionization	SMOKEI	\$ 269.00
Photoelectric	SMOKEP	\$ 269.00
Mounting base	MB	\$ 70.00
<b>FLAME DETECTORS (AVAILABLE UPON REQUEST)</b>		
<b>THERMAL DETECTORS</b>		
135° Interior — Vertical Mounted	6611442030	\$ 139.20
200° Interior — Vertical Mounted	6611442035	\$ 139.20
135° Weatherproof — Vertical Mounted	6611442010	\$ 148.10
200° Weatherproof — Vertical Mounted	6611442015	\$ 148.10
135° Interior — Horizontal Mounted	6611442020	\$ 152.60
200° Interior — Horizontal Mounted	6611442025	\$ 152.60
Adaptor Plate	6611782010	\$ 27.00

SPECIAL HAZARDS  
SPECIAL SYSTEMS

• See Bulletin 707

Description	Part Number	List Price
<b>ELECTRIC ALARM BELLS</b>		
6" — 24 VDC	6KMS	\$ 72.69
8" — 24 VDC	8KMS	\$ 90.86
10" — 24VDC	10KMS	\$ 102.62
6" — 120 VAC	6KBS	\$ 72.69
8" — 120 VAC	8KBS	\$ 90.86
10" — 120 VAC	10KBS	\$ 102.62
WBB Weatherproof Back Box	WBB	\$ 44.25
<b>SUPERVISORY AIR SUPPLY</b>		
B Air Compressor Panel (120 V/AC)	BACP	\$ 4,038.00
B Air Compressor Panel (220 V/AC)	BACP2	\$ 4,728.00
A-2 Air Maint. Dev. (Owner's Air)	AMDAG	\$ 950.00
B-1 Air Maint. Dev. (Ind. Compress)	AMDBG	\$ 1,079.00
C Air Maint. Dev. (Supertrol System)	AMDCG	\$ 1,425.00
<b>VALVE SEAT WRENCHES</b>		
4" Model B & BX Deluge Valve	W4DV	\$ 210.00
6" Model B & BX Deluge Valve	W6DV	\$ 225.00

LPC SYSTEMS

Description	Part Number	Price
<b>LPC PREACTION SYSTEMS (COMPLETE)</b>		
100mm	6503004010	\$ 26,346.49
150mm	6503004015	\$ 27,787.30
<b>PREACTION SYSTEM COMPONENTS</b>		
CEL Prescient Panel	6999991602	\$ 4,260.71
CEL 3.2A Batteries	6999991603	\$ 247.02
Battery Cabinet	6999991604	\$ 247.02
LPC Single Interlock Trim	6503001605	\$ 2,058.32
<b>MISCELLANEOUS ITEMS</b>		
Explosion proof solenoid valve	6999990322	\$ 1,080.63

SPECIAL HAZARDS  
SPECIAL SYSTEMS

**Protectowire Linear  
Heat Detector (LHD)**



Description	Part Number	Short Code	List Price - Per Foot
<b>TYPE EPC CONSTRUCTION (VINYL JACKET)</b>			
Protectowire (155°F / 68°C) on Msg Wire	6999995589	PHSC-155-EPC-M	\$ 3.50
Protectowire (190°F / 88°C)	6999995590	PHSC-190-EPC	\$ 3.03
Protectowire (190°F / 88°C) on Msg Wire	6999995591	PHSC-190-EPC-M	\$ 3.50
Protectowire (220°F / 105°C)	6999995592	PHSC-220-EPC	\$ 2.92
Protectowire (220°F / 105°C) on Msg Wire	6999995593	PHSC-220-EPC-M	\$ 3.38
Protectowire (280°F / 138°C)	6999995594	PHSC-280-EPC	\$ 3.03
Protectowire (280°F / 138°C) on Msg Wire	6999995595	PHSC-280-EPC-M	\$ 3.50
Protectowire (356°F / 180°C) on Msg Wire	6999995596	PHSC-356-EPC-M	\$ 3.62
<b>TYPE EPN CONSTRUCTION (NYLON OVER VINYL JACKET)</b>			
Protectowire (190°F / 88°C)	6999995597	PHSC-190-EPN	\$ 3.38
Protectowire (190°F / 88°C) on Msg Wire	6999995598	PHSC-190-EPN-M	\$ 3.85
<b>TYPE EPR CONSTRUCTION (POLYPROPYLENE ELASTOMER JACKET)</b>			
Protectowire (155°F / 68°C)	6999995599	PHSC-155-EPR	\$ 3.27
Protectowire (155°F / 68°C) on Msg Wire	6999995600	PHSC-155-EPR-M	\$ 3.73
Protectowire (190°F / 88°C)	6999995601	PHSC-190-EPR	\$ 3.27
Protectowire (190°F / 88°C) on Msg Wire	6999995602	PHSC-190-EPR-M	\$ 3.73
Protectowire (280°F / 138°C)	6999995603	PHSC-280-EPR	\$ 3.27
Protectowire (280°F / 138°C) on Msg Wire	6999995604	PHSC-280-EPR-M	\$ 3.73
Protectowire (356°F / 180°C)	6999995605	PHSC-356-EPR	\$ 3.38
Protectowire (356°F / 180°C) on Msg Wire	6999995606	PHSC-356-EPR-M	\$ 3.85
<b>TYPE TRI CONSTRUCTION DUAL TEMPERATURE TRI-WIRE (VINYL JACKET)</b>			
Protectowire Dual Temp (155/200°F - 68/93°C)	6999995607	PHSC-6893-TRI	\$ 3.38
Protectowire Dual Temp (155/200°F - 68/93°C) on Msg Wire	6999995608	PHSC-6893-TRI-M	\$ 3.85
<b>TYPE XLT CONSTRUCTION (VINYL POLYMER JACKET)</b>			
Protectowire Type XLT (135°F / 57 °C)	6999995582	PHSC-135-XLT	\$ 3.03
Protectowire Type XLT (135°F / 57 °C) on MSG Wire	6999995609	PHSC-135-XLT-M	\$ 3.50

**Notes:**

- **Standard Packaging** - Standard packaging consists of 500 ft. (152m) coils and spools ranging in length from 2300 ft. (710m) to 3280 ft. (1000m) depending upon model ordered. In general, smaller lengths of 500 ft. or less will be on coils, and longer lengths on spools. The exact length of wire per spool used to complete each order is at the sole discretion of the factory. The policy is to send as few spools / coils as possible based upon stock availability.
- **Custom Lengths** - Custom cut single piece coils in lengths up to 1000 ft. (305m) or spools up to 3280 ft. (1000m) can be provided. Limitations may apply depending upon specific model ordered.
- **Messenger Wire Models** - Messenger wire reduces the maximum length of Protectowire that can be accommodated on a standard spool. Types EPC-M, EPR-M and XLT-M are limited to 2500 ft (762m) per spool. Types EPN-M and TRI-M are limited to 2300 ft. (701m) per spool.

SPECIAL HAZARDS  
SPECIAL SYSTEMS

**Protectowire Linear  
Heat Detector (LHD)  
Installation Accessories**



Description	Part Number	Short Code	List Price
<b>COMMERCIAL TYPE ZONE/END-OF-LINE JUNCTION BOXES</b>			
Non-metallic Moisture Proof box w/compression terminals	6999995610	ZB-4-QC-MP	\$ 43.15
Strain Relief Connector (One each req'd per penetration)	6999995585	SR-502	\$ 10.50
<b>HEAVY DUTY TYPE ZONE/END-OF-LINE JUNCTION BOXES</b>			
Fiberglass NEMA-4X Type JIC Enclosure w/compression terminals	6999995584	ZB-HD-4-QC (N4X)	\$ 174.95
Strain Relief Connector (One each req'd per penetration)	6999995585	SR-502	\$ 10.50
<b>WIRING ACCESSORIES</b>			
Splicing Connectors (10/pk, SFTS Sealant Recommended)	6999995586	PWSC	\$ 14.00
3 Pole Splicing Connectors for TRI-Wire (10/pk, SFTS Sealant Recommended)	6999995611	PWSC - 3	\$ 14.00
Splicing Sleeves (10/pk)	6999995612	PWS	\$ 14.00
Tape Sealant for PWSC Splice Connectors (20-30 splices)	6999995613	SFTS-1-8F	\$ 20.99
Flexible Leads	6999995614	PFL	\$ 20.99
Splicing Tape - White	6999995615	#35 White	\$ 11.66
Splicing Tape - Red	6999995616	#35 Red	\$ 11.66
Splicing Tape - Blue	6999995617	#35 Blue	\$ 11.66
Splicing Tape - Black (Low Temp Tape for freezer applications)	6999995618	33+	\$ 10.50
Wire Dispensing Reel for Coils	6999995619	SU-15	\$ 233.26
<b>FASTENERS - GENERAL PURPOSE APPLICATIONS</b>			
Clips, Corner, Nylon - White	6999995583	WAW-N	\$ 0.47
Clips, Corner, Polypropylene - Clear	6999995620	WAW-P	\$ 0.47
Clips, Line (Use with Type EPR, EPC, EPN & TRI Protectowire)	6999995621	OHS-1	\$ 0.59
304 Stainless Steel Line Clip w/ 1/4" hole (Use w/ all LHD types)	6999995622	OHS-SS	\$ 2.33
Beam Clamp Assembly (Steel)	6999995623	BC-2	\$ 2.92
Iron Zinc Plated Beam Clamp Assembly (w/ Polypropylene clip)	6999995624	BC-3P	\$ 3.50
Iron Zinc Plated Beam Clamp Assembly (w/ Nylon clip)	6999995625	BC-3N	\$ 3.50
Drive Rings	6999995626	PDR	\$ 0.35
L-Bracket (Rim Seal Type)	6999995627	RMC-2	\$ 3.50
Stainless Steel L-Bracket (Rim Seal Type)	6999995628	RMC-3	\$ 11.66
Insulated Standoff	6999995629	TR-5G	\$ 5.83
Cable Mount (Requires Sikaflex adhesive)	6999995630	EMS-A-CO	\$ 1.75
Cable Tie (for EMS-A-CO)	6999995631	PLTIS-CO	\$ 0.94
<b>FASTENERS - CABLE TRAY APPLICATIONS</b>			
Mounting Clip (single piece)	6999995633	HPC-2	\$ 2.33
Mounting Clip Assembly	6999995634	CC-2N	\$ 2.33
Mounting Clip Assembly	6999995635	CC-2W	\$ 2.33
Mounting Clip Assembly	6999995636	CC-10N	\$ 2.92
Mounting Clip Assembly	6999995637	CC-10W	\$ 2.92
Mounting Clip Assembly w/ screw & lock nut	6999995638	CC-10N-S	\$ 3.50
Mounting Clip Assembly w/ screw & lock nut	6999995639	CC-10W-S	\$ 3.50
<b>FASTENERS - SPRINKLER PIPE MOUNTING</b>			
Pipe Mounting Strap - Nylon (3/4" to 2" pipe)	6999995640	PM-3A	\$ 1.05
Pipe Mounting Strap - Nylon (2-1/2" to 3-1/2" pipe)	6999995641	PM-3B	\$ 1.40
Pipe Mounting Strap - Nylon (4" to 6" pipe)	6999995642	PM-3C	\$ 7.00
<b>MESSENGER WIRE APPLICATIONS</b>			
Eyebolt	6999995643	TR-4A	\$ 2.33
Turnbuckle	6999995644	TR-24	\$ 6.42
304 Stainless Steel Eyebolt	6999995645	TR-4A-S	\$ 5.83
304 Stainless Steel Turnbuckle	6999995646	TR-24-S	\$ 14.00
<b>TEST EQUIPMENT</b>			
Fault Locator System	6999995647	MFL-92	\$ 10,869.92
Protectowire Alarm Point Locator Meter Adapter	6999995648	APL-90	\$ 921.38