

MODEL F1S5

- Special Application
- Upright/Pendent
- Glass Bulb Sprinklers
- Special Response (VDS)

Part Number	Temperature	Finish	List Price
UPRIGHT 15MM THREADS (1/2")			
F1S5UB	155°F 68°C	Bronze	\$ 18.00
F1S5UC	155°F 68°C	Chrome	\$ 21.66
UPRIGHT 20MM THREADS (3/4")			
F1S5ULB	155°F 68°C	Bronze	\$ 22.58
F1S5ULC	155°F 68°C	Chrome	\$ 27.16
PENDENT 15MM THREADS (1/2")			
F1S5PB	155°F 68°C	Bronze	\$ 18.00
F1S5PC	155°F 68°C	Chrome	\$ 21.66
PENDENT 20MM THREADS (3/4")			
F1S5PLB	155°F 68°C	Bronze	\$ 22.58
F1S5PLC	155°F 68°C	Chrome	\$ 27.16

Please refer to the latest sales bulletin for specific approval listings and available finishes.

See our "Specialties Page" for special finish charges — including Teflon Tape.

Items that are MTO allow 7-10 work days.