

Flexhead - Flexible Drops



Part Name	Part Number	List Price
COMMERCIAL TYPE 1/2"		
Model 2024SS, 2'	7M99000128	\$ 127.00
Model 2036SS, 3'	7M99000129	\$ 146.50
Model 2048SS, 4'	7M99000130	\$ 167.00
Model 2060SS, 5'	7M99000131	\$ 187.00
Model 2072SS, 6'	7M99000132	\$ 208.00
COMMERCIAL TYPE 3/4"		
Model 2024SS, 2'	7M99000133	\$ 127.00
Model 2036SS, 3'	7M99000134	\$ 146.50
Model 2048SS, 4'	7M99000135	\$ 167.00
Model 2060SS, 5'	7M99000136	\$ 187.00
Model 2072SS, 6'	7M99000137	\$ 208.00
REPLACEMENT BRACKETS		
Standard Multi Port bracket (MP24BKT2)	6990008249	\$ 26.25
Adjustable bracket, 24" (AD24BKT-2)	6990005691	\$ 31.25
Adjustable Bracket, 16" (AD16BKT-2)	6990005690	\$ 26.25
COMMERCIAL TYPE 1/2" ***DOMESTIC***		
Model 2024SS, 2'	6990005616	\$ 153.00
Model 2036SS, 3'	6990005071	\$ 173.40
Model 2048SS, 4'	6990006441	\$ 193.80
Model 2060SS, 5'	6990007522	\$ 214.20
Model 2072SS, 6'	6990006972	\$ 234.60
COMMERCIAL TYPE 3/4" ***DOMESTIC***		
Model 2024SS, 2'	6990007552	\$ 153.00
Model 2036SS, 3'	6990007348	\$ 173.40
Model 2048SS, 4'	6990007553	\$ 193.80
Model 2060SS, 5'	6990008169	\$ 214.20
Model 2072SS, 6'	6990006692	\$ 234.60
ELBOW UNITS 1/2"		
Model 2024E, 2'	6990002029	\$ 146.50
Model 2036E, 3'	6990001998	\$ 167.00
Model 2048E, 4'	6990002548	\$ 188.00
Model 2060E, 5'	6990002068	\$ 208.00
Model 2072E, 6'	6990002549	\$ 229.00
ELBOW UNITS 3/4"		
Model 2024E, 2'	6990002030	\$ 146.50
Model 2036E, 3'	6990001999	\$ 167.00
Model 2048E, 4'	6990002415	\$ 188.00
Model 2060E, 5'	6990007207	\$ 208.00
Model 2072E, 6'	6990002857	\$ 229.00

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

Flexhead - Flexible Drops



Part Name	Part Number	List Price
DUCT TYPE		
Model 1024, FRP/Phenolic	6999994971	\$ 1,585.00
Model 1036, FRP/Phenolic	6999994972	\$ 1,585.00
Model 1048, FRP/Phenolic	6999994973	\$ 1,665.00
Model 1124, SS/Galv.	6999994974	\$ 1,665.00
Model 1136, SS/Galv.	6999994975	\$ 1,665.00
Model 1148, SS/Galv.	6999994976	\$ 1,750.00
Model 1224, Polypro.	6999994977	\$ 1,615.00
Model 1236, Polypro.	6999994978	\$ 1,615.00
Model 1248, Polypro.	6999994979	\$ 1,685.00
Model 1324, PVC	6999994980	\$ 1,615.00
Model 1336, PVC	6999994981	\$ 1,615.00
Model 1348, PVC	6999994982	\$ 1,685.00
INSTITUTIONAL TYPE 1/2"		
Model 2024l, 2'	6990001226	\$ 127.00
Model 2036l, 3'	6990001227	\$ 146.50
Model 2048l, 4'	6990001228	\$ 167.00
Model 2060l, 5'	6990001229	\$ 187.00
Model 2072l, 6'	6990001230	\$ 208.00
INSTITUTIONAL TYPE 3/4"		
Model 2024l, 2'	6990001231	\$ 127.00
Model 2036l, 3'	6990001232	\$ 146.50
Model 2048l, 4'	6990001233	\$ 167.00
Model 2060l, 5'	6990001234	\$ 187.00
Model 2072l, 6'	6990001235	\$ 208.00

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

SPRINKFLEX

Flexible Drops

Part Name	Part Number	Box Qty.	List Price
UNBRAIDED - UL APPROVED			
1/2" x 28"	7M99001877	25	\$ 103.26
3/4" x 28"	7M99001878	25	\$ 103.26
1/2" x 40"	7M99001879	25	\$ 108.36
3/4" x 40"	7M99001880	25	\$ 108.36
1/2" x 48"	7M99001881	25	\$ 116.04
3/4" x 48"	7M99001882	25	\$ 116.04
1/2" x 59"	7M99001883	25	\$ 124.98
3/4" x 59"	7M99001884	25	\$ 124.98
1/2" x 71"	7M99001885	25	\$ 135.18
3/4" x 71"	7M99001886	25	\$ 135.18
BRAIDED - UL & FM APPROVED			
1/2" x 28"	7M99001887	25	\$ 127.50
3/4" x 28"	7M99001888	25	\$ 127.50
1/2" x 40"	7M99001889	25	\$ 141.54
3/4" x 40"	7M99001890	25	\$ 141.54
1/2" x 48"	7M99001891	25	\$ 151.74
3/4" x 48"	7M99001892	25	\$ 151.74
1/2" x 59"	7M99001893	25	\$ 165.78
3/4" x 59"	7M99001894	25	\$ 165.78
1/2" x 71"	7M99001895	25	\$ 179.76
3/4" x 71"	7M99001896	25	\$ 179.76
ELBOW ADAPTORS			
1" X 1/2", SHORT	7M99002324		\$ 25.55
1" X 3/4", SHORT	7M99002325		\$ 25.55
1" X 1/2", TALL	7M99002326		\$ 25.55
1" X 3/4", TALL	7M99002327		\$ 25.55
REPLACEMENT BRACKETS			
24" Bracket	7M99001897	25	\$ 30.00

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

RESIDENTIAL FIRE PUMPS & ACCESSORIES



Part Name	Part Number	List Price
13D RESIDENTIAL FIRE PUMPS		
LSF-150-SP, 1.5HP	6990011734	\$ 3,943.01
LSF-150-C, 1.5HP	6990001951	\$ 4,874.62
LSF-300-C, 3HP	6990007670	\$ 5,545.46
LSF-300-CIF, 3HP	6990010279	\$ 5,793.60
LSF-500-CIF, 5HP	6990011268	\$ 6,664.22
LSF-500-CIG, 5HP	6990003324	\$ 9,555.76
LSF-500-CIG3, 5HP	6990012619	\$ 9,391.74
LSF-750-CIF, 7.5HP	6990012169	\$ 9,780.78
LSF-1000-CIF, 10HP	6990012299	\$ 10,508.40
13R RESIDENTIAL FIRE PUMPS		
13R-500-CIF	6990009578	\$ 15,319.93
13R-750-CIF	6990012620	\$ 16,789.88
13R-1000-CIG5	6990012465	\$ 18,348.16
13R-1000-CIF	6990009328	\$ 25,998.66
WATER STORAGE TANKS		
300V (34.5'D X 78' H)	6990010919	\$ 1,734.93
400V (42D X 62H)	6990007821	\$ 2,586.62
550V (48D X 75H)	6990011270	\$ 2,687.56
300R (62"L X 29"W X 48"H)	6990001952	\$ 2,285.90
400R (62"L X 29"W X 64"H)	6990008758	\$ 3,038.75
TANK FITTING KITS		
TF-1.5	6990008603	\$ 521.53
TF-2	6990012621	\$ 565.69
SH-1.5	6990012622	\$ 382.74
SH-2	6990012623	\$ 439.51
FLOW SMART - 13D RESIDENTIAL FIRE PUMPS		
FS200W	7M99002371	\$ 2,281.69
FS150SP	7M99002372	\$ 2,731.72
FS150C	7M99002373	\$ 3,385.74
FS300C	7M99002374	\$ 3,772.68
HOME HYDRANT - 13D PUMP/TANK PACKAGE		
HH200W	7M99002375	\$ 5,955.53
HH150SP	7M99002376	\$ 6,485.47
HH150C	7M99002377	\$ 7,139.49
HH300C	7M99002378	\$ 7,736.72

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.