



# CONTINUING TO CHANGE THE SHAPE OF SPRINKLER PROTECTION

## Reliable's DH56 & Dry DH56 Sprinklers

For Decks, Halls or Rooms up to 28 feet wide and 10 feet deep.

- UL Listed for Extended Coverage, Light Hazard Applications – 5.6K Factor
- Deflector to ceiling dimensions are: 4" min. to 12" max.
- **Install 1 sprinkler instead of 2**
- Min. spacing 14', 250 psi rated for wet & dry versions
- 1/2" adjustment, available corrosion resistant finish
- Available in recessed and concealed

Coverage	Flow	Pressure
28'x 8'	23 gpm	16.9 psi
28'x 10'	28 gpm	25.0 psi

Bulletins 015 & 016

**RELIABLE ONE SOURCE**  
For all your fire protection needs.



1.800.431.1588  
www.reliablesprinkler.com