

New

Storage Sprinklers from Reliable

NOW FM APPROVED!



N252 EC, K-25 EC Pendent & Recessed Pendent

- An Extended Coverage Pendent & Recessed Pendent for Density/Area Design
- Approved for coverage up to 196 square feet (14' x 14') for extra hazard and storage applications
- Can be installed directly on the piping for exposed pipe systems. Unlike upright sprinklers, sprig-ups are not required for larger diameter piping
- cULus Listed for a minimum of deflector to commodity distance of 36" and for unobstructed or non-combustible obstructed construction
- Pendent version is **FM Approved**
- Complies with the criteria for protection of retail stores as described in NFPA 2002, section 12-7.2
- Installations for finished ceilings utilize the push-on, thread off FP recessed escutcheon which provides a 1/2" (13mm) adjustment
- No Safety Caps - saves time and labor
- Temperatures: 165°F (74°C) & 212°F (100°C)
Finishes: Brass, Chrome, White & Black Plated
- Refer to Bulletin 008

J168, K-16.8 Upright

- New control mode, density/area upright sprinkler
- Primarily for extra hazard and storage occupancies as designed and installed under NFPA 13 requirements
- Can allow reduced design areas, higher storage, reduced ceiling clearance to storage, and other savings in sprinkler design
- Uses the robust Model G solder capsule that has been installed in millions of sprinklers over the last 30 years
- No Safety Caps - saves time and labor
- cULus Listed and **FM Approved**
- Available with various temperature ratings and finishes
- Refer to Bulletin 011

RELIABLE ONE SOURCE
For all your fire protection needs.

P/N 9999970309

Reliable®

TECHNOLOGY • QUALITY • SERVICE

1.800.431.1588

www.reliablesprinkler.com

The Reliable Automatic Sprinkler Co., Inc.
Manufacturer & Distributor of Fire Protection Equipment