

Changing the Shape of Sidewall Sprinkler Coverage!

The DH80 Sprinkler

LIGHT HAZARD/EC QUICK RESPONSE

Coverage up to 28ft. in **width** and a length of 14ft.

NYC MEA
APPROVED!



Install 1 Sprinkler Instead of 2!

- **The Sprinkler Designed for Long & Narrow Applications:**

- Hallways - Corridors
- Breezeways - Balconies
- Decks - Rooms up to 28' (8,5m) long

- **Installation:**

- Up to 28' (8,5m) apart
- Smooth flat ceilings
- Up to 14' (4,3m) from any end wall
- Minimum of 12" (3,6m) apart
- 4" (102mm) to 12" (305mm) from the finished ceilings
- Flow: 40 gpm @ 25psi (K = 8.0)

- **Available Styles:**

- Conical Concealed, Recessed, Standard

- **Finishes:**

- CCP Concealed versions: White and other painted finishes
- FP Recessed Push-On/Thread-Off Escutcheon: White & Chrome, Sprinkler: White, Chrome & Bronze

- **Temperature Rating:**

- Sprinkler: 155°F (68°C)
- Cover plate: 135°F (57°C)

- **cULus Listed and NYC MEA Approved**

- **US Patented**

- **For technical information refer to Bulletin 003.**

HOW MANY SPRINKLERS CAN YOU SAVE?