

Reliable®

Open Sprinklers

Reliable Open Sprinklers are Reliable automatic sprinklers that are not equipped with an operating element. Open sprinklers are used on deluge systems where water flow is controlled by an automatically or manually operated deluge valve. All current models of Reliable automatic sprinklers can be ordered and installed as Open Sprinklers.

“Open Sprinklers” are available with the same finishes as listed on their corresponding Reliable automatic sprinkler bulletins. Open sprinklers ordered with a finish are generally provided with the waterway uncoated.

Select open sprinklers with electroless nickel PTFE plating are UL Listed with the waterway coated (please reference Table A below).

Refer to the appropriate automatic sprinkler product bulletins for listing and approvals, installation, maintenance, warranty, and ordering information.



F1FR56 Pendant




F1FR56 Upright



F1FR80 Pendant



F1FR80 Upright



GFR VELO ECOH Pendant



GFR VELO ECOH Upright

UL Listed for Electroless Nickel PTFE Plating of Waterway

Table A

Sprinkler Model	Orientation	Nominal K-factor US (metric)	Sprinkler Identification Number (SIN)
F156	Pendent	5.6 (80)	RA1314
F156	Upright	5.6 (80)	RA1325
F180	Pendent	8.0 (115)	R1712
F180	Upright	8.0 (115)	R1722
GFR VELO ECOH	Pendent	14 (200)	R6043
GFR VELO ECOH	Upright	14 (200)	R6553