

#### Stainless Is Here

Model F1-SS and F1FR-SS series sprinklers are cULus Listed and FM Approved Corrosion Resistant sprinklers featuring a frame and deflector made of Type 316 stainless steel alloy. All Model F1-SS and F1FR-SS series sprinklers use a glass bulb operating element and beryllium-nickel sealing washer with PTFE tape on both sides.

For pendent sprinklers, Reliable offers Type 316 stainless steel Model B, F1, F2, and FP escutcheons. The Model F1, F2, and FP recessed escutcheons are cULus Listed for use with Model F1-SS and F1FR-SS pendent sprinklers. The Model F2 recessed escutcheon is FM Approved for use with Model F1-SS and F1FR-SS pendent sprinklers.

\* See Bulletins 064 & 065 for full details



F1-80 Upright Stainless



F1FR80 Upright Stainless



F1FR56 Upright Stainless



F1-56 Upright Stainless



F1-80 Pendent Stainless



F1FR80 Pendent Stainless



F1FR56 Pendent Stainless



F1-56 Pendent Stainless

Sprinkler Model	Nominal K-factor gpm/psi <sup>1/2</sup> (l/min/bar <sup>1/2</sup> )	Thread Size NPT or ISO7-1	Sprinkler Identification Number (SIN)	Sensitivity
F1-56SS Upright	5.6 (80)	1/2	RA6424	Standard Response
F1-56SS Pendent	5.6 (80)	1/2	RA6414	Standard Response
F1FR-56SS Upright	5.6 (80)	1/2	RA6524	Quick Response
F1FR-56SS Pendent	5.6 (80)	1/2	RA6514	Quick Response
F1-80SS Upright	8.0 (115)	3/4	RA6422	Standard Response
F1-80SS Pendent	8.0 (115)	3/4	RA6412	Standard Response
F1FR-80SS Upright	8.0 (115)	3/4	RA6522	Quick Response
F1FR-80SS Pendent	8.0 (115)	3/4	RA6512	Quick Response