

WP56 Glass Bulb Sprinkler, SIN R501

- 155°F (68°C)
- 200°F (93°C)

WP56L Fusible-link Sprinkler, SIN R502

- 165°F (74°C)
- 212°F (100°C)

## **Industry-leading Protection**

The Model WP Series Sprinklers used with fixed glazed assemblies create a cULus Listed alternative to a fire-rated wall. The **Fast Response Specific Application Pendent Vertical Sidewall** sprinklers can be spaced up to 12 ft (3.7 m) on-center and requires only 15 gpm (57 l/min) flow per sprinkler.

- Sleek profile available in bronze, chrome, white polyester, and special finishes to complement architectural glazing
- cULus Listed as corrosion resistant with ENT, white polyester or black polyester finish on WP56 glass bulb sprinkler