

MODEL DDV DIAPHRAGM DELUGE VALVE

Performance Under Pressure

**FM Approved for up to
400 psi/27.6 bar.**

Diaphragm is the only moving internal valve component.

No trim connections to the valve cover for easy internal inspection

Compact footprint.

6 Available trim options:

- Remote Resetting
- Remote Resetting/Pressure Regulating
- Dry Pilot/Pressure Regulating
- Electric Actuation
- Dry Pilot
- Wet Pilot

Sizes: 1½" (40 mm), 2" (50 mm),
2½" (65 mm), 76 mm, 3" (80 mm),
4" (100 mm), 6" (150 mm), 165 mm

See Technical Bulletins 550 & 551

Reliable®

www.reliablesprinkler.com/ddv

