

# KFR SERIES SPRINKLERS

## Unmatched Value

The KFR series sprinklers are standard spray, quick response sprinklers with a fusible link operating element. The durable design provides additional protection against impact damage. The link does not extend beyond wrench boss, reducing risk of damage during installation.

The robust design allows the KFR to be shipped and installed without protective cover. No need to return to the jobsite to remove, and no “forgotten” protectors.

### Unmatched Reliable® Quality & Service

- EVERY thermal link is X-ray validated.
- EVERY sprinkler is visually inspected and pressure tested to at least 500 psi before packaging.
- High-capacity fully automated assembly ensures your product arrives on time, every time.

### Specifications

- **KFR56** *cULus* 250 psi (17,2 bar); *FM* 175 psi (12 bar) and **KFR56-300** *cULus* 300 psi (20,7 bar): K5.6 (80) Standard Spray Quick Response Upright, Pendent, and Horizontal Sidewall Sprinklers.
- **KFR80** *cULus* 250 psi (17,2 bar); *FM* 175 psi (12 bar): K8.0 (115) Standard Spray Quick Response Upright and Pendent Sprinklers.

### Our Manufacturing

- Industry-leading proprietary link manufacturing process perfected over the past 100 years.
- Most rigorous quality control process in the Industry.
- Visit our competitors, then tour our plant. Decide for yourself.

**Reliable®**

[www.reliablesprinkler.com/kfr](http://www.reliablesprinkler.com/kfr)

