



## PRODUCT SOLUTIONS

### Model F1-SS & F1FRSS Series Sprinklers

Model F1-SS and F1FR-SS series sprinklers are cULus Listed Corrosion Resistant sprinklers featuring a frame and deflector made of Type 316 stainless steel alloy. All Model F1-SS and F1FR-SS series sprinklers use a glass bulb operating element and beryllium-nickel sealing washer with PTFE tape on both sides.

Model F1-SS and F1FR-SS series pendent sprinklers are cULus listed for installation with Reliable Model F1 and FP recessed escutcheons, which are available in Type 316 stainless steel alloy. In addition, Reliable Model B one-piece escutcheons are also available in Type 316 stainless steel alloy.

*\* See Bulletins 064 & 065 for full details*



F1-56 Upright Stainless



F1FR56 Upright Stainless



F1-80 Upright Stainless



F1FR80 Upright Stainless



F1-56 Pendent Stainless



F1FR56 Pendent Stainless



F1-80 Pendent Stainless



F1FR80 Pendent Stainless

Sprinkler Model	K-factor	Thread Size NPT or ISO7-1	Sprinkler Identification Number (SIN)	Sensitivity
F1-56SS Upright	5.6 (80)	1/2	RA6424	Standard Response
F1-56SS Pendent	5.6 (80)	1/2	RA6414	Standard Response
F1FR-56SS Upright	5.6 (80)	1/2	RA6524	Quick Response
F1FR-56SS Pendent	5.6 (80)	1/2	RA6514	Quick Response
F1-80SS Upright	8.0 (115)	3/4	RA6422	Standard Response
F1-80SS Pendent	8.0 (115)	3/4	RA6412	Standard Response
F1FR-80SS Upright	8.0 (115)	3/4	RA6522	Quick Response
F1FR-80SS Pendent	8.0 (115)	3/4	RA6512	Quick Response

