SPRINKLERS

Standard Spray QR - Quick Response

S-1 F1FR - Upright
S-5 F1FR-300 - Upright
S-6 F1FR - Pendent, Recessed
S-10 F1FR-300 - Pendent, Recessed
S-11 F1FR - Horizontal Sidewall
S-13 F1FR56-300 - HSW, Rec HSW and SWC56 Concealed
S-14 F1FR - Vertical Sidewall
S-15 F1FR - Conventional
S-17 F1FR-SS Stainless Steel - Upright and Pendent
S-18 F1FR LL - Pendent and CCP
S-19 F1FR - FS LO Large Orfice
S-20 F1FR-FS56 & F1FR-FS42 FLAT SPRAY
S-21 KFR56 - Upright and Pendent
S-22 KFR56-300 - Upright & Pendent
S-23 KFR56-300 - HSW and CCP
S-24 KFR56 HSW and CCP
S-25 KFR80 Upright and Pendent
S-26 GFR Upright
S-27 GFR - Pendent & HSW
S-28 G5-80, G5-56, G5-42 & G5-28
S-29 G6-56 HSW QR
S-30 G5-80, G5-56, G5-42 and G5-28 QR "Sealing" Concealed
S-31 G5-56 300 QR "Sealing" Concealed
S-32 G5-56 300 Concealer
S-33 F1FR CCP and F1FR-300 CCP
S-34 XL Commercial - Pendent and HSW

Standard Spray SR - Standard Response

S-35 F1 - Upright
S-39 F1-SS Stainless Steel - Upright & Pendent
S-40 F1-300 - Upright
S-41 F1 - Pendent, Recessed
S-44 F1-300 - Pendent, Recessed
S-45 F1 - Conventional
S-48 F1 - Horizontal Sidewall
S-49 F1 - Vertical Sidewall
S-50 G - Upright
S-52 G - Pendent
S-54 G - Conventional
S-54 G - Vertical Sidewall
S-55 G - Horizontal Sidewall, Recessed
S-57 G - Recessed
S-59 G4
S-60 G4-11
S-61 G4-300 - Concealed
S-63 G5-80, G5-56, G5-42 and G5-28 SR "Sealing" Concealed
S-64 G5-56 300 SR "Sealing" Concealed

Extended Coverage

S-65 G6-80 HSW QR EC
S-66 JL112 and J112 - Upright, Pendent and Rec Pendent
S-67 F1FR56 QREC and F1FR EC - Pendent, Recessed
S-68 F1FR 56-300 and F1FR-300 QREC - Pendent, Recessed
S-69 F1FR 56-300 and F1FR-300 QREC EC9 - HSW, Recessed
S-70 F1FR 56 EC8 and F1FR QREC EC9 - HSW, Recessed
S-71 F1FR 56-300 and F1FR-300 QREC CCP - Concealed
S-72 DH56 - HSW, HSW Recessed, HSW Concealed
S-73 DH80 - HSW, HSW Recessed, HSW Concealed
S-74 G4 XLO-QR ECLH/ECOH
S-74 KFR-CCS Combustible Concealed Space
S-75 SWC Concealed Sidewall
S-76 F1 56 SREC and F1 EC - Pendent
S-77 F1 56-300 SREC and F1-300 EC - Pendent, Recessed
S-78 G – EC4 - HSW
S-78 GFR VELO ECOH - Upright
S-78 GFR VELO ECOH - Pendent, Recessed
S-79 MBEC-14- HSW

Residential

S-80 F1RES 30, KRES 30 - Pendent, Rec Pendent, CCP
S-81 F1RES 49 & KRES49 - Pendent, Rec Pendent, CCP
S-82 F1RES 44, KRES 44- HSW, REC HSW, SWC44
S-83 F1RES 58, KRES 58 - Pendent, Rec Pendent, CCP, HSW
S-84 F1RES 58 HSWX & KRES 58 HSWX
S-85 F1RES 76 - Pendent, Rec Pendent, CCP
S-86 RFC43 Flat Concealed
S-86 RFC30 Flat Concealed
S-86 RFC49 Flat Concealed
S-86 RFC58 Flat Concealed
S-86 RFC76 Flat Concealed
S-87 RFC49plus Flat Concealed
S-88 RFS42 Flat Plate Concealed HSW
S-89 F3RES44 Dry HSW
S-90 F3RES44 Dry Recessed HSW/F2
S-91 F3RES44 Dry HSW/HB
S-92 F1RES 30 LL - Pendent, Rec Pendent, CCP
S-93 F1RES 49 LL - Pendent, Rec Pendent, CCP
S-94 F1RES 44 LL - HSW, Rec HSW, SWC
S-95 F1RES 58 LL - Pendent, Rec Pendent, CCP, HSW
S-96 RFC30 LL Flat Concealed
S-96 RFC43 LL Flat Concealed
S-96 RFC49 LL Flat Concealed

Storage

S-97 JL14 ESFR
S-97 JL17 ESFR
S-99 P22 ESFR
S-99 P25 ESFR
S-100 M336 ESFR
S-101 N28 ESFR
S-102 GXLO Upright and Pendent
S-102 GXLO Intermediate
S-103 J168 - Upright
S-103 N252 EC - Pendent and Recessed Pendent
S-103 LB11 HSW
S-104 GL112 Upright and Pendent
S-104 G VELO Pendent
S-106 GSR112 Upright and Pendent
S-107 GQR112 Upright and Pendent
S-108 F1FR 56 & F1FR Intermediate - Upright and Pendent
S-109 F1 56 & F1 Intermediate - Upright and Pendent
S-110 KFR56 Intermediate - Upright and Pendent
S-111 Intermediate Level Sprinkler with D-3 and D-5 Guard Assembly
S-113 GFR Intermediate - Upright and Pendent
S-114 G Intermediate Level - with D-3 and D-5 Guards/Shields
S-117 D-1 - Int. Level Sprinkler and Guard Assembly

Special
S-118 Attic Sprinklers
S-119 LT56 Series Pendent
S-120 LT56 Series CCP
S-121 LT56C Flat Concealed
S-122 XL INST - Institutional
S-123 F4FR-NF
S-123 KFR CCS Combustible Concealed
S-124 WP56 & WP56L Window Sprinklers
S-125 F1S5-FLAT SPARY

Dry
S-129 F3QR56-Upright
S-130 F3QR56 - Pendent
S-132 F3QR56 - Pendent / HB
S-134 F3QR56 - Recessed Pendent /FP
S-136 F3QR56 - Recessed Pendent / F1
S-138 F3QR56 - Horizontal Sidewall
S-140 F3QR56 - Horizontal Sidewall / HB
S-142 F3QR56 - Recessed Horizontal Sidewall / FP
S-144 F3QR56 - Recessed Horizontal Sidewall / F1
S-146 F3QR56 - Concealed
S-148 F3QR80 - Pendent
S-149 F3QR80 - Pendent / HB
S-150 F3QR80 - Recessed Pendent / FP
S-151 F3QR80 - Horizontal Sidewall
S-152 F3QR80 - Horizontal Sidewall / HB
S-153 F3QR80 - Horizontal Sidewall / FP
S-154 F3QR80 - Concealed
S-155 G5-56 Dry
S-156 DH56 Dry - Horizontal Sidewall
S-157 DH56 Dry - Horizontal Sidewall / HB
S-158 DH56 Dry - Recessed Horizontal Sidewall
S-159 DH56 Dry - Concealed
S-160 DH80 Dry - Horizontal Sidewall
S-161 DH80 Dry - Horizontal Sidewall / HB
S-162 DH80 Dry - Recessed Horizontal Sidewall
S-163 DH80 Dry - Concealed
S-164 F3-56 Upright
S-165 F3-56 - Pendent
S-167 F3-56 - Pendent / HB
S-169 F3-56 - Recessed Pendent / FP
S-171 F3-56 - Recessed Pendent / F1
S-173 F3-56 - Horizontal Sidewall
S-175 F3-56 - Horizontal Sidewall / HB
S-177 F3-56 - Recessed Horizontal Sidewall / FP
S-179 F3-56 - Recessed Horizontal Sidewall / F1
S-181 F3-56 - Concealed
S-183 F3-80 - Pendent
S-184 F3-80 - Pendent / HB
S-185 F3-80 - Recessed Pendent / FP
S-186 F3-80 - Horizontal Sidewall
S-187 F3-80 - Horizontal Sidewall / HB
S-188 F3-80 - Horizontal Sidewall / FP
S-189 F3-80 - Concealed

Nozzles
S-190 TNL280 Pendent Spray Nozzle
S-191 B & FM - Spray Nozzles - Window & Cornice Types
S-192 F1-FTR - Pilot Line Detector (PLD)
S-192 HV - High Velocity Nozzles

Multipurpose Residential Risers and Accessories
S-197 Accessories - Cabinets & Escutcheons
S-199 Accessories - Multipurpose LL Residential Riser
S-199 Accessories - Gauges, Connections, Drips, Misc.

Special Application
S-201 F1S5 - Upright / Pendent (for UK use only)

Accessories

Escutcheons
S-202 FP Push-On / Thread Off Escutcheons
S-202 G/F1 Escutcheon and Collar Assembly
S-202 G/F1 Escutcheon Only
S-202 G/F1 Collar Only
S-202 G/F1 and G/F2 Escutcheon Extender Ring
S-202 G/F2 Escutcheon & Collar Assembly
S-202 G/F2 Escutcheon Only
S-202 G/F2 Collar Only
S-203 B, C & HB Two Sprinkler Escutcheons
S-203 Sure-Off Tester

Spk Guards/Emergency Cabinets
S-204 Sprinkler Guards & Shields
S-204 Emergency Cabinets
S-206 For Sprinklers Wrenches

Printed Coverplates
S-207 Models G6, G5, RFS42

Replacement Coverplates
S-208 G1 Concealed Replacement Coverplates

Special Services
S-209 Special Services / Special Finishes

VALVES

Valve Stations
V-1 Alarm Valve Stations & Wet Alarm Valves
V-2 FM Wet Alarm Valve & VdS Alarm Valve Stations
V-2 VdS DDX-Dry LP Valve Stations & Trim Kits

Alarm And Check Valves
V-3 E and E3 Alarm Valves - FxF, FxG, GxG
V-4 E3 - Trim Segmented & Loose
V-4 LPC - Valve Sets
V-6 Miscellaneous Alarm Valve Trim
V-6 Retard Chamber and Mechanical Spk. Alarm
V-6 Valve Seat Wrenches
V-6 G - Riser Check - 2½", 3", 4", 6"
V-6 G - Grooved Check - 2½", 3", 4", 6"
V-6 CVE - Swing Check - 4", 6", 165mm, 8"

Deluge Valves
V-7 DDV Deluge Valves - Electric Trim
V-8 DDV Deluge Valves - Wet Pilot Line Trim
V-9 DDV Deluge Valves - Dry Pilot Line Trim
V-10 DDV Deluge Valves-Remote Reset
V-11 DDV Deluge Valves-Remote Reset Pressure Regulating
V-12 DDV Deluge Valves-Dry Pilot Pressure Regulating
V-13 DDV Drain Trims & Accessories
V-14 DDX Deluge Valves & Trim
V-14 DDX Deluge Valves-Electric,Wet Pilot, Dry Pilot-Fully Assembled

Pressure Control Valves
V-16 PRV Diaphragm Pressure Regulating Valves

Low Pressure Dry Systems
V-17 DDX-LP Dry Pipe Valve Systems
V-18 DDX-LP Dry Pipe/DDX Valve Systems-VDS

Dry Pipe Valves
V-19 A, D - 2½", 4", 6"
V-19 A, D - Loose/Preassembled Trim, Factory Trimmed
V-20 FX- 2",2 1/2",3" 4",6" Valve and Trim
V-22 FX- 2",2 1/2",3" 4",6" Fully Assembled

Control Valves
V-23 PIV, OSY Gate Valves & Bronze Butterfly Valves
V-25 Supervised Butterfly Valves

Accessories
V-26 ACD Dry Systems Auxiliary
V-26 B-1 – Accelerator, A-2 Air Maintenance Device, B-1 Air Maintenance Device
V-27 Electronic Accelerators
V-27 Test and Drain,Pressure Relief Valves,AAV Auto Air Vent
V-28 Air Compressors
V-31 Pressure Gauges
V-31 Inspectors Test Connections
V-31 Automatic Ball Drips
V-31 Mechanical Ball Drips
V-31 Strainers (Misc. Items)
V-31 Sprinkler/Valve System Signs
V-32 Residential Riser
V-33 CR2 Commercial Riser
V-36 FCA2 Floor Control Valves

SPECIAL HAZARDS/SPECIAL SYSTEMS

Model H Deluge, Preaction, PrePak 1 1/2"
SS-1 Model H Deluge / Riser Assemblies and Trim

Single, Double, Interlock
SS-2 DDX Single Interlock - Fully Assembled
SS-4 DDX Double Interlock - Fully Assembled
SS-5 DDX Preaction Trim

PrePaK
SS-8 DDX Type D PrePaK
SS-9 DDX Type F PrePaK
SS-10 DDX Electric Release PrePaK
SS-11 DDX Wet Pilot PrePaK
SS-12 DDX Dry Pilot PrePaK
SS-13 DDX-LP PrePaK System
SS-14 DDX N2 Blast PrePak Systems

Accessories
SS-15 Accelerator
SS-15 Pull Boxes
SS-15 RPC 4410 RC Control Panel
SS-15 System Modules / Batteries
SS-16 Electric Alarm Bells, Supervisory Air Supply, Valve Seat Wrenches
SS-16 LPC Components
Protectowire

SYSTEM COMPONENTS

Grooved Couplings And Fittings - Europe
SC-1 Rigid Couplings
SC-2 Flexible Couplings
SC-3 Reducing Couplings
SC-4 Flange Adaptors
SC-5 Standard 90° Elbows
SC-6 Standard 45° Elbows
SC-7 Standard Tees
SC-8 Short Radius 90° Elbows & Straight Tees
SC-9 Grooved Reducing Tees
SC-10 Concentric Reducers
SC-12 Universal Flange Adaptors
SC-13 Caps
SC-14 Threaded Mechanical Tees
SC-15 Grooved Mechanical Tees
SC-16 Ubolt Mechanical Tees & Pitcher Tees
SC-18 Threaded & Grooved Mechanical Cross

Grooved Couplings And Fittings - Middle East/Australia
SC-18 Rigid & Flex Couplings
SC-19 Flexible Couplings
SC-20 Reducing Couplings
SC-22 Flange Adaptors & Flange Adaptors Nipples
SC-23 Elbows
SC-24 Elbows, Tees, & End Caps
SC-25 End Caps with Holes, Reducing & Drain Elbows
SC-26 Concentric Reducers
SC-28 Straight Crosses
SC-29 Reducing Tees
SC-31 Eccentric Reducers
SC-32 Mechanical Tees
SC-34 U-Bolt Mechanical Tees
SC-35 Rigid & Flexible Couplings
SC-36 Flexiible & Reducing Couplings, Flange Adaptors
SC-37 Flange Adaptors - Galvanized
SC-38 Elbows
SC-39 Elbows, Tees, Radius & End Caps
SC-40 End Caps with Holes, Reducing & Drain Elbows
SC-41 Concentric Reducers
SC-43 Crosses
SC-44 Reducing Tees
SC-46 Eccentric Elbows
SC-47 Mechanical Grooved Tees
SC-48 Threaded Tees
SC-49 U-Bolt Mechanical Tees

US Made Cast Iron Fittings
SC-50 90° and 45° Elbows, Reduc. 90° Elbows, Reduc. Couplings, Standard Tees
SC-52 Reducing Tees
SC-53 Bullhead Tees, Crosses, Plugs, Caps (malleable), Couplings (malleable), Unions (malleable)
SC-54 Hex Bushings, Companion Flanges, Pipe Dope, Teflon Tape, Cutting Oil
SC-55 90° Elbows, Reducing 90° Elbows, 45° Elbows Reducing Couplings, Standard Tees
SC-56 Reducing Tees, Couplings, Caps, Unions
SC-58 Reducing Tees
SC-58 Bullhead Tees, Crosses (Standard & Reduc.) Plugs, Pipe Dope, Teflon Tape

Cast Iron & Ductile Fittings - Foreign Anvil
SC-58 90° and 45° Elbows, Reduc. 90° Elbows, Reduc. Couplings, Standard Tees
SC-62 Bullhead Tees, Crosses, Caps, Couplings Pipe Dope, Teflon Tape, Cutting Oil

US Made Flanged Fittings
SC-65 Flanged Elbows, Reducing
SC-66 Flange Tees
SC-67 Flanged Reducers
SC-68 Companion, Reducing Flange

Expansion Loops
SC-69 Threaded & Grooved Models

CPVC Pipe, Fittings, & Hangers
SC-71 Pipe, Anti-Freeze
SC-72 Hangers (Single, Double, Sidemount, Stand-Off)
SC-73 Sealant, Caulk
SC-74 Elbows, Head Adapters, Standard Tees, Tees (Reduc. and Run Reduc.), Tee Head
SC-75 Adapters Tee Head Adapters (cont'd), Bushings,
SC-77 Head Adapters, Adapters, Couplings, Reduc. Couplings
SC-78 Grooved Adapters, Caps, Crosses, Cement, Thread Sealant
SC-79 Torque Safe Fittings

Tee-lets
SC-80 Tee-lets
SC-82 Grooved Shape Nipples - Sch 40
SC-83 Grooved Shape Nipples - Sch 10
SC-84 Import Olets
SC-85 Welded Outlets

Hangers
SC-86 Ring Hangers, Beam Clamps, Riser Clamps, Wall Plates
SC-87 Earthquake Bracing
SC-88 Eye Sockets, All Thread Rod, Hex Nuts, Washers, Drop Anchors

Super Screws
SC-89 Sammy Super Screws

Fire Department Equipment
SC-91 Fire Department Connections, Hose Valves, Accessories

Nipples
SC-93 Adjustable Wet Drop Nipples (M x F, M x M)
SC-94 Steel Nipples, Blck & Galvanized

Valves
SC-99 Flanged Check, Gasket Kits
SC-100 OS&Y, PIV, Butterfly Valves (GxG and Wafer)
SC-101 Reliable PIV,OSY Gate & Bronze Butterfly Valves
SC-103 Butterball Valves (Threaded and Grooved)
SC-104 Foreign Trim Valves - Globe, Ck, 3-way Angle
SC-105 Valves, FDC, and Accessories
SC-108 Air Release Valves & 50GG Check Valves
SC-110 US Made Trim Valves - Globe, Ck, 3-way, Angle
SC-112 Detector Check, In-Building Riser, Wafer Check, Test & Drains

Backflows
SC-114 2000ss, 2001ss, 3000ss, 30001ss
SC-115 4000ss, 4001ss, 5000ss, 5001ss
SC-116 Colt Series: C-200 OS&Y, C-200 BFV, C-300 OS&Y, C-300 BFV
SC-117 Colt Series: C-400 OS&Y, C-400 N or Z, C-500 OS&Y, C-500 N or Z
SC-118 Maxim Series: M-200 OS&Y, M-200 BFV, M-300 OS&Y, M-300 BFV
SC-119 Maxim Series: M-400 OS&Y, M-400 N or Z, M-500 OS&Y, M-500 N or Z
SC-120 Deringer
SC-122 OS & Y

Air Compressors
SC-127 Bare, with Check, Tank Mounted

Electrical Equipment
SC-133 Waterflow Detector, Tamper Switches, Electric Bells, Accessories
SC-134 Canadian versions
SC-135 System Sensor - Europe
SC-136 System Sensor - Far East/Australia
SC-137 System Sensor - Middle East

Flexible Drops
SC-138 Flexible Drops

Residential Fire Pumps & Accessories
SC-139 Residential Fire Pumps, Tanks, Kits

Steel Pipe
SC-140 Schedule 40 & 10, Flowpipe, Threadable Lightwall, and Special Requests

Expansion Tanks
SC-141 Expansion Tanks

REPLACEMENT PARTS

Valve Service Kits & Valve Seat Wrenches
RP-1 Model A Dry Pipe Valve
RP-1 Model D Dry Pipe Valve
RP-2 Model EX Dry Pipe Valve
RP-3 Model FX Dry Pipe Valve
RP-4 DDX Valve With Stainless Steel Clapper
RP-5 Early Gen DDX Valves with Brass Clapper
RP-6 Model E3 (Small) Alarm Valve
RP-6 Model E (Large) Alarm Valve / CVE Check Valve

Valve Spares Kits
RP-7 Wet Alarm Valve Spares Kits
RP-7 Dry Alarm Valve Spares Kits
RP-8 Deluge Valve Spares Kits

Alarm Valves
RP-9 Alarm Valves & Trimmings

Dry Pipe Valves
RP-14 Dry Pipe Valves and Trimmings
RP-17 Accelerator

Deluge Valves
RP-18 Deluge Valves and Trimmings
RP-25 External Reset Device
RP-25 Air Maintenance Devices

Miscellaneous
RP-26 Sight Test Connection
RP-27 Sight Drain, Emergency Pull Box, Copper Tubing, Parts for Model B Air Compressor Panel
RP-28 Air Compressor