

## Concealed, Horizontal Sidewall Quick Response Sprinklers

March 2015

Dear Valued Customer:

Reliable's new Concealed, Horizontal Sidewall Sprinklers - **G6-80 HSW QR EC, (K-8.0)** and **G6-56 HSW QR, (K-5.6)**.

### **G6-80 HSW QR EC, (K-8.0)**

- **With Listed Spacing - up to 16' x 24' (4.9m x 6.7m)**
- UL Listed as QR EC for Light Hazard Applications
- Rated to 175 psi (12.0 bar)
- Push-on/pull-off flat cover plate - solid or perforated
- 1/4" (6.3mm) cover plate adjustment
- 3/4" NPT (R3/4) Male Thread
- SIN RA4762, **Bulletin 047**

### **G6-56 HSW QR, (K-5.6)**

- **For installation in accordance with NFPA 13**
- UL Listed as QR, Standard Coverage for Light and Ordinary Hazard Applications
- Rated to 175 psi (12.0 bar)
- Push-on/pull-off flat cover plate - solid or perforated
- 1/4" (6.3mm) cover plate adjustment
- 1/2" NPT (R1/2) Thread
- SIN RA5035, **Bulletin 050**

For more information, please refer to the bulletins on our website or call your local Reliable sales office.

Thank you again for choosing Reliable - your one source for all your fire protection needs.

Sincerely,



Michael R. Fee  
Vice President