



Industry-leading Coverage Areas

- cULus Listed Special Application Sprinklers for Sloped Combustible and Noncombustible Light Hazard Concealed Spaces.
- All models use a 212°F (100°C) temperature rated fusible-link operating element.
- Coverage for spans up to 70 ft (21 m) with one row of Model DD80 sprinklers.
- Coverage for spans up to 100 ft (30 m) with three rows of sprinklers: one row of Model DD80 sprinklers near the ridge and one row of Model GP56 sprinklers near each eave.

Sprinkler Model	Nominal K-Factor gpm/psi ^{1/2} (L/min/bar ^{1/2})	Max. Coverage Area (Measured on Floor) ft x ft (m x m)	Roof Slope	Sprinkler Identification Number (SIN)
DD56-6	5.6 (80)	6 x 40 (1.8 x 12)	4:12 to <6:12	RA5624
DD56-27	5.6 (80)	6 x 40 (1.8 x 12)	6:12 to 8:12	RA5694
DD80-6	8.0 (115)	6 x 66 or 5 x 70 (1.8 x 20 or 1.5 x 21)	4:12 to <6:12	RA5622
DD80-27	8.0 (115)	6 x 66 or 5 x 70 (1.8 x 20 or 1.5 x 21)	6:12 to 8:12	RA5692
DS56	5.6 (80)	6 x 40 (1.8 x 12)	4:12 to 8:12	RA5625
GP56	5.6 (80)	10 x 15 (3.0 x 4.6)	4:12 to 8:12	RA5695

- For more information, please see [Bulletin 056](#)
- For pricing, [click here](#)

One Family. One Industry.



One Source



Thank you again for choosing Reliable for all your fire protection needs.



Reliable Automatic Sprinkler Co., Inc.
www.reliablesprinkler.com * 1 (800) 431-1588
[Sales Offices](#)