

## New RASCO Iron Gate Valves OS&Y / NRS / PIV

December 2015

Dear Valued Customer:

**OS&Y, NRS, and Indicator Wall Posts** with the **RASCO brand**, which means **quality products**.

### OS&Y Gate Valves

- Flanged End
- 300 psi (21 bar) rated working pressure
- UL/FM Approved
- Available sizes: 2" (50mm) through 12" (300mm)

### Non-Rising Stem Gate Valves

- Flanged End
- 300 psi (21 bar) rated working pressure
- UL/FM Approved
- Available sizes: 4" (100mm) through 10" (250mm)

### Wall and Vertical Indicator Posts

- Identify whether the valve is opened or closed

For more information on these products, call your local Reliable Sales Office.

All of us at Reliable want to thank you for your business and continued support of Reliable's System Components product line.

Sincerely,



Rex Schwendiman  
Vice President, System Components