



Stainless Steel Sprinklers



- cULus Listed Corrosion Resistant Sprinklers
- Type 316 stainless steel alloy frame, deflector, cap, and load screw
- Available with Type 316 alloy stainless steel escutcheons (pendent only)

Sprinkler Model	Nominal K-factor gpm/psi ^{1/2} (l/min/bar ^{1/2})	Thread Size NPT or ISO7-1	Sprinkler Identification Number (SIN)	Sensitivity
F1-56SS Upright	5.6 (80)	1/2	RA6424	Standard Response
F1-56SS Pendent	5.6 (80)	1/2	RA6414	Standard Response
F1FR-56SS Upright	5.6 (80)	1/2	RA6524	Quick Response
F1FR-56SS Pendent	5.6 (80)	1/2	RA6514	Quick Response
F1-80SS Upright	8.0 (115)	3/4	RA6422	Standard Response
F1-80SS Pendent	8.0 (115)	3/4	RA6412	Standard Response
F1FR-80SS Upright	8.0 (115)	3/4	RA6522	Quick Response
F1FR-80SS Pendent	8.0 (115)	3/4	RA6512	Quick Response

- For more information, please see [Bulletin 064](#) (F1-SS) and [Bulletin 065](#) (F1FR-SS)
- For pricing, [click here](#)

One Family. One Industry.



One Source



Thank you again for choosing Reliable for all your fire protection needs.



Reliable Automatic Sprinkler Co., Inc.
www.reliablesprinkler.com * 1 (800) 431-1588
[Sales Offices](#)