

ACCESSORIES

CABINETS

Description	Part Number	Short Code	List Price
A4 EMERGENCY CABINETS FOR LL RESIDENTIAL SPRINKLERS			
3 Capacity	6999991473	3CAB	\$ 82.36
6 Capacity	6999991470	6CAB	\$ 82.36
6 Capacity (Large)	6999991472	6LCAB	\$ 147.55
12 Capacity	6999991471	12CAB	\$ 102.18
A3 EMERGENCY CABINETS FOR RECESSED, CONCEALED LL RESIDENTIAL SPRINKLERS			
12 Capacity	6803200000	A312CAB	\$ 445.52

ESCUTCHEONS

Part Number	Short Code	Temperature	Finish	List Price
ONE PIECE TYPE - MODEL B 1/2"				
6800110000	BB	165°F	Bright Brass	\$ 3.94
6800150000	BC	165°F	Chrome	\$ 2.70
6800120000	BW	165°F	White	\$ 3.04
ONE PIECE TYPE - MODEL B 3/4"				
6800080000	BLB	165°F	Bright Brass	\$ 4.16
6800070000	BLC	165°F	Chrome	\$ 2.92
6800090000	BLW	165°F	White	\$ 2.92
ONE PIECE TYPE - MODEL C 1/2"				
6800340000	CBB	165°F	Bright Brass	\$ 5.44
6800350000	CC	165°F	Chrome	\$ 2.89
6800380000	CW	165°F	White	\$ 2.89
TWO PIECE TYPE - MODEL HB 1/2"				
6800210000	HBB	165°F	Bronze	\$ 6.86
6800270000	HBC	165°F	Chrome	\$ 6.18
6800200000	HBW	165°F	White	\$ 6.41
TWO PIECE TYPE - MODEL HB 3/4"				
6800220000	HBLB	165°F	Bronze	\$ 7.08
6800240000	HBLC	165°F	Chrome	\$ 6.41
6800250000	HBLW	165°F	White	\$ 6.86
FLUSH ESCUTCHEONS - MODEL B				
86791100	BFB	165°F		\$ 47.86
86792100	BFC	165°F	Chrome	\$ 74.33
86797200	BFW	165°F	White	\$ 74.33



ESCUTCHEONS

Description	Part Number	Short Code	List Price
MODEL FP PUSH-ON/THREAD-OFF ESCUTCHEONS			
1/2" Chrome	6801412100	FPC	\$ 18.39
1/2" White	6801417200	FPW	\$ 18.39
3/4" Chrome	6801402100	FPLC	\$ 18.39
3/4" White	6801407200	FPLW	\$ 18.39
MODEL F1 RECESSED ESCUTCHEONS & COLLAR ASSEMBLY			
1/2" Brass	6800630001	GF1B	\$ 17.68
1/2" Chrome	6800600001	GF1C	\$ 9.54
1/2" White	6800640001	GF1W	\$ 9.54
3/4" Brass	6801030000	GF1LB	\$ 17.68
3/4" Chrome	6801000000	GF1LC	\$ 9.54
3/4" White	6801040000	GF1LW	\$ 9.54
ESCUTCHEON ONLY			
Brass	6800430000	BZESCF1	\$ 13.48
Chrome Bright	6800400000	CBESCF1	\$ 5.73
White	6800440000	WHESCF1	\$ 5.73
COLLAR ONLY			
1/2" Brass	6800530000	B2COLLAR12	\$ 10.56
1/2" Chrome Bright	6800500000	CBCOLLAR12	\$ 8.66
1/2" White	6800540000	WHCOLLAR12	\$ 8.66
3/4" Brass	6800560004	B2COLLAR34	\$ Call
3/4" Chrome Bright	6800560001	CBCOLLAR34	\$ 8.66
3/4" White	6800551003	WHCOLLAR34	\$ 8.66
ESCUTCHEON EXTENDER RING			
Chrome	6814002100	EERC	\$ 12.25
White	6814001500	EERW	\$ 13.06
F1 OR F2			
4-1/2" Chrome	6814002100	EERC	\$ 12.25
4-1/2" White	6814001500	EERW	\$ 13.06
5-1/2" Chrome	6814042100	EERC5	\$ 12.25
5-1/2" White	6814041500		\$ 13.06
FP / G4 / RFC43 / F4FR / CCP / SWC / DH80 / DH56			
4-1/2" Chrome	6814022100	G4ERC	\$ 12.25
4-1/2" White	6814021800		\$ 13.06
5-1/2" Chrome	6814032100	G4ERC5	\$ 12.25
5-1/2" White	6814031800	G4ERW5	\$ 13.06

MODEL F2 RECESSED ESCUTCHEONS & COLLAR ASSEMBLY			
1/2" Brass	6800830000	GF2B	\$ 17.68
1/2" Chrome	6800800000	GF2C	\$ 9.54
1/2" White	6800840000	GF2W	\$ 9.54
3/4" Brass	6800880004	GF2LB	\$ 17.68
3/4" Chrome	6800880001	GF2LC	\$ 9.54
3/4" White	6800880005	GF2LW	\$ 9.54
ESCUTCHEON ONLY			
Brass	6800730000	BZESCF2	\$ 13.39
Chrome	6800100000		\$ 8.63
White	6800740000	WHESCF2	\$ 8.63
COLLAR ONLY			
1/2" Brass	6800530000	B2COLLAR12	\$ 10.56
1/2" Chrome	6800500000	CBCOLLAR12	\$ 8.66
1/2" White	6800540000	WHCOLLAR12	\$ 8.66
3/4" Brass	6800560004	B2COLLAR34	\$ Call
3/4" Chrome	6800560001	CBCOLLAR34	\$ 8.66
3/4" White	6800551003	WHCOLLAR34	\$ 8.66

G/F1 for use with SP & HSW Sprinklers
G/F2 for use with SP & HSW Sprinklers
G/F2 for use with SP & HSW Sprinklers



MP LL Multipurpose Residential Riser

- See Bulletin 426

Accessories

Description	Part Number	Short Code	List Price
MODEL MPLL MULTIPURPOSE RESIDENTIAL RISER			
Model MP LL 1" (30mm)	6501200125	1MPLL	\$ 964.98
RISER ACCESSORIES			
Optional Support Bracket Kit	6899190001	RRB	\$ 94.10

Description	Part Number	Short Code	List Price
PRESSURE GAUGES			
WATER	98248001	WATER	\$ 96.30
AIR	98248000	AIR	\$ 102.96
Air (0-60 oz/in ²)	98248002	AIRO	\$ 364.70
INSPECTORS TEST CONNECTIONS			
Sight Test Type (Model B)	6851010000	ISC	\$ 397.72
Blind Test Type (Model A)	6851020000	IBC	\$ 132.57
AUTOMATIC BALL DRIPS			
1/2" NPT (Female)	78653500	5ABD	\$ 232.82
3/4" NPT (Female)	78653700	75ABD	\$ 266.04
MECHANICAL BALL DRIPS			
1/2" NPT (Female)	78653100	5MBD	\$ 415.62
STRAINER			
3/4" NPT (Female)	78650200	34ST	\$ 244.26
MISCELLANEOUS			
Model C Sight Drain 2" NPT (Female)	6863000000	2ISC	\$ 431.42
Model B Drum Drip Only 3/4" NPT (Female)	71010448		\$ 266.94
Model A Fill Cup 1/2" NPT (Female)	75000050	5FC	\$ 125.99
Model A Fill Cup 3/4" NPT (Female)	75000075	75FC	\$ 142.55
Model A Control Valve Seal Only	6869800000		\$ 34.50
SIGNS—MODEL A			
Valve Control Sign	6892011000	VCS	\$ 14.40
SIGNS—MODEL B			
Inspector Test Sign	6892110000	ITS	\$ 2.80
Open Sprinkler Control Sign	6892030000	OSCS	\$ 3.00
Open Sprinkler Drain Sign	6892040000	OSDS	\$ 3.00
Test Valve Sign	6892050000	TVS	\$ 3.00
Water Motor Line Sign	6892060000	WMLS	\$ 3.00
Auxiliary Drain Sign	6892070000	ADS	\$ 2.80
Main Drain Sign	6892080000	MDS	\$ 2.80
Drain Sign	6892090000	DS	\$ 2.70
Alarm Test Sign	6892100000	ATS	\$ 3.00
SIGNS—MODEL C			
Cold Weather Sign	6892010000	CWS	\$ 12.00
SIGNS—MODEL D			
Fire Alarm Sign	6892020000	FAS	\$ 14.40
SIGNS—MODEL E			
Hydraulically Calculated System	6892120000	HCS	\$ 7.90

ELECTRICAL COMPONENTS



Description	Part Number	Short Code	List Price
MODEL WFDT - WATERFLOW DETECTOR			
1" - 2", w/1" NPT T-Tap Waterflow	7M99003216	TTAPN	\$ 295.16
ACCESSORIES			
1 & 1-1/2" Waterflow Detector Gasket	6999990717		\$ 15.19
2 & 3-1/2" Waterflow Detector Gasket	6999990357		\$ 15.19
4 - 8" Waterflow Detector Gasket	6999990356		\$ 15.19
Repl. Terminal block	6999990957	TERMBLK	\$ 75.45
Repl. Timer	6999992444	TIMER	\$ 101.18
Waterflow Detector Tamper Switch Kit	6923000000	5467000	\$ 54.79
Wrench Cover (Key)	6999990769	WFDW	\$ 17.78
Cover	6999991174		\$ 26.50
ELECTRIC ALARM BELLS & HORN/STROBE			
6" -- 24 VDC	6611220400	6KMS	\$ 93.25
8" -- 24 VDC	6611220500	8KMS	\$ 116.26
10" -- 24VDC	6611220600	10KMS	\$ 129.09
BRK MA Polarized Sounder -- 24 VDC	6999993325	HORNWBB24	\$ 166.80
BRK MASS Polarized Sounder Strobe (#P2R)	6990006617	P2RL	\$ 123.16
P2RHK-120	6990001425	HORNWBB	\$ 189.90
6" -- 120 VAC	6611221100	6KBS	\$ 93.25
8" -- 120 VAC	6611221200	8KBS	\$ 116.26
10" -- 120 VAC	6611221300	10KBS	\$ 129.09
WBB Weatherproof Back Box	6611660200	WBB	\$ 49.97



**TNL280 SPRAY
 NOZZLE**

- K-Factor = 28 (400)
- Pendent, Open Nozzle
- See Bulletin 099

Description	Part Number	Short Code	List Price
MODEL TNL280 PENDENT K28 (400) THREADS 1" (25MM)			
Electroless Nickel PTFE (ENT)	DB00436591	TNL280	\$ 160.50
IS07-1RI THREADS - INTERNATIONAL ONLY			
Electroless Nickel PTFE (ENT)	DB00436593	TNL280M	\$ 160.50
Requires N1 Wrench	6880070001	WN1	\$ 115.72

NEW