

Reliable Attic Sprinklers

- See Bulletin 056
- Specific Application
- Sprinklers for Sloped
- Combustible and Noncombustible
- Light Hazard Concealed Spaces



AH42 / AH56



DD56-6 / DD56-27



DS56



GP56



Part Number	Short Code	Temperature	Finish	List Price
MODEL AH42 UPRIGHT K4.2 (60) THREAD 1/2" RA5623 • Roof Slope = 4:12 to 8:12				
MN21112699	AH42	212°F	100°C Brass	\$ 74.80
MODEL AH56 UPRIGHT K5.6 (80) THREAD 1/2" RA5626 • Roof Slope = 4:12 to 8:12				
MN21112799	AH56	212°F	100°C Brass	\$ 74.80
MODEL DD56-6 UPRIGHT K5.6 (80) THREAD 1/2" RA5624 • Roof Slope = 4:12 to <6:12				
MN21113099	DD566	212°F	100°C Brass	\$ 405.56
MODEL DD56-27 UPRIGHT K5.6 (80) THREAD 1/2" RA5694 • Roof Slope = 6:12 to 8:12				
MN21113199	DD5627	212°F	100°C Brass	\$ 405.56
MODEL DS56 UPRIGHT K5.6 (80) THREAD 1/2" RA5625 • Roof Slope = 4:12 to 8:12				
MN21112899	DS56	212°F	100°C Brass	\$ 405.56
MODEL GP56 UPRIGHT K5.6 (80) THREAD 1/2" RA5695 • Roof Slope = 4:12 to 8:12				
MN21112999	GP56	212°F	100°C Brass	\$ 68.54
MODEL DD80-6 UPRIGHT K8.0 (115) THREAD 3/4" RA5622 • Roof Slope = 4:12 to <6:12				
MN21113398	DD806	212°F	100°C Brass	\$ 405.56
MODEL DD80-27 UPRIGHT K8.0 (115) THREAD 3/4" RA5692 • Roof Slope = 6:12 to 8:12				
MN21113498	DD8027	212°F	100°C Brass	\$ 405.56

6880130002	WDS56	Model DS56 Sprinkler Wrench - Model DS56	\$ 259.47
6880050100	WW2	Model W2 Sprinkler Wrench - Models: AH42, AH56, DD56, DD80, & GP56	\$ 122.53



LT56 PENDENT

- K-Factor = 5.6 (80)
- **SIN RA5814**
- See Bulletin 058
- Glass Bulb



LT56L PENDENT

- K-Factor = 5.6 (80)
- **SIN R5814**
- See Bulletin 058
- Link

LT56 300 PENDENT

- K-Factor = 5.6 (80)
- **SIN RA5914**
- See Bulletin 058
- Glass Bulb

LT56L-300

PENDENT

- K-Factor = 5.6 (80)
- **SIN R5914**
- See Bulletin 058
- Link

Part Number	Short Code	Temperature		Finish	List Price
MODEL LT56 PENDENT K5.6 (80) THREADS 1/2" (15MM) RA5814					
BY15113299	LT56P1B	155°F	68°C	Brass	\$ 72.07
BY15213299	LT56P1C	155°F	68°C	Chrome	\$ 79.28
BY15873299	LT56P1W	155°F	68°C	Poly White	\$ 79.28
BY20113299	LT56P2B	200°F	93°C	Brass	\$ 72.07
BY20213299	LT56P2C	200°F	93°C	Chrome	\$ 79.28
BY20873299	LT56P2W	200°F	93°C	Poly White	\$ 79.28
MODEL LT56L PENDENT K5.6 (80) THREADS 1/2" (15MM) R5814					
MY16113299	LT56LP1B	165°F	74°C	Brass	\$ 72.07
MY16213299	LT56LP1C	165°F	74°C	Chrome	\$ 79.28
MY16873299	LT56LP1W	165°F	74°C	Poly White	\$ 79.28
MY21113299	LT56LP2B	212°F	100°C	Brass	\$ 72.07
MY21213299	LT56LP2C	212°F	100°C	Chrome	\$ 79.28
MY21873299	LT56LP2W	212°F	100°C	Poly White	\$ 79.28
MODEL LT56-300 PENDENT K5.6 (80) THREADS 1/2" (15MM) RA5914					
B015113299	LT56P1B3	155°F	68°C	Brass	\$ 72.07
B015213299	LT56P1C3	155°F	68°C	Chrome	\$ 79.28
B015873299	LT56P1W3	155°F	68°C	Poly White	\$ 79.28
B020113299	LT56P2B3	200°F	93°C	Brass	\$ 72.07
B020213299	LT56P2C3	200°F	93°C	Chrome	\$ 79.28
B020873299	LT56P2W3	200°F	93°C	Poly White	\$ 79.28
MODEL LT56L-300 PENDENT K5.6 (80) THREADS 1/2" (15MM) R5914					
M016113299	LT56LP1B3	165°F	74°C	Brass	\$ 72.07
M016213299	LT56LP1C3	165°F	74°C	Chrome	\$ 79.28
M016873299	LT56LP1W3	165°F	74°C	Poly White	\$ 79.28
M021113299	LT56LP2B3	212°F	100°C	Brass	\$ 72.07
M021213299	LT56LP2C3	212°F	100°C	Chrome	\$ 79.28
M021873299	LT56LP2W3	212°F	100°C	Poly White	\$ 79.28
MODEL FV TWO-PIECE RECESSED ESCUTCHEONS & COLLAR ASSEMBLY					
6801720600	FVB	1/2" (15mm)		Brass	\$ 21.63
6801722100	FVC	1/2" (15mm)		Chrome	\$ 14.41
6801728700	FVW	1/2" (15mm)		Poly White	\$ 14.41
MODEL FP TWO-PIECE RECESSED ESCUTCHEONS & COLLAR ASSEMBLY					
6801412100	FPC	1/2" (15mm)		Chrome	\$ 23.82
6801417200	FPW	1/2" (15mm)		White	\$ 23.82

6880050100	WW2	Wrench, W2, Pendent, Upright, HSW		\$ 122.53
6880100120	WW4	Wrench, W4, Recessed, Concealed		\$ 370.47



LT56 CCP

- K-Factor = 5.6 (80)
- **SIN RA5814**
- See Bulletin 058
- Glass Bulb

LT56L CCP

- K-Factor = 5.6 (80)
- **SIN R5814**
- See Bulletin 058
- Fusible Link

LT56 300 CCP

- K-Factor = 5.6 (80)
- **SIN RA5914**
- See Bulletin 058
- Glass Bulb

LT56L-300 CCP

- K-Factor = 5.6 (80)
- **SIN R5914**
- See Bulletin 058
- Fusible Link

Part Number	Short Code	Temperature		Finish	List Price
MODEL LT56 CCP CONCEALED K5.6 (80) THREADS 1/2" (15MM) RA5814					
BZ15173299	LT56CCP1	155°F	68°C	W/O	\$ 86.48
BZ20173299	LT56CCP2	200°F	93°C	W/O	\$ 86.48
MODEL LT56-300 CCP CONCEALED K5.6 (80) THREADS 1/2" (15MM) RA5914					
BI15173299	LT56CCP13	155°F	68°C	W/O	\$ 86.48
BI20173299	LT56CCP23	200°F	93°C	Brass	\$ 86.48
MODEL LT56L CCP CONCEALED K5.6 (80) THREADS 1/2" (15MM) R5814					
MZ16173299	LT56LCCP1	165°F	74°C	W/O	\$ 86.48
MZ21173299	LT56LCCP2	212°F	100°C	Brass	\$ 86.48
MODEL LT56L-300 CCP CONCEALED K5.6 (80) THREADS 1/2" (15MM) R5914					
MI16173299	LT56LCCP13	165°F	74°C	W/O	\$ 86.48
MI21173299	LT56LCCP23	212°F	100°C	Brass	\$ 86.48
MODEL CCP CONICAL CONCEALED COVERPLATES					
6887161321	CCP0C76	135°F	57°C	Chrome	\$ 100.69
6887161318	CCP0W76	135°F	57°C	Flat White	\$ 39.24
6887161390	CCP0SP76	135°F	57°C	Specialty	\$ 65.90
6887161621	CCP1C76	165°F	74°C	Chrome	\$ 100.69
6887161618	CCP1W76	165°F	74°C	Flat White	\$ 39.24
6887161690	CCP1SP76	165°F	74°C	Specialty	\$ 65.90
6880050100	WW2	Wrench, W2, Pendent, Upright, HSW			\$ 122.53
6880100120	WW4	Wrench, W4, Recessed, Concealed			\$ 370.47



LT56C FLAT CONCEALED

- K-Factor = 5.6 (80)
- **SIN RA5994**
- See Bulletin 058

Part Number	Short Code	Temperature		Finish	List Price
MODEL LT56C CONCEALED K5.6 (80) THREADS 1/2" (15MM) RA5994					
M916173299	LTC1	165°F	74°C	W/O	\$ 100.91
M921173299	LTC2	212°F	100°C	W/O	\$ 100.91
MODEL LT56C CONCEALED BSPT THREADS 1/2" (15MM) RA5994					
M916173292	LTC1M	165°F	74°C	W/O	\$ 100.91
M921173292	LTC2M	212°F	100°C	W/O	\$ 100.91
MODEL G5 COVERPLATES					
6887271321	CG50C	135°F	57°C	Chrome	\$ 47.52
6887271372	CG50W	135°F	57°C	White	\$ 43.31
6887271311	CG50B	135°F	57°C	Finished Bronze	\$ 59.54
6887271374	CG50OW	135°F	57°C	Off-White	\$ 58.91
6887271390	CG50SP	135°F	57°C	Specialty	\$ 59.06
6887271316	CG50FB	135°F	57°C	Black Painted	\$ 58.98
6887271305	CG50BB	135°F	57°C	Bright Brass	\$ 72.07
6887271323	CG50CD	135°F	57°C	Satin Chrome	\$ 72.07
6887271310	CG50SS	135°F	57°C	Stainless Steel	\$ 72.07
6887271319	CG50EW	135°F	57°C	EW	\$ 43.31
6887271621	CG51C	165°F	74°C	Chrome	\$ 47.52
6887271672	CG51W	165°F	74°C	White	\$ 43.31
6887271611	CG51B	165°F	74°C	Finished Bronze	\$ 59.54
6887271674	CG51OW	165°F	74°C	Off-White	\$ 58.91
6887271690	CG51SP	165°F	74°C	Specialty	\$ 59.06
6887271616	CG51FB	165°F	74°C	Black Painted	\$ 58.98
6887271605	CG51BB	165°F	74°C	Bright Brass	\$ 72.07
6887271623	CG51CD	165°F	74°C	Satin Chrome	\$ 72.07
6887271610	CG51SS	165°F	74°C	Stainless Steel	\$ 72.07
6887271619	CG51EW	165°F	74°C	EW	\$ 43.31

Notes:

Sprinklers and coverplates sold and packaged separately



XL INSTITUTIONAL

- K-Factor = 5.6 (80)
- Pendent EC= SIN R1344
- HSW EC = SIN R1364
- Pendent = SIN R1314
- HSW = SIN R1334
- See Bulletin 113

Part Number	Short Code	Temperature		Finish	List Price
MODEL XL EC INST PENDENT K5.6 (80) THREADS 1/2" (15MM) R1344					
1572213299	XLEPC	165°F	74°C	Chrome	\$ 245.80
MODEL XL EC INST HORIZONTAL K5.6 (80) THREADS 1/2" (15MM) R1364					
1482213299	XLEHC	165°F	74°C	Chrome	\$ 255.48
MODEL XL INST PENDENT K5.6 (80) THREADS 1/2" (15MM) R1314					
1512213299	XLPC	165°F	74°C	Chrome	\$ 229.52
MODEL XL INST HORIZONTAL K5.6 (80) THREADS 1/2" (15MM) R1334					
1452213299	XLHC	165°F	74°C	Chrome	\$ 239.24
REPLACEMENT PARTS					
6801321223	IKEC	EC HSW ESCUTCHEON KIT, SATIN			\$ Call
6801321272	IKEW	EC HSW ESCUTCHEON KIT, WHITE PAINT			\$ Call
6801320123	IKPC	PENDENT, EC PENDENT ESCUTCHEON KIT, SATIN			\$ Call
6801320172	IKPW	PENDENT, EC PENDENT ESCUTCHEON KIT, WHITE PAINT			\$ Call
6801322223	IXLHC	HSW ESCUTCHEON KIT, SATIN			\$ Call
6801322272	IXLHW	HSW ESCUTCHEON KIT, WHITE PAINT			\$ Call
6801350001		Retainer Flange			\$ 34.60
88795014		Escutcheon Retaining Ring			\$ 13.28
88007901		Tamper Resistant Fasteners			\$ 7.05
6880160020	ZXT	Tamper Resistant Tool Bit			\$ 41.65

6880160000	WZXP	Requires Model ZX (Pendent) Sprinkler Wrench			\$ 369.03
6880160010	WZXH	Requires Model ZX (Horizontal) Sprinkler Wrench			\$ 369.03



Non-Ferrous

Part Number	Short Code	Temperature		Finish	List Price
MODEL F4FR-NF CONCEALED K5.6 (80) THREADS 1/2" (15MM) RA0212					
0615723299	F4FRNF1W	155°F	68°C	White	\$ 236.51
0615213299	F4FRNF1C	155°F	68°C	Chrome	\$ 236.51

6880170000 WG4 Requires Model G4 Sprinkler Wrench \$ 369.03

MODEL KFR- CCS K5.6 (80) THREADS 1/2" (15MM) RA4454					
MN211132R9	KFRCCS	212°F	100°C	Brass	\$ 82.62

6880050100 WW2 Wrench, W2, Pendent, Upright, HSW \$ 122.53

F4FR-NF

- K-Factor = 5.6 (80)
- **SIN RA0212**
- See Bulletin 002



KFR CCS

- K-Factor = 5.6 (80)
- **SIN RA4454**
- See Bulletin 044



WP56 PENDENT VERTICAL SIDEWALL

- K-Factor 5.6
- **SIN #501 (Bulb)**
- See Bulletin 181



WP56L PENDENT VERTICAL SIDEWALL

- K-Factor 5.6
- **SIN #R502 (Link)**
- See Bulletin 181



WP56C CONCEALED PENDENT VERTICAL SIDEWALL

- K-Factor 5.6
- **SIN #R504**
- See Bulletin 181

Part Number	Short Code	Temperature		Finish	List Price
MODEL WP56 PENDENT VERTICAL SIDEWALL K5.6 (80) THREADS 1/2" (15MM) R501 BULB					
BW151132S9	WP561B	155°F	68°C	Bronze	\$ 641.52
BW152132S9	WP561C	155°F	68°C	Chrome	\$ 667.18
BW158732S9	WP561W	155°F	68°C	White	\$ 667.18
BW151032S9	WP561SS	155°F	68°C	Stainless Steel	\$ 1,320.00
BW201132S9	WP562B	200°F	93°C	Brass	\$ 641.52
BW202132S9	WP562C	200°F	93°C	Chrome	\$ 667.18
BW208732S9	WP562W	200°F	93°C	White	\$ 667.18
BW201032S9	WP562SS	200°F	93°C	Stainless Steel	\$ 1,320.00
MODEL WP56L PENDENT VERTICAL SIDEWALL K5.6 (80) THREADS 1/2" (15MM) R502 LINK					
MW161132S9	WP56L1B	165°F	74°C	Bronze	\$ 641.52
MW162132S9	WP56L1C	165°F	74°C	Chrome	\$ 667.18
MW168732S9	WP56L1W	165°F	74°C	White	\$ 667.18
MW211132S9	WP56L2B	212°F	100°C	Bronze	\$ 641.52
MW212132S9	WP56L2C	212°F	100°C	Chrome	\$ 667.18
MW218732S9	WP56L2W	212°F	100°C	White	\$ 667.18
6880050100	WW2	Wrench, W2, Pendent, Upright, HSW			\$ 122.53
MODEL WP56C WINDOW CONCEALER K5.6 (80) THREADS 1/2" NPT R504					
1W16173299	WP56C1B	165°F	74°C	W/O	\$ 769.82
1W21173299	WP56C2B	212°F	100°C	W/O	\$ 769.82
MODEL WP56C WINDOW CONCEALER K5.6 (80) THREADS 1/2" BSPT R504					
1W16173292	WP56C1BM	165°F	74°C	W/O	\$ 769.82
1W21173292	WP56C2BM	212°F	100°C	W/O	\$ 769.82
6880170020	WFC	WRENCH,FC,CONCEALED			\$ 372.45
MODEL G5 COVERPLATES FOR WP56C CONCEALED SPRINKLERS					
6887271372	CG50W	135°F	57°C	White	\$ 43.31
6887271321	CG50C	135°F	57°C	Chrome	\$ 47.52
6887271672	CG51W	165°F	74°C	White	\$ 43.31
6887271621	CG51C	165°F	74°C	Chrome	\$ 47.52

Features

- cULus Listed to provide complete wetting of various glass surfaces
- Fast Response Specific Applications Pendent Vertical Sidewall sprinkler
- Listed corrosion resistant finishes available (WP56 only)

Notes:

Other Coverplate finishes available upon request.



**F1S5 LO LARGE
 ORIFICE SPECIAL
 RESPONSE
 STANDARD SPRAY**

- K-Factor = 115 (8.0)
- Thread Size = R1/2
- Bulletin 024



Part Number	Short Code	Temperature	Finish	List Price
MODEL F1S5 LO UPRIGHT K8.0(115) THREADS 1/2"(15MM) BSPT THREADS				
KA13113492		135°F	57°C	Brass \$ 39.95
KA15113492		155°F	68°C	Brass \$ 39.95
KA17113492		175°F	79°C	Brass \$ 39.95
KA20113492		200°F	93°C	Brass \$ 39.95
KA28113492		286°F	141°C	Brass \$ 39.95
KA13213492		135°F	57°C	Chrome \$ 46.63
KA15213492		155°F	68°C	Chrome \$ 46.63
MODEL F1S5 LO PENDENT K8.0(115) THREADS 1/2"(15MM) BSPT THREADS				
KB13113492		135°F	57°C	Brass \$ 39.95
KB15113492		155°F	68°C	Brass \$ 39.95
KB17113492		175°F	79°C	Brass \$ 39.95
KB20113492		200°F	93°C	Brass \$ 39.95
KB28113492		286°F	141°C	Brass \$ 39.95
KB28213492		286°F	141°C	Chrome \$ 46.63
F1 ESCUTCHEONS				
6800630001	GF1B	15mm (1/2")	Brass	\$ 22.89
6800600001	GF1C	15mm (1/2")	Chrome	\$ 12.35
6800640001	GF1W	15mm (1/2")	White	\$ 12.35
F2 ESCUTCHEONS				
6800830000	GF2B	15mm (1/2")	Brass	\$ 22.89
6800800000	GF2C	15mm (1/2")	Chrome	\$ 12.35
6800840000	GF2W	15mm (1/2")	White	\$ 12.35
FP PUSH-ON/THREADS-OFF ESCUTCHEONS				
6801412100	FPC	FP PUSH-ON/THREADS-OFF	Chrome	\$ 23.82
6801417200	FPW	FP PUSH-ON/THREADS-OFF	White	\$ 23.82

6880050100	WW2	Wrench, W2, Pendent, Upright, HSW	\$ 122.53
6880100120	WW4	Wrench, W4, Recessed, Concealed	\$ 370.47