



G RECESSED

Non-Adjustable -

- K2.8 = SIN R1011
- K4.2 = SIN R1013
- K5.6 = SIN R1015
- K8.0 = SIN R1016
- See Bulletin 111

Part Number	Short Code	Temperature		Finish	List Price
MODEL G RECESSED K5.6 (80) THREADS 1/2" (15MM) R1015					
5513343270	GR0B	135°F	57°C	Bronze	\$ 44.55
5513323270	GR0C	135°F	57°C	Bronze	\$ 40.42
5513463270	GR0W	135°F	57°C	White	\$ 44.55
5516343270	GR1B	165°F	74°C	Bronze	\$ 44.55
5516323270	GR1C	165°F	74°C	Chrome	\$ 40.42
5516463270	GR1W	165°F	74°C	White	\$ 44.55
5521343270	GR2B	212°F	100°C	Bronze	\$ 44.55
5521323270	GR2C	212°F	100°C	Chrome	\$ 40.42
5521463270	GR2W	212°F	100°C	Bronze	\$ 44.55
MODEL G RECESSED K8.0 (115) THREADS 1/2" (15MM) R1016					
5513343470	GR0LHB	135°F	57°C	Bronze	\$ 54.11
5513323470	GR0LHC	135°F	57°C	Bronze	\$ 52.60
5516343470	GR1LHB	165°F	74°C	Bronze	\$ 54.11
5516323470	GR1LHC	165°F	74°C	Chrome	\$ 52.60
5521343470	GR2LHB	212°F	100°C	Bronze	\$ 54.11
5521323470	GR2LHC	212°F	100°C	Chrome	\$ 52.60
MODEL G RECESSED K2.8 (40) THREADS 1/2" (15MM) R1011					
5513342470	GR03B	135°F	57°C	Bronze	\$ 60.64
5513322470	GR03C	135°F	57°C	Bronze	\$ 57.54
5516342470	GR13B	165°F	74°C	Bronze	\$ 60.64
5516322470	GR13C	165°F	74°C	Chrome	\$ 57.54
5521342470	GR23B	212°F	100°C	Bronze	\$ 60.64
5521322470	GR23C	212°F	100°C	Chrome	\$ 57.54
MODEL G RECESSED ESCUTCHEONS					
6801361101	GRB	Threaded		Bronze	\$ 24.69
6801362101	GRC	Threaded		Chrome	\$ 12.91
6801367201	GRW	Threaded		White	\$ 12.91
6801369001	GRSP	Threaded		Specialty	\$ 31.75
6880100000	WRC	Requires Model RC1 Sprinkler Wrench			\$ 288.74
6880040000	WFEA	For Escutcheon Use Model FEA Wrench			\$ 91.00

Notes:

Sprinklers and Escutcheons sold and packaged separately



G (CONT.)

- K4.2 = SIN R1013
- K5.6 1" M AND 1" F SIN R1118
- See Bulletin 111

Part Number	Short Code	Temperature		Finish	List Price
MODEL G RECESSED K4.2 (40) THREADS 1/2" (15MM) R1013					
5513342870	GR07B	135°F	57°C	Bronze	\$ 60.64
5513322870	GR07C	135°F	57°C	Bronze	\$ 57.54
5516342870	GR17B	165°F	74°C	Bronze	\$ 60.64
5516322870	GR17C	165°F	74°C	Chrome	\$ 57.54
5521342870	GR27B	212°F	100°C	Bronze	\$ 60.64
5521322870	GR27C	212°F	100°C	Chrome	\$ 57.54
MODEL G RECESSED K5.6 (80) THREADS 1" MALE (25MM) R1113					
5513373298	GR0MB	135°F	57°C	Bronze	\$ 107.90
5513323298	GR0MC	135°F	57°C	Chrome	\$ 104.83
5513463298	GR0MW	135°F	57°C	White	\$ 107.90
5516343298	GR1MB	165°F	74°C	Bronze	\$ 107.90
5516323298	GR1MC	165°F	74°C	W/O ESC CB	\$ 104.83
5516463298	GR1MW	165°F	74°C	White	\$ 107.90
5521343298	GR2MB	212°F	100°C	Bronze	\$ 107.90
5521323298	GR2MC	212°F	100°C	Chrome	\$ 104.83
5521463298	GR2MW	212°F	100°C	White	\$ 107.90
MODEL G RECESSED K5.6 (80) THREADS 1" FEMALE (25MM) R1018					
5513343297	GR0FB	135°F	57°C	Bronze	\$ 107.90
5513323297	GR0FC	135°F	57°C	Chrome	\$ 104.83
5513463297	GR0FW	135°F	57°C	White	\$ 107.90
5516343297	GR1FB	165°F	74°C	Bronze	\$ 107.90
5516323297	GR1FC	165°F	74°C	W/O ESC CB	\$ 104.83
5516463297	GR1FW	165°F	74°C	White	\$ 107.90
5521343297	GR2FB	212°F	100°C	Bronze	\$ 107.90
5521323297	GR2FC	212°F	100°C	Chrome	\$ 104.83
5521463297	GR2FW	212°F	100°C	White	\$ 107.90
MODEL G RECESSED ESCUTCHEONS					
6801361101	GRB	Threaded		Bronze	\$ 24.69
6801362101	GRC	Threaded		Chrome	\$ 12.91
6801367201	GRW	Threaded		White	\$ 12.91
6801369001	GRSP	Threaded		Specialty	\$ 31.75

6880100000	WRC	For Recessed Use Model RC1 Wrench	\$ 288.74
6880040000	WFEA	For Escutcheon Use Model FEA Wrench	\$ 91.00

Notes:

Sprinklers and Escutcheons sold and packaged separately



G4 CONCEALED

- K2.8 = SIN R2111
- K4.2 = SIN R2113
- K5.6 = SIN R2115

Sprinkler	Coverplate
135°F/57°C	135°F/57°C
165°F/74°C	165°F/74°C
212°F/100°C	165°F/74°C

Part Number	Short Code	Temperature		Finish	List Price
MODEL G4 CONCEALED K5.6 (80) THREADS 1/2" (15MM) R2115					
5713173299	G40	135°F	57°C	Bronze	\$ 49.43
5716173299	G41	165°F	74°C	Bronze	\$ 47.95
5721173299	G42	212°F	100°C	Bronze	\$ 49.43
MODEL G4 CONCEALED K2.8 (40) THREADS 1/2" (15MM) R2111					
5713172499	G403	135°F	57°C	Bronze	\$ 52.25
5716172499	G413	165°F	74°C	Bronze	\$ 52.25
5721172499	G423	212°F	100°C	Bronze	\$ 52.25
MODEL G4 CONCEALED K4.2 (60) THREADS 1/2" (15MM) R2113					
5713172899	G407	135°F	57°C	Bronze	\$ 52.25
5716172899	G417	165°F	74°C	Bronze	\$ 52.25
5721172899	G427	212°F	100°C	Bronze	\$ 52.25
MODEL G4 CONCEALED COVER PLATES					
6887011321	CG40C	135°F	57°C	Chrome	\$ 33.75
6887011372	CG40W	135°F	57°C	White	\$ 33.75
6887011390	CG40SP	135°F	57°C	Specialty	\$ 46.03
6887011374	CG40OW	135°F	57°C	Off-White	\$ 45.91
6887011390	CG40SP	135°F	57°C	Specialty	\$ 46.03
6887011316	CG40FB	135°F	57°C	Black Painted	\$ 45.97
6887011367	CG40BP	135°F	57°C	Black Plated	\$ 56.18
6887011305	CG40BB	135°F	57°C	Bright Brass	\$ 56.18
6887011323	CG40CD	135°F	57°C	Satin Chrome	\$ 56.18
6887011310	CG40SS	135°F	57°C	Stainless Steel	\$ 56.18
6887011621	CG41C	165°F	74°C	Chrome	\$ 33.75
6887011672	CG41W	165°F	74°C	White	\$ 33.75
6887011690	CG41SP	165°F	74°C	Specialty	\$ 46.03
6887011674	CG41OW	165°F	74°C	Off-White	\$ 45.91
6887011690	CG41SP	165°F	74°C	Specialty	\$ 46.03
6887011616	CG41FB	165°F	74°C	Black Painted	\$ 45.91
6887011667	CG41BP	165°F	74°C	Black Plated	\$ 56.18
6887011605	CG41BB	165°F	74°C	Bright Brass	\$ 56.18
6887011623	CG41CD	165°F	74°C	Satin Chrome	\$ 56.18
6887011610	CG41SS	165°F	74°C	Stainless Steel	\$ 56.18

6880170000 WG4 Requires Model G4 Sprinkler Wrench \$ 287.62

Notes:

Sprinklers and coverplates sold and packaged separately



G4-300 CONCEALED

- K-Factor = 5.6 (80)
- **SIN R6115**
- See Bulletin 161

Sprinkler	Coverplate
135°F/57°C	135°F/57°C
165°F/74°C	165°F/74°C
212°F/100°C	165°F/74°C

Part Number	Short Code	Temperature		Finish	List Price
MODEL G4 - 300 CONCEALED K5.6 (80) THREADS 1/2" (15MM) R6115					
57A1173299	G40300	135°F	57°C	Bronze	\$ 51.20
57A2173299	G41300	165°F	74°C	Bronze	\$ 51.20
57A6173299	G42300	212°F	100°C	Bronze	\$ 51.20
MODEL G4 COVER PLATES					
6887011321	CG40C	135°F	57°C	Chrome	\$ 33.75
6887011372	CG40W	135°F	57°C	White	\$ 33.75
6887011311	CG40B	135°F	57°C	Bronze	\$ 46.41
6887011374	CG40OW	135°F	57°C	Off-White	\$ 45.91
6887011390	CG40SP	135°F	57°C	Specialty	\$ 46.03
6887011316	CG40FB	135°F	57°C	Black Painted	\$ 45.97
6887011367	CG40BP	135°F	57°C	Black Plated	\$ 56.18
6887011305	CG40BB	135°F	57°C	Bright Brass	\$ 56.18
6887011323	CG40CD	135°F	57°C	Satin Chrome	\$ 56.18
6887011310	CG40SS	135°F	57°C	Stainless Steel	\$ 56.18
6887011621	CG41C	165°F	74°C	Chrome	\$ 33.75
6887011672	CG41W	165°F	74°C	White	\$ 33.75
6887011611	CG41B	165°F	74°C	Bronze	\$ 46.41
6887011674	CG41OW	165°F	74°C	Off-White	\$ 45.91
6887011690	CG41SP	165°F	74°C	Specialty	\$ 46.03
6887011616	CG41FB	165°F	74°C	Black Painted	\$ 45.91
6887011667	CG41BP	165°F	74°C	Black Plated	\$ 56.18
6887011605	CG41BB	165°F	74°C	Bright Brass	\$ 56.18
6887011623	CG41CD	165°F	74°C	Satin Chrome	\$ 56.18
6887011610	CG41SS	165°F	74°C	Stainless Steel	\$ 56.18

6880170000 WG4 Requires Model G4 Sprinkler Wrench \$ 287.62

Notes:

Sprinklers and coverplates sold and packaged separately



**G5-80 SR "Sealing"
 Concealed**

- K-Factor = 8.0 (115)
- **SIN RA3412**
- See Bulletin 034

**G5-56 SR "Sealing"
 Concealed**

- K-Factor = 5.6 (80)
- **SIN RA3415**
- See Bulletin 034

**G5-42 SR "Sealing"
 Concealed**

- K-Factor = 4.2 (60)
- **SIN RA3413**
- See Bulletin 034

**G5-28 SR "Sealing"
 Concealed**

- K-Factor = 2.8 (40)
- **SIN RA3411**
- See Bulletin 034

Part Number	Short Code	Temperature		Finish	List Price
MODEL G5-80 SR CONCEALED K8.0 (115) THREADS 3/4" (20MM) RA3412					
1916173498	G5801B	165°F	74°C	Bronze	\$ 65.02
1921173498	G5802B	212°F	100°C	Bronze	\$ 65.02
MODEL G5-56 SR SEALING CONCEALED K5.6 (80) THREADS 1/2"(15MM) RA3415					
1916173299	G51B	165°F	74°C	Bronze	\$ 52.43
1921173299	G52B	212°F	100°C	Bronze	\$ 52.43
MODEL G5-42 SR CONCEALED K4.2 (60) THREADS 1/2" RA3413					
1916172899	G5421B	165°F	74°C	Bronze	\$ 65.02
1921172899	G5422B	212°F	100°C	Bronze	\$ 65.02
MODEL G5-28 SR CONCEALED K2.8 (40) THREADS 1/2" (15MM) RA3411					
1916172499	G5281B	165°F	74°C	Bronze	\$ 65.02
1921172499	G5282B	212°F	100°C	Bronze	\$ 65.02
MODEL G5 SEALING CONCEALED COVER PLATES					
6887031372	CG4S0W	135°F	57°C	White	\$ 86.33
6887031672	CG4S1W	165°F	74°C	White	\$ 86.33
6887031310	CG4S0SS	135°F	57°C	Stainless Steel	\$ 89.88
6887031610	CG4S1SS	165°F	74°C	Stainless Steel	\$ 56.18
6880170020	WFC	Requires Model FC Wrench			\$ 287.62

Notes:

Sprinklers and coverplates sold and packaged separately



**G5-56 300 SR
 "Sealing" Concealed**

- K-Factor = 5.6 (80)
- **SIN RA4014**
- See Bulletin 034

Part Number	Short Code	Temperature		Finish	List Price
MODEL G5-56 300 SR CONCEALED K5.6 (80) THREADS 1/2" (15MM) RA4014					
2016173299	G51B3	165°F	74°C	Bronze	\$ 55.41
MODEL G5 SEALING CONCEALED COVER PLATE					
6887031372	CG4S0W	135°F	57°C	White	\$ 86.33
6887031672	CG4S1W	165°F	74°C	White	\$ 86.33
6887031310	CG4S0SS	135°F	57°C	Stainless Steel	\$ 89.88
6887031610	CG4S1SS	165°F	74°C	Stainless Steel	\$ 56.18
6880170020	WFC	Requires Model FC Wrench			\$ 287.62

Notes:

Sprinklers and coverplates sold and packaged separately