

FIRE DEPARTMENT EQUIPMENT

| Description | Part Number | Short Code | List Price |
|---|-------------|------------|-------------|
| RASCO Hose Valves, Accessories and FDC's | | | |
| RASCO,#REL-HVT,1.5",FXM,HOSE VALVE | 7M99004574 | 15RAHV | \$ 512.39 |
| RASCO,#REL-HVTA,1.5",FXF,HOSE VALVE | 7M99004575 | | \$ 512.39 |
| RASCO,#REL-HVT,2.5",FXM,HOSE VALVE | 7M99004576 | 25RAHV | \$ 818.83 |
| RASCO,#REL-HVTA,2.5",FXF,HOSE VALVE | 7M99004577 | | \$ 818.83 |
| RASCO,#REL-HVG,2.5",GXM,HOSE VALVE | 7M99004578 | 25RAHVG | \$ 877.19 |
| RASCO,#REL-HVGA,2.5",GXF,HOSE VALVE | 7M99004579 | | \$ 927.84 |
| RASCO,#REL-CC15,1.5",CAP+CHAIN,BRASS | 7M99004621 | 15RHVC | \$ 97.69 |
| RASCO,#REL-CC25,2.5",CAP+CHAIN,BRASS | 7M99004620 | 25RHVC | \$ 122.83 |
| RASCO,#REL-RDCR2515,2.5"X1.5",BR RED NPT | 7M99004758 | 2515HVRR | \$ 107.75 |
| RASCO,#REL-PLTBR25,2.5",BR FDC WALLPLT | 7M99004752 | WP25R | \$ 212.19 |
| RASCO,#REL-PLTBR4,4",BR FDC WALLPLATE | 7M99004753 | WPBR | \$ 347.60 |
| RASCO,#REL-PLTAL25,2.5",ALUM FDC WALLPLT | 7M99004757 | 25WPR | \$ 85.00 |
| RASCO,#REL-PLTAL4,4",ALUM FDC WALLPLATE | 7M99004754 | WPR | \$ 110.28 |
| RASCO,#REL-PLG25,2.5",ALUM,PLUG+CHAIN | 7M99004755 | 25PLUGR | \$ 120.06 |
| RASCO,#REL-PLCAP25,2.5",BRKABLE CAP(2) | 7M99004756 | PBCR | \$ 13.26 |
| RASCO,#REL-ALCAP25,2.5",BRKBLE CAP(2),AL | 7M99004782 | EOPR | \$ 37.70 |
| RASCO,#REL-HV,1.5",REPL HANDWHEEL W/NUT | 7M99004740 | | \$ 27.29 |
| RASCO,#REL-HV,2.5",REPL HANDWHEEL W/NUT | 7M99004741 | | \$ 43.28 |
| RASCO,#REL-FDC-425,4X2.5,STRT,RB,FDC | 7M99004746 | FDCR | \$ 785.05 |
| RASCO,#REL-FDC-42590,4X2.5,90,RB,FDC | 7M99004747 | 90FDCR | \$ 884.83 |
| RASCO,#REL-FDC25,2.5",SINGLE,BR FDC KIT | 7M99004759 | 25FDCR | \$ 753.84 |
| RASCO,#REL-FDC15,1.5" FDC,W/PLUG+PLATE | 7M99004783 | 15FDCR | \$ 340.62 |
| RASCO,#REL-STRZ-44,4"X4",STORZ W/CAP | 7M99004760 | | \$ 1,301.07 |
| RASCO,#REL-STRZ-54,5"X4",STORZ W/CAP | 7M99004761 | | \$ 2,398.85 |
| RASCO,#REL-STRZ-4430,4X4,30D,STORZ W/CAP | 7M99004762 | | \$ 1,813.37 |
| RASCO,#REL-STRZ-5430,5X4,30D,STORZ W/CAP | 7M99004763 | | \$ 2,724.12 |
| RASCO,#REL-STRZKIT-4530,5X4 30D STORZ KT | 7M99004784 | 54STORZ30R | \$ 2,642.80 |
| RASCO,#REL-STRZKIT-4430,4X4 30D STORZ KT | 7M99004785 | 44STORZ30R | \$ 1,951.61 |
| RASCO,#REL-STRZKIT-45,4X5 STORZ KIT | 7M99004786 | 45STORZRKT | \$ 1,886.55 |
| RASCO,#REL-STRZKIT-44,4X4 STORZ KIT | 7M99004787 | 44STORZR | \$ 1,366.12 |
| RASCO,#REL-STRZB-44,4X4 STORZ BODY | 7M99004788 | | \$ 487.90 |
| RASCO,#REL-STRZB-54,5X4 STORZ BODY | 7M99004789 | 45STORZR | \$ 943.28 |
| RASCO,#REL-STRZB-4430,4X4 30D STORZ BODY | 7M99004790 | | \$ 1,016.46 |
| RASCO,#REL-STRZB-5430,5X4 30D STORZ BODY | 7M99004791 | | \$ 1,463.70 |
| RASCO,#REL-STRZ-CAP4,4" STORZ CAP | 7M99004792 | 4STORZCAPR | \$ 561.09 |
| RASCO,#REL-STRZ-CAP5,5" STORZ CAP | 7M99004793 | 5STORZCAPR | \$ 935.14 |

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

FIRE DEPARTMENT EQUIPMENT



| Description | Part Number | Short Code | List Price |
|---|-------------|------------|-------------|
| FPPI BRASS HOSE VALVES, FDC, AND ACCESSORIES | | | |
| FPPI,#07-000 HOSE VALVE,2.5" FXM | 6999991595 | 25AHV | \$ 998.41 |
| FPPI,#07-020,2.5",FXF HOSE VALVE | 6990004742 | 25FAHV | \$ 1,030.33 |
| FPPI,#07-022 HOSE VALVE 1.5" FXM | 6999991980 | 15AHV | \$ 562.09 |
| FPPI,#07-024,1.5",FXF,HOSE VALVE | 6990001387 | 15FAHV | \$ 562.09 |
| FPPI,#07-250,CAP+CHAIN,2.5" | 6999991576 | 25HVC | \$ 127.80 |
| FPPI,#07-270 HOSE VALVE CAP 1.5" | 6999992182 | 15HVC | \$ 90.98 |
| FPPI,#07-420,HOSE VLV REDUC,2.5 X 1.5 | 6999991701 | 2515HVR | \$ 164.93 |
| FPPI,#07-450,2.5" PLUG/CHAIN,RB | 6990001137 | 25FDCP | \$ 238.47 |
| FPPI,#07-470,1.5" PLUG/CHAIN,RB | 6990005263 | | \$ 137.59 |
| FPPI,#09-000,4X2.5X2.5,STRAIGHT FDC,RB | 7C99000001 | FDC425 | \$ 920.49 |
| FPPI,#09-020 4 X 2.5 2WAY 90 DEG FDC | 6999993973 | FDC42590 | \$ 1,098.89 |
| FPPI,#09-600,2.5,W/O PL&CH,OPN SNOOT | 7C99000008 | 09600 | \$ 449.56 |
| FPPI,#09-650,FDC,2.5,W/PLG&CHN | 7C99000007 | FDC25 | \$ 896.00 |
| FPPI,#09-502 1.5" STRAIGHT FDC | 6999994279 | FDC15 | \$ 467.01 |
| FPPI,#09-505,ALUMINUM BREAK CAP,(PAIR) | 6999994230 | ABC | \$ 42.35 |
| FPPI,#09-506,PLASTIC BREAK CAPS(PAIR) | 6990005264 | PBC | \$ 17.19 |
| FPPI,#09-508 WP "AUTO SPR" 4" | 7C99000006 | 09508 | \$ 73.74 |
| FPPI,#09-510 BRASS A/S WP 4" | 6990000013 | WPB | \$ 313.31 |
| FPPI,#09-520,FDC W/P,BR,2.5"IPS,A/S | 6990002999 | | \$ 184.96 |
| FPPI,#09-200 4X4 STORZ | 6990002175 | 44STORZ | \$ 1,195.33 |
| FPPI,#09-202 4X5 STORZ | 6990001139 | 45STORZFP | \$ 1,810.58 |
| FPPI,#09-210 4" STORZ 30DEG | 6999995022 | 44STORZ30 | \$ 1,895.80 |
| FPPI,#09-212,5X4 STORZ,30 DEGREE | 6990000025 | 45STORZ30 | \$ 2,680.72 |
| FPPI,#09-220 4" STORZ CAP | 6999995023 | 4STORZCAP | \$ 975.89 |
| FPPI,#09-222,5" STORZ CAP+CHAIN | 6990004199 | 5STORZCAP | \$ 1,421.64 |
| FPPI,#06-850-00,1"X1/2",T&D | 7M99003057 | 1TD | \$ 504.76 |
| FPPI,#06-852-00,1-1/4"X1/2",T&D | 7M99003058 | 125TD | \$ 643.11 |
| FPPI,#08-540 BALL DRIP 1/2" | 6999992705 | 5BD | \$ 46.90 |
| FPPI,#08-541 BALL DRIP 3/4 | 6999992706 | 75BD | \$ 68.62 |

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

FIRE DEPARTMENT EQUIPMENT



| Description | Part Number | Short Code | List Price |
|--|-------------|--------------|-------------|
| CROKER,#6405,4X2.5X2.5 STRT FDC,IMPORT | 7C75120002 | FDC | \$ 990.40 |
| CROKER,#6407,90 FDC,4X2.5X2.5 RB | 6999991802 | 90FDC | \$ 1,103.76 |
| CROKER,#6410,4X2.5X2.5,ROUGH BRASS | 6990005394 | FDC6410 | \$ 2,249.28 |
| CROKER,#6341,STRT FDC,2.5",A/S,W/PLG&CHN | 6999991878 | 25FDC | \$ 793.51 |
| CROKER,#6345,1.5,STRT.FDC,RB(IMPORT) | 7C75120004 | 15FDC | \$ 367.52 |
| CROKER,#6766AS,ALUM WALL PLATE,AUTO SPKR | 7C75100000 | WP | \$ 77.56 |
| | | | \$ Call |
| CROKER,#6747,PLUG&CHAIN,2.5,RB | 6999991815 | CROKER25PLUG | \$ 167.90 |
| CROKER,#6752,BREAKABLE CAP,RED,(PAIR) | 7C75110000 | EOP | \$ 40.27 |
| CROKER,#6753 BREAKABLE CAPS 2.5,RED | 6999992311 | | \$ 21.50 |
| CROKER,#6360,STORZ 4 X 4 FDC | 6999992697 | | \$ 666.05 |
| CROKER,#6362-B,STORZ,5 X 4 STRT | 6999992779 | | \$ 992.14 |
| CROKER,#6350,4X4,30 DEG,ALUM,STORZ ONLY | 6990008558 | | \$ 1,056.03 |
| | | | \$ Call |
| CROKER,#6360-C,4" STORZ CAP/CHAIN | 6990010268 | | \$ 555.04 |
| CROKER,#6362-CAP,STORZ CAP+CHAIN | 6999994130 | | \$ 777.06 |
| | | | \$ Call |
| CROKER,#5035 HOSE VLV 2.5 RB | 6999994858 | 25AHVC | \$ 832.57 |
| CROKER,#5709 CAP & CHAIN,1.5",CB | 6999993264 | 15CAP | \$ 83.53 |
| CROKER,#5713,RB,2.5",CAP&CHAIN | 6999993265 | 25CAP | \$ 120.52 |
| CROKER,#5722,2.5",PLASTIC CAP & CHAIN | 6990008143 | | \$ 46.54 |
| | | | \$ Call |
| CROKER,#3010-CB,1.5X100FT,HOSE RACK | 6990001685 | C15HRA | \$ 2,267.18 |
| CROKER,#3401,HOSE,1.5,(50FT) | 6990005672 | | \$ 680.15 |
| CROKER,#3401-CB,1.5X75',SINGLE JACK.HOSE | 6990002383 | | \$ 906.87 |
| CROKER,#3401 HOSE 1.5X100 | 6999993857 | | \$ 1,133.59 |
| CROKER,#3460,1.5 FOG NOZZLE,CB,NST | 6999994251 | | \$ 352.01 |
| CROKER,#3478 1.5" NOZZLE | 6990000976 | | \$ 126.48 |

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.