

SPRINKLERS**I. Standard Spray QR - Quick Response****Basic**

- S-1 F1FR - Upright
- S-3 F1FR-300 - Upright
- S-4 F1FR - Pendent, Recessed
- S-6 F1FR-300 - Pendent, Recessed
- S-7 F1FR - Horizontal Sidewall
- S-8 F1FR56-300 HSW, Rec HSW and SWC56 Concealed
- S-9 F1FR - Vertical Sidewall
- S-10 F1FR - Conventional
- S-11 F1FR-SS Stainless Steel - Upright and Pendent
- S-12 F1FR LL - Pendent and CCP
- S-13 KFR56 - Upright and Pendent
- S-14 KFR56-300 Upright & Pendent
- S-15 KFR56-300 - HSW and CCP
- S-16 KFR56 - HSW and CCP
- S-17 GFR - Upright
- S-18 GFR - Pendent & HSW

Decorative

- S-19 G5-80, G5-56, G5-42 & G5-28
- S-20 G6-56 HSW QR
- S-21 G5-80, G5-56, G5-42 and G5-28 QR "Sealing" Concealed
- S-22 G5-56 300 QR "Sealing" Concealed
- S-23 G5-56 300 Concealer
- S-24 F1FR CCP and F1FR-300 CCP
- S-25 F4FR-NF
- S-26 XL Commercial - Pendent and HSW

Extended Coverage

- S-27 G6-80 HSW QR EC
- S-28 JL112 and J112 - Upright, Pendent and Rec Pendent
- S-29 F1FR 56 QREC and F1FR EC - Pendent, Recessed
- S-30 F1FR 56-300 and F1FR-300 QREC - Pendent, Recessed
- S-31 F1FR 56-300 and F1FR-300 QREC EC9 - HSW, Recessed
- S-32 F1FR 56 EC8 and F1FR QREC EC9 - HSW, Recessed
- S-33 F1FR 56-300 and F1FR-300 QREC CCP - Concealed
- S-34 DH56 - HSW, HSW Recessed, HSW Concealed
- S-35 DH80 - HSW, HSW Recessed, HSW Concealed
- S-36 G4 XLO-QR ECLH/ECOH
- S-36 KFR-CCS Combustible Concealed Space
- S-37 SWC Concealed Sidewall

Dry

- S-38 F3QR56 - Pendent
- S-40 F3QR56 - Pendent / HB
- S-42 F3QR56 - Recessed Pendent / FP
- S-44 F3QR56 - Recessed Pendent / F1
- S-46 F3QR56 - Horizontal Sidewall
- S-48 F3QR56 - Horizontal Sidewall / HB
- S-50 F3QR56 - Recessed Horizontal Sidewall / FP
- S-52 F3QR56 - Recessed Horizontal Sidewall / F1
- S-54 F3QR56 - Concealed
- S-56 F3QR80 - Pendent
- S-57 F3QR80 - Pendent / HB
- S-58 F3QR80 - Recessed Pendent / FP
- S-59 F3QR80 - Horizontal Sidewall
- S-60 F3QR80 - Horizontal Sidewall / HB
- S-61 F3QR80 - Horizontal Sidewall / FP
- S-62 F3QR80 - Concealed

- S-63 G5-56 Dry
- S-64 DH56 Dry - Horizontal Sidewall
- S-65 DH56 Dry - Horizontal Sidewall / HB
- S-66 DH56 Dry - Recessed Horizontal Sidewall
- S-67 DH56 Dry - Concealed
- S-68 DH80 Dry - Horizontal Sidewall
- S-69 DH80 Dry - Horizontal Sidewall / HB
- S-70 DH80 Dry - Recessed Horizontal Sidewall
- S-71 DH80 Dry - Concealed

Institutional

- S-72 XL INST - Institutional

II. Standard Spray SR - Standard Response**Basic**

- S-73 F1 - Upright
- S-75 F1-SS Stainless Steel - Upright & Pendent
- S-76 F1-300 - Upright
- S-77 F1 - Pendent, Recessed
- S-79 F1-300 - Pendent, Recessed
- S-80 F1 - Conventional
- S-81 F1 - Horizontal Sidewall
- S-82 F1 - Vertical Sidewall
- S-83 G - Upright
- S-85 G - Pendent
- S-87 G - Conventional
- S-88 G - Vertical Sidewall
- S-89 G - Horizontal Sidewall, Recessed

Decorative

- S-91 G - Recessed
- S-93 G4
- S-94 G4-300 - Concealed
- S-95 G5-80, G5-56, G5-42 and G5-28 SR "Sealing" Concealed
- S-96 G5-56 300 SR "Sealing" Concealed

Extended Coverage

- S-97 F1 56 SREC and F1 EC - Pendent
- S-98 F1 56-300 SREC and F1-300 EC - Pendent, Recessed
- S-99 G - EC4 - HSW
- S-100 GFR VELO ECOH - Upright
- S-100 GFR VELO ECOH - Pendent, Recessed
- S-101 MBEC-14- HSW

Dry

- S-102 F3-56 - Pendent
- S-104 F3-56 - Pendent / HB
- S-106 F3-56 - Recessed Pendent / FP
- S-108 F3-56 - Recessed Pendent / F1
- S-110 F3-56 - Horizontal Sidewall
- S-112 F3-56 - Horizontal Sidewall / HB
- S-114 F3-56 - Recessed Horizontal Sidewall / FP
- S-116 F3-56 - Recessed Horizontal Sidewall / F1
- S-118 F3-56 - Concealed
- S-120 F3-80 - Pendent
- S-121 F3-80 - Pendent / HB
- S-122 F3-80 - Recessed Pendent / FP
- S-123 F3-80 - Horizontal Sidewall
- S-124 F3-80 - Horizontal Sidewall / HB
- S-125 F3-80 - Horizontal Sidewall / FP
- S-126 F3-80 - Concealed

III. Special

- S-127 Attic Sprinklers
- S-128 LT56 Series Pendent
- S-129 LT56 Series CCP
- S-130 LT56C Flat Concealed

IV. Storage

- S-132 JL-14 ESFR
- S-132 JL-17 ESFR
- S-133 HL-22 ESFR
- S-133 N25 ESFR
- S-134 J168 - Upright
- S-134 N252 EC - Pendant and Recessed Pendant
- S-135 G XLO Upright and Pendant
- S-135 GL 112 Upright and Pendant
- S-135 G - VELO Pendant
- S-136 G,XLO Intermediate and GL112 Intermediate
- S-137 F1FR 56 & F1FR Intermediate - Upright and Pendant
- S-138 F1 56 & F1 Intermediate - Upright and Pendant
- S-139 KFR56 Intermediate - Upright and Pendant
- S-140 Intermediate Level Sprinkler with D-3 and D-5 Guard Assembly
- S-142 GFR Intermediate - Upright and Pendant
- S-143 G Intermediate Level - with D-3 and D-5 Guards/Shields
- S-146 D-1 - Int. Level Sprinkler and Guard Assembly

V. Residential

- S-148 F1RES 30 - Pendant, Rec Pendant, CCP
- S-149 F1RES 49 - Pendant, Rec Pendant, CCP
- S-150 F1RES 44 - HSW, Rec HSW, SWC
- S-151 F1RES 58 - Pendant, Rec Pendant, CCP, HSW
- S-152 F1RES 58 HSWX & KRES 58 HSWX
- S-153 F1RES 76 - Pendant, Rec Pendant, CCP
- S-154 RFC30 Flat Concealed
- S-154 RFC43 Flat Concealed
- S-154 RFC49 Flat Concealed
- S-154 RFC58 Flat Concealed
- S-155 RFS42 Flat Plate Concealed HSW
- S-156 F3RES44 Dry HSW
- S-157 F3RES44 Dry Recessed HSW/F2
- S-158 F3RES44 Dry HSW/HB
- S-159 F1RES 30 LL - Pendant, Rec Pendant, CCP
- S-160 F1RES 49 LL - Pendant, Rec Pendant, CCP
- S-161 F1RES 44 LL - HSW, Rec HSW, SWC
- S-162 F1RES 58 LL - Pendant, Rec Pendant, CCP, HSW
- S-163 RFC30 LL Flat Concealed
- S-163 RFC43 LL Flat Concealed
- S-163 RFC49 LL Flat Concealed

VI. Multipurpose Residential Risers and Accessories

- S-164 Accessories - Cabinets & Escutcheons
- S-166 Accessories - Multipurpose LL Residential Riser
- S-166 Accessories - Gauges, Connections, Drips, Misc.
- S-167 Accessories - Electrical Components

VII. Open, Nozzles, PLD

- S-169 B & FM - Spray Nozzles - Window & Cornice Types
- S-170 HV - High Velocity Nozzles
- S-170 F1-FTR - Pilot Line Detector (PLD)
- S-171 A - Spray Nozzles, R20, R30, R60

VIII. Accessories**Escutcheons**

- S-172 FP Push-On / Thread Off Escutcheons
- S-172 G/F1 Escutcheon and Collar Assembly
- S-172 G/F1 Escutcheon Only
- S-172 G/F1 Collar Only
- S-172 G/F1 and G/F2 Escutcheon Extender Ring
- S-172 G/F2 Escutcheon & Collar Assembly
- S-172 G/F2 Escutcheon Only
- S-172 G/F2 Collar Only
- S-173 B, C & HB Two Sprinkler Escutcheons
- S-173 Sure-Off Tester

Spk Guards/Emergency Cabinets

- S-174 Sprinkler Guards & Shields
- S-174 Emergency Cabinets

Wrenches

- S-175 For Sprinklers or Seat / Valve Wrenches

Replacement Coverplates

- S-176 G1 Concealed Replacement Coverplates

IX. Special Services

- S-177 Special Services / Special Finishes

VALVES**Alarm And Check Valves**

- V-1 E and E3 Alarm Valves - FxF, FxG, GxG
- V-2 E3 - Trim Segmented & Loose
- V-2 LPC - Valve Sets
- V-3 Miscellaneous Alarm Valve Trim
- V-3 Retard Chamber and Mechanical Spk. Alarm
- V-3 Valve Seat Wrenches
- V-3 G - Riser Check - 2½", 3", 4", 6"
- V-3 G - Grooved Check - 2½", 3", 4", 6"
- V-3 CVE - Swing Check - 4", 6", 165mm, 8"

Low Pressure Dry Systems

- V-4 DDX-LP Dry Pipe Valve Systems
- V-5 EX Low Pressure Dry Pipe Valve

Dry Pipe Valves

- V-7 A, D - 2½", 4", 6"
- V-7 A, D - Loose/Preassembled Trim, Factory Trimmed

Accessories

- V-8 ACD Dry Systems Auxiliary
- V-8 B-1 - Accelerator, A-2 Air Maintenance Device, B-1 Air Maintenance Device
- V-9 Test and Drain, Pressure Relief Valves, AAV Auto Air Vent
- V-10 Air Compressors
- V-12 Pressure Gauges
- V-12 Inspectors Test Connections
- V-12 Automatic Ball Drips
- V-12 Mechanical Ball Drips
- V-12 Strainers (Misc. Items)
- V-12 Sprinkler/Valve System Signs
- V-13 Residential Riser
- V-14 CR Commercial Riser

SPECIAL HAZARDS/SPECIAL SYSTEMS**Deluge, Preaction**

- SS-1 Model H Deluge / Riser Assemblies and Trim
- SS-2 DDX Deluge Valves - Electric Trim
- SS-2 DDX Deluge Valves - Wet Pilot Line Trim
- SS-2 DDX Deluge Valves - Dry Pilot Line Trim
- SS-3 DDX Deluge Valves
- SS-3 DDX Deluge Trim

Single, Double, Interlock

- SS-4 Single Interlock - Fully Assembled
- SS-5 Double Interlock - Fully Assembled
- SS-6 Preaction Trim

PrePaK

- SS-7 DDX Type D PrePaK
- SS-8 DDX Type F PrePaK
- SS-9 DDX Electric Release DelPaK
- SS-10 DDX Wet Pilot DelPaK
- SS-10 DDX Dry Pilot DelPaK

DryPaK

- SS-11 DDX-LP DryPaK System

Accessories

- SS-12 Accelerator
- SS-12 Pull Boxes
- SS-12 RPC 4410 RC Control Panel
- SS-12 System Modules / Batteries
- SS-13 Drain Assemblies, Dry Pilot Actuator
- SS-14 Electric Alarm Bells, Supervisory Air Supply, Valve Seat Wrenches
- SS-14 LPC Preaction Systems, Components
- SS-15 Protectowire

SYSTEM COMPONENTS**Grooved Couplings And Fittings**

- SC-1 Couplings, Lightweight and Rigid
- SC-2 Couplings, Standard and Reducing
- SC-3 Couplings, Standard and Rigid w/Flush Seal
- SC-4 90° Elbows
- SC-5 45° Elbows
- SC-6 Tees
- SC-7 Flanges, Short Radius 90° Elbows
- SC-8 Short Radius 45° Elbows and Tees
- SC-9 Concentric Reducers, Caps
- SC-10 Caps (cont'd), Star-let Tees (MT3)
- SC-11 Mechanical Tees (Threaded and Grooved)
- SC-12 Mechanical Tees (cont'd)
- SC-13 Mechanical Tee-Cross (Threaded)
- SC-14 Mechanical Tee-Cross (Grooved), Replacement Gaskets
- SC-15 End of Run Fittings (SE-5)
- SC-16 Couplings, Lightweight and Rigid
- SC-18 Couplings, Lightweight and Rigid w/Flush Gasket
- SC-19 Couplings, Reducing
- SC-20 45° Elbows and 90° Elbows
- SC-21 Fire Rite 90° Elbows and Standard Tees
- SC-22 Fire Rite Tees & Concentric Reducers (GxG)
- SC-24 Concentric Reducers (GxT)
- SC-26 Caps, Gruvlok Flanges
- SC-27 Clamp-T (Grooved Outlet)
- SC-28 Clamp-T (Female Threaded Outlet)
- SC-30 Steel Cross
- SC-31 Replacement Gaskets

- SC-32 Sock-Iets, 90° Straight and Reducing, Tees

US Made Cast Iron Fittings

- SC-34 90° and 45° Elbows, Reduc. 90° Elbows, Reduc. Couplings, Standard Tees
- SC-36 Reducing Tees
- SC-37 Bullhead Tees, Crosses, Plugs, Caps (malleable), Couplings (malleable), Unions (malleable)
- SC-38 Hex Bushings, Companion Flanges, Pipe Dope, Teflon Tape, Cutting Oil
- SC-39 90° Elbows, Reducing 90° Elbows, 45° Elbows Reducing Couplings, Standard Tees
- SC-40 Reducing Tees, Couplings, Caps, Unions

Cast Iron Fittings - Foreign

- SC-42 90° and 45° Elbows, Reduc. 90° Elbows, Reduc. Couplings, Standard Tees
- SC-43 Reducing Tees
- SC-44 Bullhead Tees, Crosses (Standard & Reduc.) Plugs, Pipe Dope, Teflon Tape, Cutting Oil

Ductile Iron Fittings - Foreign

- SC-45 90° and 45° Elbows, Reduc. 90° Elbows, Reduc. Couplings, Standard Tees
- SC-46 Reducing Tees
- SC-47 Bullhead Tees, Crosses, Caps, Couplings Pipe Dope, Teflon Tape, Cutting Oil

US Made Flanged Fittings

- SC-48 Flanged Elbows, Reducing
- SC-49 Flange Tees
- SC-50 Flanged Reducers
- SC-51 Companion, Reducing Flange

Expansion Loops

- SC-52 Threaded & Grooved Models

CPVC Pipe, Fittings, & Hangers

- SC-54 Pipe, Anti-Freeze
- SC-55 Hangers (Single, Double, Sidemount, Stand-Off)
- SC-56 Sealant, Caulk
- SC-57 Elbows, Head Adapters, Standard Tees, Tees (Reduc. and Run Reduc.), Tee Head
- SC-58 Adapters Tee Head Adapters (cont'd), Bushings,
- SC-60 Head Adapters, Adapters, Couplings, Reduc. Couplings
- SC-61 Grooved Adapters, Caps, Crosses, Cement, Thread Sealant
- SC-62 Torque Safe Fittings

PEX

- SC-63 PEX Pipe
- SC-64 PEX Fittings
- SC-67 J-Fit Fittings
- SC-68 PEX Tools

Tee-Iets

- SC-69 Tee-Iets
- SC-71 Grooved Shape Nipples - Sch 40
- SC-72 Grooved Shape Nipples - Sch 10
- SC-73 Import Olets
- SC-74 Unilets

Hangers

- SC-75 Ring Hangers, Beam Clamps, Riser Clamps, Wall Plates
- SC-76 Earthquake Bracing
- SC-77 Eye Sockets, All Thread Rod, Hex Nuts, Washers, Drop Anchors

Super Screws

SC-78 Sammy Super Screws

Fire Department EquipmentSC-80 Fire Department Connections, Hose Valves,
Accessories**Nipples**SC-82 Adjustable Wet Drop Nipples (M x F, M x M)
SC-83 Steel Nipples, Blck & Galvanized**Valves**SC-88 Riser Check, Grooved Check, Swing Check,
Flanged Check, Gasket Kits
SC-89 OS&Y, PIV, Butterfly Valves (GxG and Wafer)
SC-90 Butterfly Valves
SC-91 Butterball Valves (Threaded and Grooved)
SC-92 Foreign Trim Valves - Globe, Ck, 3-way Angle
SC-93 Valves, FDC, and Accessories
SC-96 US Made Trim Valves - Globe, Ck, 3-way, Angle
SC-97 Detector Check, In-Building Riser, Wafer Check,
Test & Drains**Backflows**SC-99 2000ss, 2001ss, 3000ss, 30001ss
SC-100 4000ss, 4001ss, 5000ss, 5001ss
SC-101 Colt Series: C-200 OS&Y, C-200 BFV, C-300
OS&Y, C-300 BFV
SC-102 Colt Series: C-400 OS&Y, C-400 N or Z, C-500
OS&Y, C-500 N or Z
SC-103 Maxim Series: M-200 OS&Y, M-200 BFV, M-300
OS&Y, M-300 BFV
SC-104 Maxim Series: M-400 OS&Y, M-400 N or Z, M-
500 OS&Y, M-500 N or Z
SC-105 OS & Y**Air Compressors**

SC-109 Bare, with Check, Tank Mounted

Electrical EquipmentSC-111 Waterflow Detector, Tamper Switches, Electric
Bells, Accessories
SC-112 Canadian versions**Flexible Drops**

SC-113 Flexible Drops

Residential Fire Pumps & Accessories

SC-114 Residential Fire Pumps, Tanks, Kits

Steel PipeSC-115 Schedule 40 & 10, Flowpipe, Threadable
Lightwall, and Special Requests**Expansion Tanks**

SC-116 Expansion Tanks

Deluge ValvesRP-9 Deluge Valves and Trimmings
RP-15 External Reset Device
RP-15 Air Maintenance Devices**Miscellaneous**RP-16 Sight Test Connection
RP-17 Sight Drain, Emergency Pull Box, Copper
Tubing, Parts for Model B Air Compressor Panel
RP-18 Air Compressor**REPLACEMENT PARTS****Alarm Valves**RP-1 Alarm Valves & Trimmings
RP-5 Retard Chamber
RP-5 Mechanical Sprinkler Alarm**Dry Pipe Valves**RP-5 Dry Pipe Valves and Trimmings
RP-8 Accelerator