

FOREIGN CAST IRON FITTINGS



Description	Part Number	List Price
90° ELBOWS		
1"	7307040400	A\$ 25.56
1-1/4"	7307050500	A\$ 45.15
1-1/2"	7307060600	A\$ 56.55
2"	7307080800	A\$ 88.22
2-1/2"	7307101000	A\$ 208.52
REDUCING 90° ELBOWS		
1 x 1/2"	7311040200	A\$ 27.86
1 x 3/4"	7311040300	A\$ 41.44
1-1/4 x 1/2"	7311050200	A\$ 51.93
1-1/4 x 3/4"	7311050300	A\$ 51.93
1-1/4 x 1"	7311050400	A\$ 51.93
1-1/2 x 1/2"	7311060200	A\$ 73.30
1-1/2 x 3/4"	7311060300	A\$ 73.30
1-1/2 x 1"	7311060400	A\$ 73.30
1-1/2 x 1-1/4"	7311060500	A\$ 73.30
2 x 1/2"	7311080200	A\$ 104.88
2 x 3/4"	7311080300	A\$ 104.88
2 x 1"	7311080400	A\$ 104.88
2 x 1-1/4"	7311080500	A\$ 104.88
2 x 1-1/2"	7311080600	A\$ 104.88
45° ELBOWS		
1"	7303040400	A\$ 41.34
1-1/4"	7303050500	A\$ 57.58
1-1/2"	7303060600	A\$ 95.84
2"	7303080800	A\$ 110.01
REDUCING COUPLINGS		
1 x 1/2"	7315040200	A\$ 20.79
1 x 3/4"	7315040300	A\$ 26.62
TEES STANDARD		
1"	7319040404	A\$ 34.85
1-1/4"	7319050505	A\$ 69.82
1-1/2"	7319060606	A\$ 90.07
2"	7319080808	A\$ 126.78
2-1/2"	7319101010	A\$ 335.41

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

FOREIGN CAST IRON FITTINGS



Description	Part Number	List Price
REDUCING TEES		
1 x .5 x 1"	7323040204	A\$ 47.51
1 x .75 x 1"	7323040304	A\$ 47.51
1 x 1 x .5"	7323040402	A\$ 40.41
1 x 1 x .75"	7323040403	A\$ 47.51
1.25 x 1 x .5"	7323050402	A\$ 69.82
1.25 x 1 x .75"	7323050403	A\$ 69.82
1.25 x 1 x 1"	7323050404	A\$ 68.47
1.25 x 1 x 1.25"	7323050405	A\$ 68.47
1.25 x 1.25 x .5"	7323050502	A\$ 68.47
1.25 x 1.25 x .75"	7323050503	A\$ 69.82
1.25 x 1.25 x 1"	7323050504	A\$ 68.47
1.5 x 1 x .5"	7323060402	A\$ 89.45
1.5 x 1 x .75"	7323060403	A\$ 89.45
1.5 x 1 x 1"	7323060404	A\$ 89.45
1.5 x 1 x 1.25"	7323060405	A\$ 95.31
1.5 x 1 x 1.5"	7323060406	A\$ 95.31
1.5 x 1.25 x .5"	7323060502	A\$ 89.45
1.5 x 1.25 x .75"	7323060503	A\$ 89.45
1.5 x 1.25 x 1"	7323060504	A\$ 89.45
1.5 x 1.25 x 1.25"	7323060505	A\$ 98.29
1.5 x 1.25 x 1.5"	7323060506	A\$ 98.29
1.5 x 1.5 x .5"	7323060602	A\$ 87.82
1.5 x 1.5 x .75"	7323060603	A\$ 89.45
1.5 x 1.5 x 1"	7323060604	A\$ 89.45
1.5 x 1.5 x 1.25"	7323060605	A\$ 104.88
2 x 1 x 2"	7323080408	A\$ 131.19
2 x 1.25 x 2"	7323080508	A\$ 141.89
2 x 1.5 x .5"	7323080602	A\$ 128.11
2 x 1.5 x .75"	7323080603	A\$ 128.11
2 x 1.5 x 1.5"	7323080606	A\$ 149.00
2 x 1.5 x 2"	7323080608	A\$ 149.00
2 x 1.5 x 1"	7323080604	A\$ 125.74
2 x 1.5 x 1.25"	7323080605	A\$ 149.00
2 x 2 x .5"	7323080802	A\$ 128.11
2 x 2 x .75"	7323080803	A\$ 130.49
2 x 2 x 1"	7323080804	A\$ 128.11
2 x 2 x 1.25"	7323080805	A\$ 151.45
2 x 2 x 1.5"	7323080806	A\$ 154.23

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

FOREIGN CAST IRON FITTINGS



Description	Part Number	List Price
BULLHEAD TEES		
1 x 1 x 1.25"	7325040405	A\$ 71.97
1 x 1 x 1.5"	7325040406	A\$ 76.40
1.25 x 1.25 x 1.5"	7325050506	A\$ 117.31
1.25 x 1 x 1.5"	7325050406	A\$ 98.29
1.25 x 1.25 x 2"	7325050508	A\$ 117.31
1.5 x 1.25 x 2"	7325060508	A\$ 126.26
1.5 x 1.5 x 2"	7325060608	A\$ 131.19
2 x 2 x 2-1/2"	7325080810	A\$ 348.99
CROSSES STANDARD		
1"	7327040000	A\$ 74.45
1-1/4"	7327050000	A\$ 117.22
1-1/2"	7327060000	A\$ 147.12
2"	7327080000	A\$ 252.42
CROSSES REDUCING		
1-1/4 x 1"	7331554400	A\$ 236.70
1-1/2 x 1"	7331664400	A\$ 282.45
2 x 1"	7331884400	A\$ 409.23
PLUG HEX HEAD CORED		
1/2"	7339020000	A\$ 8.74
3/4"	7339030000	A\$ 12.34
1"	7339040000	A\$ 13.27
1-1/4"	7339050000	A\$ 25.49
1-1/2"	7339060000	A\$ 35.78
2"	7339080000	A\$ 42.77
PIPE DOPE		
Pipe Dope, pint	6999993287	A\$ 76.10
Pipe Dope, quart	7395000000	A\$ 122.44
Slicite	6990002541	A\$ 352.60
TEFLON TAPE		
3/4"	6999991902	A\$ 5.77
1/2"	6999992086	A\$ 4.03
CUTTING OIL		
1 Gallon	6999991577	A\$ 180.82

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.