

HANGERS



Description	Part Number	Short Code	Box Qty	List Price
RING HANGERS				
1"	6990010526	1HPHD	100	A\$ 1.66
1-1/4"	6990010527	125HPHD	100	A\$ 1.66
1-1/2"	6990010528	15HPHD	100	A\$ 1.79
2"	6990010529	2HPHD	100	A\$ 1.88
2-1/2"	6990010590	25HPHD	50	A\$ 3.44
3"	6990010530	3HPHD	50	A\$ 3.84
4"	6990010531	4HPHD	25	A\$ 4.77
5"	7M99001923	5HPHD	25	A\$ 9.38
6"	6990010532	6HPHD	20	A\$ 10.52
8"	7M99001924	8HPHD	10	A\$ 15.00
BEAM CLAMPS - DOMESTIC				
3/8" - BLACK	7M99001925	38BCPHD	100	A\$ 6.33
1/2" - BLACK	7M99001926	12BCPHD	100	A\$ 7.95
3/8" - GALVANIZED	7M99001929	38BCGPHD	100	A\$ 8.32
1/2" - GALVANIZED	7M99001930	12BCGPHD	100	A\$ 11.25
WIDE MOUTH BEAM CLAMP - DOMESTIC				
3/8" - BLACK	7M99001939	38WBCPHD	100	A\$ 7.77
1/2" - BLACK	7M99001940	12WBCPHD	100	A\$ 9.30
STEEL BEAM CLAMP - DOMESTIC				
3/8"	7M99002897	SURELOK	100	A\$ 3.78
SIDE BEAM BRACKET				
3/8"	7M99001947	38SBBPHD	100	A\$ 4.99
RISER CLAMPS - GALVANIZED				
1-1/4"	7M99001950	125CPHD	25	A\$ 24.22
1-1/2"	7M99001951	15CPHD	25	A\$ 25.18
2"	7M99001952	2CPHD	25	A\$ 26.01
2-1/2"	7M99001953	25CPHD	25	A\$ 32.52
3"	7M99001954	3CPHD	25	A\$ 33.23
4"	7M99001955	4CPHD	15	A\$ 44.59
6"	7M99001956	6CPHD	10	A\$ 72.75
8"	7M99001957	8CPHD		A\$ 159.07
PLASTIC, CHROME				
1"	7W15040000	WP1CP	N/A	A\$ 2.42
1-1/4"	7W15050000	WP125CP	N/A	A\$ 2.75
1-1/2"	7W15060000	WP15CP	N/A	A\$ 3.15
2"	7W15080000	WP2CP	N/A	A\$ 3.62
CAST IRON, GALVANIZED				
1"	7W09040000	WP1G	N/A	A\$ 14.38
1-1/4"	7W09050000	WP125G	N/A	A\$ 15.34
1-1/2"	7W09060000	WP15G	N/A	A\$ 16.44
2"	7W09080000	WP2G	N/A	A\$ 21.03
SPLIT RING HANGERS - #508R - BLACK				
1/2"	7M99001973	5SRPHD	100	A\$ 5.40
3/4"	7M99001974	75SRPHD	100	A\$ 6.58
1"	7M99001975	1SRPHD	100	A\$ 7.18
1-1/4"	7M99001976	125SRPHD	100	A\$ 7.88
1-1/2"	7M99001977	15SRPHD	100	A\$ 9.74
2"	7M99001978	2SRPHD	100	A\$ 14.03
2-1/2"	7M99001979	25SRPHD	50	A\$ 19.68
3"	7M99001980	3SRPHD	25	A\$ 28.03
4"	7M99001981	4SRPHD	25	A\$ 36.36

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

EARTHQUAKE BRACING



Description	Part Number	Short Code	List Price
SWAY BRACE ATTACHMENT - # 010			
1 x 1	7M99002052	PHD01011	A\$ 33.48
1-1/4 x 1	7M99002053	PHD0101251	A\$ 33.48
1-1/2 x 1	7M99002054	PHD010151	A\$ 33.48
2 x 1	7M99002055	PHD01021	A\$ 33.48
2-1/2 x 1	7M99002056	PHD010251	A\$ 34.55
3 x 1	7M99002057	PHD01031	A\$ 35.22
4 x 1	7M99002058	PHD01041	A\$ 43.21
1 x 1-1/4	7M99002059	PHD0101125	A\$ 39.93
1-1/4 x 1-1/4	7M99002060	PHD010125125	A\$ 40.31
1-1/2 x 1-1/4	7M99002061	PHD01015125	A\$ 40.31
2 x 1-1/4	7M99002062	PHD0102125	A\$ 40.31
2-1/2 x 1-1/4	7M99002063	PHD01025125	A\$ 41.77
3 x 1-1/4	7M99002064	PHD0103125	A\$ 42.15
4 x 1-1/4	7M99002065	PHD0104125	A\$ 51.19
6 x 1-1/4	7M99002066	PHD0106125	A\$ 71.30
SWAY BRACE ATTACHMENT - # 015			
2-1/2 x 1	6990016517	PHD015251	A\$ 39.23
3 x 1	6990016518	PHD01531	A\$ 41.10
4 x 1	6990016519	PHD01541	A\$ 43.90
6 x 1	6990017097	PHD01561	A\$ 49.51
8 x 1	6990017467	PHD01581	A\$ 54.18
2-1/2 x 1-1/4	6990017556	PHD01525125	A\$ 43.90
3 x 1-1/4	6990017557	PHD0153125	A\$ 44.84
4 x 1-1/4	6990017558	PHD0154125	A\$ 49.51
6 x 1-1/4	6990016955	PHD0156125	A\$ 55.59
8 x 1-1/4	6990016956	PHD0158125	A\$ 60.26
MULTI-FASTENER ADAPTOR - # 025			
3/4"	7M99002067		A\$ 45.14
1/2"	7M99002068		A\$ 45.14
C-CLAMP STRUCTURAL ATTACHMENT - # 030			
****	7M99002069	PHD030	A\$ 42.71
CLAMPING PIPE ATTACHMENT - # 031			
2"	7M99002485	PHD0312	A\$ 67.55
2-1/2"	7M99002486	PHD03125	A\$ 68.70
3"	7M99002487	PHD0313	A\$ 70.04
4"	7M99002488	PHD0314	A\$ 72.36
5"	7M99002489	PHD0315	A\$ 89.48
6"	7M99002490	PHD0316	A\$ 94.58
8"	7M99002491	PHD0318	A\$ 143.36
SWAY BRACE BAR JOIST ADAPTOR - # 035			
****	7M99002070	PHD035	A\$ 70.23
SUPPORTING PIPE ATTACHMENT - # 040			
2"	7M99002492		A\$ 91.58
2-1/2"	7M99002493		A\$ 93.49
3"	7M99002494		A\$ 96.70
4"	7M99002495		A\$ 118.18
5"	7M99002496		A\$ 144.33
6"	7M99002497		A\$ 173.19
8"	7M99002498		A\$ 235.90
SUPPORTING PIPE ATTACHMENT - # 045			
***	7M99002613	PHD045	A\$ 115.45

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

HANGERS



Description	Part Number	Short Code	Box Qty	List Price
EYE SOCKETS - #37				
3/8"	7817030000	38ESPHD	250	A\$ 5.78
1/2"	7M99001948	12ESPHD	100	A\$ 9.25
IN-RACK FLUE HANGERS				
ADJUSTABLE #990	7M99003055		BULK	A\$ 135.63
SINGLE #995	7M99003106		BULK	A\$ 70.08
ALL THREAD ROD (BLACK)				
3/8" x 12'	7875011200	38TR12	250	A\$ 2.47
3/8" x 10'	7875010000	38TR	250	A\$ 2.47
3/8" x 6'	7875010600	38TR6	150	A\$ 2.47
1/2" x 12'	7875021200	12TR12	250	A\$ 4.52
1/2" x 10'	7875020000	12TR	120	A\$ 4.52
1/2" x 6'	7875020600	12TR6	72	A\$ 4.52
ALL THREAD ROD PLATED				
3/8" x 12'	7875011201	38TRP12	250	A\$ 2.62
3/8" x 10'	7875010001	38TRP	250	A\$ 2.62
3/8" x 6'	7875010601	38TRP6	150	A\$ 2.62
1/2" x 12'	7875021201	12TRP12	250	A\$ 4.73
1/2" x 10'	7875020001	12TRP	120	A\$ 4.73
1/2" x 6'	7875020601	12TRP6	72	A\$ 4.73
HEX NUTS				
3/8"	7851010000	38N	N/A	A\$ 0.36
1/2"	7851020000	12N	N/A	A\$ 0.55
5/8"	7851050000	58N	N/A	A\$ 1.00
3/4"	7851030000	34N	N/A	A\$ 1.62
ZINC FLAT WASHERS				
3/8"	7853010000	38W	N/A	A\$ 0.41
1/2"	7853020000	12W	N/A	A\$ 0.63
ZINC ROD COUPLINGS				
3/8" x 1-3/4"	7855010002	38C	N/A	A\$ 1.53
3/8" x 1-1/8"	7855010000	38CS	N/A	A\$ 0.81
1/2" x 1-3/4"	7855020000	12C	N/A	A\$ 2.16
DROP IN ANCHORS				
3/8"	6999991999	DROPIN	100	A\$ 2.40
1/2"	6999992000	12DROPIN	N/A	A\$ 4.58

¹ Available in 6' (38TR6) and 10' (12TR6) lengths.

Special Note:

Earthquake and other Hanger requirements available upon request.

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.