



PRV DIAPHRAGM PRESSURE REGULATING VALVE

- See Bulletin 820
- 400 psi (27.6 Bar) Rated Pressure
- Adjusted with Pilot Operated Regulator
- Trim Includes Relief Valve
- No Trim Connections to Cover

Description	Part Number	Short Code	List Price
MODEL PRV DIAPHRAGM PRESSURE REGULATING VALVES			
2-1/2" Groove/Groove (ANSI/AWWA C606)	6507018000		A\$10,273.95
2-1/2" Flange/Flange Class 150 (ASME B16.5)	6507118000		A\$10,273.95
2-1/2" Flange/Flange Class 300 (ASME B16.5)	6507218000		A\$10,273.95
2-1/2" Flange/Flange PN16 (ISO 7005-2)	6507318000		A\$10,273.95
2-1/2" NPT Thread/Thread (ANSI/ASME B1.20.1)	6507518000		A\$10,273.95
2-1/2" ISO7-1 Thread/Thread	6507618000		A\$10,273.95
76MM Groove/Groove (ANSI/AWWA C606)	6507078000		A\$10,273.95
3" Groove/Groove (ANSI/AWWA C606)	6507038000		A\$10,273.95
3" Flange/Flange Class 150 (ASME B16.5)	6507138000		A\$10,273.95
3" Flange/Flange Class 300 (ASME B16.5)	6507238000		A\$10,273.95
3" Flange/Flange PN16 (ISO 7005-2)	6507338000		A\$10,273.95
3" NPT Thread/Thread (ANSI/ASME B1.20.1)	6507538000		A\$10,273.95
3" ISO7-1 Thread/Thread	6507638000		A\$10,273.95
4" Groove/Groove (ANSI/AWWA C606)	6507048000		A\$12,328.74
4" Flange/Flange Class 150 (ASME B16.5)	6507148000		A\$12,328.74
4" Flange/Flange Class 300 (ASME B16.5)	6507248000		A\$12,328.74
4" Flange/Flange PN16 (ISO 7005-2)	6507348000		A\$12,328.74
6" Groove/Groove (ANSI/AWWA C606)	6507068000		A\$15,068.46
6" Flange/Flange Class 150 (ASME B16.5)	6507168000		A\$15,068.46
6" Flange/Flange Class 300 (ASME B16.5)	6507268000		A\$15,068.46
6" Flange/Flange PN16 (ISO 7005-2)	6507368000		A\$15,068.46
165MM Groove/Groove (ANSI/AWWA C606)	6507058000		A\$15,068.46

Notes:

Part numbers shown include a 185 psi (12.8 Bar) relief valve and 300 psi (20.7 Bar) gauges. Replace the last digit in the part number as follows for other relief valve and gauge combinations:

- "0"-185 psi (12.8 Bar) relief valve and 300 psi (20 Bar) gauges
- "1"-260 psi (17.9 Bar) relief valve and 300 psi (20 Bar) gauges
- "2"-185 psi (12.8 Bar) relief valve and 600 psi (40 Bar) gauges
- "3"-260 psi (17.9 Bar) relief valve and 600 psi (40 Bar) gauges