



Model A



Model D

DRY PIPE VALVES

- See Bulletins 350, 351, 352, 353

Description	Part Number	Short Code	List Price
MODEL A THREADED OR GROOVED			
Model A - 2-1/2" — Threaded			£ Call
Model A - 2-1/2" — Grooved			£ Call
MODEL A METRIC			
Model A - 65mm			£ Call
MODEL D FLANGED OR GROOVED			
4" — Flanged			£ Call
4" — Grooved			£ Call
6" — Flanged			£ Call
6" — Grooved			£ Call
MODEL D METRIC			
Model D — 100mm			£ Call
Model D — 150mm			£ Call
TRIM (ONLY) — INDIVIDUAL PARTS			
2-1/2"			£ Call
4"			£ Call
6"			£ Call
TRIM (ONLY) — SEGMENTALLY ASSEMBLED			
2-1/2"			£ Call
4"			£ Call
6"			£ Call
FACTORY TRIMMED VALVES¹			
4" — Flanged			£ Call
4" — Grooved			£ Call
4" w/ Accelerator — Flanged			£ Call
4" w/ Accelerator — Grooved			£ Call
6" — Flanged			£ Call
6" — Grooved			£ Call
6" w/ Accelerator — Flanged	6505060113	6DFTAG	£ 11,414.22
6" w/ Accelerator — Grooved			£ Call

¹ Factory Trimmed Valve Includes Valve and Trim



DELUGE VALVES

- **MODEL DDX DELUGE VALVE**
- Electric, Wet Pilot Line, and Dry Pilot Line Trims
- See Bulletin 519

Description	Part Number	Short Code	List Price
MODEL DDX - DELUGE VALVE ONLY (GROOVED/GROOVED)			
Model DDX - 2"	6103022000	2DDX	£ 5,329.32
Model DDX - 2-1/2"	6103022500	25DDX	£ 5,329.32
Model DDX - 2 1/2 (76MM) Red	6103027600	76DDXMM	£ 5,329.32
Model DDX-3"	6103030000	3DDX	£ 5,501.84
Model DDX- 4"	6103040026	4DDX	£ 5,623.05
Model DDX - 6"	6103060024	6DDX	£ 6,912.51
Model 165MM	6103060028	165DDXMM	£ 6,912.51
Model DDX - 8"	6103080001	8DDX	£ 11,483.00
MODEL DDX - DELUGE VALVE ONLY (FLANGE/FLANGE)			
Model DDX- 4"	6103040045	4DDXF	£ 5,623.05
Model DDX - 6"	6103060046	6DDXF	£ 6,912.51
Model DDX - 8"	6103080016	8DDXF	£ 11,483.00
MODEL DDX - DELUGE VALVE ONLY (FLANGE/GROOVED)			
Model DDX- 4"	6103040044	4DDXFG	£ 5,623.05
Model DDX - 6"	6103060045	6DDXFG	£ 6,912.51
Model 165MM	6103060052	165DDXFG	£ 6,912.51
DELUGE TRIM ONLY — SEGMENTALLY ASSEMBLED-WITH PRESSURE SWITCH			
Wet Pilot Line 2", 2-1/2" & 3"	6520702010	25DDXWPN	£ 3,393.69
Wet Pilot Line 4", 6" & 8"	6520703010	4DDXWPN	£ 3,393.69
Dry Pilot Line 2", 2-1/2" & 3"	6520802010	25DDXDPPN	£ 5,083.87
Dry Pilot Line 4", 6" & 8"	6520803010	4DDXDPPN	£ 5,083.87
Electric Release 2", 2-1/2" & 3"	6520902110	25DDXEPN	£ 4,750.86
Electric Release 4", 6" & 8"	6520903110	4DDXEPN	£ 4,750.86
DELUGE TRIM ONLY — INDIVIDUAL PARTS-WITH PRESSURE SWITCH			
Wet Pilot Line 2", 2-1/2" & 3"	6520700010	25DDXWLN	£ 3,220.08
Wet Pilot Line 4", 6" & 8"	6520701010	4DDXWLN	£ 3,220.08
Dry Pilot Line 2", 2-1/2" & 3"	6520800010	25DDXDPLN	£ 4,761.78
Dry Pilot Line 4", 6" & 8"	6520801010	4DDXDPLN	£ 4,761.78
Electric Release 2", 2-1/2" & 3"	6520900110	25DDXELN	£ 4,409.11
Electric Release 4", 6" & 8"	6520901110	4DDXELN	£ 4,409.11
DELUGE TRIM ONLY - SEGMENTALLY ASSEMBLED-WITHOUT PRESSURE SWITCH			
2,2.5&3,DDX,WET PILOT TRIM,SEG W/O PS N	6520702000		£ 2,903.19
4,6&8,DDX,WET PILOT TRIM,SEG W/O PS N	6520703000		£ 2,903.19
2,2.5&3,DDX,DRY PILOT TRIM,SEG.W/O PS	6520802000		£ 4,102.87
4,6&8,DDX,DRY PILOT TRIM,SEG W/O PS	6520803000		£ 4,102.87
2,2.5&3,DDX,ELECTRIC TRIM,175,SEG W/O PS	6520902100		£ 4,260.36
4,6&8,DDX,ELECTRIC TRIM,175,SEG W/O PS	6520903100		£ 4,260.36
DELUGE TRIM ONLY - INDIVIDUAL PARTS-WITHOUT PRESSURE SWITCH			
2,2.5&3,DDX,WET PILOT TRIM,LOOSE W/O PS	6520700000	25DDXWLWOS	£ 2,729.58
4,6&8,DDX,WET PILOT TRIM,LOOSE W/O PS	6520701000	4DDXWLWOS	£ 2,729.58
2,2.5&3,DDX,DRY PILOT TRIM,LOOSE W/O PS	6520800000		£ 3,780.78
4,6&8,DDX,DRY PILOT TRIM,LOOSE W/O PS	6520801000	4DDXDPLWOS	£ 3,780.78
2,2.5&3,DDX,ELECTRIC TRIM,LOOSE W/O PS	6520900100	25DDXELWOS	£ 3,918.61
4,6&8,DDX,ELECTRIC TRIM,175,LOOSE W/O PS	6520901100	4DDXELWOS	£ 3,918.61

Notes:

We have an option to order our trim with or without the Pressure Switches



MODEL FX DRY PIPE VALVE

- Convenient external reset; no priming water required
- See Bulletin 360
- Fully assembled valves include the Potter pressure switches
- Loose and segmented trim do not include the Potter pressure switches

Description	Part Number	Short Code	List Price
MODEL FX DRY PIPE VALVE - GROOVED/GROOVED - VALVE ONLY			
2(50MM),FX DRY VALVE,GE/GE,RED	6101020607	2FX	£ 3,207.60
2 1/2(65MM),FX DRY VALVE,GE/GE,RED	6101025607	25FX	£ 3,888.00
76MM,FX DRY VALVE,GE/GE,RED	6101076607	76MMFX	£ 3,888.00
3(80MM),FX DRY VALVE,GE/GE,RED	6101030607	3FX	£ 3,888.00
4(100MM),FX DRY VALVE,GE/GE,RED	6101040607	4FX	£ 4,179.59
6(150MM),FX DRY VALVE,GE/GE,RED	6101060607	6FX	£ 5,831.99
165MM,FX DRY VALVE,GE/GE,RED	6101065607	165MMFX	£ 5,831.99
MODEL FX DRY PIPE VALVE - FLANGE/GROOVED - VALVE ONLY			
4(100MM),FX DRY VALVE,FL/GE,RED	6101040608	4FXFG	£ 4,179.59
4(100MM),FX DRY VALVE,FL/GE,BS-E,RED	6101040609	4FXFGBS	£ 4,179.59
4(100MM),FX DRY VALVE,FL/GE,PN16,RED	610104060A	4FXFGPN16	£ 4,179.59
6(150MM),FX DRY VALVE,FL/GE,RED	6101060608	6FXFG	£ 5,831.99
6(150MM),FX DRY VALVE,FL/GE,BS-E,RED	6101060609	6FXFGBS	£ 5,831.99
6(150MM),FX DRY VALVE,FL/GE,PN16,RED	610106060A	6FXFGPN16	£ 5,831.99
MODEL FX DRY PIPE VALVE - FLANGE/FLANGE - VALVE ONLY			
4(100MM),FX DRY VALVE,FL/FL,RED	610104060B	4FXF	£ 4,179.59
4(100MM),FX DRY VALVE,FL/FL,BS-E,RED	610104060C	4FXFBS	£ 4,179.59
4(100MM),FX DRY VALVE,FL/FL,PN16,RED	610104060E	4FXFPN16	£ 4,179.59
6(150MM),FX DRY VALVE,FL/FL,RED	610106060B	6FXF	£ 5,831.99
6(150MM),FX DRY VALVE,FL/FL,BS-E,RED	610106060C	6FXFBS	£ 5,831.99
6(150MM),FX DRY VALVE,FL/FL,PN16,RED	610106060E	6FXFPN16	£ 5,831.99
MODEL FX TRIM ONLY - INDIVIDUAL PARTS (LOOSE)			
2 BASIC DRY TRIM,FX,LOOSE	6508000001	2FXDRYL	£ 972.00
2 1/2 & 3 BASIC DRY TRIM,FX,LOOSE	6508000002	25FXDRYL	£ 972.00
4 & 6 BASIC DRY TRIM,FX,LOOSE	6508000003	4FXDRYL	£ 1,263.60
MODEL FX TRIM ONLY - SEGMENTALLY ASSEMBLED			
2 BASIC DRY TRIM,FX,SEGMENTED	6508000011	2FXDRYP	£ 1,360.80
2 1/2 & 3 BASIC DRY TRIM,FX,SEGMENTED	6508000012	25FXDRYP	£ 1,360.80
4 & 6 BASIC DRY TRIM,FX,SEGMENTED	6508000013	4FXDRYP	£ 1,458.00
MODEL FX ACCELERATOR AND TRIM			
FX ACCELERATOR AND TRIM KIT LOOSE	650120001A	AEFX	£ 2,256.30

Features

- Lightweight ductile iron body with compact trim
- External reset reduces setup and commissioning time
- Does not require priming water
- Available fully assembled, with or without control valve



MODEL FX DRY PIPE VALVE

- Convenient external reset; no priming water required
- See Bulletin 360
- Fully assembled valves include the Potter pressure switches
- Loose and segmented trim do not include the Potter pressure switches

Description	Part Number	Short Code	List Price
MODEL FX FULLY ASSEMBLED VALVE - GROOVED/GROOVED WITH BASIC TRIM			
2(50MM),FX DRY VALVE,GE/GE,RED	6508027000	2FXFB	£5,540.40
2 1/2(65MM),FX DRY VALVE,GE/GE,RED	6508017000	25FXFB	£6,026.40
76MM,FX DRY VALVE,GE/GE,RED	6508077000	76MMFXFB	£6,026.40
3(80MM),FX DRY VALVE,GE/GE,RED	6508037000	3FXFB	£6,026.40
4(100MM),FX DRY VALVE,GE/GE,RED	6508047000	4FXFB	£6,317.99
6(150MM),FX DRY VALVE,GE/GE,RED	6508067000	6FXFB	£6,998.39
165MM,FX DRY VALVE,GE/GE,RED	6508057000	165MMFXFB	£6,998.39
MODEL FX FULLY ASSEMBLED VALVE - FLANGE/GROOVED WITH BASIC TRIM			
4(100MM),FX DRY VALVE,FL/GE,PN16,RED	650804A000	4FXPN16GFB	£6,317.99
4(100MM),FX DRY VALVE,FL/GE,RED	6508048000	4FXFGFB	£6,317.99
6(150MM),FX DRY VALVE,FL/GE,PN16,RED	650806A000	6FXPN16GFB	£6,998.39
6(150MM),FX DRY VALVE,FL/GE,RED	6508068000	6FXFGFB	£6,998.39
MODEL FX FULLY ASSEMBLED VALVE - FLANGE/FLANGE WITH BASIC TRIM			
4(100MM),FX DRY VALVE,FL/FL,PN16,RED	650804E000	4FXPN16FFB	£6,317.99
4(100MM),FX DRY VALVE,FL/FL,RED	650804B000	4FXFFB	£6,317.99
6(150MM),FX DRY VALVE,FL/FL,PN16,RED	650806E000	6FXPN16FFB	£6,998.39
6(150MM),FX DRY VALVE,FL/FL,RED	650806B000	6FXFFB	£6,998.39
MODEL FX FULLY ASSEMBLED VALVE - GROOVED/GROOVED W/CONTROL VALVE			
2(50MM),FX DRY VALVE,GE/GE,RED	6508027100	2FXFBV	£6,415.19
2 1/2(65MM),FX DRY VALVE,GE/GE,RED	6508017100	25FXFBV	£6,415.19
76MM,FX DRY VALVE,GE/GE,RED			£ Call
3(80MM),FX DRY VALVE,GE/GE,RED	6508037100	3FXFBV	£6,415.19
4(100MM),FX DRY VALVE,GE/GE,RED	6508047100	4FXFBV	£6,803.99
6(150MM),FX DRY VALVE,GE/GE,RED	6508067100	6FXFBV	£7,775.99
165MM,FX DRY VALVE,GE/GE,RED	6508057100	165MMFXFBV	£7,775.99

Features

- Lightweight ductile iron body with compact trim
- External reset reduces setup and commissioning time
- Does not require priming water
- Available fully assembled, with or without control valve