

US MADE CI FLANGED FITTINGS



Description	Part Number	List Price	
FLANGED 90° ELBOW			
1-1/2"	7A61060600	S\$	1,565.83
2"	7A69080800	S\$	902.94
2-1/2"	7A61101000	S\$	976.70
3"	7A61121200	S\$	815.22
4"	7A61161600	S\$	1,008.18
6"	7A61242400	S\$	1,578.53
8"	7A61323200	S\$	2,725.69
10"	7A61404000	S\$	5,973.83
12"	7A61484800	S\$	12,025.66
FLANGED 45° ELBOW			
1-1/2"		S\$	Call
2"	7A63080800	S\$	1,308.34
2-1/2"	7A63101000	S\$	1,395.48
3"	7A63121200	S\$	1,357.03
4"	7A63161600	S\$	1,527.41
6"	7A63242400	S\$	2,497.08
8"	7A63323200	S\$	3,651.55
10"	7A63404000	S\$	7,715.90
12"	7A63484800	S\$	11,789.85
FLANGED REDUCING 90°			
2-1/2 x 2"	7A61100800	S\$	3,037.25
3 x 2-1/2"	7A61121000	S\$	3,020.24
3 x 2"	7A61120800	S\$	2,768.60
4 x 3"	7A61161200	S\$	2,236.62
4 x 2-1/2"	7A61161000	S\$	3,418.42
6 x 4"	7A61241600	S\$	2,773.63
6 x 3"	7A61241200	S\$	4,926.31
8 x 6"	7A63322400	S\$	4,046.79
8 x 4"	7A61321600	S\$	5,457.10
10 x 8"	7A61403200	S\$	7,705.33
12 x 10"	7A61484000	S\$	14,765.80
12 x 8"	7A61483200	S\$	19,512.46

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

US MADE CI FLANGED FITTINGS



Description	Part Number	List Price
FLANGED TEE		
1-1/2"	7A69060606	S\$ 1,800.27
2"	7A69080808	S\$ 988.65
2-1/2"	7A69101010	S\$ 1,439.96
3"	7A69121212	S\$ 1,009.17
4"	7A69161616	S\$ 1,535.10
6"	7A69242424	S\$ 2,227.69
8"	7A69323232	S\$ 3,805.91
10"	7A69404040	S\$ 10,240.70
12"	7A69484848	S\$ 16,087.08
FLANGED REDUCING TEE		
3 x 3 x 2"	7A69121208	S\$ 2,345.07
4 x 4 x 3"	7A69161612	S\$ 3,159.69
4 x 4 x 2"	7A69161608	S\$ 3,159.69
6 x 6 x 4"	7A69242416	S\$ 3,041.79
6 x 6 x 3"	7A69242412	S\$ 4,425.01
6 x 6 x 2-1/2"	7A69242410	S\$ 5,920.56
6 x 6 x 2"	7A69242408	S\$ 6,216.66
8 x 8 x 6"	7A69323224	S\$ 4,751.79
8 x 8 x 4"	7A69323216	S\$ 5,709.97
10 x 10 x 8"	7A69404032	S\$ 10,862.50
10 x 10 x 6"	7A69404024	S\$ 12,632.91
12 x 12 x 8"	7A69484832	S\$ 19,073.22
12 x 12 x 6"	7A69484824	S\$ 16,119.91

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

US MADE CI FLANGED FITTINGS



Description	Part Number	List Price
FLANGED CONCENTRIC REDUCER		
2 x 1-1/2"	7A47080600	S\$ 3,000.46
2-1/2 x 2"	7A47100800	S\$ 2,278.90
2-1/2 x 1-1/2"	7A47100600	S\$ 3,000.46
3 x 2-1/2"	7A47121000	S\$ 1,809.15
3 x 2"	7A47120800	S\$ 1,809.15
4 x 3"	7A47161200	S\$ 2,032.73
4 x 2-1/2"	7A47161000	S\$ 2,186.53
4 x 2"	7A47160800	S\$ 2,416.63
6 x 4"	7A47241600	S\$ 2,722.25
6 x 3"	7A47241200	S\$ 3,133.79
6 x 2-1/2"	7A47241000	S\$ 4,134.35
6 x 2"	7A47240800	S\$ 5,466.43
8 x 6"	7A47322400	S\$ 3,426.07
8 x 4"	7A47321600	S\$ 3,946.70
10 x 8"	7A47403200	S\$ 7,065.60
10 x 6"	7A47402400	S\$ 7,695.74
12 x 10"	7A47484000	S\$ 12,187.05
12 x 8"	7A47483200	S\$ 13,470.11
FLANGED ECCENTRIC REDUCER		
3 x 2-1/2"	7A57121000	S\$ 2,768.60
3 x 2"	7A57120800	S\$ 2,729.08
4 x 3"	7A57161200	S\$ 3,299.27
4 x 2-1/2"	7A57161000	S\$ 3,839.73
4 x 2"	7A57160800	S\$ 3,812.36
6 x 4"	7A57241600	S\$ 3,116.28
6 x 3"	7A57241200	S\$ 5,201.70
8 x 6"	7A57322400	S\$ 3,947.49
8 x 4"	7A57321600	S\$ 5,353.17
10 x 8"	7A57403200	S\$ 10,055.25
10 x 6"	7A57402400	S\$ 11,793.92

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

US MADE CI FLANGED FITTINGS



Description	Part Number	List Price
COMPANION FLANGE		
3/4 x 3-7/8"	7A47031600	S\$ 207.17
1 x 4-1/4"	7A47041600	S\$ 131.73
1-1/4 x 4-5/8"	7A47051600	S\$ 157.62
1-1/2 x 5"	7A47062000	S\$ 145.66
2 x 6"	7A47082400	S\$ 145.37
2-1/2 x 7"	7A47102800	S\$ 170.07
3 x 7-1/2"	7A47123000	S\$ 219.07
4 x 9"	7A47163600	S\$ 295.23
6 x 11"	7A47244400	S\$ 471.84
8 x 13-1/2"	7A47325400	S\$ 744.82
10 x 16"	7A47406400	S\$ 1,320.01
12 x 19"	7A47406900	S\$ 2,987.34
REDUCING FLANGE		
2 x 7"	7A51082800	S\$ 284.75
2 x 7-1/2"	7A51083000	S\$ 379.65
2-1/2 x 7-1/2"	7A51103000	S\$ 407.41
3 x 8-1/2"	7A51123200	S\$ 740.11
2 x 9"	7A51083600	S\$ 516.01
2-1/2 x 9"	7A51103600	S\$ 553.68
3 x 9"	7A51123600	S\$ 516.01
3 x 10"	7A51124000	S\$ 953.83
4 x 10"	7A51164000	S\$ 798.46
2 x 11"	7A51084400	S\$ 943.66
2-1/2 x 11"	7A51104400	S\$ 1,121.18
3 x 11"	7A51124400	S\$ 943.66
4 x 11"	7A51164400	S\$ 778.22
2 x 13-1/2"	7A51085400	S\$ 1,729.59
3 x 13-1/2"	7A51125400	S\$ 1,729.59
4 x 13-1/2"	7A51165400	S\$ 1,332.06
6 x 13-1/2"	7A51245400	S\$ 1,207.51
6 x 16"	7A51246400	S\$ 3,603.00
8 x 16"	7A51326400	S\$ 3,413.24
6 x 19"	7A51246900	S\$ 3,915.31
8 x 19"	7A51346900	S\$ 4,190.66

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.