

SPRINKLERS**Standard Spray QR - Quick Response**

- S-1 F1FR - Upright
- S-5 F1FR-300 - Upright
- S-6 F1FR - Pendent, Recessed
- S-10 F1FR-300 - Pendent, Recessed
- S-11 F1FR - Horizontal Sidewall
- S-13 F1FR56-300 - HSW, Rec HSW and SWC56 Concealed
- S-14 F1FR - Vertical Sidewall
- S-15 F1FR - Conventional
- S-17 F1FR-SS Stainless Steel - Upright and Pendent
- S-18 F1FR LL - Pendent and CCP
- S-19 F1FR - FS LO Large Orifice
- S-20 F1FR-FS56 & F1FR-FS42 FLAT SPRAY
- S-21 KFR56 - Upright and Pendent
- S-22 KFR56-300 - Upright & Pendent
- S-23 KFR56-300 - HSW and CCP
- S-24 KFR56 HSW and CCP
- S-25 KFR80 Upright and Pendent
- S-26 GFR Upright
- S-27 GFR - Pendent & HSW
- S-28 G5-80, G5-56, G5-42 & G5-28
- S-29 G6-56 HSW QR
- S-30 G5-80, G5-56, G5-42 and G5-28 QR "Sealing" Concealed
- S-31 G5-56 300 QR "Sealing" Concealed
- S-32 G5-56 300 Concealer
- S-33 F1FR CCP and F1FR-300 CCP
- S-34 XL Commercial - Pendent and HSW

Standard Spray SR - Standard Response

- S-35 F1 - Upright
- S-39 F1-SS Stainless Steel - Upright & Pendent
- S-40 F1-300 - Upright
- S-41 F1 - Pendent, Recessed
- S-44 F1-300 - Pendent, Recessed
- S-45 F1 - Conventional
- S-47 F1 - Horizontal Sidewall
- S-48 F1 - Vertical Sidewall
- S-49 G - Upright
- S-51 G - Pendent
- S-53 G - Conventional
- S-53 G - Vertical Sidewall
- S-54 G - Horizontal Sidewall, Recessed
- S-56 G - Recessed
- S-58 G4
- S-59 G4-300 - Concealed
- S-61 G5-80, G5-56, G5-42 and G5-28 SR "Sealing" Concealed
- S-62 G5-56 300 SR "Sealing" Concealed

Extended Coverage

- S-63 G6-80 HSW QR EC
- S-64 JL112 and J112 - Upright, Pendent and Rec Pendent
- S-65 F1FR56 QREC and F1FR EC - Pendent, Recessed
- S-66 F1FR 56-300 and F1FR-300 QREC - Pendent, Recessed
- S-67 F1FR 56-300 and F1FR-300 QREC EC9 - HSW, Recessed
- S-68 F1FR 56 EC8 and F1FR QREC EC9 - HSW, Recessed
- S-69 F1FR 56-300 and F1FR-300 QREC CCP - Concealed
- S-70 DH56 - HSW, HSW Recessed, HSW Concealed
- S-71 DH80 - HSW, HSW Recessed, HSW Concealed
- S-72 G4 XLO-QR ECLH/ECOH
- S-72 KFR-CCS Combustible Concealed Space
- S-73 SWC Concealed Sidewall

- S-74 F1 56 SREC and F1 EC - Pendent
- S-75 F1 56-300 SREC and F1-300 EC - Pendent, Recessed
- S-76 G - EC4 - HSW
- S-76 GFR VELO ECOH - Upright
- S-76 GFR VELO ECOH - Pendent, Recessed
- S-77 MBEC-14- HSW

Residential

- S-78 F1RES 30, KRES 30 - Pendent, Rec Pendent, CCP
- S-79 F1RES 49 & KRES49 - Pendent, Rec Pendent, CCP
- S-80 F1RES 44, KRES 44- HSW, REC HSW, SWC44
- S-81 F1RES 58, KRES 58 - Pendent, Rec Pendent, CCP, HSW
- S-82 F1RES 58 HSWX & KRES 58 HSWX
- S-83 F1RES 76 - Pendent, Rec Pendent, CCP
- S-84 RFC43 Flat Concealed
- S-84 RFC30 Flat Concealed
- S-84 RFC49 Flat Concealed
- S-84 RFC58 Flat Concealed
- S-84 RFC76 Flat Concealed
- S-85 RFC49plus Flat Concealed
- S-86 RFS42 Flat Plate Concealed HSW
- S-87 F3RES44 Dry HSW
- S-88 F3RES44 Dry Recessed HSW/F2
- S-89 F3RES44 Dry HSW/HB
- S-90 F1RES 30 LL - Pendent, Rec Pendent, CCP
- S-91 F1RES 49 LL - Pendent, Rec Pendent, CCP
- S-92 F1RES 44 LL - HSW, Rec HSW, SWC
- S-93 F1RES 58 LL - Pendent, Rec Pendent, CCP, HSW
- S-94 RFC30 LL Flat Concealed
- S-94 RFC43 LL Flat Concealed
- S-94 RFC49 LL Flat Concealed

Storage

- S-95 JL14 ESFR
- S-95 JL17 ESFR
- S-97 P22 ESFR
- S-97 P25 ESFR
- S-98 N28 ESFR
- S-99 GXLO Upright and Pendent
- S-99 GXLO Intermediate
- S-100 J168 - Upright
- S-100 N252 EC - Pendent and Recessed Pendent
- S-100 LB11 HSW
- S-101 GL112 Upright and Pendent
- S-101 G VELO Pendent
- S-102 F1FR 56 & F1FR Intermediate - Upright and Pendent
- S-103 F1 56 & F1 Intermediate - Upright and Pendent
- S-104 KFR56 Intermediate - Upright and Pendent
- S-105 Intermediate Level Sprinkler with D-3 and D-5 Guard Assembly
- S-107 GFR Intermediate - Upright and Pendent
- S-108 G Intermediate Level - with D-3 and D-5 Guards/Shields
- S-111 D-1 - Int. Level Sprinkler and Guard Assembly

Special

- S-113 Attic Sprinklers
- S-114 LT56 Series Pendent
- S-115 LT56 Series CCP
- S-116 LT56C Flat Concealed
- S-117 XL INST - Institutional
- S-118 F4FR-NF
- S-118 KFR CCS Combustible Concealed
- S-119 WP56 & WP56L Window Sprinklers
- S-120 F1S5-FLAT SPARY

Dry

- S-124 F3QR56-Upright
- S-125 F3QR56 - Pendent
- S-127 F3QR56 - Pendent / HB
- S-129 F3QR56 - Recessed Pendent /FP
- S-131 F3QR56 - Recessed Pendent / F1
- S-133 F3QR56 - Horizontal Sidewall
- S-135 F3QR56 - Horizontal Sidewall / HB
- S-137 F3QR56 - Recessed Horizontal Sidewall / FP
- S-139 F3QR56 - Recessed Horizontal Sidewall / F1
- S-141 F3QR56 - Concealed
- S-143 F3QR80 - Pendent
- S-144 F3QR80 - Pendent / HB
- S-145 F3QR80 - Recessed Pendent / FP
- S-146 F3QR80 - Horizontal Sidewall
- S-147 F3QR80 - Horizontal Sidewall / HB
- S-148 F3QR80 - Horizontal Sidewall / FP
- S-149 F3QR80 - Concealed
- S-150 G5-56 Dry
- S-151 DH56 Dry - Horizontal Sidewall
- S-152 DH56 Dry - Horizontal Sidewall / HB
- S-153 DH56 Dry - Recessed Horizontal Sidewall
- S-154 DH56 Dry - Concealed
- S-155 DH80 Dry - Horizontal Sidewall
- S-156 DH80 Dry - Horizontal Sidewall / HB
- S-157 DH80 Dry - Recessed Horizontal Sidewall
- S-158 DH80 Dry - Concealed
- S-159 F3-56 Upright
- S-160 F3-56 - Pendent
- S-162 F3-56 - Pendent / HB
- S-164 F3-56 - Recessed Pendent / FP
- S-166 F3-56 - Recessed Pendent / F1
- S-168 F3-56 - Horizontal Sidewall
- S-170 F3-56 - Horizontal Sidewall / HB
- S-172 F3-56 - Recessed Horizontal Sidewall / FP
- S-174 F3-56 - Recessed Horizontal Sidewall / F1
- S-176 F3-56 - Concealed
- S-178 F3-80 - Pendent
- S-179 F3-80 - Pendent / HB
- S-180 F3-80 - Recessed Pendent / FP
- S-181 F3-80 - Horizontal Sidewall
- S-182 F3-80 - Horizontal Sidewall / HB
- S-183 F3-80 - Horizontal Sidewall / FP
- S-184 F3-80 - Concealed

Nozzles

- S-185 TNL280 Pendent Spray Nozzle
- S-186 B & FM - Spray Nozzles - Window & Cornice Types
- S-187 F1-FTR - Pilot Line Detector (PLD)
- S-187 HV - High Velocity Nozzles

Multipurpose Residential Risers and Accessories

- S-192 Accessories - Cabinets & Escutcheons
- S-194 Accessories - Multipurpose LL Residential Riser
- S-194 Accessories - Gauges, Connections, Drips, Misc.

Special Application

- S-196 F1S5 - Upright / Pendent (for UK use only)

Accessories**Escutcheons**

- S-197 FP Push-On / Thread Off Escutcheons
- S-197 G/F1 Escutcheon and Collar Assembly

- S-197 G/F1 Escutcheon Only
- S-197 G/F1 Collar Only
- S-197 G/F1 and G/F2 Escutcheon Extender Ring
- S-197 G/F2 Escutcheon & Collar Assembly
- S-197 G/F2 Escutcheon Only
- S-197 G/F2 Collar Only
- S-198 B, C & HB Two Sprinkler Escutcheons
- S-198 Sure-Off Tester

Spk Guards/Emergency Cabinets

- S-199 Sprinkler Guards & Shields
- S-199 Emergency Cabinets
- S-201 For Sprinklers or Seat / Valve Wrenches

Printed Coverplates

- S-202 Models G6, G5, RFS42

Replacement Coverplates

- S-203 G1 Concealed Replacement Coverplates

Special Services

- S-204 Special Services / Special Finishes

VALVES**Valve Stations**

- V-1 Alarm Valve Stations & Wet Alarm Valves
- V-2 FM Wet Alarm Valve & VdS Alarm Valve Stations
- V-2 VdS DDX-Dry LP Valve Stations & Trim Kits

Alarm And Check Valves

- V-3 E and E3 Alarm Valves - FxF, FxG, GxG
- V-4 E3 - Trim Segmented & Loose
- V-4 LPC - Valve Sets
- V-6 Miscellaneous Alarm Valve Trim
- V-6 Retard Chamber and Mechanical Spk. Alarm Valve Seat Wrenches
- V-6 G - Riser Check - 2½", 3", 4", 6"
- V-6 G - Grooved Check - 2½", 3", 4", 6"
- V-6 CVE - Swing Check - 4", 6", 165mm, 8"

Deluge Valves

- V-7 DDV Deluge Valves - Electric Trim
- V-8 DDV Deluge Valves - Wet Pilot Line Trim
- V-9 DDV Deluge Valves - Dry Pilot Line Trim
- V-10 DDV Deluge Valves-Remote Reset
- V-11 DDV Deluge Valves-Remote Reset Pressure Regulating
- V-12 DDV Deluge Valves-Dry Pilot Pressure Regulating
- V-13 DDV Drain Trims & Accessories
- V-14 DDX Deluge Valves & Trim
- V-14 DDX Deluge Valves-Electric,Wet Pilot, Dry Pilot-Fully Assembled

Pressure Control Valves

- V-15 PRV Diaphragm Pressure Regulating Valves

Low Pressure Dry Systems

- V-16 DDX-LP Dry Pipe Valve Systems
- V-17 DDX-LP Dry Pipe/DDX Valve Systems-VDS

Dry Pipe Valves

- V-18 A, D - 2 1/2", 4", 6"
- V-18 A, D - Loose/Preassembled Trim, Factory Trimmed
- V-19 FX- 2", 2 1/2", 3" 4", 6" Valve and Trim
- V-21 FX- 2", 2 1/2", 3" 4", 6" Fully Assembled

Control Valves

- V-22 PIV, OSY Gate Valves & Bronze Butterfly Valves
- V-24 Supervised Butterfly Valves

Accessories

- V-25 ACD Dry Systems Auxiliary
- V-25 B-1 – Accelerator, A-2 Air Maintenance Device, B-1 Air Maintenance Device
- V-26 Electronic Accelerators
- V-27 Test and Drain, Pressure Relief Valves, AAV Auto Air Vent
- V-28 Air Compressors
- V-31 Pressure Gauges
- V-31 Inspectors Test Connections
- V-31 Automatic Ball Drips
- V-31 Mechanical Ball Drips
- V-31 Strainers (Misc. Items)
- V-31 Sprinkler/Valve System Signs
- V-32 Residential Riser
- V-33 CR Commercial Riser
- V-35 FCA Floor Control Valves
- V-35 Steamline Drain Hoses
- V-35 HV Hose Valves

SPECIAL HAZARDS/SPECIAL SYSTEMS**Model H Deluge, Preaction, PrePak 1 1/2"**

- SS-1 Model H Deluge / Riser Assemblies and Trim

Single, Double, Interlock

- SS-2 DDX Single Interlock - Fully Assembled
- SS-4 DDX Double Interlock - Fully Assembled
- SS-5 DDX Preaction Trim

PrePaK

- SS-7 DDX Type D PrePaK
- SS-8 DDX Type F PrePaK
- SS-9 DDX Electric Release PrePaK
- SS-10 DDX Wet Pilot PrePaK
- SS-11 DDX Dry Pilot PrePaK
- SS-12 DDX-LP PrePaK System
- SS-13 DDX N2 Blast PrePaK Systems

Accessories

- SS-14 Accelerator
- SS-14 Pull Boxes
- SS-14 RPC 4410 RC Control Panel
- SS-14 System Modules / Batteries
- SS-15 Drain Assemblies, Dry Pilot Actuator
- SS-16 Electric Alarm Bells, Supervisory Air Supply, Valve Seat Wrenches
- SS-16 LPC Components
- Protectowire

SYSTEM COMPONENTS**Grooved Couplings And Fittings - Europe**

- SC-1 Rigid Couplings
- SC-2 Flexible Couplings
- SC-3 Reducing Couplings
- SC-4 Flange Adaptors
- SC-5 Standard 90° Elbows
- SC-6 Standard 45° Elbows
- SC-7 Standard Tees
- SC-8 Short Radius 90° Elbows & Straight Tees
- SC-9 Grooved Reducing Tees
- SC-10 Concentric Reducers
- SC-12 Universal Flange Adaptors
- SC-13 Caps
- SC-14 Threaded Mechanical Tees
- SC-15 Grooved Mechanical Tees
- SC-16 Ubolt Mechanical Tees & Pitcher Tees
- SC-18 Threaded & Grooved Mechanical Cross

Grooved Couplings And Fittings - Middle East/Australia

- SC-18 Rigid & Flex Couplings
- SC-19 Flexible Couplings
- SC-20 Reducing Couplings
- SC-22 Flange Adaptors & Flange Adaptors Nipples
- SC-23 Elbows
- SC-24 Elbows, Tees, & End Caps
- SC-25 End Caps with Holes, Reducing & Drain Elbows
- SC-26 Concentric Reducers
- SC-28 Straight Crosses
- SC-29 Reducing Tees
- SC-31 Eccentric Reducers
- SC-32 Mechanical Tees
- SC-34 U-Bolt Mechanical Tees
- SC-35 Rigid & Flexible Couplings
- SC-36 Flexiible & Reducing Couplings, Flange Adaptors
- SC-37 Flange Adaptors - Galvanized
- SC-38 Elbows
- SC-39 Elbows, Tees, Radius & End Caps
- SC-40 End Caps with Holes, Reducing & Drain Elbows
- SC-41 Concentric Reducers
- SC-43 Crosses
- SC-44 Reducing Tees
- SC-46 Eccentric Elbows
- SC-47 Mechanical Grooved Tees
- SC-48 Threaded Tees
- SC-49 U-Bolt Mechanical Tees

US Made Cast Iron Fittings

- SC-50 90° and 45° Elbows, Reduc. 90° Elbows, Reduc. Couplings, Standard Tees
- SC-52 Reducing Tees
- SC-53 Bullhead Tees, Crosses, Plugs, Caps (malleable), Couplings (malleable), Unions (malleable)
- SC-54 Hex Bushings, Companion Flanges, Pipe Dope, Teflon Tape, Cutting Oil
- SC-55 90° Elbows, Reducing 90° Elbows, 45° Elbows Reducing Couplings, Standard Tees
- SC-56 Reducing Tees, Couplings, Caps, Unions
- SC-58 Reducing Tees
- SC-58 Bullhead Tees, Crosses (Standard & Reduc.) Plugs, Pipe Dope, Teflon Tape

Cast Iron & Ductile Fittings - Foreign Anvil

- SC-58 90° and 45° Elbows, Reduc. 90° Elbows, Reduc. Couplings, Standard Tees
- SC-62 Bullhead Tees, Crosses, Caps, Couplings Pipe Dope, Teflon Tape, Cutting Oil

US Made Flanged Fittings

- SC-65 Flanged Elbows, Reducing
- SC-66 Flange Tees
- SC-67 Flanged Reducers
- SC-68 Companion, Reducing Flange

Expansion Loops

- SC-69 Threaded & Grooved Models

CPVC Pipe, Fittings, & Hangers

- SC-71 Pipe, Anti-Freeze
- SC-72 Hangers (Single, Double, Sidemount, Stand-Off)
- SC-73 Sealant, Caulk
- SC-74 Elbows, Head Adapters, Standard Tees, Tees (Reduc. and Run Reduc.), Tee Head
- SC-75 Adapters Tee Head Adapters (cont'd), Bushings,
- SC-77 Head Adapters, Adapters, Couplings, Reduc. Couplings
- SC-78 Grooved Adapters, Caps, Crosses, Cement, Thread Sealant
- SC-79 Torque Safe Fittings

Tee-lets

- SC-80 Tee-lets
- SC-82 Grooved Shape Nipples - Sch 40
- SC-83 Grooved Shape Nipples - Sch 10
- SC-84 Import Olets
- SC-85 Welded Outlets

Hangers

- SC-86 Ring Hangers, Beam Clamps, Riser Clamps, Wall Plates
- SC-87 Earthquake Bracing
- SC-88 Eye Sockets, All Thread Rod, Hex Nuts, Washers, Drop Anchors

Super Screws

- SC-89 Sammy Super Screws

Fire Department Equipment

- SC-91 Fire Department Connections, Hose Valves, Accessories

Nipples

- SC-93 Adjustable Wet Drop Nipples (M x F, M x M)
- SC-94 Steel Nipples, Blck & Galvanized

Valves

- SC-99 Riser Check, Grooved Check, Swing Check, Flanged Check, Gasket Kits
- SC-101 OS&Y, PIV, Butterfly Valves (GxG and Wafer)
- SC-102 Reliable PIV, OSY Gate & Bronze Butterfly Valves
- SC-104 Butterball Valves (Threaded and Grooved)
- SC-105 Foreign Trim Valves - Globe, Ck, 3-way Angle
- SC-106 Valves, FDC, and Accessories
- SC-109 Air Release Valves & 50GG Check Valves
- SC-111 US Made Trim Valves - Globe, Ck, 3-way, Angle
- SC-113 Detector Check, In-Building Riser, Wafer Check, Test & Drains

Backflows

- SC-115 2000ss, 2001ss, 3000ss, 30001ss
- SC-116 4000ss, 4001ss, 5000ss, 5001ss
- SC-117 Colt Series: C-200 OS&Y, C-200 BFV, C-300 OS&Y, C-300 BFV
- SC-118 Colt Series: C-400 OS&Y, C-400 N or Z, C-500 OS&Y, C-500 N or Z
- SC-119 Maxim Series: M-200 OS&Y, M-200 BFV, M-300 OS&Y, M-300 BFV

- SC-120 Maxim Series: M-400 OS&Y, M-400 N or Z, M-500 OS&Y, M-500 N or Z
- SC-121 Deringer
- SC-123 OS & Y

Air Compressors

- SC-128 Bare, with Check, Tank Mounted

Electrical Equipment

- SC-134 Waterflow Detector, Tamper Switches, Electric Bells, Accessories
- SC-135 Canadian versions
- SC-136 System Sensor - Europe
- SC-137 System Sensor - Far East/Australia
- SC-138 System Sensor - Middle East

Flexible Drops

- SC-139 Flexible Drops

Residential Fire Pumps & Accessories

- SC-140 Residential Fire Pumps, Tanks, Kits

Steel Pipe

- SC-141 Schedule 40 & 10, Flowpipe, Threadable Lightwall, and Special Requests

Expansion Tanks

- SC-142 Expansion Tanks

VALVE SERVICE KITS

- RK1 Model A Dry Pipe Valve
- RK1 Model D Dry Pipe Valve
- RK1 DDX Valve With Stainless Steel Clapper
- RK1 Early Gen DDX Valves with Brass Clapper
- RK1 Model EX Dry Pipe Valve
- RK1 Model FX Dry Pipe Valve
- RK1 Model E3 (Small) Alarm Valve
- RK1 Model E (Large) Alarm Valve / CVE Check Valve

REPLACEMENT PARTS**Valve Spares Kits**

- RP-1 Wet Alarm Valve Spares Kits
- RP-1 Dry Alarm Valve Spares Kits
- RP-2 Deluge Valve Spares Kits

Alarm Valves

- RP-3 Alarm Valves & Trimmings

Dry Pipe Valves

- RP-8 Dry Pipe Valves and Trimmings
- RP-11 Accelerator

Deluge Valves

- RP-12 Deluge Valves and Trimmings
- RP-19 External Reset Device
- RP-19 Air Maintenance Devices

Miscellaneous

- RP-20 Sight Test Connection
- RP-21 Sight Drain, Emergency Pull Box, Copper Tubing, Parts for Model B Air Compressor Panel
- RP-22 Air Compressor