

# EX Low Pressure Dry Pipe Valve



**Another Reliable  
Product Solution**

- Lightweight, low friction loss
- Low air pressure 8 to 28 psi (0.6 to 1.9 bar) reduces size of air compressor or quantity of nitrogen
- Optional: air pressure up to 40 psi (2.8 bar)
- Convenient and safe external reset; no priming water required
- Latching type valve is less susceptible to false trips caused by pressure surges
- Grooved/Grooved, Grooved/Flange, Flange/Flange with pressure rating of 250 psi (17.2 bar) or 300 psi (20.7 bar) for 4", 6", and 165mm only
- Available Sizes: 2" (50mm), 2-1/2" (65mm), 76mm, 3" (80mm), 4" (100mm), 165mm, 6" (150mm) & 8" (200mm)
- cULus Listed and FM Approved, Bulletins 358 & 359