

Product Solutions

Stainless Steel Clad Cover Plates



SS Clad Cover Plate
w/SR Gasket



SS Clad Cover Plate



SS Clad Cover Plate
w/QR Gasket

Stainless steel (316) clad cover plates are now available for:

Standard Coverage G5-28; G5-42, G5-56; G5-56 300; G5-80; G4; G4 300; G4A Adjustable

Standard Coverage with Quick-response Gasket G5-28; G5-42, G5-56; G5-56 300; G5-80


Standard Coverage with Standard-response Gasket G5-28; G5-42, G5-56; G5-56 300; G5-80

Extended Coverage G4XLO QR ECLH/ECOH

Residential RFC30; RFC43; RFC49; RFC56; RFC30LL; RFC43LL; RFC49LL

Dry Sprinkler with or without Gasket G5-56 Dry Pendant

Stainless steel clad cover plates are Type 316 Stainless Steel on the finished side and C102 Copper Alloy on the backside. Cover plates are not listed or approved as corrosion resistant.



*Corroded copper makes beautiful wall art,
but it doesn't look good on cover plates*

www.reliablesprinkler.com

Reliable