DDX VALVE TRIMS PART NUMBER CONFIGURATION

*SELECTIONS IN **BOLD** ARE STANDARD OPTIONS*

DDX VALVE SIZE AND ENDS CONNECTION TYPE
0 = NONE (NO VALVE, LOOSE AND SEGMENTED TRIM ONLY)[1]
1 = 2 ½" GE X GE
2 = 2" GE X GE
3 = 3" GE X GE
5 = 76 MM GE X GE[9]

TRIM FINISH[4]
0 = GALVANIZED
1 = BLACK PIPE
2 = BRASS
3 = STAINLESS STEEL
4 = GALV. (U.S. SOURCED)
5 = BLACK PIPE (U.S. SOURCED)
6 = BRASS (U.S. SOURCED)
7 = STAINLESS STEEL (U.S. SOURCED)

ASSEMBLY CONFIGURATION, VALVE COLOR & INSTALLED CONTROL VALVE OPTIONS
0 = LOOSE TRIM FOR 2"- 3" VALVES[1,3]
2 = SEGMENTALLY ASSEMBLED FOR 2"- 3" VALVES[1,3]
4 = FULLY ASSEM. TO BLACK DDX VALVE, W/O CONTROL VALVE
5 = FULLY ASSEM. TO RED DDX VALVE, W/O CONTROL VALVE
7 = FULLY ASSEM. TO RED CCCF APPROVED DDX VALVE, W/O CONTROL VALVE[5]
8 = FULLY ASSEM. TO BLACK DDX VALVE, WITH CONTROL VALVE[7]
9 = FULLY ASSEM. TO RED DDX VALVE, WITH CONTROL VALVE[7]
A = FULLY ASSEM. TO RED CCCF APPROVED DDX VALVE, WITH CONTROL VALVE[6,7]

6	5	2	2	8	0	8	0	1	0
1st	2nd	3rd	4th	5th	6th	7th	8th	9th	10th

SUB-ASSEMBLY, BASE TRIM
0 = SUB-ASSY, TRIM BASE, WITH MECHANICAL BALL DRIP
1 = SUB-ASSY, TRIM BASE, WITH SEMI-AUTOMATIC BALL DRIP, LPCB

SYSTEM PRESSURE SWITCH[8]
0 = NONE
1 = POTTER FM, cULusAPPROVED
2 = SYSTEM SENSOR FM/UL APPROVED
3 = SYSTEM SENSOR FM/ULC APPROVED
4 = POTTER, EXPOSION PROOF

NOTES:
1. FOR THE 4TH DIGIT, SELECT "0" FOR LOOSE OR SEGMENTED TRIMS. 7TH DIGIT MUST BE "0", OR "2". FOR ANY 4TH DIGIT SELECTION OTHER THAN "0", THE 7TH HAS TO BE A FULLY-ASSEMBLED SELECTION ("4", "5" ...ETC).
2. STANDARD FLANGE TYPE IS CLASS 150 PER ASME B16.5.
3. NO SOLENOID VALVE REQUIRED, THE 8TH DIGIT MUST BE "0".
4. GALVANIZED PIPE FITTINGS ARE THE DEFAULT OFFERING. ALL OTHERS TRIM FINISHES ARE MAKE TO ORDER (MTO).
5. FOR LOOSE AND SEGMENTED ASSEMBLED TRIM CONFIGURATIONS, THE DDX VALVE IS SOLD SEPARATELY (SEE BULLETIN 519 FOR DDX VALVE'S PART NUMBER).
6. CHINA COMPULSORY CERTIFICATE FOR FIRE PRODUCTS.
7. FLANGED VALVES ARE NOT AVAILABLE WITH A CONTROL VALVE (REFER TO DIGIT #7).
8. A SYSTEM PRESSURE SWITCH IS INCLUDED BY DEFAULT WITH THE FOLLOWING TRIMS: TYPE D DOUBLE INTERLOCK, TYPE F DOUBLE INTERLOCK, DRY PILOT SINGLE INTERLOCK, DOUBLE INTERLOCK TYPE PL SYSTEMS.
9. 76 MM AND 165 MM ARE NOT AVAILABLE WITH A CONTROL VALVE (REFER TO DIGIT #7).

REVISIONS			
LTR	DESCRIPTION	DATE	DRAWN BY
	SEE PAGE 1		

DDX. VALVE	VALVE PART NUMBER	DRAWING FILE NUMBER
2" DUCTILE IRON G/G BLACK	6103022000	6103030000
2" DUCTILE IRON G/G RED	6103022001	
2-½" DUCTILE IRON G/G BLACK	6103022500	
2-½" DUCTILE IRON G/G RED	6103022501	
3" DUCTILE IRON G/G BLACK	6103030000	
3" DUCTILE IRON G/G RED	6103030001	
76MM DUCTILE IRON G/G RED	6103027600	



MODEL DDX 2"- 3" DELUGE DRY PLOT

ASSEMBLY P/N 6520800010 REV. H

ITEM NO.	PART NO.	DESCRIPTION		QTY.
25	89141112	TIE, RETAINING	NOT SHOWN	9
24	6990006382	SWITCH, POTTER PRESSURE (PSI0-2)	(ULC, UL, FM)	1
	6990012997	SWITCH, POTTER PRESSURE (PSI0-EX)	(ULC, UL, FM)	
	6999992360	SWITCH, PRESSURE (EPSAI0-2)	(ULC)	
	6999991212	SWITCH, PRESSURE (EPSI0-2)	(UL/FM)	
23	96686756	TUBING, PVC, 3/8" I.D. x 6 FT.		1
22	95516915	PERMA-LOK	NOT SHOWN	A/R
21	77000263	SUB-ASSY, TRIM BASE, WITH MECHANICAL BALL DRIP	SEE P/N CONFIG.	1
	77000264	SUB-ASSY, TRIM BASE, WITH SEMI-AUTOMATIC BALL DRIP, LPCB		
20	98604406	PIPE, PLUG, IRON, SQUARE HEAD, 1/2		1
19	98840228	VALVE, RELIEF, 1/2", 50 PSI		1
18	98840237	VALVE, BALL, 1/4" NPTF x 1/4" NPTM		1
17	98614401	PIPE, PLUG, IRON, SQUARE HEAD, 3/4		1
16	99080002	PAD-ADHESIVE, VALVE NAME PLATES		1
15	98543226	NIPPLE,1/4X1-1/2,GALVANIZED STEEL		1
14	98543210	NIPPLE,1/2X2-1/2,GALVANIZED STEEL		1
13	98543223	NIPPLE,1/2X1-1/2,GALVANIZED STEEL		2
12	94616915	NAMEPLATE, DELUGE VALVE		1
11	71030010	MODEL LP PILOT LINE ACTUATOR		1
10	91004299	MANIFOLD, DRAIN, BARBED, 6-3/16		1
9	98248000	GAUGE, AIR PRESSURE (0-80 PSI)		1
8	98751003	FITTING, MULTIPORT, 1/2x1/2x1/2x1/2x1/2x1/4		1
7	98174404	ELBOW, 1/4", MALL IRON, GALV.		1
6	98174401	ELBOW, 1/2", MALL IRON, GALV.		1
5	92056704	CONNECTOR, ELBOW, 3/8" ID TUBE x 1/2" NPT		1
4	95306255	CLAMP, HOSE, 1/2" CONSTANT TENSION, ZINC		8
3	77000303	SUBASSEMBLY, CONTROL VALVE, 3"	FULLY ASSEMBLED WITH CONTROL VALVE ONLY	1
	77000302	SUBASSEMBLY, CONTROL VALVE, 2-1/2"		
	77000301	SUBASSEMBLY, CONTROL VALVE, 2"		
2	6990003756	SWITCH, PRESSURE (PS40-EX)	(ULC, UL, FM)	1
	6990019313	SWITCH, PRESSURE (PS25-2)	(ULC, UL, FM)	
	699999236I	SWITCH, PRESSURE (EPSA40-2)	(ULC)	
	6999991340	SWITCH, PRESSURE (EPS40-2)	(UL/FM)	
1	SEE DDX VALVE P/N TABLE			1

BILL OF MATERIALS

THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO THE RELIABLE AUTOMATIC SPRINKLER CO. IT MAY NOT BE REPRODUCED NOR MAY ANY INFORMATION HEREON BE DISCLOSED TO OTHERS WITHOUT THE SPECIFIC WRITTEN PERMISSION OF RELIABLE.

DO NOT SCALE DRAWING. REMOVE BURRS, BREAK SHARP EDGES

TOLERANCE UNLESS OTHERWISE SPECIFIED

ANGLE ± 1/2°
MACH. FINISH 63

FRACT. ± 1/32 [0.79]
DEC. XX ± .010 [0.25]
DEC. XXX ± .005 [0.13]

8540-4

THE RELIABLE AUTOMATIC SPRINKLER CO., INC.
LIBERTY, S.C.

PART NO: VARIOUS — DWG.SIZE: C

PART: ASSEMBLY, TRIM, DRY PILOT

PRODUCT: DDX, 2", 2 1/2", 3" — (B)

FILE NO: 6520800010 — ENG: JT — DRW BY: PH — SCALE: 1:6 — DATE: 12/06/17 — SHEET 2 of 3

REVISIONS			
LTR	DESCRIPTION	DATE	DRAWN BY
	SEE PAGE 1		

MODEL DDX 2"-3" BASIC TRIMS

SUBASSEMBLY P/N 77000263 REV. J



ITEM NO.	PART NO.	DESCRIPTION	REMARKS	QTY.
39	95516915	THREAD, SEALANT	NOT SHOWN	A/R
38	SEE P/N TABLE	ASSEMBLY, BALL DRIP, 1/2"		1
37	98840111A	VALVE, BALL, 1/2 NPTF X 1/2 NPTM		1
36	98840237	VALVE, BALL, 1/4" NPTF x 1/4" NPTM		3
35	98840188	VALVE, CHECK, 1/4" NPTM x 1/4" NPTF		1
34	98840147	CHECK VALVE, 1/4, NPT, POPPET TYPE INLINE		1
33	98840246	VALVE, SWING CHECK, F-F, 1 NPT, TIEMME		1
32	98840106	VALVE, ANGLE, 1 1/4		1
31	98840103	VALVE, ANGLE, 1/2"		1
30	98815201	UNION, 1/4, IRON, G.J., GALV.		1
29	98815200	UNION, 1/2, IRON, G.J., GALV.		2
28	98761651	TEE,1/2X1/2X1/2,GALVANIZED		1
27	98761649	TEE,1/2X1/4X1/2,GALVANIZED		1
26	98751005	FITTING, MULTIPORT, 3/4x1/2x1/2x1/2x1/2		1
25	98727617	STRAINER, 1/4 NPT		1
24	98614403	PIPE, PLUG, IRON, SQUARE HEAD, 1/4		1
23	98614401	PIPE, PLUG, IRON, SQUARE HEAD, 3/4		1
22	98604406	PIPE, PLUG, IRON, SQUARE HEAD, 1/2		1
21	98543285	NIPPLE,1-1/4XCLOSE,GALVANIZED STEEL		1
20	98543284	NIPPLE,1-1/4X5,GALVANIZED STEEL		1
19	98543244	NIPPLE,1/4X2,GALVANIZED STEEL		1
18	98543226	NIPPLE,1/4X1-1/2,GALVANIZED STEEL		1
17	98543224	NIPPLE,1/4X4-1/2,GALVANIZED STEEL		1
16	98543223	NIPPLE,1/2X1-1/2,GALVANIZED STEEL		8
15	98543209	NIPPLE,1/2X2,GALVANIZED STEEL		3
14	98248001	GAUGE, WATER PRESSURE (0-300 PSI)		2
13	98174414	ELBOW, 1-1/4", MALL IRON, GALV.		1
12	98174404	ELBOW, 1/4", MALL IRON, GALV.		2
11	98174400	ELBOW, STREET, 1/2", GALV.		1
10	98048022	BUSHING, REDUCER, 3/4X1/2, GALVANIZED		1
9	96920944	HOSE, FLEXIBLE, STAINLESS STEEL, 1/4 NPT X 18 LONG		1
8	96920912	FLEX LINE, 12		1
7	98840243	VALVE, SWING CHECK, M-M, 1/2 NPT, TIEMME		1
6	96606607	TEE,1/2X1/2X1/4,GALVANIZED		1
5	92056810	CONNECTOR, 3/8" ID TUBE x 1/2" NPT		1
4	92056704	CONNECTOR, ELBOW, 3/8" ID TUBE x 1/2" NPT		2
3	9101423C	MANIFOLD, 1-1/4 X 1-1/4 X 1, GRV/THD/THD		1
2	78653004	ASSEMBLY, VALVE CAUTION STATION, 1/2"		1
1	78653000	ASSEMBLY, MANUAL EMERGENCY STATION		1

BILL OF MATERIALS

PART NO. TABLE			
ASSEMBLY P/N	DESCRIPTION	BALL DRIP P/N	DESCRIPTION
77000263	SUB-ASSY, TRIM BASE	78653800	ASSEMBLY, MECHANICAL BALL DRIP 1/2"
77000264	SUB-ASSY, TRIM BASE (LPCB)	78653801	ASSEMBLY, SEMI-AUTOMATIC BALL DRIP, 1/2" LPCB

THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO THE RELIABLE AUTOMATIC SPRINKLER CO. IT MAY NOT BE REPRODUCED NOR MAY ANY INFORMATION HEREON BE DISCLOSED TO OTHERS WITHOUT THE SPECIFIC WRITTEN PERMISSION OF RELIABLE.

VOLUME CU. IN. 0.000

DO NOT SCALE DRAWING. REMOVE BURRS, BREAK SHARP EDGES

TOLERANCE UNLESS OTHERWISE SPECIFIED

ANGLE ± 1/2°
MACH. FINISH 63

FRACT. ± 1/32 [0.79]
DEC. XX ± .010 [0.25]
DEC. XXX ± .005 [0.13]

THE RELIABLE AUTOMATIC SPRINKLER CO., INC.
LIBERTY, S.C.

PART NO: SEE P/N TABLE | DWG.SIZE: C

PART: SUB-ASSEMBLY, TRIM, BASE, GALVANIZED PIPE

PRODUCT: DDX 2"-3"

FILE NO: 77000263 | ENG: JJ | DRW BY: PH

SCALE: 1:5 | DATE: 04/25/17 | SHEET 2 of 2

DDX VALVE TRIM S PART NUMBER CONFIGURATION

*SELECTIONS IN **BOLD** ARE STANDARD OPTIONS*

DDX VALVE SIZE AND ENDS CONNECTION TYPE
0 = NONE (NO VALVE, LOOSE AND SEGMENTED TRIM ONLY)[1]
4 = 4" GE X GE
6 = 6" GE X GE
7 = 165 MM GE X GE[4]
8 = 8" GE X GE
A = 4" FLANGE[2,3] INLET X GE OUTLET
B = 4" FLANGE[2,3] INLET X FLANGE[2,3] OUTLET
C = 4" PN16 FLANGE[4] INLET X GE OUTLET
D = 4" PN16 FLANGE[4] INLET X PN16 FLANGE[4] OUTLET
E = 6" FLANGE[2,3] INLET X GE OUTLET
F = 6" FLANGE[2,3] INLET X FLANGE[2,3] OUTLET
G = 6" PN16 FLANGE[4] INLET X GE OUTLET
H = 6" PN16 FLANGE[4] INLET X PN16 FLANGE[4] OUTLET
I = 165 MM FLANGE[2,4] INLET X GE OUTLET
J = 165 MM PN16 FLANGE[4] INLET X GE OUTLET
K = 8" FLANGE[2,3] INLET X FLANGE[2,3] OUTLET
L = 8" PN16 FLANGE[4] INLET X PN16 FLANGE[4] OUTLET

TRIM FINISH[7]
0 = GALVANIZED
1 = BLACK PIPE
2 = BRASS
3 = STAINLESS STEEL
4 = GALV. (U.S. SOURCED)
5 = BLACK PIPE (U.S. SOURCED)
6 = BRASS (U.S. SOURCED)
7 = STAINLESS STEEL (U.S. SOURCED)

ASSEMBLY CONFIGURATION, VALVE COLOR & INSTALLED CONTROL VALVE OPTIONS
1 = LOOSE TRIM FOR 4"- 8" VALVES[1,2]
3 = SEGMENTTALLY ASSEMBLED FOR 4"- 8" VALVES[1,2]
4 = FULLY ASSEM. TO BLACK DDX VALVE, W/O CONTROL VALVE
5 = FULLY ASSEM. TO RED DDX VALVE, W/O CONTROL VALVE
7 = FULLY ASSEM. TO RED CCCF APPROVED DDX VALVE, W/O CONTROL VALVE[4]
8 = FULLY ASSEM. TO BLACK DDX VALVE, WITH CONTROL VALVE
9 = FULLY ASSEM. TO RED DDX VALVE, WITH CONTROL VALVE
A= FULLY ASSEM. TO RED CCCF APPROVED DDX VALVE, WITH CONTROL VALVE[4,7]

6	5	2	4	8	0	8	0	1	0
DDX VALVE SIZE AND ENDS CONNECTION TYPE			TRIM FINISH[7]		ASSEMBLY CONFIGURATION, VALVE COLOR & INSTALLED CONTROL VALVE OPTIONS		SUB-ASSEMBLY, BASE TRIM		SYSTEM PRESSURE SWITCH[5]

SUB-ASSEMBLY, BASE TRIM
0 = SUB-ASSY,TRIM BASE, WITH MECHANICAL BALL DRIP
1 = SUB-ASSY,TRIM BASE WITH SEMI-AUTOMATIC BALL DRIP,LPCB

SYSTEM PRESSURE SWITCH[5]
0 = NONE
1 = **POTTER FM, cULus APPROVED**
2 = SYSTEM SENSOR FM/UL APPROVED
3 = SYSTEM SENSOR FM/ULC APPROVED
4 = POTTER, EXPOSION PROOF

NOTES:
1. FOR 4"- 8" DUCTILE IRON GROOVE X GROOVE OR GROOVE X PLAIN END SEGMENTED TRIM VALVES, 2"- 8" DUCTILE IRON VALVE BODIES, FOR ANY 4"- 8" DUCTILE IRON SEGMENTED TRIM ASSEMBLY, SELECT "0" FOR "TRIM ASSEMBLED FOR FULLY ASSEMBLED DDX VALVE" AND SELECT "0" FOR "NONE" FOR "SYSTEM PRESSURE SWITCH".
2. STANDARD FLANGES ARE CLASS 150 RESILIENT SEATED.
3. GROOVED END DUCTILE IRON 2"- 8" DUCTILE IRON VALVE BODIES.
4. GALVANIZED PREFERRED, BLACK IS A DISPLACEMENT DIFFERING ALLOY. RESTRICTIVE FINISHES ARE MARKETED ORDER INTO.
5. FOR LOOSE AND SEGMENTED ASSEMBLED TRIM CONFIGURATIONS, SELECT DDX VALVE SOLD SEPARATELY (SEE SHEET 3 FOR DDX VALVES PART NUMBERS).
6. FOR ADDITIONAL BODY OPTIONS FOR THESE PRODUCTS.
7. FLANGED VALVES ARE NOT AVAILABLE WITH ADJUSTABLE VALVE (REFER TO DDS #71).
8. A SYSTEM PRESSURE SWITCH IS NOT INCLUDED BY DEFAULT WITH THE FIRE-DEX LYNX TRIM, INCLUDED DDX SIZE INTERLOCK TYPE DDX SIZE INTERLOCK DRY PILOT SYSTEM (REFER TO DDX TYPES 3 AND 5).
9. 78 VV AND 165 VV ARE NOT AVAILABLE WITH ADJUSTABLE VALVE (REFER TO DDS #71).

MODEL DDX 4", 6" & 8" DELUGE DRY PILOT ASSEMBLY P/N 6520801010 REV. H



DDX VALVE PART NUMBER TABLE

DDX. VALVE	VALVE PART NUMBER	DRAWING FILE NUMBER
4" DUCTILE IRON G/G BLACK	6103040026	6103040026
4" DUCTILE IRON G/G RED	6103040030	
4" DUCTILE IRON F/G CLASS 150 BLACK	6103040044	
4" DUCTILE IRON F/G CLASS 150 RED	6103040046	
4" DUCTILE IRON F/G PN16 RED	6103040048	
4" DUCTILE IRON F/F CLASS 150 BLACK	6103040045	
4" DUCTILE IRON F/F CLASS 150 RED	6103040047	
4" DUCTILE IRON F/F PN16 RED	6103040049	
6" DUCTILE IRON G/G BLACK	6103060024	6103060024
6" DUCTILE IRON G/G RED	6103060030	
6" DUCTILE IRON F/G CLASS 150 BLACK	6103060045	
6" DUCTILE IRON F/G CLASS 150 RED	6103060048	
6" DUCTILE IRON F/G PN16 RED	6103060049	
6" DUCTILE IRON F/F CLASS 150 BLACK	6103060046	
6" DUCTILE IRON F/F CLASS 150 RED	6103060047	
6" DUCTILE IRON F/F PN16 RED	6103060050	
165MM DUCTILE IRON G/G RED	6103060028	6103060024
165MM DUCTILE IRON F/G CLASS 150 RED	6103060051	
165MM DUCTILE IRON F/G PN16 RED	6103060052	
8" DUCTILE IRON G/G BLACK	6103080001	6103080001
8" DUCTILE IRON G/G RED	6103080003	
8" DUCTILE IRON F/F CLASS 150 BLACK	6103080016	
8" DUCTILE IRON F/F CLASS 150 RED	6103080018	
8" DUCTILE IRON F/F PN16 RED	6103080020	

BILL OF MATERIALS

ITEM NO.	PART NO.	DESCRIPTION	REMARKS	QTY.
25	89141112	TIE, RETAINING	NOT SHOWN	9
24	6990012997	SWITCH, POTTER PRESSURE (PSI0-EX)	(ULC, UL, FM)	1
	6990006382	SWITCH, POTTER PRESSURE (PSI0-2)	(ULC, UL, FM)	
	6999992360	SWITCH, PRESSURE (EPSAI0-2)	(ULC)	
	6999991212	SWITCH, PRESSURE (EPSI-2)	(UL/FM)	
23	96686756	TUBING, PVC, 3/8" I.D. X 6 FT.		1
22	95516915	PERMA-LOK	NOT SHOWN	A/R
21	77000266	SUB-ASSY, TRIM BASE, WITH MECHANICAL BALL DRIP	SEE P/N CONFIG.	1
	77000267	SUB-ASSY,TRIM BASE,WITH SEMI-AUTOMATIC BALL DRIP,LPCB		
20	98840228	VALVE, RELIEF. 1/2", 50 PSI		1
19	98840237	VALVE, BALL, 1/4" NPTF x 1/4" NPTM		1
18	98614401	PIPE, PLUG, IRON, SQUARE HEAD, 3/4		1
17	98604406	PIPE, PLUG, IRON, SQUARE HEAD, 1/2		1
16	99080002	PAD-ADHESIVE, VALVE NAME PLATES		1
15	98543226	NIPPLE,1/4X1-1/2,GALVANIZED STEEL		1
14	98543210	NIPPLE,1/2X2-1/2,GALVANIZED STEEL		1
13	98543223	NIPPLE,1/2X1-1/2,GALVANIZED STEEL		2
12	94616915	NAMEPLATE, DELUGE VALVE		1
11	71030010	MODEL LP PILOT LINE ACTUATOR		1
10	91004299	MANIFOLD, DRAIN, BARBED, 6-3/16		1
9	98248000	GAUGE, AIR PRESSURE (0-80 PSI)		1
8	98751003	FITTING, MULTIPORT, 1/2x1/2x1/2x1/2x1/2x1/4		1
7	98174404	ELBOW, 1/4", MALL IRON, GALV.		1
6	98174401	ELBOW, 1/2", MALL IRON, GALV.		1
5	92056704	CONNECTOR, ELBOW, 3/8" ID TUBE x 1/2" NPT		1
4	95306255	CLAMP, HOSE, 1/2" CONSTANT TENSION, ZINC		8
3	77000308	SUBASSEMBLY, CONTROL VALVE, 8" (200MM)	FULLY ASSEMBLED WITH CONTROL VALVE ONLY	1
	77000306	SUBASSEMBLY, CONTROL VALVE, 6" (150MM)		
	77000304	SUBASSEMBLY, CONTROL VALVE, 4" (100MM)		
2	6990003756	SWITCH, PRESSURE (PS40-EX)	(ULC, UL, FM)	1
	6990019313	SWITCH, PRESSURE (PS25-2)	(ULC, UL, FM)	
	6999992361	SWITCH, PRESSURE (EPSA40-2)	(ULC)	
	6999991340	SWITCH, PRESSURE (EPS40-2)	(UL/FM)	
1	SEE DDX VALVE P/N TABLE			1

REVISIONS			
LTR	DESCRIPTION	DATE	DRAWN BY
	SEE PAGE 1		

THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO THE RELIABLE AUTOMATIC SPRINKLER CO. IT MAY NOT BE REPRODUCED NOR MAY ANY INFORMATION HEREON BE DISCLOSED TO OTHERS WITHOUT THE SPECIFIC WRITTEN PERMISSION OF RELIABLE.

DO NOT SCALE DRAWING. REMOVE BURRS, BREAK SHARP EDGES

TOLERANCE UNLESS OTHERWISE SPECIFIED

ANGLE ± 1/2° | MACH. FINISH 63 | FRACT. ± 1/32 [0.79] | DEC. XX ± .010 [0.25] | DEC. XXX ± .005 [0.13]

THE RELIABLE AUTOMATIC SPRINKLER CO., INC.
LIBERTY, S.C.

PART NO: VARIOUS | DWG.SIZE: C

PART: ASSEMBLY, TRIM, DRY PILOT

PRODUCT: DDX 4", 6", 8" (B)

FILE NO: 6520801010 | ENG: JJ | DRW BY: PH | SCALE: 1:6 | DATE: 12/04/17 | SHEET 2 of 3

REVISIONS			
LTR	DESCRIPTION	DATE	DRAWN BY
	SEE PAGE 1		

MODEL DDX 4", 6", 8" BASIC TRIMS

SUBASSEMBLY P/N 77000266 REV. M











ITEM NO.	PART NO.	DESCRIPTION	REMARKS	QTY.
42	95516915	PERMA-LOK	NOT SHOWN	A/R
41	98543216	NIPPLE, STEEL, GALV., 1/2" X 3-1/2"	4" & 6" VERSIONS	1
	98543205	NIPPLE, STEEL, GALV., 1/2" X 9"	8" VERSION	
40	98543224	NIPPLE, STEEL, GALV., 1/4" X 4-1/2"	4" & 6" VERSIONS	1
	98543217	NIPPLE, STEEL, GALV., 1/4" X 6"	8" VERSION	
39	SEE P/N TABLE	ASSEMBLY, BALL DRIP, 1/2"		1
38	98840111A	VALVE, BALL, 1/2 NPTF X 1/2 NPTM		1
37	9101423B	MANIFOLD, 2 X 2 X 1, GRV/THD/THD		1
36	98840237	VALVE, BALL, 1/4" NPTF x 1/4" NPTM		3
35	98840188	VALVE, CHECK, 1/4" NPTM x 1/4" NPTF		1
34	98840147	CHECK VALVE, 1/4, NPT, POPPET TYPE INLINE		1
33	98840246	VALVE, SWING CHECK, F-F, 1 NPT, TIEMME		1
32	98840136	VALVE, BALL, 2"		1
31	98840103	VALVE, ANGLE, 1/2"		1
30	98815201	UNION, 1/4, IRON, G.J., GALV.		1
29	98815200	UNION, 1/2, IRON, G.J., GALV.		2
28	98761651	TEE,1/2X1/2X1/2,GALVANIZED		1
27	98761649	TEE,1/2X1/4X1/2,GALVANIZED		1
26	98751005	FITTING, MULTIPORT, 3/4x1/2x1/2x1/2x1/2		1
25	98727607	STRAINER, 1/4"		1
24	98614403	PIPE, PLUG, IRON, SQUARE HEAD, 1/4		1
23	98614401	PIPE, PLUG, IRON, SQUARE HEAD, 3/4		1
22	98604406	PIPE, PLUG, IRON, SQUARE HEAD, 1/2		1
21	98543262	NIPPLE,2X3-1/2,GALVANIZED STEEL		1
20	98543238	NIPPLE,2XCLOSE,GALVANIZED STEEL		2
19	98543226	NIPPLE,1/4X1-1/2,GALVANIZED STEEL		1
18	98543225	NIPPLE,1/4X2-1/2,GALVANIZED STEEL		1
17	98543223	NIPPLE,1/2X1-1/2,GALVANIZED STEEL		7
16	98543209	NIPPLE,1/2X2,GALVANIZED STEEL		3
15	98248001	GAUGE, WATER PRESSURE (0-300 PSI)		2
14	98174408	ELBOW, STREET, 1/4", GALV.		1
13	98174405	ELBOW, 2", MALL IRON, GALV.		2
12	98174404	ELBOW, 1/4", MALL IRON, GALV.		2
11	98174400	ELBOW, STREET, 1/2", GALV.		1
10	98048022	BUSHING, REDUCER, 3/4X1/2, GALVANIZED		1
9	98048000	BUSHING, REDUCER, 1/2X1/4, GALVANIZED		1
8	96920944	HOSE, FLEXIBLE, STAINLESS STEEL, 1/4 NPT X 18 LONG		1
7	96920912	FLEX LINE, 12		1
6	98840243	VALVE, SWING CHECK, M-M, 1/2 NPT, TIEMME		1
5	96606607	TEE,1/2X1/2X1/4,GALVANIZED		1
4	92056810	CONNECTOR, 3/8" ID TUBE x 1/2" NPT		1
3	92056704	CONNECTOR, ELBOW, 3/8" ID TUBE x 1/2" NPT		2
2	78653004	ASSEMBLY, VALVE CAUTION STATION, 1/2"		1
1	78653000	ASSEMBLY, MANUAL EMERGENCY STATION		1

BILL OF MATERIALS

PART NO. TABLE			
ASSEMBLY P/N	DESCRIPTION	BALL DRIP P/N	DESCRIPTION
77000266	SUB-ASSY, TRIM BASE	78653800	ASSEMBLY, MECHANICAL BALL DRIP 1/2"
77000267	SUB-ASSY, TRIM BASE (LPCB)	78653801	ASSEMBLY, SEMI-AUTOMATIC BALL DRIP, 1/2" LPCB

THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO THE RELIABLE AUTOMATIC SPRINKLER CO. IT MAY NOT BE REPRODUCED NOR MAY ANY INFORMATION HEREON BE DISCLOSED TO OTHERS WITHOUT THE SPECIFIC WRITTEN PERMISSION OF RELIABLE.

DO NOT SCALE DRAWING. REMOVE BURRS, BREAK SHARP EDGES

TOLERANCE UNLESS OTHERWISE SPECIFIED

ANGLE ± 1/2°
MACH. FINISH 63

FRACT. ± 1/32 [0.79]
DEC. XX ± .010 [0.25]
DEC. XXX ± .005 [0.13]

THE RELIABLE AUTOMATIC SPRINKLER CO., INC.
LIBERTY, S.C.

PART NO: SEE P/N TABLE | DWG.SIZE: C

PART: SUB-ASSEMBLY, TRIM, BASE, GALVANIZED PIPE

PRODUCT: DDX 4", 6", 8"

FILE NO: 77000266 | ENG: JJ | DRW BY: PH

SCALE: 1:6 | DATE: 07/13/17 | SHEET 2 of 2

MODEL DDX VALVE WITH STAINLESS STEEL SCREW-IN SEAT

IMPORTANT NOTE: Early generation 4" and 6" DDX valves may incorporate a brass drop-in seat. Prior to ordering replacement parts, confirm the presence of a stainless steel screw-in seat or brass drop-in seat. For replacement parts for valves with brass drop-in seat, please contact Reliable Sprinkler Company Technical Services (techserv@reliablesprinkler.com)





EXTERNAL RESET ASSEMBLY



Model DDX (Screw-In Seat Configuration) Deluge Valves Parts List

Item No.	Part No. 2" (50mm)	2½" (65mm)	76mm	3" (80mm)	4" (100mm)	165mm	6" (150mm)	8" (200mm)	Part Description	QTY.	Material
1	91006011	91006012	91006023	91006013	91006005	91006027	91006007	91006028	Valve Body Groove/Groove	1	Ductile Iron 65-45-12
	N/A	N/A	N/A	N/A	91006045	N/A	91006067	N/A	Valve Body Flange/Groove		
	N/A	N/A	N/A	N/A	91006035	N/A	91006037	91006039	Valve Body Flange/Flange		
2	N/A	N/A	N/A	N/A	N/A	N/A		95406414	O-ring (Mounting Ring)	1	Buna-N
3	71040416								Pushrod Cover Assembly	1	Ductile Iron 65-45-12 & Brass C360000
4	91106123				N/A	N/A		N/A	Hex Bolt ½"-13 x 1¼"	6	Zinc Plated Steel
	N/A				95606107	N/A		N/A	Hex Bolt ½"-13 x 1½"	6	
	N/A				N/A	91106006		N/A	Hex Bolt ⅝"-11 x 1¾"	6	
	N/A				N/A	N/A		95606110	Hex Bolt ⅝"-11 x 2"	8	
5	91306013				91306014	91306016		91306018	Mounting Ring	1	Stainless Steel CF8 or CF8M
6	91916003				91916014	91916016		91916008	Clapper	1	Stainless Steel CF8 or CF8M
7	92116063				92116064	92116065	92116066	92116068	Access Cover	1	Ductile Iron 65-45-12
8	93416003				93416014	93416016		93416008	Seal Assembly	1	Stainless Steel 304 & EPDM
9	93706003				93706004	93706006		93706008	Access Cover Gasket	1	Buna-N or Neoprene
10	93722000				93722000	N/A		N/A	Bumpstop Assembly	1	Stainless Steel UNS S31600 & EPDM
	N/A				N/A	93722000		N/A		2	
	N/A				N/A	N/A		93722000		3	
11	93916006								Pushrod Guide	1	Acetal
12	93916066								Reset Shaft	1	Brass UNS C36000
13	94106066								Reset Housing	1	Brass UNS C36000
14	94356006								Reset Knob	1	Aluminum 6061
15	94506003				94506004	94506016		94506008	Lever	1	Stainless Steel UNS S17400
16	95006412				94006412	95006410		95006410	Striker	1	Aluminum Bronze C95400
17	95106006								Piston	1	Stainless Steel CF8M
18	95276006								Diaphragm	1	EPDM & Polyester
19	95306267				N/A	N/A		N/A	Retaining Ring, ⅜" Shaft, Lever Pin	2	Stainless Steel 15-7 or 17-7
	N/A				95306267	N/A		N/A	Retaining Ring, ½" Shaft, Lever Pin		
	N/A				N/A	95306269		N/A	Retaining Ring, ⅝" Shaft, Lever Pin		
	N/A				N/A	N/A		95316408	Retaining Ring, ¾" Shaft, Lever Pin		
20	95306268				N/A	N/A		N/A	Retaining Ring, ⅜" Shaft, Hinge Pin	2	Stainless Steel 15-7 or 17-7
	N/A				95306267	95306267		N/A	Retaining Ring, ½" Shaft, Hinge Pin		
	N/A				N/A	N/A		95316408	Retaining Ring, ¾" Shaft, Hinge Pin		
21	95406007								O-Ring, Reset Housing ID	1	Buna-N
22	95406024								O-Ring, Reset Housing & Pushrod Guide OD	2	Buna-N
23	95406407								O-Ring, Pushrod Guide ID	1	Buna-N
24	95406410				95406409	95436126		95406413	O-Ring, Upper Seat	1	Buna-N
25	95406411				95406420	95446226		95406412	O-Ring, Lower Seat	1	Buna-N
26	95506006								Pushrod	1	Stainless Steel UNS S30300
27	95606114								Socket Head Screw, ¼"-20 x ⅝"	6	Steel
28	95606127								Flat Head Socket Cap Screw ⅜"-16 x ¾"	1	Steel
29	95606133				N/A	N/A		N/A	Socket Head Screw #6-32 x ½"	1	Stainless Steel 18-8
	N/A				95606130	95606130		95606130	Socket Head Screw #10-32 x 1"		Stainless Steel UNS S31600
30	96016003				96016014	96016016		96016008	Seat	1	Stainless Steel CF8M
31	96206003				N/A	N/A		N/A	Hinge Pin	1	Stainless Steel UNS S30400
	N/A				96216086	96216086		96206008			Stainless Steel UNS S21800
32	96216003				N/A	N/A		N/A	Lever Pin	1	Stainless Steel UNS S17400
	N/A				96216044	96216047		96216008			Stainless Steel UNS S21800
33	96310003				96906904	96906904		96310008	Clapper Spacer	2	Teflon or Acetal
34	96406003				N/A	N/A		N/A	Lever Spring	1	Stainless Steel UNS S30400
	N/A				96406004	96406005		96406008			Stainless Steel UNS S31600
35	96406906								Piston/ Reset Spring	2	Stainless Steel UNS S31600
36	96906112				N/A	N/A		N/A	Spring Lock Washer, #6	1	Stainless Steel 18-8
	N/A				96906111	96906111		96906111	Spring Lock Washer, #10		Stainless Steel UNS S31600
37	95606140				N/A	N/A		N/A	Flat Head Socket Cap Screw ¼"-20 x ½"	2	Stainless Steel 18-8
	N/A				95606139	N/A		N/A			Stainless Steel UNS S31600
	N/A				N/A	N/A		95606135	Flat Head Socket Cap Screw ½"-13 x ¾"		Stainless Steel UNS S31600
38	98604402								Plug, ½" NPT	1	Steel
39	94616921								Knob Caution Label (Not Shown)	1	Polystyrene
40	91556922								Ball Chain, 1/8" (Not Shown) (Length is in Inches)	6	Nickel Plated Brass
41	91556923								Clamping Link, Ball Chain (Not Shown)	1	
42	6999993406								O-Ring Grease, Dupont™ Krytox® GPL-205	A/R	Krytox®