REVISIONS			
LTR	DESCRIPTION	DATE	DRAWN BY
	SEE PAGE 1		

DDX VALVE TRIMS PART NUMBER CONFIGURATION

*SELECTIONS IN **BOLD** ARE STANDARD OPTIONS*

TRIM TYPE & B1 ACCELERATOR OPTION
G = NON-INTERLOCK, W/O B1 ACCELERATOR[1]
H = NON-INTERLOCK, WITH B1 ACCELERATOR[2]

TRIM FINISH[4]
0 = GALVANIZED
1 = BLACK PIPE
2 = BRASS
3 = STAINLESS STEEL
4 = GALV. (U.S. SOURCED)
5 = BLACK PIPE (U.S. SOURCED)
6 = BRASS (U.S. SOURCED)
7 = STAINLESS STEEL (U.S. SOURCED)

ASSEMBLY CONFIGURATION, VALVE COLOR & INSTALLED CONTROL VALVE OPTIONS
0 = LOOSE TRIM FOR 2"- 3" VALVES[1,5]
2 = SEGMENTALLY ASSEMBLED FOR 2"- 3" VALVES[1,5]
4 = FULLY ASSEM. TO BLACK DDX VALVE, W/O CONTROL VALVE
5 = FULLY ASSEM. TO RED DDX VALVE, W/O CONTROL VALVE
7 = FULLY ASSEM. TO RED CCC APPROVED DDX VALVE, W/O CONTROL VALVE[3]
8 = FULLY ASSEM. TO BLACK DDX VALVE, WITH CONTROL VALVE
9 = FULLY ASSEM. TO RED DDX VALVE, WITH CONTROL VALVE[7]
A= FULLY ASSEM. TO RED CCC APPROVED DDX VALVE, WITH CONTROL VALVE[6,7]

DDX VALVE SIZE AND ENDS CONNECTION TYPE
0 = NONE (NO VALVE, LOOSE AND SEGMENTED TRIM ONLY)[1]
1 = 2 ½" GE X GE
2 = 2" GE X GE
3 = 3" GE X GE
5 = 76 MM GE X GE[9]

6	5	2	2	G	0	8	1	0	0
1ST	2ND	3RD	4TH	5TH	6TH	7TH	8TH	9TH	10TH

SOLENOID VALVE
1 = 175 PSI
2 = 300 PSI
3 = 175 PSI, EXPLOSION PROOF
4 = 300 PSI, EXPLOSION PROOF

SYSTEM PRESSURE SWITCH[8]
0 = NONE
1 = POTTER FM, cULus APPROVED
2 = SYSTEM SENSOR FM/UL APPROVED
3 = SYSTEM SENSOR FM/ULC APPROVED
4 = POTTER, EXPLOSION PROOF

NOTES:
1. FOR THE 4TH DIGIT, SELECT "0" FOR LOOSE OR SEGMENTED TRIMS. 7TH DIGIT MUST BE "0", OR "2". FOR ANY 4TH DIGIT SELECTION OTHER THAN "0", THE 7TH HAS TO BE A FULLY-ASSEMBLED SELECTION ("4", "5" ...ETC).
2. STANDARD FLANGE TYPE IS CLASS 150 PER ASME B16.5.
3. NO SOLENOID VALVE REQUIRED, THE 8TH DIGIT MUST BE "0".
4. GALVANIZED PIPE FITTINGS ARE THE DEFAULT OFFERING. ALL OTHERS TRIM FINISHES ARE MAKE TO ORDER (MTO).
5. FOR LOOSE AND SEGMENTED ASSEMBLED TRIM CONFIGURATIONS, THE DDX VALVE IS SOLD SEPARATELY (SEE BULLETIN 519 FOR DDX VALVE'S PART NUMBER).
6. CHINA COMPULSORY CERTIFICATE FOR FIRE PRODUCTS.
7. FLANGED VALVES ARE NOT AVAILABLE WITH A CONTROL VALVE (REFER TO DIGIT #7).
8. (EMPTY)
9. 76 MM AND 165 MM ARE NOT AVAILABLE WITH A CONTROL VALVE (REFER TO DIGIT #7).

DDX VALVE PART NUMBER TABLE

DDX. VALVE	VALVE PART NUMBER	DRAWING FILE NUMBER
2" DUCTILE IRON G/G BLACK	6103022000	6103030000
2" DUCTILE IRON G/G RED	6103022001	
2-½" DUCTILE IRON G/G BLACK	6103022500	
2-½" DUCTILE IRON G/G RED	6103022501	
3" DUCTILE IRON G/G BLACK	6103030000	
3" DUCTILE IRON G/G RED	6103030001	
76MM DUCTILE IRON G/G RED	6103027600	

BILL OF MATERIALS

ITEM NO.	PART NO.	DESCRIPTION		QTY.
36	89097903	TAPE, TEFLON	NOT SHOWN	A/R
35	89141112	TIE, RETAINING		9
34	6990003756	SWITCH, POTTER PRESSURE (PS40-EX)	(ULC, UL, FM)	1
	6990019313	SWITCH, POTTER PRESSURE (PS25-2)	(ULC, UL, FM)	
	6999992361	SWITCH, PRESSURE (EPSA40-2)	(ULC)	
	6999991340	SWITCH, PRESSURE (EPS40-2)	(UL/FM)	
33	6990012997	SWITCH, POTTER PRESSURE (PS10-EX)	(ULC, UL, FM)	1
	6990006382	SWITCH, POTTER PRESSURE (PS10-2)	(ULC, UL, FM)	
	6999992360	SWITCH, PRESSURE (EPSA10-2)	(ULC)	
	6999991212	SWITCH, PRESSURE (EPS10-2)	(UL/FM)	
32	96686756	TUBING, PVC, 3/8" I.D. x 6 FT.		1
31	95516915	PERMA-LOK	NOT SHOWN	A/R
30	6871020033	VALVE, SOLENOID, 300 PSI, EXPLOSION PROOF		1
	6999990322	VALVE, SOLENOID, 175 PSI, EXPLOSION PROOF		
	6871020020	VALVE, SOLENOID, 300 PSI		
	6871020000	VALVE, SOLENOID, 175 PSI		
29	98840228	VALVE, RELIEF, 1/2", 50 PSI		1
28	98840237	VALVE, BALL, 1/4" NPTF x 1/4" NPTM		1
27	98815204	UNION, ORING SEAL, GALV., 1/2		1
26	98761651	TEE,1/2X1/2X1/2,GALVANIZED		1
25	77060020	SUB-ASSEMBLY, TRIM, BASE, NON-INTERLOCK GALV.		1
24	98604406	PIPE, PLUG, IRON, SQUARE HEAD, 1/2		2
23	99080002	PAD-ADHESIVE, VALVE NAME PLATES		1
22	98543243	NIPPLE,1/4X4,GALVANIZED STEEL		1
21	98543212	NIPPLE,1/2XCLOSE,GALVANIZED STEEL		2
20	98543219	NIPPLE,1/2X5,GALVANIZED STEEL		1
19	98543230	NIPPLE,1/2X3,GALVANIZED STEEL		1
18	98543209	NIPPLE,1/2X2,GALVANIZED STEEL		1
17	98543210	NIPPLE,1/2X2-1/2,GALVANIZED STEEL		1
16	98543223	NIPPLE,1/2X1-1/2,GALVANIZED STEEL		1
15	94616916	NAMEPLATE, DRY PIPE VALVE		1
14	71030010	MODEL LP PILOT LINE ACTUATOR		1
13	91004300	MANIFOLD, DRAIN, BARBED, 6-3/8		1
12	98840181	HORIZ. SWING CHECK VALVE, 1/2" NPT		1
11	98248000	GAUGE, AIR PRESSURE (0-80 PSI)		1
10	98751004	FITTING, MULTIPORT, 1/2x1/2x1/2x1/2x1/2		1
9	98174408	ELBOW, STREET, 1/4", GALV.		1
8	98174400	ELBOW, STREET, 1/2", GALV.		2
7	98174404	ELBOW, 1/4", MALL IRON, GALV.		1
6	92056704	CONNECTOR, ELBOW, 3/8" ID TUBE x 1/2" NPT		3
5	95306255	CLAMP, HOSE, 1/2" CONSTANT TENSION, ZINC		10
4	98048022	BUSHING, REDUCER, 3/4X1/2, GALVANIZED		1
3	98048000	BUSHING, REDUCER, 1/2X1/4, GALVANIZED		1
2	77000303	SUBASSEMBLY, CONTROL VALVE, 3"	FULLY ASSEMBLED WITH CONTROL VALVE ONLY	1
	77000302	SUBASSEMBLY, CONTROL VALVE, 2-1/2"		
	77000252	SUBASSEMBLY, CONTROL VALVE, 2"		
1	SEE DDX VALVE P/N TABLE			1



MODEL DDX 2"-3" DELUGE NON-INTERLOCK
CA-334 P/N 89241311
ASSEMBLY P/N 6520G00110 REV. -



THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO THE RELIABLE AUTOMATIC SPRINKLER CORP. IT MAY NOT BE REPRODUCED NOR MAY ANY INFORMATION HEREON BE DISCLOSED TO OTHERS WITHOUT THE SPECIFIC WRITTEN PERMISSION OF RELIABLE.

MTL: N/A	
FINISH:	
DO NOT SCALE DRAWING REMOVE BURRS, BREAK SHARP EDGES TOLERANCE UNLESS OTHERWISE SPECIFIED: ANGLE ± 1/2 63 MACH. FINISH CONC. TIR SQUARENESS - PARALLELISM	FRACT. ± 1/32 [0.79] DEC. XX ± .010 [0.25] DEC. XXX ± .005 [0.13] 1885P

THE RELIABLE AUTOMATIC SPRINKLER CO., INC. LIBERTY, S.C.			
PART NO: VARIOUS		DWG SIZE: E	
PART: ASSEMBLY, TRIM, NON-INTERLOCK			
PRODUCT: DDX, 2", 2-1/2", 3"			
FILE NO: 6520G00110	ENG: JJ	DRW BY: MK	CK'D: -
	SCALE: 1:4	DATE: 03/09/23	SHEET 2 of 3

REVISIONS			
LTR	DESCRIPTION	DATE	DRAWN BY
	SEE PAGE 1		













MODEL DDX NON INTERLOCK 2", 2-1/2" & 3" BASIC TRIMS SUBASSEMBLY P/N 77060020 REV. A

ITEM NO.	PART NO.	DESCRIPTION	REMARKS	QTY.
41	95516915	THREAD, SEALANT	NOT SHOWN	A/R
39	98048034	BUSHING, REDUCER, 3/8X1/4, GALVANIZED		1
38	98840111A	VALVE, BALL, 1/2 NPTF X 1/2 NPTM		1
37	98840246	VALVE, SWING CHECK, F-F, 1 NPT, TIEMME		1
36	98840237	VALVE, BALL, 1/4" NPTF x 1/4" NPTM		3
35	98840188	VALVE, CHECK, 1/4" NPTM x 1/4" NPTF		1
34	98840147	CHECK VALVE, 1/4, NPT, POPPET TYPE INLINE		1
33	98840106	VALVE, ANGLE, 1 1/4		1
32	98840103	VALVE, ANGLE, 1/2"		1
31	98815201	UNION, 1/4, IRON, G.J., GALV.		1
30	98815200	UNION, 1/2, IRON, G.J., GALV.		2
29	98761649	TEE,1/2X1/4X1/2,GALVANIZED		1
28	98751005	FITTING, MULTIPORT, 3/4x1/2x1/2x1/2x1/2		1
27	98750003	PIPE CROSS, 1/2", GALV.		1
26	98727617	STRAINER, 1/4 NPT		1
25	98614403	PIPE, PLUG, IRON, SQUARE HEAD, 1/4		1
24	98614401	PIPE, PLUG, IRON, SQUARE HEAD, 3/4		1
23	98604406	PIPE, PLUG, IRON, SQUARE HEAD, 1/2		1
22	98543285	NIPPLE,1-1/4XCLOSE,GALVANIZED STEEL		1
21	98543284	NIPPLE,1-1/4X5,GALVANIZED STEEL		1
20	98543230	NIPPLE,1/2X3,GALVANIZED STEEL		2
19	98543226	NIPPLE,1/4X1-1/2,GALVANIZED STEEL		2
18	98543224	NIPPLE,1/4X4-1/2,GALVANIZED STEEL		1
17	98543223	NIPPLE,1/2X1-1/2,GALVANIZED STEEL		8
16	98543209	NIPPLE,1/2X2,GALVANIZED STEEL		1
15	98248001	GAUGE, WATER PRESSURE (0-300 PSI)		2
14	98174414	ELBOW, 1-1/4", MALL IRON, GALV.		1
13	98174404	ELBOW, 1/4", MALL IRON, GALV.		2
12	98174400	ELBOW, STREET, 1/2", GALV.		1
11	98048022	BUSHING, REDUCER, 3/4X1/2, GALVANIZED		1
10	96920944	HOSE, FLEXIBLE, STAINLESS STEEL, 1/4 NPT X 18 LONG		1
9	96920912	FLEX LINE, 12		1
8	96816907	VALVE, IN-LINE CHECK, M-M, 1/2NPT, TIEMME		1
7	96606607	TEE,1/2X1/2X1/4,GALVANIZED		1
6	92056810	CONNECTOR, 3/8" ID TUBE x 1/2" NPT		1
5	92056704	CONNECTOR, ELBOW, 3/8" ID TUBE x 1/2" NPT		2
4	9101423C	MANIFOLD, 1-1/4 X 1-1/4 X 1, GRV/THD/THD		1
3	78653800	ASSEMBLY, MECHANICAL BALL DRIP, 1/2"		1
2	78653004	ASSEMBLY, VALVE CAUTION STATION, 1/2"		1
1	78653000	ASSEMBLY, MANUAL EMERGENCY STATION		1

BILL OF MATERIALS

THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO THE RELIABLE AUTOMATIC SPRINKLER CORP. IT MAY NOT BE REPRODUCED NOR MAY ANY INFORMATION HEREON BE DISCLOSED TO OTHERS WITHOUT THE SPECIFIC WRITTEN PERMISSION OF RELIABLE.

MTL.
N/A

FINISH:

DO NOT SCALE DRAWING
REMOVE BURRS, BREAK SHARP EDGES
TOLERANCE UNLESS OTHERWISE SPECIFIED:
ANGLE ± 1/2 63/ FRACT. ± 1/32 [0.79]
MACH. FINISH DEC. XX ± .010 [0.25]
CONC. T.I.R. DEC. XXX ± .005 [0.13]
SQUARENESS - PARALLELISM

THE RELIABLE AUTOMATIC SPRINKLER CO., INC.
LIBERTY, S.C.

PART NO: 77060020 | DWG.SIZE: C

PART: SUB-ASSEMBLY, TRIM, BASE, NON-INTERLOCK GALV.

PRODUCT: DDX 2"-3"

FILE NO:	ENG:	DRW BY:	C'K'D:
77060020	SCALE: 1:4	DATE: 03/09/23	SHEET 2of2

REVISIONS			
LTR	DESCRIPTION	DATE	DRAWN BY
	SEE PAGE 1		

DDX VALVE PART NUMBER TABLE

DDX. VALVE	VALVE PART NUMBER	DRAWING FILE NUMBER
4" DUCTILE IRON G/G BLACK	6103040026	61C3040026
4" DUCTILE IRON G/G RED	6103040030	
4" DUCTILE IRON F/G CLASS 150 BLACK	6103040044	
4" DUCTILE IRON F/G CLASS 150 RED	6103040046	
4" DUCTILE IRON F/G PN16 RED	6103040048	
4" DUCTILE IRON F/F CLASS 150 BLACK	6103040045	
4" DUCTILE IRON F/F CLASS 150 RED	6103040047	
4" DUCTILE IRON F/F PN16 RED	6103040049	
6" DUCTILE IRON G/G BLACK	6103060024	61C3060024
6" DUCTILE IRON G/G RED	6103060030	
6" DUCTILE IRON F/G CLASS 150 BLACK	6103060045	
6" DUCTILE IRON F/G CLASS 150 RED	6103060048	
6" DUCTILE IRON F/G PN16 RED	6103060049	
6" DUCTILE IRON F/F CLASS 150 BLACK	6103060046	
6" DUCTILE IRON F/F CLASS 150 RED	6103060047	
6" DUCTILE IRON F/F PN16 RED	6103060050	
165MM DUCTILE IRON G/G RED	6103060028	61C3060024
165MM DUCTILE IRON F/G CLASS 150 RED	6103060051	
165MM DUCTILE IRON F/G PN16 RED	6103060052	
8" DUCTILE IRON G/G BLACK	6103080001	61C3080001
8" DUCTILE IRON G/G RED	6103080003	
8" DUCTILE IRON F/F CLASS 150 BLACK	6103080016	
8" DUCTILE IRON F/F CLASS 150 RED	6103080018	
8" DUCTILE IRON F/F PN16 RED	6103080020	

DDX VALVE TRIMS PART NUMBER CONFIGURATION

*SELECTIONS IN **BOLD** ARE STANDARD OPTIONS*

DDX VALVE SIZE AND ENDS CONNECTION TYPE
0 = NONE (NO VALVE, LOOSE AND SEGMENTED TRIM ONLY)[1]
4 = 4" GE X GE
6 = 6" GE X GE
7 = 165 MM GE X GE[9]
8 = 8" GE X GE
A = 4" FLANGE[2,7] INLET X GE OUTLET
B = 4" FLANGE[2,7] INLET X FLANGE[2,7] OUTLET
C = 4" PN16 FLANGE[2] INLET X GE OUTLET
D = 4" PN16 FLANGE[2] INLET X PN16 FLANGE[2] OUTLET
E = 6" FLANGE[2,7] INLET X GE OUTLET
F = 6" FLANGE[2,7] INLET X FLANGE[2,7] OUTLET
G = 6" PN16 FLANGE[2] INLET X GE OUTLET
H = 6" PN16 FLANGE[2] INLET X PN16 FLANGE[2] OUTLET
I = 165 MM FLANGE[2,7] INLET X GE OUTLET
J = 165 MM PN16 FLANGE[2] INLET X GE OUTLET
K = 8" FLANGE[2,7] INLET X FLANGE[2,7] OUTLET
L = 8" PN16 FLANGE[2] INLET X PN16 FLANGE[2] OUTLET

TRIM TYPE & B1 ACCELERATOR OPTION
0 = NON-INTERLOCK, W/O B1 ACCELERATOR[8]
H = NON-INTERLOCK, WITH B1 ACCELERATOR[8]

TRIM FINISH[7]
0 = GALVANIZED
1 = BLACK PIPE
2 = BRASS
3 = STAINLESS STEEL
4 = GALV. (U.S. SOURCED)
5 = BLACK PIPE (U.S. SOURCED)
6 = BRASS (U.S. SOURCED)
7 = STAINLESS STEEL (U.S. SOURCED)

ASSEMBLY CONFIGURATION, VALVE COLOR & INSTALLED CONTROL VALVE OPTIONS
1 = LOOSE TRIM FOR 4"- 8" VALVES[3,4]
3 = SEGMENTALLY ASSEMBLED FOR 4"- 8" VALVES[3,5]
4 = FULLY ASSEM. TO BLACK DDX VALVE, W/O CONTROL VALVE
5 = FULLY ASSEM. TO RED DDX VALVE, W/O CONTROL VALVE
7 = FULLY ASSEM. TO RED CCC APPROVED DDX VALVE, W/O CONTROL VALVE[6]
8 = FULLY ASSEM. TO BLACK DDX VALVE, WITH CONTROL VALVE
9 = FULLY ASSEM. TO RED DDX VALVE, WITH CONTROL VALVE
A= FULLY ASSEM. TO RED CCC APPROVED DDX VALVE, WITH CONTROL VALVE[6,7]

1ST	2ND	3RD	4TH	5TH	6TH	7TH	8TH	9TH	10TH
6	5	2	4	G	0	8	1	0	0

SOLENOID VALVE
1 = 175 PSI
2 = 300 PSI
3 = 175 PSI, EXPLOSION PROOF
4 = 300 PSI, EXPLOSION PROOF

SYSTEM PRESSURE SWITCH[7]
0 = NONE
1 = POTTER FM, cULus APPROVED
2 = SYSTEM SENSOR FM/UL APPROVED
3 = SYSTEM SENSOR FM/ULC APPROVED
4 = POTTER, EXPLOSION PROOF

NOTES:
1. FOR THE 4TH DIGIT, SELECT "0" FOR LOOSE OR SEGMENTED TRIMS. 7TH DIGIT MUST BE "1", OR "3". FOR ANY 4TH DIGIT SELECTION OTHER THAN "0", THE 7TH HAS TO BE A FULLY-ASSEMBLED SELECTION ("4", "5" ...ETC).
2. STANDARD FLANGE TYPE IS CLASS 150 PER ASME B16.5.
3. NO SOLENOID VALVE REQUIRED, THE 8TH DIGIT MUST BE "0".
4. GALVANIZED PIPE FITTINGS ARE THE DEFAULT OFFERING. ALL OTHERS TRIM FINISHES ARE MAKE TO ORDER (MTO).
5. FOR LOOSE AND SEGMENTED ASSEMBLED TRIM CONFIGURATIONS, THE DDX VALVE IS SOLD SEPARATELY (SEE BULLETIN 519 FOR DDX VALVE'S PART NUMBER).
6. CHINA COMPULSORY CERTIFICATE FOR FIRE PRODUCTS.
7. FLANGED VALVES ARE NOT AVAILABLE WITH A CONTROL VALVE (REFER TO DIGIT #7).
8. (ENTPTY)
9. 76 MM AND 165 MM ARE NOT AVAILABLE WITH A CONTROL VALVE (REFER TO DIGIT #7).

MODEL DDX 4", 6" & 8" DELUGE NON-INTERLOCK

CA-335 P/N 89241312

ASSEMBLY P/N 6520G01110 REV. -

ITEM NO.	PART NO.	DESCRIPTION	REMARKS	QTY.
38	89141112	TIE, RETAINING		9
37	6990003756	SWITCH, POTTER PRESSURE (PS40-EX)	(ULC, UL, FM)	1
	6990019313	SWITCH, POTTER PRESSURE (PS25-2)	(ULC, UL, FM)	
	6959992361	SWITCH, PRESSURE (EPSA40-2)	(ULC)	
	6959991340	SWITCH, PRESSURE (EPS40-2)	(UL/FM)	
36	6990012997	SWITCH, POTTER PRESSURE (PS10-EX)	(ULC, UL, FM)	1
	6990006382	SWITCH, POTTER PRESSURE (PS10-2)	(ULC, UL, FM)	
	6959992360	SWITCH, PRESSURE (EPSA10-2)	(ULC)	
	6959991212	SWITCH, PRESSURE (EPS10-2)	(UL/FM)	
35	96686756	TUBNG, PVC, 3/8 I.D. x 6 FT.		1
34	95516915	PERMA-LOK	NOT SHOWN	A/R
33	6811020033	VALVE, SOLENOID, 300 PSI, EXPLOSION PROOF		1
	6959990322	VALVE, SOLENOID, 175 PSI, EXPLOSION PROOF		
	6811020020	VALVE, SOLENOID, 300 PSI		
	6811020000	VALVE, SOLENOID, 175 PSI		
32	96840228	VALVE, RELIEF, 1/2", 50 PSI		1
31	96840237	VALVE, BALL, 1/4" NPTF x 1/4" NPTM		1
30	96815204	UNION, ORING SEAL, GALV., 1/2		1
29	96815200	UNION, 1/2, IRON, G.J., GALV.		1
28	9676165I	TEE,1/2XI/2XI/2,GALVANIZED		1
27	71000266	SUB-ASSEMBLY, TRIM, BASE, GALVANIZED PIPE		1
26	96604406	PIPE, PLUG, IRON, SQUARE HEAD, 1/2		2
25	95080002	PAD-ADHESIVE, VALVE NAME PLATES		1
24	94616916	NAMEPLATE, DRY PIPE VALVE		1
23	71030010	MODEL LP PILOT LINE ACTUATOR		1
22	91004300	MANIFOLD, DRAIN, BARBED, 6-3/8		1
21	96840181	HORIZ. SWING CHECK VALVE, 1/2" NPT		1
20	96248000	GAUGE, AIR PRESSURE (0-80 PSI)		1
19	96751004	FITTING, MULTIPORT, 1/2x1/2x1/2x1/2x1/2		1
18	96174408	ELBOW, STREET, 1/4", GALV.		1
17	96174400	ELBOW, STREET, 1/2", GALV.		1
16	96174700	ELBOW, SIDE OUTLET, 1/2", 90° GALV.		1
15	96174404	ELBOW, 1/4", MALL IRON, GALV.		1
14	92056704	CONNECTOR, ELBOW, 3/8" ID TUBE x 1/2" NPT		3
13	95306255	CLAMP, HOSE, 1/2" CONSTANT TENSION, ZINC		10
12	96048022	BUSHING, REDUCER, 3/4XI/2, GALVANIZED		1
11	96048000	BUSHING, REDUCER, 1/2XI/4, GALVANIZED		1
10	96543217	NIPPLE,1/4X6,GALVANIZED STEEL		1
9	96543212	NIPPLE,1/2CLOSE,GALVANIZED STEEL		1
8	96543216	NIPPLE,1/2X3-1/2,GALVANIZED STEEL		1
7	96543223	NIPPLE,1/2XI-1/2,GALVANIZED STEEL		2
6	96543209	NIPPLE,1/2X2,GALVANIZED STEEL		2
5	96543230	NIPPLE,1/2X3,GALVANIZED STEEL	4" & 6" VERSION	1
	96543202	NIPPLE,1/2X5-1/2,GALVANIZED STEEL	8" VERSION	
4	96543209	NIPPLE,1/2X2,GALVANIZED STEEL	4" & 6" VERSIONS	1
	96543230	NIPPLE,1/2X3,GALVANIZED STEEL	8" VERSION	
3	96543230	NIPPLE,1/2X3,GALVANIZED STEEL	4" VERSION	1
	96543228	NIPPLE,1/2X4-1/2,GALVANIZED STEEL	6" VERSION	
	96543204	NIPPLE,1/2X6,GALVANIZED STEEL	8" VERSION	
2	77000308	SUBASSEMBLY, CONTROL VALVE, 8"	FULLY ASSEMBLED WITH CONTROL VALVE ONLY	1
	77000306	SUBASSEMBLY, CONTROL VALVE, 6"		
	77000304	SUBASSEMBLY, CONTROL VALVE, 4"		
1	SEE DDX VALVE P/N TABLE			1

BILL OF MATERIALS



THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO THE RELIABLE AUTOMATIC SPRINKLER CORP. IT MAY NOT BE REPRODUCED NOR MAY ANY INFORMATION HEREON BE DISCLOSED TO OTHERS WITHOUT THE SPECIFIC WRITTEN PERMISSION OF RELIABLE

MTL: N/A
FINISH:

DO NOT SCALE DRAWING
REMOVE BURRS, BREAK SHARP EDGES
TOLERANCE UNLESS OTHERWISE SPECIFIED:
ANGLE ± 1/2° 63 MACH. FINISH
CONC. TIR.
SQUARENESS - PARALLELISM
FRACT. ± 1/32 [0.79]
DEC. XX ± .010 [0.25]
DEC. XXX ± .005 [0.13]
1884P

THE RELIABLE AUTOMATIC SPRINKLER CO., INC.
LIBERTY, S.C.

PART NO: VARIOUS — DWG.SIZE: E
PART: ASSEMBLY, TRIM, NON-INTERLOCK
PRODUCT: DDX, 4", 6", 8"

FILE NO:	ENG:	DRW BY:	CK'D:
6520G01110	JJ	MK	-
	SCALE: 1:4	DATE: 03/13/23	SHEET: 2 of 3

REVISIONS			
LTR	DESCRIPTION	DATE	DRAWN BY
	SEE PAGE 1		

MODEL DDX 4", 6", 8" BASIC TRIMS

SUBASSEMBLY P/N 77000266 REV. M











ITEM NO.	PART NO.	DESCRIPTION	REMARKS	QTY.
42	95516915	PERMA-LOK	NOT SHOWN	A/R
41	98543216	NIPPLE, STEEL, GALV., 1/2" X 3-1/2"	4" & 6" VERSIONS	1
	98543205	NIPPLE, STEEL, GALV., 1/2" X 9"	8" VERSION	
40	98543224	NIPPLE, STEEL, GALV., 1/4" X 4-1/2"	4" & 6" VERSIONS	1
	98543217	NIPPLE, STEEL, GALV., 1/4" X 6"	8" VERSION	
39	SEE P/N TABLE	ASSEMBLY, BALL DRIP, 1/2"		1
38	98840111A	VALVE, BALL, 1/2 NPTF X 1/2 NPTM		1
37	9101423B	MANIFOLD, 2 X 2 X 1, GRV/THD/THD		1
36	98840237	VALVE, BALL, 1/4" NPTF x 1/4" NPTM		3
35	98840188	VALVE, CHECK, 1/4" NPTM x 1/4" NPTF		1
34	98840147	CHECK VALVE, 1/4, NPT, POPPET TYPE INLINE		1
33	98840246	VALVE, SWING CHECK, F-F, 1 NPT, TIEMME		1
32	98840136	VALVE, BALL, 2"		1
31	98840103	VALVE, ANGLE, 1/2"		1
30	98815201	UNION, 1/4, IRON, G.J., GALV.		1
29	98815200	UNION, 1/2, IRON, G.J., GALV.		2
28	98761651	TEE,1/2X1/2X1/2,GALVANIZED		1
27	98761649	TEE,1/2X1/4X1/2,GALVANIZED		1
26	98751005	FITTING, MULTIPORT, 3/4x1/2x1/2x1/2x1/2		1
25	98727607	STRAINER, 1/4"		1
24	98614403	PIPE, PLUG, IRON, SQUARE HEAD, 1/4		1
23	98614401	PIPE, PLUG, IRON, SQUARE HEAD, 3/4		1
22	98604406	PIPE, PLUG, IRON, SQUARE HEAD, 1/2		1
21	98543262	NIPPLE,2X3-1/2,GALVANIZED STEEL		1
20	98543238	NIPPLE,2XCLOSE,GALVANIZED STEEL		2
19	98543226	NIPPLE,1/4X1-1/2,GALVANIZED STEEL		1
18	98543225	NIPPLE,1/4X2-1/2,GALVANIZED STEEL		1
17	98543223	NIPPLE,1/2X1-1/2,GALVANIZED STEEL		7
16	98543209	NIPPLE,1/2X2,GALVANIZED STEEL		3
15	98248001	GAUGE, WATER PRESSURE (0-300 PSI)		2
14	98174408	ELBOW, STREET, 1/4", GALV.		1
13	98174405	ELBOW, 2", MALL IRON, GALV.		2
12	98174404	ELBOW, 1/4", MALL IRON, GALV.		2
11	98174400	ELBOW, STREET, 1/2", GALV.		1
10	98048022	BUSHING, REDUCER, 3/4X1/2, GALVANIZED		1
9	98048000	BUSHING, REDUCER, 1/2X1/4, GALVANIZED		1
8	96920944	HOSE, FLEXIBLE, STAINLESS STEEL, 1/4 NPT X 18 LONG		1
7	96920912	FLEX LINE, 12		1
6	98840243	VALVE, SWING CHECK, M-M, 1/2 NPT, TIEMME		1
5	96606607	TEE,1/2X1/2X1/4,GALVANIZED		1
4	92056810	CONNECTOR, 3/8" ID TUBE x 1/2" NPT		1
3	92056704	CONNECTOR, ELBOW, 3/8" ID TUBE x 1/2" NPT		2
2	78653004	ASSEMBLY, VALVE CAUTION STATION, 1/2"		1
1	78653000	ASSEMBLY, MANUAL EMERGENCY STATION		1

BILL OF MATERIALS

PART NO. TABLE			
ASSEMBLY P/N	DESCRIPTION	BALL DRIP P/N	DESCRIPTION
77000266	SUB-ASSY, TRIM BASE	78653800	ASSEMBLY, MECHANICAL BALL DRIP 1/2"
77000267	SUB-ASSY, TRIM BASE (LPCB)	78653801	ASSEMBLY, SEMI-AUTOMATIC BALL DRIP, 1/2" LPCB

THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO THE RELIABLE AUTOMATIC SPRINKLER CO. IT MAY NOT BE REPRODUCED NOR MAY ANY INFORMATION HEREON BE DISCLOSED TO OTHERS WITHOUT THE SPECIFIC WRITTEN PERMISSION OF RELIABLE.

DO NOT SCALE DRAWING. REMOVE BURRS, BREAK SHARP EDGES

TOLERANCE UNLESS OTHERWISE SPECIFIED

ANGLE ± 1/2°
MACH. FINISH 63

FRACT. ± 1/32 [0.79]
DEC. XX ± .010 [0.25]
DEC. XXX ± .005 [0.13]

THE RELIABLE AUTOMATIC SPRINKLER CO., INC.
LIBERTY, S.C.

PART NO: SEE P/N TABLE | DWG.SIZE: C

PART: SUB-ASSEMBLY, TRIM, BASE, GALVANIZED PIPE

PRODUCT: DDX 4", 6", 8"

FILE NO: 77000266 | ENG: JJ | DRW BY: PH

SCALE: 1:6 | DATE: 07/13/17 | SHEET 2 of 2

MODEL DDX VALVE WITH STAINLESS STEEL SCREW-IN SEAT

IMPORTANT NOTE: Early generation 4" and 6" DDX valves may incorporate a brass drop-in seat. Prior to ordering replacement parts, confirm the presence of a stainless steel screw-in seat or brass drop-in seat. For replacement parts for valves with brass drop-in seat, please contact Reliable Sprinkler Company Technical Services (techserv@reliablesprinkler.com)





EXTERNAL RESET ASSEMBLY



Model DDX (Screw-In Seat Configuration) Deluge Valves Parts List

Item No.	Part No.								Part Description	QTY.	Material
	2" (50mm)	2½" (65mm)	76mm	3" (80mm)	4" (100mm)	165mm	6" (150mm)	8" (200mm)			
1	91006011	91006012	91006023	91006013	91006005	91006027	91006007	91006028	Valve Body Groove/Groove	1	Ductile Iron 65-45-12
	N/A	N/A	N/A	N/A	91006045	N/A	91006067	N/A	Valve Body Flange/Groove		
	N/A	N/A	N/A	N/A	91006035	N/A	91006037	91006039	Valve Body Flange/Flange		
2	N/A	N/A	N/A	N/A	N/A	N/A		95406414	O-ring (Mounting Ring)	1	Buna-N
3	71040416								Pushrod Cover Assembly	1	Ductile Iron 65-45-12 & Brass C360000
4	91106123				N/A	N/A		N/A	Hex Bolt ½"-13 x 1¼"	6	Zinc Plated Steel
	N/A				95606107	N/A		N/A	Hex Bolt ½"-13 x 1½"	6	
	N/A				N/A	91106006		N/A	Hex Bolt 5/8"-11 x 1¾"	6	
	N/A				N/A	N/A		95606110	Hex Bolt 5/8"-11 x 2"	8	
5	91306013				91306014	91306016		91306018	Mounting Ring	1	Stainless Steel CF8 or CF8M
6	91916003				91916014	91916016		91916008	Clapper	1	Stainless Steel CF8 or CF8M
7	92116063				92116064	92116065	92116066	92116068	Access Cover	1	Ductile Iron 65-45-12
8	93416003				93416014	93416016		93416008	Seal Assembly	1	Stainless Steel 304 & EPDM
9	93706003				93706004	93706006		93706008	Access Cover Gasket	1	Buna-N or Neoprene
10	93722000				93722000	N/A		N/A	Bumpstop Assembly	1	Stainless Steel UNS S31600 & EPDM
	N/A				N/A	93722000		N/A		2	
	N/A				N/A	N/A		93722000		3	
11	93916006								Pushrod Guide	1	Acetal
12	93916066								Reset Shaft	1	Brass UNS C36000
13	94106066								Reset Housing	1	Brass UNS C36000
14	94356006								Reset Knob	1	Aluminum 6061
15	94506003				94506004	94506016		94506008	Lever	1	Stainless Steel UNS S17400
16	95006412				94006412	95006410		95006410	Striker	1	Aluminum Bronze C95400
17	95106006								Piston	1	Stainless Steel CF8M
18	95276006								Diaphragm	1	EPDM & Polyester
19	95306267				N/A	N/A		N/A	Retaining Ring, 3/8" Shaft, Lever Pin	2	Stainless Steel 15-7 or 17-7
	N/A				95306267	N/A		N/A	Retaining Ring, ½" Shaft, Lever Pin		
	N/A				N/A	95306269		N/A	Retaining Ring, 5/8" Shaft, Lever Pin		
	N/A				N/A	N/A		95316408	Retaining Ring, ¾" Shaft, Lever Pin		
20	95306268				N/A	N/A		N/A	Retaining Ring, 3/8" Shaft, Hinge Pin	2	Stainless Steel 15-7 or 17-7
	N/A				95306267	95306267		N/A	Retaining Ring, ½" Shaft, Hinge Pin		
	N/A				N/A	N/A		95316408	Retaining Ring, ¾" Shaft, Hinge Pin		
21	95406007								O-Ring, Reset Housing ID	1	Buna-N
22	95406024								O-Ring, Reset Housing & Pushrod Guide OD	2	Buna-N
23	95406407								O-Ring, Pushrod Guide ID	1	Buna-N
24	95406410				95406409	95436126		95406413	O-Ring, Upper Seat	1	Buna-N
25	95406411				95406420	95446226		95406412	O-Ring, Lower Seat	1	Buna-N
26	95506006								Pushrod	1	Stainless Steel UNS S30300
27	95606114								Socket Head Screw, ¼"-20 x 5/8"	6	Steel
28	95606127								Flat Head Socket Cap Screw 3/8"-16 x ¾"	1	Steel
29	95606133				N/A	N/A		N/A	Socket Head Screw #6-32 x ½"	1	Stainless Steel 18-8
	N/A				95606130	95606130		95606130	Socket Head Screw #10-32 x 1"		Stainless Steel UNS S31600
30	96016003				96016014	96016016		96016008	Seat	1	Stainless Steel CF8M
31	96206003				N/A	N/A		N/A	Hinge Pin	1	Stainless Steel UNS S30400
	N/A				96216086	9216086		96206008			Stainless Steel UNS S21800
32	96216003				N/A	N/A		N/A	Lever Pin	1	Stainless Steel UNS S17400
	N/A				96216044	96216047		96216008			Stainless Steel UNS S21800
33	96310003				96906904	96906904		96310008	Clapper Spacer	2	Teflon or Acetal
34	96406003				N/A	N/A		N/A	Lever Spring	1	Stainless Steel UNS S30400
	N/A				96406004	96406005		96406008			Stainless Steel UNS S31600
35	96406906								Piston/ Reset Spring	2	Stainless Steel UNS S31600
36	96906112				N/A	N/A		N/A	Spring Lock Washer, #6	1	Stainless Steel 18-8
	N/A				96906111	96906111		96906111	Spring Lock Washer, #10		Stainless Steel UNS S31600
37	95606140				N/A	N/A		N/A	Flat Head Socket Cap Screw ¼"-20 x ½"	2	Stainless Steel 18-8
	N/A				95606139	N/A		N/A			Stainless Steel UNS S31600
	N/A				N/A	N/A		95606135	Flat Head Socket Cap Screw ½"-13 x ¾"		Stainless Steel UNS S31600
38	98604402								Plug, ½" NPT	1	Steel
39	94616921								Knob Caution Label (Not Shown)	1	Polystyrene
40	91556922								Ball Chain, 1/8" (Not Shown) (Length is in Inches)	6	Nickel Plated Brass
41	91556923								Clamping Link, Ball Chain (Not Shown)	1	
42	6999993406								O-Ring Grease, Dupont™ Krytox® GPL-205	A/R	Krytox®