

# MODEL RFC43

*Being held hostage by a 25 gpm maximum flow water meter?*

**Optimized for use with 25 gpm domestic water meters.**

Combined two-sprinkler flow of 24 gpm at coverage area of 15' x 15'.

Ordinary (165°F) and Intermediate (212°F) temperature ratings.

Cover plates available in both Standard (White, Chrome) and Special Application Finishes, including custom paint to match any décor.

Available in a low-lead version (RFC43LL) cULus Certified for Health Affects to NSF/ANSI Standard 61 Annex G.

Features "Wrench-able" protective cap: no need to remove cap during rough-in.

**See Technical Bulletin 006**

**Reliable®**

[www.reliablesprinkler.com/rfc43](http://www.reliablesprinkler.com/rfc43)

