



FP PUSH-ON/THREAD-OFF ESCUTCHEONS

Description	Part Number	Short Code	List Price
MODEL FP PUSH-ON/THREAD-OFF ESCUTCHEONS			
1/2" Chrome	6801412100	FPC	C\$ 37.38
1/2" White	6801417200	FPW	C\$ 37.38
1/2" Stainless Steel	6801411000	FPSS	C\$ 171.24
3/4" Chrome	6801402100	FPLC	C\$ 37.38
3/4" White	6801407200	FPLW	C\$ 37.38
3/4" Stainless Steel	6801401000	FPLSS	C\$ 171.24
MODEL F1 RECESSED ESCUTCHEONS & COLLAR ASSEMBLY			
1/2" Brass	6800630001	GF1B	C\$ 35.96
1/2" Chrome	6800600001	GF1C	C\$ 19.38
1/2" White	6800640001	GF1W	C\$ 19.38
1/2" Stainless Steel	6800610010	GF1SS	C\$ 114.15
3/4" Brass	6801030000	GF1LB	C\$ 35.96
3/4" Chrome	6801000000	GF1LC	C\$ 19.38
3/4" White	6801040000	GF1LW	C\$ 19.38
3/4" Stainless Steel	6800970010	GF1LSS	C\$ 114.15
MODEL F1 ESCUTCHEON ONLY			
Brass	6800430000	BZESCF1	C\$ 27.43
Chrome Bright	6800400000	CBESCF1	C\$ 11.67
White	6800440000	WHESCF1	C\$ 11.67
MODEL F1/F2 COLLAR ONLY			
1/2" Brass	6800530000	B2COLLAR12	C\$ 21.47
1/2" Chrome Bright	6800500000	CBCOLLAR12	C\$ 17.61
1/2" White	6800540000	WHCOLLAR12	C\$ 17.61
3/4" Brass	6800560004	B2COLLAR34	C\$ Call
3/4" Chrome Bright	6800560001	CBCOLLAR34	C\$ 17.61
3/4" White	6800551003	WHCOLLAR34	C\$ 17.61
ESCUTCHEON EXTENDER RING			
Chrome	6814002100	EERC	C\$ 24.92
White	6814001500	EERW	C\$ 26.56
MODEL F1 OR F2 EXTENDER RINGS			
4-1/2" Chrome	6814002100	EERC	C\$ 24.92
4-1/2" White	6814001500	EERW	C\$ 26.56
5-1/2" Chrome	6814042100	EERC5	C\$ 24.92
5-1/2" White	6814041500	EERW5	C\$ 26.56
FP / G5 / G4 / RFC / CCP / SWC COVERPLATE EXTENDER RINGS			
4-1/2" Chrome	6814022100	G4ERC	C\$ 24.92
4-1/2" White	6814021800	G4ERW	C\$ 26.56
5-1/2" Chrome	6814032100	G4ERC5	C\$ 24.92
5-1/2" White	6814031800	G4ERW5	C\$ 26.56

MODEL F2 RECESSED ESCUTCHEONS & COLLAR ASSEMBLY			
1/2" Brass	6800830000	GF2B	C\$ 35.96
1/2" Chrome	6800800000	GF2C	C\$ 19.38
1/2" White	6800840000	GF2W	C\$ 19.38
1/2" Stainless Steel	6800840010	GF2SS	C\$ 114.15
3/4" Brass	6800880004	GF2LB	C\$ 35.96
3/4" Chrome	6800880001	GF2LC	C\$ 19.38
3/4" White	6800880005	GF2LW	C\$ 19.38
3/4" Stainless Steel	6800880110	GF2LSS	C\$ 114.15
ESCUTCHEON ONLY			
Brass	6800730000	BZESCF2	C\$ 27.24
Chrome	6800700000	CBESCF2	C\$ 17.56
White	6800740000	WHESCF2	C\$ 17.56
COLLAR ONLY			
1/2" Brass	6800530000	B2COLLAR12	C\$ 21.47
1/2" Chrome	6800500000	CBCOLLAR12	C\$ 17.61
1/2" White	6800540000	WHCOLLAR12	C\$ 17.61
3/4" Brass	6800560004	B2COLLAR34	C\$ Call
3/4" Chrome	6800560001	CBCOLLAR34	C\$ 17.61
3/4" White	6800551003	WHCOLLAR34	C\$ 17.61

Notes:

All SS Escutcheons are Type 316 Stainless Steel.
Other escutcheon finishes are available upon request.



B One Piece



C One Piece



HB Two Piece

ESCUTCHEONS (CONT.)

- Sprinkler Accessories

F1S ESCUTCHEON



F2S ESCUTCHEON

- See Bulletin 204

NEW



SURE-OFF TESTER

- See Bulletin 277

The simple way to determine if the system you are about to work on has been shut-off and drained!

1.800.431.1588
www.reliablesprinkler.com

Description	Size	Part Number	Short Code	List Price
MODEL B ONE PIECE TYPE 1/2"				
Bronze	1/2"	6800110000	BB	C\$ 8.01
Chrome	1/2"	6800150000	BC	C\$ 5.50
White	1/2"	6800120000	BW	C\$ 6.20
Stainless Steel	1/2"	6800121002	BSS	C\$ 68.52
MODEL B ONE PIECE TYPE 3/4"				
Bronze	3/4"	6800080000	BLB	C\$ 8.45
Chrome	3/4"	6800070000	BLC	C\$ 5.92
White	3/4"	6800090000	BLW	C\$ 5.92
Stainless Steel	3/4"	6800091002	BLSS	C\$ 68.52
MODEL C ONE PIECE TYPE 1/2"				
Bronze	1/2"	6800340000	CBB	C\$ 61.03
Chrome	1/2"	6800350000	CC	C\$ 5.88
White	1/2"	6800380000	CW	C\$ 5.88
MODEL HB TWO PIECE TYPE 1/2"				
Bronze	1/2"	6800210000	HBB	C\$ 13.96
Chrome	1/2"	6800270000	HBC	C\$ 12.57
White	1/2"	6800200000	HBW	C\$ 13.02
MODEL HB TWO PIECE TYPE 3/4"				
Bronze	3/4"	6800220000	HBLB	C\$ 14.40
Chrome	3/4"	6800240000	HBLC	C\$ 13.02
White	3/4"	6800250000	HBLW	C\$ 13.96

Chrome	1/2" (15mm)	6801752100	F1SC	C\$ 34.48
White	1/2" (15mm)	6801758700	F1SW	C\$ 34.48
Chrome	3/4" (20mm)	6801762100	F1SLC	C\$ 34.48
White	3/4" (20mm)	6801768700	F1SLW	C\$ 34.48
MODEL F2S TWO PIECE RECESSED ESCUTCHEONS				
Chrome	1/2" (15mm)	6801772100	F2SC	C\$ 34.48
White	1/2" (15mm)	6801778700	F2SW	C\$ 34.48
Chrome	3/4" (20mm)	6801782100	F2SLC	C\$ 34.48
White	3/4" (20mm)	6801788700	F2SLW	C\$ 34.48

Description	Part Number	Short Code	List Price
PRESSURE TESTER			
Sure-Off Tester 1"	6501220000	SURE	C\$ 2,754.51
Sure-Off Tester 1 1/4 - 1 1/2"	6501220002	SURE125	C\$ 2,754.51
Sure-Off Tester 2"	6501220003	SURE2	C\$ 2,754.51
Drill & Collar Assembly	6888000011		C\$ 372.36
Guide Bushing, Drill, Reducer	94905000		C\$ 123.36

Sprinkler Accessories

Description	Part Number	Short Code	List Price
SPRINKLER GUARDS & WATER SHIELD/GUARD ASSEMBLY			
C1,GUARD,SU,SP,HORIZONTAL,ZINC,FM ONLY	6802251400	GC1	C\$ 19.82
C1,GUARD,SU,SP,HORIZONTAL,SS,FM ONLY	6802251000	GC1SS	C\$ 198.02
C2,GUARD,DRY PENDENTS,UL/FM	6802201400	GC2	C\$ 27.48
C3,GUARD,SHIELD,UPRIGHT-I,ZINC,UL/FM	6802501400	GC3	C\$ 40.57
C5,GUARD/SHIELD KIT,SP-I,1/2,ZINC,FM	6802611412	GC51	C\$ 56.70
C5,GUARD/SHIELD KIT,SP-I,3/4,ZINC,FM	6802611434	GC53	C\$ 56.70
D1,GUARD,SU/SP/HORIZONTAL,UL/FM ZINC	6802251410	GD1	C\$ 27.20
D3,GUARD/SHIELD KIT,SU-I,ZINC,UL ONLY	6802501410	GD3	C\$ 32.16
D5,GUARD/SHIELD KIT,SP-I,1/2,ZINC,UL	6802631412	GD51	C\$ 61.75
D5,GUARD/SHIELD KIT,SP-I,3/4,ZINC,UL	6802631434	GD53	C\$ 61.75
D4,GUARD/SHIELD KIT,SP-I,1/2,ZINC,UL	6802621412	GD41	C\$ 69.20
D4,GUARD/SHIELD KIT,SP-I,3/4,ZINC	6802621434	GD43	C\$ 69.20
D-7 for use w/ GL112 Upright Intermediate	6802611614	GD7	C\$ 32.16
D-8 for use w/ GL112 & GXLO Pendent	6802251714	GD8	C\$ 27.20
D-9 for use w- GL112 & GXLO Pendent Intermediate	6802621714	GD91	C\$ 61.75
D-6 for use w/ GXLO Upright Intermediate	6802611514	GD6	C\$ 30.53
F-6,GUARD/SHIELD KIT,3/4 NPS,ZINC	68026A1434	GF63	C\$ 65.65
F-1,GUARD,ZINC	6802651400	GF1	C\$ 27.20
F-2,GUARD,ZINC	6802661400	GF2	C\$ 57.44
F-3,GUARD,SHIELD	6802671400	GF3	C\$ 57.44
F-7,GUARD,ZINC	6802701400	GF7	C\$ 57.44
F-8,GUARD/SHIELD KIT,1/2 NPS,ZINC	68026B1412	GF81	C\$ 65.65
F-8,GUARD/SHIELD KIT,3/4 NPS,ZINC	68026B1434	GF83	C\$ 65.65
22 - (guard only) for use w/ HL22 ESFR	6802641422	G22	C\$ 61.55
25 - (guard only) for use w/ N25 ESFR	6802641425	G25	C\$ 61.55
D14,GUARD KIT,ZINC,SP,FM P22/P25	6802622514	GD14	C\$ 61.55
RELIABLE MODEL RHB1 SPARE SPRINKLER STORAGE CABINET			
RASCO,RHB1 HEADBOX 3 COUNT	7M99005006	RHB3	C\$ 117.54
RASCO,RHB1 HEADBOX 6 COUNT	7M99005007	RHB6	C\$ 179.68
RASCO,RHB1 HEADBOX 6 COUNT ESFR	7M99005008	RHB6E	C\$ 218.30
RASCO,RHB1 HEADBOX 12 COUNT	7M99005009	RHB12	C\$ 199.83
RASCO,RHB1 HEADBOX 24 COUNT	7M99005010	RHB24	C\$ 308.97
RASCO,RHB1 HEADBOX 36 COUNT	7M99005011	RHB36	C\$ 428.20
A3 EMERGENCY CABINETS FOR RECESSED, CONCEALED & ZX SPK			
12 Capacity	6803200000	A312CAB	C\$ 905.37

Sprinkler Accessories

Description	Part Number	Short Code	List Price
MODEL F SERIES SPRINKLER GUARDS & WATER SHIELD/GUARD ASSEMBLY			
F-1,GUARD,ZINC	6802651400	GF1	C\$ 27.20
F-2,GUARD,ZINC	6802661400	GF2	C\$ 57.44
F-3,GUARD,SHIELD	6802671400	GF3	C\$ 57.44
F-4,GUARD,ZINC	6802681400	GF4	C\$ 57.44
F-5,GUARD/SHIELD KIT,1/2 NPS,ZINC	6802691412	GF51	C\$ 65.65
F-6,GUARD/SHIELD KIT,3/4 NPS,ZINC	68026A1434	GF63	C\$ 65.65
F-7,GUARD,ZINC	6802701400	GF7	C\$ 57.44
F-8,GUARD/SHIELD KIT,1/2 NPS,ZINC	68026B1412	GF81	C\$ 65.65
F-8,GUARD/SHIELD KIT,3/4 NPS,ZINC	68026B1434	GF83	C\$ 65.65
MODEL S WATER SHIELDS			
MODEL S-1 SHIELD,3.25,1/2-14NPS, GALV	88709001	S1SHIELD	C\$ 23.54
MODEL S-2 SHIELD,3.25,3/4-14NPS, GALV	88709002	S2SHIELD	C\$ 23.54
MODEL S-3 SHIELD,3.75,3/4-14NPS, GALV	88709003	S3SHIELD	C\$ 23.54
MODEL S-5 SHIELD,4.5,1"NPS,GALV	887G9010	S5SHIELD	C\$ 23.54

Notes:

For additional info see Bulletin 208



Description	Part Number	Short Code	List Price
STANDARD WRENCHES			
WRENCH,DS56	6880130002	WDS56	C\$407.20
WRENCH,F3R,DRY	6880130001	WF3R	C\$307.65
WRENCH,H,XLO/GL112,BLUE	6880070000	WH	C\$233.02
WRENCH,J1,SPKR J112,J14,J17,ZINC.	6880090000	WJ1	C\$233.02
WRENCH,W2(PENDENT,UPRIGHT,HSW)	6880050100	WW2	C\$195.92
WRENCH, W8, RFC PLASTIC SERVICE WRENCH	6880050105	WW5	C\$233.02
WRENCH,W13	6880108000	W13	C\$276.00
WRENCH,W14	6880108100	W14	C\$276.00
WRENCH,W15 (USE WITH GUARD)	6880108200	W15	C\$276.00
WRENCH,W16	6880108300	W16	C\$233.02
RECESSED & CONCEALED WRENCHES			
WRENCH,FC,CONCEALED	6880170020	WFC	C\$584.51
WRENCH,G4,CONCEALED,ADJ,SP	6880170000	WG4	C\$579.13
WRENCH,GFR2,RECESSED,CONCEALED,SP	6880060000	WGFR	C\$581.40
WRENCH,G6 HSW SOCKET	6880101010	WG6	C\$579.13
WRENCH,N,RECESSED	6880170030	WN	C\$579.13
WRENCH,RC1 SOCKET,RECESSED	6880100000	WRC	C\$581.40
WRENCH,RJ,J112/J112 REC CHROME	6880170032	WRJ	C\$579.13
WRENCH,W1 (RECESSED PENDENT,CCP,& HSW)	6880100100	WW1	C\$581.40
WRENCH W3 FOR WRENCH-ABLE PROTECTIVE CAP	6880100110	W3	C\$584.51
WRENCH,W4,RECESSED,CONCEALED	6880100120	WW4	C\$581.40
WRENCH,W10,WITH PROTECTIVE CAP,RFC49+	6880105000	W10	C\$584.51
WRENCH,XLO2,REC,CONCEALED SP	6880070100	WXLO	C\$305.39
WRENCH,XL,ZX,PENDENT	6880160000	WZXP	C\$579.13
WRENCH,XL,ZX,HORIZONTAL	6880160010	WZXH	C\$579.13
LIMITED SERVICE WRENCHES			
WRENCH,W8, RFC PLASTIC SERVICE WRENCH	6880103000	W8	C\$362.45
WRENCH,W11,PLASTIC,RFC49+	6880107000	W11	C\$362.45

Notes:

Each sprinkler bulletin will show required wrench

WRENCHES

- See Bulletin 205

PRINTED COVERPLATES


• See Bulletin 203



Slate Grey



Warm Maple



Dark Walnut



Silver Birch

Note: Please see Bulletin 203 for additional finishes

Part Number	Short Code	Temperature		Finish	List Price
MODEL G6 PRINTED COVERPLATES					
688721139A		135°F	57°C	Custom Ink	C\$ 98.95
688721139B		135°F	57°C	White Wash	C\$ 95.39
688721139C		135°F	57°C	Silver Birch	C\$ 95.39
688721139D		135°F	57°C	Beige Birch	C\$ 95.39
688721139E		135°F	57°C	Weathered Grey	C\$ 95.39
688721139F		135°F	57°C	Slate Grey	C\$ 95.39
688721139G		135°F	57°C	Golden Pine	C\$ 95.39
688721139H		135°F	57°C	Red Oak	C\$ 95.39
688721139J		135°F	57°C	Red Cherry	C\$ 95.39
688721139K		135°F	57°C	Warm Maple	C\$ 95.39
688721139M		135°F	57°C	Dark Walnut	C\$ 95.39
688721139N		135°F	57°C	Espresso	C\$ 95.39
688721139P		135°F	57°C	Rustic Beige	C\$ 95.39
MODEL RFS42 PRINTED COVERPLATES					
688723139A		135°F	57°C	Custom Ink	C\$ 99.87
688723139B		135°F	57°C	White Wash	C\$ 96.26
688723139C		135°F	57°C	Silver Birch	C\$ 96.26
688723139D		135°F	57°C	Beige Birch	C\$ 96.26
688723139E		135°F	57°C	Weathered Grey	C\$ 96.26
688723139F		135°F	57°C	Slate Grey	C\$ 96.26
688723139G		135°F	57°C	Golden Pine	C\$ 96.26
688723139H		135°F	57°C	Red Oak	C\$ 96.26
688723139J		135°F	57°C	Red Cherry	C\$ 96.26
688723139K		135°F	57°C	Warm Maple	C\$ 96.26
688723139M		135°F	57°C	Dark Walnut	C\$ 96.26
688723139N		135°F	57°C	Espresso	C\$ 96.26
688723139P		135°F	57°C	Rustic Beige	C\$ 96.26
MODEL G5 PRINTED COVERPLATES					
688727139A		135°F	57°C	Custom Ink	C\$ 92.77
688727139B		135°F	57°C	White Wash	C\$ 89.43
688727139C		135°F	57°C	Silver Birch	C\$ 89.43
688727139D		135°F	57°C	Beige Birch	C\$ 89.43
688727139E		135°F	57°C	Weathered Grey	C\$ 89.43
688727139F		135°F	57°C	Slate Grey	C\$ 89.43
688727139G		135°F	57°C	Golden Pine	C\$ 89.43
688727139H		135°F	57°C	Red Oak	C\$ 89.43
688727139J		135°F	57°C	Red Cherry	C\$ 89.43
688727139K		135°F	57°C	Warm Maple	C\$ 89.43
688727139M		135°F	57°C	Dark Walnut	C\$ 89.43
688727139N		135°F	57°C	Espresso	C\$ 89.43
688727139P		135°F	57°C	Rustic Beige	C\$ 89.43
688727169A		165°F	74°C	Custom Ink	C\$ 92.77
688727169B		165°F	74°C	White Wash	C\$ 89.43
688727169C		165°F	74°C	Silver Birch	C\$ 89.43
688727169D		165°F	74°C	Beige Birch	C\$ 89.43
688727169E		165°F	74°C	Weathered Grey	C\$ 89.43
688727169F		165°F	74°C	Slate Grey	C\$ 89.43
688727169G		165°F	74°C	Golden Pine	C\$ 89.43
688727169H		165°F	74°C	Red Oak	C\$ 89.43
688727169J		165°F	74°C	Red Cherry	C\$ 89.43
688727169K		165°F	74°C	Warm Maple	C\$ 89.43
688727169M		165°F	74°C	Dark Walnut	C\$ 89.43
688727169N		165°F	74°C	Espresso	C\$ 89.43
688727169P		165°F	74°C	Rustic Beige	C\$ 89.43



**MODEL G1
 CONCEALED
 REPLACEMENT
 COVERPLATES**

Part Number	Short Code	Temperature		Finish	List Price
MODEL G1 CONCEALED COVERPLATES - REQUIRED					
6887001311	CG10B	135°F	57°C	Finished Bronze	C\$ 129.79
6887001321	CG10C	135°F	57°C	Chrome	C\$ 95.26
6887001372	CG10W	135°F	57°C	White	C\$ 95.26
6887001390	CG10SP	135°F	57°C	Special Paint	C\$ 139.64
6887001611	CG11B	165°F	74°C	Finished Bronze	C\$ 134.57
6887001621	CG11C	165°F	74°C	Chrome	C\$ 95.26
6887001672	CG11W	165°F	74°C	White	C\$ 95.26
6887001690	CG11SP	165°F	74°C	Special Paint	C\$ 139.64

6880100000 WRC Requires Model RC1 Sprinkler Wrench C\$ 581.40

***Model G1 Concealed Sprinkler is Obsolete.**
***Please note special paint is subject to a paint set-up charge.**