

FLEXIBLE DROPS



Description	Part Number	Short Code	Box Qty	List Price
BRAIDED - UL & FM APPROVED				
RASCOFLEX,#RFB24H,1/2"X24",BRAIDED HOSE	7M99003288	RFLEX24BR	20	C\$ 178.12
RASCOFLEX,#RFB24T,3/4"X24",BRAIDED HOSE	7M99003289	RFLEX24LBR	20	C\$ 178.12
RASCOFLEX,#RFB31H,1/2"X31",BRAIDED HOSE	7M99003290	RFLEX31BR	20	C\$ 187.12
RASCOFLEX,#RFB31T,3/4"X31",BRAIDED HOSE	7M99003291	RFLEX31LBR	20	C\$ 187.12
RASCOFLEX,#RFB40H,1/2"X40",BRAIDED HOSE	7M99003292	RFLEX40BR	20	C\$ 212.93
RASCOFLEX,#RFB40T,3/4"X40",BRAIDED HOSE	7M99003293	RFLEX40LBR	20	C\$ 212.93
RASCOFLEX,#RFB48H,1/2"X48",BRAIDED HOSE	7M99003294	RFLEX48BR	20	C\$ 245.39
RASCOFLEX,#RFB48T,3/4"X48",BRAIDED HOSE	7M99003295	RFLEX48LBR	20	C\$ 245.39
RASCOFLEX,#RFB60H,1/2"X60",BRAIDED HOSE	7M99003296	RFLEX60BR	20	C\$ 285.68
RASCOFLEX,#RFB60T,3/4"X60",BRAIDED HOSE	7M99003297	RFLEX60LBR	20	C\$ 285.68
RASCOFLEX,#RFB72H,1/2"X72",BRAIDED HOSE	7M99003298	RFLEX72BR	20	C\$ 328.88
RASCOFLEX,#RFB72T,3/4"X72",BRAIDED HOSE	7M99003299	RFLEX72LBR	20	C\$ 328.88
ALL WELD BRAIDED - UL & FM APPROVED				
RASCOFLEX,#RFBW24H,1/2"X24",BRD,WELD HSE	7M99004655	RFLEX24BRW	20	C\$ 167.25
RASCOFLEX,#RFBW24T,3/4"X24",BRD,WELD HSE	7M99004656	RFLEX24LBRW	20	C\$ 167.25
RASCOFLEX,#RFBW31H,1/2"X31",BRD,WELD HSE	7M99004657	RFLEX31BRW	20	C\$ 175.70
RASCOFLEX,#RFBW31T,3/4"X31",BRD,WELD HSE	7M99004658	RFLEX31LBRW	20	C\$ 175.70
RASCOFLEX,#RFBW40H,1/2"X40",BRD,WELD HSE	7M99004659	RFLEX40BRW	20	C\$ 199.93
RASCOFLEX,#RFBW40T,3/4"X40",BRD,WELD HSE	7M99004660	RFLEX40LBRW	20	C\$ 199.93
RASCOFLEX,#RFBW48H,1/2"X48",BRD,WELD HSE	7M99004661	RFLEX48BRW	20	C\$ 230.42
RASCOFLEX,#RFBW48T,3/4"X48",BRD,WELD HSE	7M99004662	RFLEX48LBRW	20	C\$ 230.42
RASCOFLEX,#RFBW60H,1/2"X60",BRD,WELD HSE	7M99004663	RFLEX60BRW	20	C\$ 268.25
RASCOFLEX,#RFBW60T,3/4"X60",BRD,WELD HSE	7M99004664	RFLEX60LBRW	20	C\$ 268.25
RASCOFLEX,#RFBW72H,1/2"X72",BRD,WELD HSE	7M99004665	RFLEX72BRW	20	C\$ 308.82
RASCOFLEX,#RFBW72T,3/4"X72",BRD,WELD HSE	7M99004666	RFLEX72LBRW	20	C\$ 308.82
BRACKETS				
RASCOFLEX,#RF24BRKT,24",BRACKET	7M99003300	RFLEXBRACKET	20	C\$ 98.08
RASCOFLEX,#RF48BRKT,48",BRACKET	7M99003301	RFLEXBRACKET48	20	C\$ 108.43
NIPPLE ADAPTORS				
RASCOFLEX,#R610H,1X1/2",REDUCER(6.10")	7M99003308	RFLEX61H		C\$ 55.26
RASCOFLEX,#R610T,1"X3/4",REDUCER(6.10")	7M99003327	RFLEX61T		C\$ 55.26
ELBOW ADAPTORS				
RASCOFLEX,#RFSHORTELL12,1/2",ELL ADPT2	7M99003303	RFLEXS		C\$ 55.26
RASCOFLEX,#RFSHORTELL34,3/4",ELL ADPT2	7M99003305	RFLEX34S		C\$ 55.26
RASCOFLEX,#RFLONGELL12,1/2",ELL ADPT2	7M99003302	RFLEXL		C\$ 61.13
RASCOFLEX,#RFLONGELL34,3/4",ELL ADPT2	7M99003304	RFLEX34L		C\$ 61.13
STREAMLINE DRAIN HOSES				
RASCOFLEX,#RFDH12524TU,1.25"X2",MNPTXUN	7M99004448		Call	C\$ 492.45
RASCOFLEX,#RFDH12548TU,1.25"X4",MNPTXUN	7M99004449		Call	C\$ 621.03
RASCOFLEX,#RFDH248TG,2"X48",MNPTXGRV	7M99004450		Call	C\$ 705.80
RASCOFLEX,#RFDH124TU,1"X2",MNPTXUNION	7M99004675		Call	C\$ 452.35
RASCOFLEX,#RFDH12536TU,1.25"X3",MNPTXUN	7M99004676		Call	C\$ 584.53

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

FLEXIBLE DROPS



Description	Part Number	Short Code	List Price
RASCOFLEX ACCESSORIES			
RASCOFLEX,#R433H,1X1/2",REDUCER(4.33")	7M99003306	RFLEX433H	C\$ 43.51
RASCOFLEX,#R533H,1X1/2",REDUCER(5.33")	7M99003307	RFLEX533H	C\$ 49.38
RASCOFLEX,#R700H,1X1/2",REDUCER(7.00")	7M99004856	RFLEX700H	C\$ 61.08
RASCOFLEX,#R1181H,1X1/2",REDUCER(11.81")	7M99003309	RFLEX1181H	C\$ 102.29
RASCOFLEX,#R433T,1"X3/4",REDUCER(4.33")	7M99003325	RFLEX433T	C\$ 43.51
RASCOFLEX,#R533T,1"X3/4",REDUCER(5.33")	7M99003326	RFLEX533T	C\$ 49.38
RASCOFLEX,#R700T,1X3/4",REDUCER(7.00")	7M99004869	R700T	C\$ 61.08
RASCOFLEX,#R1181T,1"X3/4",REDUCR(11.81")	7M99003328	RFLEX1181T	C\$ 102.29
RASCOFLEX,#HCS,HAT CHANNEL,SHORT(2.99")	7M99003310	RFLEXHCS	C\$ 31.73
RASCOFLEX,#HCL,HAT CHANNEL,LONG(3.77")	7M99003311	RFLEXHCL	C\$ 31.73
RASCOFLEX,#MSBS,MTL STD BRKT,SHRT(1.49")	7M99003312	RFLEXMSBS	C\$ 5.29
RASCOFLEX,#MSBL,MTL STD BRKT,LNG(2.09")	7M99003313	RFLEXMSBL	C\$ 11.77
RASCOFLEX,#TBBS,T-BAR BRKT,SHORT(2.68")	7M99003314	RFLEXTBBS	C\$ 12.00
RASCOFLEX,#TBBM,T-BAR BRKT,MED(3.07")	7M99003315	RFLEXTBBM	C\$ 15.88
RASCOFLEX,#TBBL,T-BAR BRKT,LONG(4.13")	7M99003316	RFLEXTBBL	C\$ 19.97
RASCOFLEX,#WBB,WOOD BEAM BRKT	7M99003317	RFLEXWBB	C\$ 14.69
RASCOFLEX,#SB25,STOCK BAR,25"	7M99003318	RFLEXSB25	C\$ 22.35
RASCOFLEX,#SB50,STOCK BAR,50"	7M99003319	RFLEXSB50	C\$ 36.44
RASCOFLEX,#CBO,CENTER BRACKET(OPEN)	7M99003321	RFLEXCBO	C\$ 49.38
RASCOFLEX,#NP1,1",NIPPLE(BRANCH)	7M99003322	RFLEXNP1	C\$ 24.12
RASCOFLEX,#NP125,1.25",NIPPLE	7M99003323	RFLEXNP125	C\$ 35.29
RASCOFLEX,#SB453,SIDE BRACKET(4.53")	7M99003324	RFLEXSB453	C\$ 34.10
RASCOFLEX,#BRT,BEND RADIUS TOOL(3")	7M99004179	RFLEXTOOL	C\$ 0.58
RASCOFLEX,#BRTS,BEND RADIUS TOOL(2")	7M99004943	RFLEXBRTS	C\$ 0.58
RASCOFLEX,#RFOR,REPLACEMENT O-RING	7M99004319	RFLEXORING	C\$ 2.94
RASCOFLEX,#RFDRIVER,BRACKET SCREW BIT	7M99004539	RFLEXDRIVER	C\$ 14.60

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.