



PRV DIAPHRAGM PRESSURE REGULATING VALVE

- See Bulletin 820
- 400 psi (27.6 Bar) Rated Pressure
- Adjusted with Pilot Operated Regulator
- Trim Includes Relief Valve
- No Trim Connections to Cover
- cULus listed and FM approved

| Description | Part Number | Short Code | List Price |
|---|-------------|------------|--------------|
| MODEL PRV DIAPHRAGM PRESSURE REGULATING VALVES | | | |
| 1-1/2" Groove/Groove (ANSI/AWWA C606) | 6507008000 | 15PRV | A\$14,588.17 |
| 1-1/2" Flange/Flange Class 150 (ASME B16.5) | 6507108000 | | A\$15,914.37 |
| 1-1/2" Flange/Flange Class 300 (ASME B16.5) | 6507208000 | | A\$15,914.37 |
| 1-1/2" Flange/Flange PN16 (ISO 7005-2) | 6507308000 | | A\$15,914.37 |
| 1-1/2" NPT Thread/Thread (ANSI/ASME B1.20.1) | 6507508000 | | A\$15,914.37 |
| 1-1/2" ISO7-1 Thread/Thread | 6507608000 | | A\$15,914.37 |
| 2" Groove/Groove (ANSI/AWWA C606) | 6507028000 | 2PRV | A\$14,588.17 |
| 2" Flange/Flange Class 150 (ASME B16.5) | 6507128000 | | A\$15,914.37 |
| 2" Flange/Flange Class 300 (ASME B16.5) | 6507228000 | | A\$15,914.37 |
| 2" Flange/Flange PN16 (ISO 7005-2) | 6507328000 | | A\$15,914.37 |
| 2" NPT Thread/Thread (ANSI/ASME B1.20.1) | 6507528000 | | A\$15,914.37 |
| 2" ISO7-1 Thread/Thread | 6507628000 | | A\$15,914.37 |
| 2-1/2" Groove/Groove (ANSI/AWWA C606) | 6507018000 | 25PRV | A\$16,909.01 |
| 76MM,PRV,GE,PRESS REG,W/O CV VERT RED | 6507078000 | | A\$16,909.01 |
| 2-1/2" Flange/Flange Class 150 (ASME B16.5) | 6507118000 | | A\$18,400.99 |
| 2-1/2" Flange/Flange Class 300 (ASME B16.5) | 6507218000 | | A\$18,400.99 |
| 2-1/2" Flange/Flange PN16 (ISO 7005-2) | 6507318000 | | A\$18,400.99 |
| 2-1/2" NPT Thread/Thread (ANSI/ASME B1.20.1) | 6507518000 | | A\$18,400.99 |
| 2-1/2" ISO7-1 Thread/Thread | 6507618000 | | A\$18,400.99 |
| 3" Groove/Groove (ANSI/AWWA C606) | 6507038000 | 3PRV | A\$16,909.01 |
| 3" Flange/Flange Class 150 (ASME B16.5) | 6507138000 | | A\$18,400.99 |
| 3" Flange/Flange Class 300 (ASME B16.5) | 6507238000 | | A\$18,400.99 |
| 3" Flange/Flange PN16 (ISO 7005-2) | 6507338000 | | A\$18,400.99 |
| 3" NPT Thread/Thread (ANSI/ASME B1.20.1) | 6507538000 | | A\$18,400.99 |
| 3" ISO7-1 Thread/Thread | 6507638000 | | A\$18,400.99 |
| 4" Groove/Groove (ANSI/AWWA C606) | 6507048000 | 4PRV | A\$20,224.51 |
| 4" Flange/Flange Class 150 (ASME B16.5) | 6507148000 | | A\$22,048.03 |
| 4" Flange/Flange Class 300 (ASME B16.5) | 6507248000 | | A\$22,048.03 |
| 4" Flange/Flange PN16 (ISO 7005-2) | 6507348000 | | A\$22,048.03 |
| 6" Groove/Groove (ANSI/AWWA C606) | 6507068000 | 6PRV | A\$24,866.20 |
| 165MM Groove/Groove (ANSI/AWWA C606) | 6507058000 | | A\$24,866.20 |
| 6" Flange/Flange Class 150 (ASME B16.5) | 6507168000 | | A\$27,352.82 |
| 6" Flange/Flange Class 300 (ASME B16.5) | 6507268000 | | A\$27,352.82 |
| 6" Flange/Flange PN16 (ISO 7005-2) | 6507368000 | | A\$27,352.82 |

Notes:

Part numbers shown include a 185 psi (12.8 Bar) relief valve and 300 psi (20.7 Bar) gauges. Replace the last digit in the part number as follows for other relief valve and gauge combinations:

"0"-185 psi (12.8 Bar) relief valve and 300 psi (20 Bar) gauges

"1"-260 psi (17.9 Bar) relief valve and 300 psi (20 Bar) gauges

"2"-185 psi (12.8 Bar) relief valve and 600 psi (40 Bar) gauges

"3"-260 psi (17.9 Bar) relief valve and 600 psi (40 Bar) gauges