

Reliable Attic Sprinklers

- See Bulletin 056
- Specific Application
- Sprinklers for Sloped
- Combustible and Noncombustible
- Light Hazard Concealed Spaces



AH42 / AH56



DD56-6 / DD56-27



DS56



GP56



Part Number	Short Code	Temperature		Finish	List Price
MODEL AH42 UPRIGHT K4.2 (60) THREAD 1/2" RA5623 • Roof Slope = 4:12 to 8:12					
MN21112699	AH42	212°F	100°C	Brass	€ 81.52
MODEL AH56 UPRIGHT K5.6 (80) THREAD 1/2" RA5626 • Roof Slope = 4:12 to 8:12					
MN21112799	AH56	212°F	100°C	Brass	€ 81.52
MODEL DD56-6 UPRIGHT K5.6 (80) THREAD 1/2" RA5624 • Roof Slope = 4:12 to <6:12					
MN21113099	DD566	212°F	100°C	Brass	€ 441.98
MODEL DD56-27 UPRIGHT K5.6 (80) THREAD 1/2" RA5694 • Roof Slope = 6:12 to 8:12					
MN21113199	DD5627	212°F	100°C	Brass	€ 441.98
MODEL DS56 UPRIGHT K5.6 (80) THREAD 1/2" RA5625 • Roof Slope = 4:12 to 8:12					
MN21112899	DS56	212°F	100°C	Brass	€ 441.98
MODEL GP56 UPRIGHT K5.6 (80) THREAD 1/2" RA5695 • Roof Slope = 4:12 to 8:12					
MN21112999	GP56	212°F	100°C	Brass	€ 74.70
MODEL DD80-6 UPRIGHT K8.0 (115) THREAD 3/4" RA5622 • Roof Slope = 4:12 to <6:12					
MN21113398	DD806	212°F	100°C	Brass	€ 441.98
MODEL DD80-27 UPRIGHT K8.0 (115) THREAD 3/4" RA5692 • Roof Slope = 6:12 to 8:12					
MN21113498	DD8027	212°F	100°C	Brass	€ 441.98

6880130002	WDS56	Model DS56 Sprinkler Wrench - Model DS56	€ 290.32
6880050100	WW2	Model W2 Sprinkler Wrench - Models: AH42, AH56, DD56, DD80, & GP56	€ 139.68



LT56 PENDENT

- K-Factor = 5.6 (80)
- **SIN RA5814**
- See Bulletin 058
- Glass Bulb



LT56L PENDENT

- K-Factor = 5.6 (80)
- **SIN R5814**
- See Bulletin 058
- Link

LT56 300 PENDENT

- K-Factor = 5.6 (80)
- **SIN RA5914**
- See Bulletin 058
- Glass Bulb

LT56L-300 PENDENT

- K-Factor = 5.6 (80)
- **SIN R5914**
- See Bulletin 058
- Link

Part Number	Short Code	Temperature		Finish	List Price
MODEL LT56 PENDENT K5.6 (80) THREADS 1/2" (15MM) RA5814					
BY151132S9	LT56P1BN	155°F	68°C	Brass	€ 77.80
BY152132S9	LT56P1CN	155°F	68°C	Chrome	€ 85.60
BY158732S9	LT56P1WN	155°F	68°C	Poly White	€ 85.60
BY201132S9	LT56P2BN	200°F	93°C	Brass	€ 77.80
BY202132S9	LT56P2CN	200°F	93°C	Chrome	€ 85.60
BY208732S9	LT56P2WN	200°F	93°C	Poly White	€ 85.60
MODEL LT56L PENDENT K5.6 (80) THREADS 1/2" (15MM) R5814					
MY16113299	LT56LP1B	165°F	74°C	Brass	€ 77.80
MY16213299	LT56LP1C	165°F	74°C	Chrome	€ 85.60
MY16873299	LT56LP1W	165°F	74°C	Poly White	€ 85.60
MY21113299	LT56LP2B	212°F	100°C	Brass	€ 77.80
MY21213299	LT56LP2C	212°F	100°C	Chrome	€ 85.60
MY21873299	LT56LP2W	212°F	100°C	Poly White	€ 85.60
MODEL LT56-300 PENDENT K5.6 (80) THREADS 1/2" (15MM) RA5914					
B0151132S9	LT56P1B3N	155°F	68°C	Brass	€ 77.80
B0152132S9	LT56P1C3N	155°F	68°C	Chrome	€ 85.60
B0158732S9	LT56P1W3N	155°F	68°C	Poly White	€ 85.60
B020113299	LT56P2B3	200°F	93°C	Brass	€ 77.80
B020213299	LT56P2C3	200°F	93°C	Chrome	€ 85.60
B020873299	LT56P2W3	200°F	93°C	Poly White	€ 85.60
MODEL LT56L-300 PENDENT K5.6 (80) THREADS 1/2" (15MM) R5914					
M016113299	LT56LP1B3	165°F	74°C	Brass	€ 77.80
M016213299	LT56LP1C3	165°F	74°C	Chrome	€ 85.60
M016873299	LT56LP1W3	165°F	74°C	Poly White	€ 85.60
M021113299	LT56LP2B3	212°F	100°C	Brass	€ 77.80
M021213299	LT56LP2C3	212°F	100°C	Chrome	€ 85.60
M021873299	LT56LP2W3	212°F	100°C	Poly White	€ 85.60
MODEL FV TWO-PIECE RECESSED ESCUTCHEONS & COLLAR ASSEMBLY					
6801720600	FVB	1/2" (15mm)		Brass	€ 24.20
6801722100	FVC	1/2" (15mm)		Chrome	€ 16.12
6801728700	FVW	1/2" (15mm)		Poly White	€ 16.12
MODEL FP TWO-PIECE RECESSED ESCUTCHEONS & COLLAR ASSEMBLY					
6801412100	FPC	1/2" (15mm)		Chrome	€ 26.65
6801417200	FPW	1/2" (15mm)		White	€ 26.65

6880050100	WW2	Wrench, W2, Pendent, Upright, HSW	€ 139.68
6880100120	WW4	Wrench, W4, Recessed, Concealed	€ 414.51



LT56 CCP

- K-Factor = 5.6 (80)
- **SIN RA5814**
- See Bulletin 058
- Glass Bulb

LT56L CCP

- K-Factor = 5.6 (80)
- **SIN R5814**
- See Bulletin 058
- Fusible Link

LT56 300 CCP

- K-Factor = 5.6 (80)
- **SIN RA5914**
- See Bulletin 058
- Glass Bulb

LT56L-300 CCP

- K-Factor = 5.6 (80)
- **SIN R5914**
- See Bulletin 058
- Fusible Link

Part Number	Short Code	Temperature		Finish	List Price
MODEL LT56 CCP CONCEALED K5.6 (80) THREADS 1/2" (15MM) RA5814					
BZ15173299	LT56CCP1	155°F	68°C	W/O	€ 93.37
BZ20173299	LT56CCP2	200°F	93°C	W/O	€ 93.37
MODEL LT56-300 CCP CONCEALED K5.6 (80) THREADS 1/2" (15MM) RA5914					
BI15173299	LT56CCP13	155°F	68°C	W/O	€ 93.37
BI20173299	LT56CCP23	200°F	93°C	Brass	€ 93.37
MODEL LT56L CCP CONCEALED K5.6 (80) THREADS 1/2" (15MM) R5814					
MZ16173299	LT56LCCP1	165°F	74°C	W/O	€ 93.37
MZ21173299	LT56LCCP2	212°F	100°C	Brass	€ 93.37
MODEL LT56L-300 CCP CONCEALED K5.6 (80) THREADS 1/2" (15MM) R5914					
MI16173299	LT56LCCP13	165°F	74°C	W/O	€ 93.37
MI21173299	LT56LCCP23	212°F	100°C	Brass	€ 93.37
MODEL CCP CONICAL CONCEALED COVERPLATES					
6887161321	CCP0C76	135°F	57°C	Chrome	€ 110.76
6887161318	CCP0W76	135°F	57°C	Flat White	€ 43.16
6887161390	CCP0SP76	135°F	57°C	Specialty	€ 72.49
6887161621	CCP1C76	165°F	74°C	Chrome	€ 110.76
6887161618	CCP1W76	165°F	74°C	Flat White	€ 43.16
6887161690	CCP1SP76	165°F	74°C	Specialty	€ 72.49
6880050100	WW2	Wrench, W2, Pendent, Upright, HSW			€ 139.68
6880100120	WW4	Wrench, W4, Recessed, Concealed			€ 414.51



LT56C FLAT CONCEALED

- K-Factor = 5.6 (80)
- **SIN RA5994**
- See Bulletin 058

Part Number	Short Code	Temperature		Finish	List Price
MODEL LT56C CONCEALED K5.6 (80) THREADS 1/2" (15MM) RA5994					
M916173299	LTC1	165°F	74°C	W/O	€ 108.94
M921173299	LTC2	212°F	100°C	W/O	€ 108.94
MODEL LT56C CONCEALED BSPT THREADS 1/2" (15MM) RA5994					
M916173292	LTC1M	165°F	74°C	W/O	€ 108.94
M921173292	LTC2M	212°F	100°C	W/O	€ 108.94
MODEL G5 COVERPLATES					
6887271321	CG50C	135°F	57°C	Chrome	€ 51.30
6887271372	CG50W	135°F	57°C	White	€ 46.76
6887271311	CG50B	135°F	57°C	Finished Bronze	€ 66.68
6887271374	CG50OW	135°F	57°C	Off-White	€ 63.60
6887271390	CG50SP	135°F	57°C	Specialty	€ 66.14
6887271316	CG50FB	135°F	57°C	Black Painted	€ 63.68
6887271305	CG50BB	135°F	57°C	Bright Brass	€ 80.72
6887271323	CG50CD	135°F	57°C	Satin Chrome	€ 80.72
6887271310	CG50SS	135°F	57°C	Stainless Steel	€ 80.72
6887271319	CG50EW	135°F	57°C	EW	€ 46.76
6887271621	CG51C	165°F	74°C	Chrome	€ 51.30
6887271672	CG51W	165°F	74°C	White	€ 46.76
6887271611	CG51B	165°F	74°C	Finished Bronze	€ 66.68
6887271674	CG51OW	165°F	74°C	Off-White	€ 63.60
6887271690	CG51SP	165°F	74°C	Specialty	€ 66.14
6887271616	CG51FB	165°F	74°C	Black Painted	€ 63.68
6887271605	CG51BB	165°F	74°C	Bright Brass	€ 80.72
6887271623	CG51CD	165°F	74°C	Satin Chrome	€ 80.72
6887271610	CG51SS	165°F	74°C	Stainless Steel	€ 80.72
6887271619	CG51EW	165°F	74°C	EW	€ 46.76

Notes:

Sprinklers and coverplates sold and packaged separately



XL INSTITUTIONAL

- K-Factor = 5.6 (80)
- Pendant EC= SIN R1344
- HSW EC = SIN R1364
- Pendant = SIN R1314
- HSW = SIN R1334
- See Bulletin 113

Part Number	Short Code	Temperature		Finish	List Price
MODEL XL EC INST PENDENT K5.6 (80) THREADS 1/2" (15MM) R1344					
1572213299	XLEPC	165°F	74°C	Chrome	€ 265.37
MODEL XL INST PENDENT K5.6 (80) THREADS 1/2" (15MM) R1314					
1512213299	XLPC	165°F	74°C	Chrome	€ 247.79
MODEL XL INST HORIZONTAL K5.6 (80) THREADS 1/2" (15MM) R1334					
1452213299	XLHC	165°F	74°C	Chrome	€ 258.28
REPLACEMENT PARTS					
6801321223	IKEC	EC HSW ESCUTCHEON KIT, SATIN			€ Call
6801321272	IKEW	EC HSW ESCUTCHEON KIT, WHITE PAINT			€ Call
6801320123	IKPC	PENDENT, EC PENDENT ESCUTCHEON KIT, SATIN			€ Call
6801320172	IKPW	PENDENT, EC PENDENT ESCUTCHEON KIT, WHITE PAINT			€ Call
6801322223	IXLHC	HSW ESCUTCHEON KIT, SATIN			€ Call
6801322272	IXLHW	HSW ESCUTCHEON KIT, WHITE PAINT			€ Call
6801350001		Retainer Flange			€ 38.75
88795014		Escutcheon Retaining Ring			€ 14.87
88007901		Tamper Resistant Fasteners			€ 7.89
6880160020	ZXT	Tamper Resistant Tool Bit			€ 46.65
6880160000	WZXP	Requires Model ZX (Pendent) Sprinkler Wrench			€ 412.90
6880160010	WZXH	Requires Model ZX (Horizontal) Sprinkler Wrench			€ 412.90



Non-Ferrous

Part Number	Short Code	Temperature		Finish	List Price
MODEL F4FR-NF CONCEALED K5.6 (80) THREADS 1/2" (15MM) RA0212					
0615723299	F4FRNF1W	155°F	68°C	White	€ 264.89
0615213299	F4FRNF1C	155°F	68°C	Chrome	€ 264.89

6880170000 WG4 Requires Model G4 Sprinkler Wrench € 412.90

MODEL KFR- CCS K5.6 (80) THREADS 1/2" (15MM) RA4454					
MN211132R9	KFRCCS	212°F	100°C	Brass	€ 89.20

6880050100 WW2 Wrench, W2, Pendant, Upright, HSW € 139.68

F4FR-NF

- K-Factor = 5.6 (80)
- **SIN RA0212**
- See Bulletin 002



KFR CCS

- K-Factor = 5.6 (80)
- **SIN RA4454**
- See Bulletin 044



WP56 PENDENT VERTICAL SIDEWALL

- K-Factor 5.6
- **SIN #501 (Bulb)**
- See Bulletin 181



WP56L PENDENT VERTICAL SIDEWALL

- K-Factor 5.6
- **SIN #R502 (Link)**
- See Bulletin 181



WP56C CONCEALED PENDENT VERTICAL SIDEWALL

- K-Factor 5.6
- **SIN #R504**
- See Bulletin 181

Part Number	Short Code	Temperature		Finish	List Price
MODEL WP56 PENDENT VERTICAL SIDEWALL K5.6 (80) THREADS 1/2" (15MM) R501 BULB					
BW151132S9	WP561B	155°F	68°C	Bronze	€ 699.14
BW152132S9	WP561C	155°F	68°C	Chrome	€ 727.10
BW158732S9	WP561W	155°F	68°C	White	€ 727.10
BW151032S9	WP561SS	155°F	68°C	Stainless Steel	€ 1,438.55
BW201132S9	WP562B	200°F	93°C	Brass	€ 699.14
BW202132S9	WP562C	200°F	93°C	Chrome	€ 727.10
BW208732S9	WP562W	200°F	93°C	White	€ 727.10
BW201032S9	WP562SS	200°F	93°C	Stainless Steel	€ 1,438.55
MODEL WP56L PENDENT VERTICAL SIDEWALL K5.6 (80) THREADS 1/2" (15MM) R502 LINK					
MW161132S9	WP56L1B	165°F	74°C	Bronze	€ 699.14
MW162132S9	WP56L1C	165°F	74°C	Chrome	€ 727.10
MW168732S9	WP56L1W	165°F	74°C	White	€ 727.10
MW211132S9	WP56L2B	212°F	100°C	Bronze	€ 699.14
MW212132S9	WP56L2C	212°F	100°C	Chrome	€ 727.10
MW218732S9	WP56L2W	212°F	100°C	White	€ 727.10
6880050100	WW2	Wrench, W2, Pendent, Upright, HSW			€ 139.68
MODEL WP56C WINDOW CONCEALER K5.6 (80) THREADS 1/2" NPT R504					
1W16173299	WP56C1B	165°F	74°C	W/O	€ 838.96
1W21173299	WP56C2B	212°F	100°C	W/O	€ 838.96
MODEL WP56C WINDOW CONCEALER K5.6 (80) THREADS 1/2" BSPT R504					
1W16173292	WP56C1BM	165°F	74°C	W/O	€ 838.96
1W21173292	WP56C2BM	212°F	100°C	W/O	€ 838.96
6880170020	WFC	WRENCH,FC,CONCEALED			€ 416.73
MODEL G5 COVERPLATES FOR WP56C CONCEALED SPRINKLERS					
6887271372	CG50W	135°F	57°C	White	€ 46.76
6887271321	CG50C	135°F	57°C	Chrome	€ 51.30
6887271672	CG51W	165°F	74°C	White	€ 46.76
6887271621	CG51C	165°F	74°C	Chrome	€ 51.30

Features

- cULus Listed to provide complete wetting of various glass surfaces
- Fast Response Specific Applications Pendent Vertical Sidewall sprinkler
- Listed corrosion resistant finishes available (WP56 only)

Notes:

Other Coverplate finishes available upon request.



**F1S5-FS56 FLAT
 SPRAY SPECIAL
 RESPONSE**

- **SIN RA2314**
- K-Factor = 80 (5.6)
- Thread Size = 15mm (1/2")
- Bulletin 023

**F1S5-FS42 FLAT
 SPRAY SPECIAL
 RESPONSE**

- **SIN RA2315**
- K-Factor = 57 (4.2)
- Thread Size = 15mm (1/2")
- Bulletin 023



Part Number	Short Code	Temperature		Finish	List Price
MODEL F1S5-FS56-I K5.6 (80) BSPT THREADS 1/2" (15MM) RA2314					
		°F	°C		€ Call
KB15114392	KB15114392	155°F	68°C	Brass	€ 71.30
		°F	°C		€ Call
		°F	°C		€ Call
KB28114392		286°F	141°C	Brass	€ 71.30
MODEL F1S5-FS42-I K4.2 (57) BSPT THREADS 1/2" (15MM) RA2315					
		°F	°C		€ Call
KB15114592	KB15114592	155°F	68°C	Brass	€ 71.30
		°F	°C		€ Call
		°F	°C		€ Call
		°F	°C		€ Call
REQUIRED PENDENT SHIELD					
		°F	°C	Galvanized	€ Call

6880050100	WW2	Requires Model W2 Sprinkler Wrench	€ 139.68
6880060000	WGFR	With Shield Use Model GFR2 Wrench	€ 414.51

Notes:

Sprinkler and Shield packaged and sold separately



**F1S5 SERIES
 SPECIAL
 RESPONSE
 STANDARD SPRAY**

- K-Factor = 80 (5.6)
- Thread Size = 15mm (1/2")
- Bulletin 024

Part Number	Short Code	Temperature	Finish	List Price
MODEL F1S5-56 UPRIGHT K5.6 (80) BSPT THREADS 1/2" (15MM)				
		135°F °C	Brass	€ Call
KA151132R2	KA151132R2	155°F 68°C	Brass	€ 35.65
KA171132R2		175°F 79°C	Brass	€ 35.65
KA201132R2		200°F 93°C	Brass	€ 35.65
KA281132R2	KA281132R2	286°F 141°C	Brass	€ 35.65
		°F °C		€ Call
KA152132R2		155°F 68°C	Chrome	€ 42.88
KA172132R2		175°F 79°C	Chrome	€ 35.65
KA202132R2		200°F 93°C	Chrome	€ 42.88
KA282132R2		286°F 141°C	Chrome	€ 42.88
MODEL F1S5-56 PENDENT K5.6 (80) BSPT THREADS 1/2" (15MM)				
KB131132R2		135°F 57°C	Brass	€ 35.65
KB151132R2		155°F 68°C	Brass	€ 35.65
KB171132R2		175°F 79°C	Brass	€ 35.65
KB201132R2	KB201132R2	200°F 93°C	Brass	€ 35.65
KB281132R2		286°F 141°C	Brass	€ 35.65
		°F °C		€ Call
KB152132R2	KB152132R2	155°F 68°C	Chrome	€ 42.88
		°F °C		€ Call
KB202132R2	KB202132R2	200°F 93°C	Chrome	€ 42.88
KB282132R2		286°F 141°C	Chrome	€ 42.88
KB138732R2		135°F 57°C	White	€ 42.88
KB158732R2		155°F 68°C	White	€ 42.88
		°F °C		€ Call
		°F °C		€ Call
		°F °C		€ Call
F1 ESCUTCHEONS				
6800630001	GF1B	GF1B	Brass	€ 25.64
6800600001	GF1C	GF1C	Chrome	€ 13.82
6800640001	GF1W	GF1W	White	€ 13.82
F2 ESCUTCHEONS				
6800830000	GF2B	GF2B	Brass	€ 25.64
6800800000	GF2C	GF2C	Chrome	€ 13.82
6800840000	GF2W	GF2W	White	€ 13.82
FP PUSH-ON/THREADS-OFF ESCUTCHEONS				
6801412100	FPC	FPC	Chrome	€ 26.65
6801417200	FPW	FPW	White	€ 26.65

6880050100	WW2	Requires Model W2 Sprinkler Wrench	€ 139.68
6880060000	WGFR	Recessed Use Model GFR2 Sprinkler Wrench	€ 414.51



**F1S5 SERIES
 SPECIAL
 RESPONSE
 STANDARD SPRAY**

- K-Factor = 80 (5.6)
- Thread Size = 15mm (1/2")
- Bulletin 024

Part Number	Short Code	Temperature		Finish	List Price
MODEL F1S5-56 CONVENTIONAL K5.6 (80) BSPT THREADS 1/2" (15MM)					
KC131132R2		135°F	57°C	Brass	€ 35.65
KC151132R2		155°F	68°C	Brass	€ 35.65
		°F	°C		€ Call
KC201132R2		200°F	93°C	Brass	€ 35.65
		°F	°C		€ Call
KC132132R2		135°F	57°C	Chrome	€ 40.08
KC152132R2		155°F	68°C	Chrome	€ 40.08
		°F	°C		€ Call
KC202132R2		200°F	93°C	Chrome	€ 40.08
		°F	°C		€ Call

6880050100 WW2 Requires Model W2 Sprinkler Wrench € 139.68



**F1S5 LO LARGE
 ORIFICE SPECIAL
 RESPONSE
 STANDARD SPRAY**

- K-Factor = 115 (8.0)
- Thread Size = R1/2
- Bulletin 024



Part Number	Short Code	Temperature		Finish	List Price
MODEL F1S5 LO UPRIGHT K8.0(115) THREADS 1/2"(15MM) BSPT THREADS					
		°F	°C		€ Call
KA15113492		155°F	68°C	Brass	€ 44.75
KA17113492		175°F	79°C	Brass	€ 44.75
KA20113492		200°F	93°C	Brass	€ 44.75
KA28113492		286°F	141°C	Brass	€ 44.75
KA13213492		135°F	57°C	Chrome	€ 52.22
KA15213492		155°F	68°C	Chrome	€ 52.22
MODEL F1S5 LO PENDENT K8.0(115) THREADS 1/2"(15MM) BSPT THREADS					
		°F	°C		€ Call
KB15113492		155°F	68°C	Brass	€ 44.75
KB17113492		175°F	79°C	Brass	€ 44.75
		°F	°C		€ Call
		°F	°C		€ Call
KB28213492		286°F	141°C	Chrome	€ 52.22
F1 ESCUTCHEONS					
6800630001	GF1B	15mm (1/2")		Brass	€ 25.64
6800600001	GF1C	15mm (1/2")		Chrome	€ 13.82
6800640001	GF1W	15mm (1/2")		White	€ 13.82
F2 ESCUTCHEONS					
6800830000	GF2B	15mm (1/2")		Brass	€ 25.64
6800800000	GF2C	15mm (1/2")		Chrome	€ 13.82
6800840000	GF2W	15mm (1/2")		White	€ 13.82
FP PUSH-ON/THREADS-OFF ESCUTCHEONS					
6801412100	FPC	FP PUSH-ON/THREADS-OFF		Chrome	€ 26.65
6801417200	FPW	FP PUSH-ON/THREADS-OFF		White	€ 26.65

6880050100	WW2	Wrench, W2, Pendent, Upright, HSW	€ 139.68
6880100120	WW4	Wrench, W4, Recessed, Concealed	€ 414.51