



PRV DIAPHRAGM PRESSURE REGULATING VALVE

- See Bulletin 820
- 400 psi (27.6 Bar) Rated Pressure
- Adjusted with Pilot Operated Regulator
- Trim Includes Relief Valve
- No Trim Connections to Cover
- cULus listed and FM approved

Description	Part Number	Short Code	List Price
MODEL PRV DIAPHRAGM PRESSURE REGULATING VALVES			
1-1/2" Groove/Groove (ANSI/AWWA C606)	6507008000	15PRV	€ 9,590.31
1-1/2" Flange/Flange Class 150 (ASME B16.5)	6507108000		€10,462.16
1-1/2" Flange/Flange Class 300 (ASME B16.5)	6507208000		€10,462.16
1-1/2" Flange/Flange PN16 (ISO 7005-2)	6507308000		€10,462.16
1-1/2" NPT Thread/Thread (ANSI/ASME B1.20.1)	6507508000		€10,462.16
1-1/2" ISO7-1 Thread/Thread	6507608000		€10,462.16
2" Groove/Groove (ANSI/AWWA C606)	6507028000	2PRV	€ 9,590.31
2" Flange/Flange Class 150 (ASME B16.5)	6507128000		€10,462.16
2" Flange/Flange Class 300 (ASME B16.5)	6507228000		€10,462.16
2" Flange/Flange PN16 (ISO 7005-2)	6507328000		€10,462.16
2" NPT Thread/Thread (ANSI/ASME B1.20.1)	6507528000		€10,462.16
2" ISO7-1 Thread/Thread	6507628000		€10,462.16
2-1/2" Groove/Groove (ANSI/AWWA C606)	6507018000	25PRV	€ 11,116.04
76MM,PRV,GE,PRESS REG,W/O CV VERT RED	6507078000		€ 11,116.04
2-1/2" Flange/Flange Class 150 (ASME B16.5)	6507118000		€12,096.87
2-1/2" Flange/Flange Class 300 (ASME B16.5)	6507218000		€12,096.87
2-1/2" Flange/Flange PN16 (ISO 7005-2)	6507318000		€12,096.87
2-1/2" NPT Thread/Thread (ANSI/ASME B1.20.1)	6507518000		€12,096.87
2-1/2" ISO7-1 Thread/Thread	6507618000		€12,096.87
3" Groove/Groove (ANSI/AWWA C606)	6507038000	3PRV	€ 11,116.04
3" Flange/Flange Class 150 (ASME B16.5)	6507138000		€12,096.87
3" Flange/Flange Class 300 (ASME B16.5)	6507238000		€12,096.87
3" Flange/Flange PN16 (ISO 7005-2)	6507338000		€12,096.87
3" NPT Thread/Thread (ANSI/ASME B1.20.1)	6507538000		€12,096.87
3" ISO7-1 Thread/Thread	6507638000		€12,096.87
4" Groove/Groove (ANSI/AWWA C606)	6507048000	4PRV	€13,295.66
4" Flange/Flange Class 150 (ASME B16.5)	6507148000		€14,494.44
4" Flange/Flange Class 300 (ASME B16.5)	6507248000		€14,494.44
4" Flange/Flange PN16 (ISO 7005-2)	6507348000		€14,494.44
6" Groove/Groove (ANSI/AWWA C606)	6507068000	6PRV	€16,347.12
165MM Groove/Groove (ANSI/AWWA C606)	6507058000		€16,347.12
6" Flange/Flange Class 150 (ASME B16.5)	6507168000		€17,981.83
6" Flange/Flange Class 300 (ASME B16.5)	6507268000		€17,981.83
6" Flange/Flange PN16 (ISO 7005-2)	6507368000		€17,981.83

Notes:

Part numbers shown include a 185 psi (12.8 Bar) relief valve and 300 psi (20.7 Bar) gauges. Replace the last digit in the part number as follows for other relief valve and gauge combinations:

"0"-185 psi (12.8 Bar) relief valve and 300 psi (20 Bar) gauges

"1"-260 psi (17.9 Bar) relief valve and 300 psi (20 Bar) gauges

"2"-185 psi (12.8 Bar) relief valve and 600 psi (40 Bar) gauges

"3"-260 psi (17.9 Bar) relief valve and 600 psi (40 Bar) gauges