

Reliable Attic Sprinklers

- See Bulletin 056
- Specific Application
- Sprinklers for Sloped
- Combustible and Noncombustible
- Light Hazard Concealed Spaces



AH42 / AH56



DD56-6 / DD56-27



DS56



GP56



Part Number	Short Code	Temperature		Finish	List Price
MODEL AH42 UPRIGHT K4.2 (60) THREAD 1/2" RA5623 • Roof Slope = 4:12 to 8:12					
MN21112699	AH42	212°F	100°C	Brass	£ 66.70
MODEL AH56 UPRIGHT K5.6 (80) THREAD 1/2" RA5626 • Roof Slope = 4:12 to 8:12					
MN21112799	AH56	212°F	100°C	Brass	£ 66.70
MODEL DD56-6 UPRIGHT K5.6 (80) THREAD 1/2" RA5624 • Roof Slope = 4:12 to <6:12					
MN21113099	DD566	212°F	100°C	Brass	£ 361.62
MODEL DD56-27 UPRIGHT K5.6 (80) THREAD 1/2" RA5694 • Roof Slope = 6:12 to 8:12					
MN21113199	DD5627	212°F	100°C	Brass	£ 361.62
MODEL DS56 UPRIGHT K5.6 (80) THREAD 1/2" RA5625 • Roof Slope = 4:12 to 8:12					
MN21112899	DS56	212°F	100°C	Brass	£ 361.62
MODEL GP56 UPRIGHT K5.6 (80) THREAD 1/2" RA5695 • Roof Slope = 4:12 to 8:12					
MN21112999	GP56	212°F	100°C	Brass	£ 61.12
MODEL DD80-6 UPRIGHT K8.0 (115) THREAD 3/4" RA5622 • Roof Slope = 4:12 to <6:12					
MN21113398	DD806	212°F	100°C	Brass	£ 361.62
MODEL DD80-27 UPRIGHT K8.0 (115) THREAD 3/4" RA5692 • Roof Slope = 6:12 to 8:12					
MN21113498	DD8027	212°F	100°C	Brass	£ 361.62

6880130002	WDS56	Model DS56 Sprinkler Wrench - Model DS56	£ 237.53
6880050100	WW2	Model W2 Sprinkler Wrench - Models: AH42, AH56, DD56, DD80, & GP56	£ 114.28



LT56 PENDENT

- K-Factor = 5.6 (80)
- **SIN RA5814**
- See Bulletin 058
- Glass Bulb



LT56L PENDENT

- K-Factor = 5.6 (80)
- **SIN R5814**
- See Bulletin 058
- Link

LT56 300 PENDENT

- K-Factor = 5.6 (80)
- **SIN RA5914**
- See Bulletin 058
- Glass Bulb

LT56L-300 PENDENT

- K-Factor = 5.6 (80)
- **SIN R5914**
- See Bulletin 058
- Link

Part Number	Short Code	Temperature		Finish	List Price
MODEL LT56 PENDENT K5.6 (80) THREADS 1/2" (15MM) RA5814					
BY151132S9	LT56P1BN	155°F	68°C	Brass	£ 63.66
BY152132S9	LT56P1CN	155°F	68°C	Chrome	£ 70.03
BY158732S9	LT56P1WN	155°F	68°C	Poly White	£ 70.03
BY201132S9	LT56P2BN	200°F	93°C	Brass	£ 63.66
BY202132S9	LT56P2CN	200°F	93°C	Chrome	£ 70.03
BY208732S9	LT56P2WN	200°F	93°C	Poly White	£ 70.03
MODEL LT56L PENDENT K5.6 (80) THREADS 1/2" (15MM) R5814					
MY16113299	LT56LP1B	165°F	74°C	Brass	£ 63.66
MY16213299	LT56LP1C	165°F	74°C	Chrome	£ 70.03
MY16873299	LT56LP1W	165°F	74°C	Poly White	£ 70.03
MY21113299	LT56LP2B	212°F	100°C	Brass	£ 63.66
MY21213299	LT56LP2C	212°F	100°C	Chrome	£ 70.03
MY21873299	LT56LP2W	212°F	100°C	Poly White	£ 70.03
MODEL LT56-300 PENDENT K5.6 (80) THREADS 1/2" (15MM) RA5914					
B0151132S9	LT56P1B3N	155°F	68°C	Brass	£ 63.66
B0152132S9	LT56P1C3N	155°F	68°C	Chrome	£ 70.03
B0158732S9	LT56P1W3N	155°F	68°C	Poly White	£ 70.03
B020113299	LT56P2B3	200°F	93°C	Brass	£ 63.66
B020213299	LT56P2C3	200°F	93°C	Chrome	£ 70.03
B020873299	LT56P2W3	200°F	93°C	Poly White	£ 70.03
MODEL LT56L-300 PENDENT K5.6 (80) THREADS 1/2" (15MM) R5914					
M016113299	LT56LP1B3	165°F	74°C	Brass	£ 63.66
M016213299	LT56LP1C3	165°F	74°C	Chrome	£ 70.03
M016873299	LT56LP1W3	165°F	74°C	Poly White	£ 70.03
M021113299	LT56LP2B3	212°F	100°C	Brass	£ 63.66
M021213299	LT56LP2C3	212°F	100°C	Chrome	£ 70.03
M021873299	LT56LP2W3	212°F	100°C	Poly White	£ 70.03
MODEL FV TWO-PIECE RECESSED ESCUTCHEONS & COLLAR ASSEMBLY					
6801720600	FVB	1/2" (15mm)		Brass	£ 19.80
6801722100	FVC	1/2" (15mm)		Chrome	£ 13.19
6801728700	FVW	1/2" (15mm)		Poly White	£ 13.19
MODEL FP TWO-PIECE RECESSED ESCUTCHEONS & COLLAR ASSEMBLY					
6801412100	FPC	1/2" (15mm)		Chrome	£ 21.81
6801417200	FPW	1/2" (15mm)		White	£ 21.81

6880050100	WW2	Wrench, W2, Pendent, Upright, HSW	£ 114.28
6880100120	WW4	Wrench, W4, Recessed, Concealed	£ 339.15



LT56 CCP

- K-Factor = 5.6 (80)
- **SIN RA5814**
- See Bulletin 058
- Glass Bulb

LT56L CCP

- K-Factor = 5.6 (80)
- **SIN R5814**
- See Bulletin 058
- Fusible Link

LT56 300 CCP

- K-Factor = 5.6 (80)
- **SIN RA5914**
- See Bulletin 058
- Glass Bulb

LT56L-300 CCP

- K-Factor = 5.6 (80)
- **SIN R5914**
- See Bulletin 058
- Fusible Link

Part Number	Short Code	Temperature		Finish	List Price
MODEL LT56 CCP CONCEALED K5.6 (80) THREADS 1/2" (15MM) RA5814					
BZ15173299	LT56CCP1	155°F	68°C	W/O	£ 76.39
BZ20173299	LT56CCP2	200°F	93°C	W/O	£ 76.39
MODEL LT56-300 CCP CONCEALED K5.6 (80) THREADS 1/2" (15MM) RA5914					
BI15173299	LT56CCP13	155°F	68°C	W/O	£ 76.39
BI20173299	LT56CCP23	200°F	93°C	Brass	£ 76.39
MODEL LT56L CCP CONCEALED K5.6 (80) THREADS 1/2" (15MM) R5814					
MZ16173299	LT56LCCP1	165°F	74°C	W/O	£ 76.39
MZ21173299	LT56LCCP2	212°F	100°C	Brass	£ 76.39
MODEL LT56L-300 CCP CONCEALED K5.6 (80) THREADS 1/2" (15MM) R5914					
MI16173299	LT56LCCP13	165°F	74°C	W/O	£ 76.39
MI21173299	LT56LCCP23	212°F	100°C	Brass	£ 76.39
MODEL CCP CONICAL CONCEALED COVERPLATES					
6887161321	CCP0C76	135°F	57°C	Chrome	£ 90.62
6887161318	CCP0W76	135°F	57°C	Flat White	£ 35.32
6887161390	CCP0SP76	135°F	57°C	Specialty	£ 59.31
6887161621	CCP1C76	165°F	74°C	Chrome	£ 90.62
6887161618	CCP1W76	165°F	74°C	Flat White	£ 35.32
6887161690	CCP1SP76	165°F	74°C	Specialty	£ 59.31
6880050100	WW2	Wrench, W2, Pendent, Upright, HSW			£ 114.28
6880100120	WW4	Wrench, W4, Recessed, Concealed			£ 339.15



LT56C FLAT CONCEALED

- K-Factor = 5.6 (80)
- **SIN RA5994**
- See Bulletin 058

Part Number	Short Code	Temperature		Finish	List Price
MODEL LT56C CONCEALED K5.6 (80) THREADS 1/2" (15MM) RA5994					
M916173299	LTC1	165°F	74°C	W/O	£ 89.13
M921173299	LTC2	212°F	100°C	W/O	£ 89.13
MODEL LT56C CONCEALED BSPT THREADS 1/2" (15MM) RA5994					
M916173292	LTC1M	165°F	74°C	W/O	£ 89.13
M921173292	LTC2M	212°F	100°C	W/O	£ 89.13
MODEL G5 COVERPLATES					
6887271321	CG50C	135°F	57°C	Chrome	£ 41.97
6887271372	CG50W	135°F	57°C	White	£ 38.26
6887271311	CG50B	135°F	57°C	Finished Bronze	£ 54.56
6887271374	CG50OW	135°F	57°C	Off-White	£ 52.03
6887271390	CG50SP	135°F	57°C	Specialty	£ 54.12
6887271316	CG50FB	135°F	57°C	Black Painted	£ 52.10
6887271305	CG50BB	135°F	57°C	Bright Brass	£ 66.05
6887271323	CG50CD	135°F	57°C	Satin Chrome	£ 66.05
6887271310	CG50SS	135°F	57°C	Stainless Steel	£ 66.05
6887271319	CG50EW	135°F	57°C	EW	£ 38.26
6887271621	CG51C	165°F	74°C	Chrome	£ 41.97
6887271672	CG51W	165°F	74°C	White	£ 38.26
6887271611	CG51B	165°F	74°C	Finished Bronze	£ 54.56
6887271674	CG51OW	165°F	74°C	Off-White	£ 52.03
6887271690	CG51SP	165°F	74°C	Specialty	£ 54.12
6887271616	CG51FB	165°F	74°C	Black Painted	£ 52.10
6887271605	CG51BB	165°F	74°C	Bright Brass	£ 66.05
6887271623	CG51CD	165°F	74°C	Satin Chrome	£ 66.05
6887271610	CG51SS	165°F	74°C	Stainless Steel	£ 66.05
6887271619	CG51EW	165°F	74°C	EW	£ 38.26

Notes:

Sprinklers and coverplates sold and packaged separately



XL INSTITUTIONAL

- K-Factor = 5.6 (80)
- Pendent EC= SIN R1344
- HSW EC = SIN R1364
- Pendent = SIN R1314
- HSW = SIN R1334
- See Bulletin 113

Part Number	Short Code	Temperature		Finish	List Price
MODEL XL EC INST PENDENT K5.6 (80) THREADS 1/2" (15MM) R1344					
1572213299	XLEPC	165°F	74°C	Chrome	£ 217.12
MODEL XL INST PENDENT K5.6 (80) THREADS 1/2" (15MM) R1314					
1512213299	XLPC	165°F	74°C	Chrome	£ 202.74
MODEL XL INST HORIZONTAL K5.6 (80) THREADS 1/2" (15MM) R1334					
1452213299	XLHC	165°F	74°C	Chrome	£ 211.32
REPLACEMENT PARTS					
6801321223	IKEC	EC HSW ESCUTCHEON KIT, SATIN			£ Call
6801321272	IKEW	EC HSW ESCUTCHEON KIT, WHITE PAINT			£ Call
6801320123	IKPC	PENDENT, EC PENDENT ESCUTCHEON KIT, SATIN			£ Call
6801320172	IKPW	PENDENT, EC PENDENT ESCUTCHEON KIT, WHITE PAINT			£ Call
6801322223	IXLHC	HSW ESCUTCHEON KIT, SATIN			£ Call
6801322272	IXLHW	HSW ESCUTCHEON KIT, WHITE PAINT			£ Call
6801350001		Retainer Flange			£ 31.71
88795014		Escutcheon Retaining Ring			£ 12.17
88007901		Tamper Resistant Fasteners			£ 6.46
6880160020	ZXT	Tamper Resistant Tool Bit			£ 38.16
6880160000	WZXP	Requires Model ZX (Pendent) Sprinkler Wrench			£ 337.83
6880160010	WZXH	Requires Model ZX (Horizontal) Sprinkler Wrench			£ 337.83



Non-Ferrous

Part Number	Short Code	Temperature		Finish	List Price
MODEL F4FR-NF CONCEALED K5.6 (80) THREADS 1/2" (15MM) RA0212					
0615723299	F4FRNF1W	155°F	68°C	White	£ 216.73
0615213299	F4FRNF1C	155°F	68°C	Chrome	£ 216.73

6880170000 WG4 Requires Model G4 Sprinkler Wrench £ 337.83

MODEL KFR- CCS K5.6 (80) THREADS 1/2" (15MM) RA4454					
MN211132R9	KFRCCS	212°F	100°C	Brass	£ 72.98

6880050100 WW2 Wrench, W2, Pendant, Upright, HSW £ 114.28

F4FR-NF

- K-Factor = 5.6 (80)
- **SIN RA0212**
- See Bulletin 002



KFR CCS

- K-Factor = 5.6 (80)
- **SIN RA4454**
- See Bulletin 044



WP56 PENDENT VERTICAL SIDEWALL

- K-Factor 5.6
- **SIN #501 (Bulb)**
- See Bulletin 181



WP56L PENDENT VERTICAL SIDEWALL

- K-Factor 5.6
- **SIN #R502 (Link)**
- See Bulletin 181



WP56C CONCEALED PENDENT VERTICAL SIDEWALL

- K-Factor 5.6
- **SIN #R504**
- See Bulletin 181

Part Number	Short Code	Temperature		Finish	List Price
MODEL WP56 PENDENT VERTICAL SIDEWALL K5.6 (80) THREADS 1/2" (15MM) R501 BULB					
BW151132S9	WP561B	155°F	68°C	Bronze	£ 572.02
BW152132S9	WP561C	155°F	68°C	Chrome	£ 594.90
BW158732S9	WP561W	155°F	68°C	White	£ 594.90
BW151032S9	WP561SS	155°F	68°C	Stainless Steel	£ 1,177.00
BW201132S9	WP562B	200°F	93°C	Brass	£ 572.02
BW202132S9	WP562C	200°F	93°C	Chrome	£ 594.90
BW208732S9	WP562W	200°F	93°C	White	£ 594.90
BW201032S9	WP562SS	200°F	93°C	Stainless Steel	£ 1,177.00
MODEL WP56L PENDENT VERTICAL SIDEWALL K5.6 (80) THREADS 1/2" (15MM) R502 LINK					
MW161132S9	WP56L1B	165°F	74°C	Bronze	£ 572.02
MW162132S9	WP56L1C	165°F	74°C	Chrome	£ 594.90
MW168732S9	WP56L1W	165°F	74°C	White	£ 594.90
MW211132S9	WP56L2B	212°F	100°C	Bronze	£ 572.02
MW212132S9	WP56L2C	212°F	100°C	Chrome	£ 594.90
MW218732S9	WP56L2W	212°F	100°C	White	£ 594.90
6880050100	WW2	Wrench, W2, Pendent, Upright, HSW			£ 114.28
MODEL WP56C WINDOW CONCEALER K5.6 (80) THREADS 1/2" NPT R504					
1W16173299	WP56C1B	165°F	74°C	W/O	£ 686.42
1W21173299	WP56C2B	212°F	100°C	W/O	£ 686.42
MODEL WP56C WINDOW CONCEALER K5.6 (80) THREADS 1/2" BSPT R504					
1W16173292	WP56C1BM	165°F	74°C	W/O	£ 686.42
1W21173292	WP56C2BM	212°F	100°C	W/O	£ 686.42
6880170020	WFC	WRENCH,FC,CONCEALED			£ 340.96
MODEL G5 COVERPLATES FOR WP56C CONCEALED SPRINKLERS					
6887271372	CG50W	135°F	57°C	White	£ 38.26
6887271321	CG50C	135°F	57°C	Chrome	£ 41.97
6887271672	CG51W	165°F	74°C	White	£ 38.26
6887271621	CG51C	165°F	74°C	Chrome	£ 41.97

Features

- cULus Listed to provide complete wetting of various glass surfaces
- Fast Response Specific Applications Pendent Vertical Sidewall sprinkler
- Listed corrosion resistant finishes available (WP56 only)

Notes:

Other Coverplate finishes available upon request.



**F1S5-FS56 FLAT
 SPRAY SPECIAL
 RESPONSE**

- **SIN RA2314**
- K-Factor = 80 (5.6)
- Thread Size = 15mm (1/2")
- Bulletin 023

**F1S5-FS42 FLAT
 SPRAY SPECIAL
 RESPONSE**

- **SIN RA2315**
- K-Factor = 57 (4.2)
- Thread Size = 15mm (1/2")
- Bulletin 023



Part Number	Short Code	Temperature		Finish	List Price
MODEL F1S5-FS56-I K5.6 (80) BSPT THREADS 1/2" (15MM) RA2314					
		°F	°C		£ Call
KB15114392	KB15114392	155°F	68°C	Brass	£ 58.33
		°F	°C		£ Call
		°F	°C		£ Call
KB28114392		286°F	141°C	Brass	£ 58.33
MODEL F1S5-FS42-I K4.2 (57) BSPT THREADS 1/2" (15MM) RA2315					
		°F	°C		£ Call
KB15114592	KB15114592	155°F	68°C	Brass	£ 58.33
		°F	°C		£ Call
		°F	°C		£ Call
		°F	°C		£ Call
REQUIRED PENDENT SHIELD					
		°F	°C	Galvanized	£ Call

6880050100	WW2	Requires Model W2 Sprinkler Wrench	£ 114.28
6880060000	WGFR	With Shield Use Model GFR2 Wrench	£ 339.15

Notes:

Sprinkler and Shield packaged and sold separately



**F1S5 SERIES
 SPECIAL
 RESPONSE
 STANDARD SPRAY**

- K-Factor = 80 (5.6)
- Thread Size = 15mm (1/2")
- Bulletin 024

Part Number	Short Code	Temperature	Finish	List Price
MODEL F1S5-56 UPRIGHT K5.6 (80) BSPT THREADS 1/2" (15MM)				
		135°F °C	Brass	£ Call
KA151132R2	KA151132R2	155°F 68°C	Brass	£ 29.17
KA171132R2		175°F 79°C	Brass	£ 29.17
KA201132R2		200°F 93°C	Brass	£ 29.17
KA281132R2	KA281132R2	286°F 141°C	Brass	£ 29.17
		°F °C		£ Call
KA152132R2		155°F 68°C	Chrome	£ 35.08
KA172132R2		175°F 79°C	Chrome	£ 29.17
KA202132R2		200°F 93°C	Chrome	£ 35.08
KA282132R2		286°F 141°C	Chrome	£ 35.08
MODEL F1S5-56 PENDENT K5.6 (80) BSPT THREADS 1/2" (15MM)				
KB131132R2		135°F 57°C	Brass	£ 29.17
KB151132R2		155°F 68°C	Brass	£ 29.17
KB171132R2		175°F 79°C	Brass	£ 29.17
KB201132R2	KB201132R2	200°F 93°C	Brass	£ 29.17
KB281132R2		286°F 141°C	Brass	£ 29.17
		°F °C		£ Call
KB152132R2	KB152132R2	155°F 68°C	Chrome	£ 35.08
		°F °C		£ Call
KB202132R2	KB202132R2	200°F 93°C	Chrome	£ 35.08
KB282132R2		286°F 141°C	Chrome	£ 35.08
KB138732R2		135°F 57°C	White	£ 35.08
KB158732R2		155°F 68°C	White	£ 35.08
		°F °C		£ Call
		°F °C		£ Call
		°F °C		£ Call
F1 ESCUTCHEONS				
6800630001	GF1B	GF1B	Brass	£ 20.97
6800600001	GF1C	GF1C	Chrome	£ 11.30
6800640001	GF1W	GF1W	White	£ 11.30
F2 ESCUTCHEONS				
6800830000	GF2B	GF2B	Brass	£ 20.97
6800800000	GF2C	GF2C	Chrome	£ 11.30
6800840000	GF2W	GF2W	White	£ 11.30
FP PUSH-ON/THREADS-OFF ESCUTCHEONS				
6801412100	FPC	FPC	Chrome	£ 21.81
6801417200	FPW	FPW	White	£ 21.81

6880050100	WW2	Requires Model W2 Sprinkler Wrench	£ 114.28
6880060000	WGFR	Recessed Use Model GFR2 Sprinkler Wrench	£ 339.15



**F1S5 SERIES
 SPECIAL
 RESPONSE
 STANDARD SPRAY**

- K-Factor = 80 (5.6)
- Thread Size = 15mm (1/2")
- Bulletin 024

Part Number	Short Code	Temperature		Finish	List Price
MODEL F1S5-56 CONVENTIONAL K5.6 (80) BSPT THREADS 1/2" (15MM)					
KC131132R2		135°F	57°C	Brass	£ 29.17
KC151132R2		155°F	68°C	Brass	£ 29.17
		°F	°C		£ Call
KC201132R2		200°F	93°C	Brass	£ 29.17
		°F	°C		£ Call
KC132132R2		135°F	57°C	Chrome	£ 32.79
KC152132R2		155°F	68°C	Chrome	£ 32.79
		°F	°C		£ Call
KC202132R2		200°F	93°C	Chrome	£ 32.79
		°F	°C		£ Call

6880050100 WW2 Requires Model W2 Sprinkler Wrench £ 114.28



**F1S5 LO LARGE
 ORIFICE SPECIAL
 RESPONSE
 STANDARD SPRAY**

- K-Factor = 115 (8.0)
- Thread Size = R1/2
- Bulletin 024



Part Number	Short Code	Temperature		Finish	List Price	
MODEL F1S5 LO UPRIGHT K8.0(115) THREADS 1/2"(15MM) BSPT THREADS						
		°F	°C		£	Call
KA15113492		155°F	68°C	Brass	£	36.61
KA17113492		175°F	79°C	Brass	£	36.61
KA20113492		200°F	93°C	Brass	£	36.61
KA28113492		286°F	141°C	Brass	£	36.61
KA13213492		135°F	57°C	Chrome	£	42.73
KA15213492		155°F	68°C	Chrome	£	42.73
MODEL F1S5 LO PENDENT K8.0(115) THREADS 1/2"(15MM) BSPT THREADS						
		°F	°C		£	Call
KB15113492		155°F	68°C	Brass	£	36.61
KB17113492		175°F	79°C	Brass	£	36.61
		°F	°C		£	Call
		°F	°C		£	Call
KB28213492		286°F	141°C	Chrome	£	42.73
F1 ESCUTCHEONS						
6800630001	GF1B	15mm (1/2")		Brass	£	20.97
6800600001	GF1C	15mm (1/2")		Chrome	£	11.30
6800640001	GF1W	15mm (1/2")		White	£	11.30
F2 ESCUTCHEONS						
6800830000	GF2B	15mm (1/2")		Brass	£	20.97
6800800000	GF2C	15mm (1/2")		Chrome	£	11.30
6800840000	GF2W	15mm (1/2")		White	£	11.30
FP PUSH-ON/THREADS-OFF ESCUTCHEONS						
6801412100	FPC	FP PUSH-ON/THREADS-OFF		Chrome	£	21.81
6801417200	FPW	FP PUSH-ON/THREADS-OFF		White	£	21.81

6880050100	WW2	Wrench, W2, Pendent, Upright, HSW		£	114.28
6880100120	WW4	Wrench, W4, Recessed, Concealed		£	339.15