

| Description | Part Number | List Price |
|--|-------------|------------|
| MODEL A — 2 1/2" DELUGE VALVE | | |
| Socket Flat Head Screw - Need to order 6 | 95616402 | \$ 38.32 |
| Socket Head Cap Screw - Need to order 8 | 95606402 | \$ 38.32 |
| Rubber Facing | 92206402 | \$ 493.48 |
| Clamping Ring | 95306402 | \$ 623.07 |
| Rubber Seal | 93406402 | \$ 147.41 |
| Cover Bolts - Need to order 8 | 91106123 | \$ 7.23 |
| MODEL B — 4" DELUGE VALVE | | |
| Cover Gasket | 93706404 | \$ 173.13 |
| Cover Bolts -Need to order 6 | 91106404 | \$ 8.73 |
| Seat "O" Ring | 95406404 | \$ 21.84 |
| Clapper Clamping Ring | | \$ Call |
| Clapper Rubber Facing | 93406404 | \$ 657.18 |
| Clamping Ring Screws -Need to order 4 | 95606404 | \$ 44.22 |
| Drain Plug | 98604403 | \$ 44.22 |
| "E" Ring, Pin Lever - Need to order 2 | 95316408 | \$ 95.65 |
| Lever Shaft | 96216404 | \$ 303.38 |
| Lever Shaft Model BX | 96216424 | \$ 216.66 |
| "O" Ring, Push Rod | 95406406 | \$ 35.30 |
| "O" Ring, Push Rod | 95406407 | \$ 35.49 |
| "O" Ring, Push Rod Guide | 95406408 | \$ 61.18 |
| Push Rod Spring | 96406406 | \$ 303.38 |
| Push Rod Cover Gasket | 93716406 | \$ 44.22 |

Important Note:

Above parts are 1241 and subsequent, 1240 and prior requires replacements part kit

| Description | Part Number | List Price |
|---------------------------------------|-------------|-------------|
| MODEL B — 4" DELUGE VALVE | | |
| Push Rod Cover Assembly ¹ | 71040419 | \$ 1,124.10 |
| MODEL B — 6" DELUGE VALVE | | |
| Cover Gasket | 93706406 | \$ 190.10 |
| Cover | 92106406 | \$ 1,124.10 |
| Cover Bolts - Need to order 8 | 91106406 | \$ 8.73 |
| Push Rod Cover | | \$ Call |
| Seat "O" Ring | 95436126 | \$ 22.02 |
| Clapper Clamping Ring | 95306406 | \$ 329.27 |
| Clapper Shaft | 96206406 | \$ 329.27 |
| Clapper Rubber Facing | 93406406 | \$ 674.66 |
| Clamper Ring Screws - Need to order 4 | 95606406 | \$ 52.28 |
| "E" Ring, Pin Lever - Need to order 2 | 95316407 | \$ 173.13 |
| Lever Shaft | 96216406 | \$ 329.27 |
| "O" Ring, Push Rod | 95406406 | \$ 35.30 |
| "O" Ring, Push Rod | 95406407 | \$ 35.49 |
| "O" Ring, Push Rod Guide | 95406408 | \$ 61.18 |
| Push Rod Cover Gasket | 93716406 | \$ 44.22 |
| Drain Plug | 98604403 | \$ 44.22 |
| Push Rod Spring | 96406406 | \$ 303.38 |
| Push Rod Cover Assembly ¹ | 71040419 | \$ 1,124.10 |

¹ Contains:

Push Rod Cover, Inlet Orifice

Important Note:

Above parts are 1239 and subsequent, 1239 and prior requires replacements part kit

| Description | Part Number | List Price |
|--|-------------|-------------|
| MODEL DDX — 2", 2-1/2" & 3" DELUGE VALVES | | |
| Cover, Pushrod, Assembly | 71040416 | \$ 1,040.92 |
| Clapper Assembly | 71041300 | \$ 3,459.21 |
| Screw, Hex Cap. 1/2-13 x 1-1/4", ZN PLTD, Grade A | 91106123 | \$ 7.23 |
| Mounting Ring, Machined | 91306013 | \$ 264.73 |
| Seal Assembly | 93416003 | \$ 147.41 |
| Gasket, Access Cover | 93706003 | \$ 160.52 |
| Pushrod, Guide | 93916006 | \$ 148.75 |
| Knob, Reset, Assembly | 94356007 | \$ 168.75 |
| Piston, Machined | 95106006 | \$ 1,021.08 |
| Diaphragm | 95276006 | \$ 104.73 |
| Clip, Retaining, 3/8" Shaft | 95306268 | \$ 16.80 |
| O-Ring - Need to order 114 | 95406007 | \$ 35.49 |
| O-Ring - Need to order 912 | 95406024 | \$ 35.49 |
| O-Ring - Need to order 014 | 95406407 | \$ 35.49 |
| O-Ring - Need to order 150 | 95406410 | \$ 35.49 |
| O-Ring - Need to order 147 | 95406411 | \$ 35.49 |
| Screw, Socket Head, 1/4"-20 x 5/8" | 95606114 | \$ 38.49 |
| Screw, Cap. #6-32 x 1/2", SS | 95606133 | \$ 38.49 |
| Seat Machined | 96016003 | \$ 993.20 |
| Pin. Hinge | 96206003 | \$ 140.35 |
| Pin. Lever | 96216003 | \$ 562.90 |
| Spacer, Clapper Pin | 96310003 | \$ 140.35 |
| Spring, Lever | 96406003 | \$ 75.81 |
| Spring, DDX | 96406906 | \$ 84.22 |
| Washer, Lock, # 6, SS | 96906112 | \$ 4.03 |

Important Note:

Above parts are 1239 and subsequent, 1239 and prior requires replacements part kit

| Description | Part Number | List Price |
|------------------------------|-------------|-------------|
| DDV REPLACEMENT PARTS | | |
| ASSY,DIAPHRAGM,DDV,2 1/2&3 | 95277630 | \$ 592.87 |
| ASSY,DIAPHRAGM,DDV,4 | 95277640 | \$ 1,185.75 |
| ASSY,DIAPHRAGM,DDV,6 | 95277660 | \$ 2,519.69 |
| SCR,HEX,1/2-13X1,ZINC | 95606179 | \$ 7.50 |
| SCR,HEX,5/8-11X1,ZINC | 95606182 | \$ 7.50 |
| SCR,HEX,7/8-9X1-1 1/2,ZINC | 95606180 | \$ 10.00 |
| STUD,7/8-9X3,ZINC | 96506604 | \$ 11.85 |
| NUT,HEX,7/8"-9 | 94906924 | \$ 6.00 |

| Description | Part Number | List Price |
|--|-------------|-------------|
| MODEL DDX — 4", & 6", DELUGE VALVES | | |
| Cover, Pushrod, Assembly | 71040416 | \$ 1,040.92 |
| Seat, 4" | 96016004 | \$ 1,030.19 |
| Clapper Assy,4" DDX | 71041401 | \$ 4,588.54 |
| Cover, 4" | 92116064 | \$ 880.75 |
| Gasket, Cover, 4" | 93706004 | \$ 160.52 |
| Lever,4" | 94506004 | \$ 174.31 |
| Clapper Assy, 6" DDX | 71041601 | \$ 7,103.50 |
| Cover, 6" | 92116066 | \$ 984.78 |
| Seal Faceplate Subassembly, 6" | 93416006 | \$ 705.94 |
| Gasket, Cover, 6" | 93706006 | \$ 207.92 |
| O-ring - Need to order 014 | 95406407 | \$ 35.49 |
| O-ring - Need to order 114 | 95406007 | \$ 35.49 |
| O-ring - Need to order 912 | 95406024 | \$ 35.49 |
| Hinge Pin, Clapper | 96216086 | \$ 140.35 |
| Piston | 95106006 | \$ 1,021.08 |
| Pushrod | 95506006 | \$ 689.13 |
| Pushrod Guide | 93916006 | \$ 148.75 |
| Ring, Retaining (2 Assembled to Item No.14) | 95306267 | \$ 15.47 |
| Screw, Hex Cap, Ø ½"-13 x 1-1/2" | 95606107 | \$ 38.49 |
| Screw, Hex Cap, Ø 5/8"-11 x 1-3/4" | 91106006 | \$ 38.49 |
| Spring Lock Washer, #10 | 96906111 | \$ 4.03 |
| Screw, C'sunk Cap Head, Ø 3/8"-16 x ¾" | 95606127 | \$ 38.49 |
| Screw, Socket Head, #10-32 x 1" | 95606130 | \$ 38.49 |
| Screw, Socket Head, Ø ¼"-20 x 5/8" | 95606114 | \$ 38.49 |
| Spring, Lever | 96406004 | \$ 75.81 |
| Spring | 96406906 | \$ 84.22 |
| Diaphragm | 95276006 | \$ 104.73 |
| Knob, Reset, Assembly | 94356007 | \$ 168.75 |

| Description | Part Number | List Price |
|---|-------------|-------------|
| MODEL DDX — 8" DELUGE VALVE | | |
| Pushrod Cover Assembly | 71040416 | \$ 1,040.92 |
| O-Ring - Need to order 256 | 95406414 | \$ 35.49 |
| Screw, Hex Cap, 5/8-11x2" | 95606110 | \$ 46.22 |
| Mounting Ring, Machined | 91306018 | \$ 67.41 |
| Clapper, Machined | 91916008 | \$ 5,155.81 |
| Access Cover | 92116068 | \$ 192.62 |
| Seal Assembly | 93416008 | \$ 340.53 |
| Gasket, Access Cover | 93706008 | \$ 207.92 |
| Bumpstop Assembly | 93722000 | \$ 147.24 |
| Pushrod Guide | 93916006 | \$ 148.75 |
| Lever | 94506008 | \$ 1,245.30 |
| Striker | 95006410 | \$ 1,225.14 |
| Piston | 95106006 | \$ 1,021.08 |
| Diaphragm | 95276006 | \$ 104.73 |
| Retaining Clip, 3/4" Shaft | 95316408 | \$ 95.65 |
| O-Ring - Need to order 114 | 95406007 | \$ 35.49 |
| O-Ring - Need to order 912 | 95406024 | \$ 35.49 |
| O-Ring - Need to order 260 | 95406407 | \$ 35.49 |
| O-Ring - Need to order 259 | 95406413 | \$ 35.49 |
| Screw, Socket Head, 1/4-20 x 5/8" | 95606114 | \$ 38.49 |
| Screw, Socket Head, #10-32 x 1" | 95606130 | \$ 38.49 |
| Seat, Machined | 96016008 | \$ 1,191.84 |
| Hinge Pin | 96206008 | \$ 168.42 |
| Lever Pin | 96216008 | \$ 689.80 |
| Clapper Spacer | 96310008 | \$ 168.42 |
| Lever Spring | 96406008 | \$ 90.93 |
| DDX Spring | 96406906 | \$ 84.22 |
| Spring Lock Washer, #10 | 96906111 | \$ 4.03 |
| Screw, Socket Cap, Flat Head, 1/2-13 x 3/4" | 95606135 | \$ 34.63 |
| Reset Knob Assembly | 94356007 | \$ 168.75 |

| Description | Part Number | List Price |
|--|-------------|-------------|
| MODEL DDX — 8" STAINLESS STEEL DELUGE VALVE | | |
| Pushrod Cover | 92126358 | \$ 463.41 |
| O-Ring - Need to order 266 | 95406414 | \$ 35.49 |
| Screw, Hex Cap, 5/8-11x2" | 95606137 | \$ 46.22 |
| Mounting Ring, Machined | 91326018 | \$ 67.41 |
| Clapper, Machined | 91926008 | \$ 5,572.14 |
| Access Cover | 92126069 | \$ 208.27 |
| Seal Assembly | 93416028 | \$ 364.39 |
| Gasket, Access Cover | 93706008 | \$ 207.92 |
| Bumpstop Assembly | 93722000 | \$ 147.24 |
| DDX:PUSHROD GUIDE | 93916006 | \$ 148.75 |
| LEVER,8" DDX VALVE 6-4, GRADE 5 | 94506028 | \$ 1,453.21 |
| Striker | 95006411 | \$ 1,249.16 |
| Piston | 95106006 | \$ 1,021.08 |
| Diaphragm | 95276006 | \$ 104.73 |
| Retaining Clip, 3/4" Shaft | 95316408 | \$ 95.65 |
| O-Ring - Need to order 114 | 95406007 | \$ 35.49 |
| O-Ring - Need to order 912 | 95406024 | \$ 35.49 |
| O-Ring - Need to order 260 | 95406407 | \$ 35.49 |
| O-Ring - Need to order 259 | 95406413 | \$ 35.49 |
| Screw, Socket Head, 1/4-20 x 5/8" | 95606114 | \$ 38.49 |
| Screw, Socket Head, #10-32 x 1" | 95606130 | \$ 38.49 |
| Seat, Machined | 96026008 | \$ 1,232.53 |
| Hinge Pin | 96206008 | \$ 168.42 |
| Lever Pin | 96216008 | \$ 689.80 |
| Clapper Spacer | 96310008 | \$ 168.42 |
| Lever Spring | 96406008 | \$ 90.93 |
| DDX Spring | 96406906 | \$ 84.22 |
| Spring Lock Washer, #10 | 96906111 | \$ 4.03 |
| Screw, Socket Cap, Flat Head, 1/2-13 x 3/4" | 95606135 | \$ 34.63 |
| Reset Knob Assembly | 94356009 | \$ 210.27 |

| Description | Part Number | List Price |
|---|-------------|-------------|
| MODEL BX — 4" & 6" EXTERNAL RESET DEVICE | | |
| Reset Knob Ext. Reset Del Mod. B 4" & 6" | 94356426 | \$ 181.86 |
| "O" Ring Shaft Ext. Reset 4" & 6" Del | 95406425 | \$ 5.38 |
| "O" Ring Bearing 4" & 6" Del Mod. B Ext. Res. | | \$ Call |
| Screw Spring 4" Del Ext. Reset | 95606424 | \$ 9.39 |
| Lever Screw Ext Reset Del Valve 4" & 6" | 95606426 | \$ 61.18 |
| Stud Threaded, BX 4" & 6" Del Ext. Reset | | \$ Call |
| Clapper Spring, 4" & 6" Del BX | | \$ Call |
| MODEL B — DELUGE VALVE TRIM PARTS | | |
| Drip Cup, Support Clip Bolt, Nut & Screw | 71010471 | \$ 380.88 |
| Strainer 3/4" | 78650200 | \$ 362.04 |
| Stop Cock Valve 1/2" | 78650300 | \$ 329.27 |
| Ball Drip Valve 1/2" Mechanical Mod. C | 78653100 | \$ 616.02 |
| Strainer 1/4" | | \$ Call |
| Angle Valve 2" | 98840100 | \$ 614.33 |
| Horizontal Check Valve 1/4" | 98840143 | \$ 354.99 |
| Globe Valve 1/2" | 98840171 | \$ 311.63 |
| Horizontal Check Valve 1/2" | 98840181 | \$ 340.88 |
| Globe Valve 1/4" | 98840172 | \$ 303.38 |
| Pressure Switch | 98728800 | \$ 1,426.83 |
| Restrictor Check Valve | 98840141 | \$ 458.85 |
| Air Pressure Gauge | 98248000 | \$ 155.46 |
| Water Pressure Gauge | 98248001 | \$ 145.40 |
| 1/4" 3 Way Bronze Gauge Valve - Need to order 2 | 98840160 | \$ 259.36 |
| Relief Valve Bronze 1/2" | | \$ Call |
| Actuator Diaphragm | 92206311 | \$ 130.43 |
| Actuator Face Plate | 95106901 | \$ 147.41 |
| Actuator Face Plate Assembly | 95106911 | \$ 130.43 |
| 1/4" 3 Way Bronze Gauge Valve | 98840160 | \$ 259.36 |
| MODEL A 2 — AUTOMATIC AIR MAINTENANCE DEVICE | | |
| Regulator | 98681630 | \$ 813.15 |
| Strainer 1/4" | 98727606 | \$ 251.11 |
| Check Valve 1/4" | 96816902 | \$ 363.91 |
| Globe Valve 3/4" | 98840170 | \$ 354.99 |
| Globe Valve 1/4" - Need to order 2 | 98840172 | \$ 303.38 |
| Restriction Nipple 1/4" | 98523100 | \$ 78.16 |