



PRV DIAPHRAGM PRESSURE REGULATING VALVE

- See Bulletin 820
- 400 psi (27.6 Bar) Rated Pressure
- Adjusted with Pilot Operated Regulator
- Trim Includes Relief Valve
- No Trim Connections to Cover
- cULus listed and FM approved

Description	Part Number	Short Code	List Price
MODEL PRV DIAPHRAGM PRESSURE REGULATING VALVES			
1-1/2" Groove/Groove (ANSI/AWWA C606)	6507008000	15PRV	C\$13,451.42
1-1/2" Flange/Flange Class 150 (ASME B16.5)	6507108000		C\$14,674.27
1-1/2" Flange/Flange Class 300 (ASME B16.5)	6507208000		C\$14,674.27
1-1/2" Flange/Flange PN16 (ISO 7005-2)	6507308000		C\$14,674.27
1-1/2" NPT Thread/Thread (ANSI/ASME B1.20.1)	6507508000		C\$14,674.27
1-1/2" ISO7-1 Thread/Thread	6507608000		C\$14,674.27
2" Groove/Groove (ANSI/AWWA C606)	6507028000	2PRV	C\$13,451.42
2" Flange/Flange Class 150 (ASME B16.5)	6507128000		C\$14,674.27
2" Flange/Flange Class 300 (ASME B16.5)	6507228000		C\$14,674.27
2" Flange/Flange PN16 (ISO 7005-2)	6507328000		C\$14,674.27
2" NPT Thread/Thread (ANSI/ASME B1.20.1)	6507528000		C\$14,674.27
2" ISO7-1 Thread/Thread	6507628000		C\$14,674.27
2-1/2" Groove/Groove (ANSI/AWWA C606)	6507018000	25PRV	C\$15,591.41
76MM,PRV,GE,PRESS REG,W/O CV VERT RED	6507078000		C\$15,591.41
2-1/2" Flange/Flange Class 150 (ASME B16.5)	6507118000		C\$16,967.13
2-1/2" Flange/Flange Class 300 (ASME B16.5)	6507218000		C\$16,967.13
2-1/2" Flange/Flange PN16 (ISO 7005-2)	6507318000		C\$16,967.13
2-1/2" NPT Thread/Thread (ANSI/ASME B1.20.1)	6507518000		C\$16,967.13
2-1/2" ISO7-1 Thread/Thread	6507618000		C\$16,967.13
3" Groove/Groove (ANSI/AWWA C606)	6507038000	3PRV	C\$15,591.41
3" Flange/Flange Class 150 (ASME B16.5)	6507138000		C\$16,967.13
3" Flange/Flange Class 300 (ASME B16.5)	6507238000		C\$16,967.13
3" Flange/Flange PN16 (ISO 7005-2)	6507338000		C\$16,967.13
3" NPT Thread/Thread (ANSI/ASME B1.20.1)	6507538000		C\$16,967.13
3" ISO7-1 Thread/Thread	6507638000		C\$16,967.13
4" Groove/Groove (ANSI/AWWA C606)	6507048000	4PRV	C\$18,648.55
4" Flange/Flange Class 150 (ASME B16.5)	6507148000		C\$20,329.98
4" Flange/Flange Class 300 (ASME B16.5)	6507248000		C\$20,329.98
4" Flange/Flange PN16 (ISO 7005-2)	6507348000		C\$20,329.98
6" Groove/Groove (ANSI/AWWA C606)	6507068000	6PRV	C\$22,928.55
165MM Groove/Groove (ANSI/AWWA C606)	6507058000		C\$22,928.55
6" Flange/Flange Class 150 (ASME B16.5)	6507168000		C\$25,221.40
6" Flange/Flange Class 300 (ASME B16.5)	6507268000		C\$25,221.40
6" Flange/Flange PN16 (ISO 7005-2)	6507368000		C\$25,221.40

Notes:

Part numbers shown include a 185 psi (12.8 Bar) relief valve and 300 psi (20.7 Bar) gauges. Replace the last digit in the part number as follows for other relief valve and gauge combinations:

"0"-185 psi (12.8 Bar) relief valve and 300 psi (20 Bar) gauges

"1"-260 psi (17.9 Bar) relief valve and 300 psi (20 Bar) gauges

"2"-185 psi (12.8 Bar) relief valve and 600 psi (40 Bar) gauges

"3"-260 psi (17.9 Bar) relief valve and 600 psi (40 Bar) gauges