

Reliable®

RASCOFLEX FLEXIBLE SPRINKLER HOSE

RELIABLE FIRE
SPRINKLER (UK)
LIMITED

www.reliablesprinkler.com



Produced in the United Kingdom.
Design and materials subject to change without notice.
Second Edition. 2017.

RASCOFLEX Accessories

RASCOFLEX Flexible Kits include:

- 1 x Hose,
- 1 x Inlet Nipple (25/32mm),
- 1 x 135mm Straight reducer (15/20mm),
- 1 x Bar (700mm),
- 2 x 105mm T-Bar Grid Brackets,
- 1 x Centre Bracket

The kits are boxed and supplied in units of 10 only.

Straight Reducer

Size (mm)	Part No.
15 x 300	RF15300MRD
15 x 155	RF15155MRD
15 x 135	RF15135MRD
15 x 110	RF15110MRD
20 x 300	RF20300MRD
20 x 155	RF20155MRD
20 x 135	RF20135MRD
20 x 110	RF20110MRD



90° Elbow Reducer

Size (mm)	Part No.
15 x 110	RF15110MER
15 x 155	RF15155MER
20 x 110	RF20110MER
20 x 155	RF20155MER



Inlet Nipple

Size (mm)	Part No.
25	RF25MINLET
32	RF32MINLET



Metal Stud End Bracket

Size (mm)	Part No.
38 (Short)	RF38MPLASB
53 (Long)	RF53MPLASB



Long Radius Reducer

Size (mm)	Part No.
15 x 150	RF15150MRE
20 X 150	RF20150MRE



Open Hat Channel Bracket

Size (mm)	Part No.
96	RFOPHATCHB



Stock Bar

Size (mm)	Part No.
700	RF0700MBAR
1270	RF15155MRD
1600	7U99001366



Centre Bracket

Size (mm)	Part No.
One Size	RFCENTR01B



Wood Beam Bracket

Size (mm)	Part No.
One Size	RFWOOD01BC



Radius Bend Indicator

Size (mm)	Part No.
One Size	7U99001692



T-Bar Grid Bracket

Size (mm)	Part No.
60	RF068MTBRC
78	RF078MTBRC
105	RF105MTBRC



RASCOFLEX Sprinkler Hose



Unbraided. LPCB Approved & UL Listed



Flexible Kit, Unbraided. LPCB & UL

Outlet (mm)	Inlet (mm)	Length (mm)	Part No.
15	25	700	RF070U2164
15	25	1000	RF100U2164
15	25	1200	RF120U2164
15	25	1500	RF150U2164
15	25	1800	RF180U2164
20	25	700	RF070U2264
20	25	1000	RF100U2264
20	25	1200	RF120U2264
20	25	1500	RF150U2264
20	25	1800	RF180U2264

Flexible Kit, Unbraided. LPCB

Outlet (mm)	Inlet (mm)	Length (mm)	Part No.
15	32	700	RF070U3164
15	32	1000	RF100U3164
15	32	1200	RF120U3164
15	32	1500	RF150U3164
15	32	1800	RF180U3164
20	32	700	RF070U3264
20	32	1000	RF100U3264
20	32	1200	RF120U3264
20	32	1500	RF150U3264
20	32	1800	RF180U3264



Braided. FM, VdS & LPCB Approved & UL Listed



Flexible Kit, Braided. FM, LPCB, VdS & UL

Outlet (mm)	Inlet (mm)	Length (mm)	Part No.
15	25	700	RF070B2164
15	25	1000	RF100B2164
15	25	1200	RF120B2164
15	25	1500	RF150B2164
15	25	1800	RF180B2164
20	25	700	RF070B2264
20	25	1000	RF100B2264
20	25	1200	RF120B2264
20	25	1500	RF150B2264
20	25	1800	RF180B2264

Flexible Kit, Braided. LPCB

Outlet (mm)	Inlet (mm)	Length (mm)	Part No.
15	32	700	RF070B3164
15	32	1000	RF100B3164
15	32	1200	RF120B3164
15	32	1500	RF150B3164
15	32	1800	RF180B3164
20	32	700	RF070B3264
20	32	1000	RF100B3264
20	32	1200	RF120B3264
20	32	1500	RF150B3264
20	32	1800	RF180B3264





WORLDWIDE DISTRIBUTION CENTRES, FABRICATION FACILITIES & SALES OFFICES.

HEADQUARTERS

Corporate
Elmsford, New York
800.432.1588
info@reliablesprinkler.com

International
Crawley, United Kingdom
+44 (0) 1342 316 800
rfs@reliablesprinkler.com

Manufacturing
Liberty, South Carolina
864.843.1700
info@reliablesprinkler.com

SALES OFFICES

America & Canada

info@reliablesprinkler.com

Seattle, Washington
877.327.2563

Atlanta, Georgia
800.652.1819

Orlando, Florida
800.801.3097

Chicago, Illinois
800.228.6274

Minneapolis, Minnesota
877.827.2816

Dallas, Texas
800.426.742

Houston, Texas
866.978.9965

Denver, Colorado
877.440.2598

Los Angeles, California
800.352.43.65

San Francisco, California
800.352.4365

Toronto, East Canada
800.790.6443

Vancouver, West Canada
604.542.1864

International

Singapore
+65 9859 0690
asiasales@reliablesprinkler.com

Australia
+61 8 816 29555
ausales@reliablesprinkler.com

Europe
+49.405589818-89
europe@reliablesprinkler.com

Dubai
+971 4 880 8830
tgoodchild@reliablesprinkler.com

Shanghai
+86 21 54037021
asiasales@reliablesprinkler.com

FABRICATION FACILITIES

Grand Prairie, Texas
972.352.6400
info@reliablesprinkler.com

Portland, Oregon
503.282.5506
info@reliablesprinkler.com

Denver, Colorado
877.440.2598
info@reliablesprinkler.com